



Model Number	Approx. Shipping Weight	Approx. Operating Weight	Heaviest Section Weight	F	H
PFI-2412N-2DXDS-X2	27070	40590	10930	4'-0 5/8"	17'-0 3/4"
PFI-2412N-2DXES-X2	28880	42490	11830	4'-8 1/8"	17'-8 1/4"
PFI-2412N-3DXDS-X2	31420	46730	13100	4'-0 5/8"	17'-0 3/4"
PFI-2412N-3DXES-X2	33790	49190	14280	5'-3 5/8"	18'-3 3/4"
PFI-2412N-4XDS-X2	34980	51400	14880	4'-8 1/8"	17'-8 1/4"
PFI-2412N-4XES-X2	37950	55150	16360	5'-11 1/8"	18'-11 1/4"
PFI-2412N-5XDS-X2	40890	59780	17830	5'-3 5/8"	18'-3 3/4"
PFI-2412N-5XES-X2	42900	61880	18830	6'-5 5/8"	19'-5 3/4"
PFI-2412N-6XDS-X2	38870	56840	16820	5'-11 1/8"	18'-11 1/4"
PFI-2412N-6XES-X2	40940	58980	17850	7'-1 1/8"	20'-1 1/4"

- Notes
- 1) Drawings are not to scale. All dimensions are in feet and inches.
 - 2) Unless otherwise indicated, connections 3" and smaller are MPT. Connections 4" and larger are grooved to suit a mechanical coupling and beveled for welding.
 - 3) Dimensions showing location of coil and basin connections are approximate and should not be used for prefabrication of connecting piping.
 - 4) For weight loadings and support requirements, refer to the suggested steel support drawing.
 - 5) Heaviest section is the combined weight of fan and coil sections, refer to the P-Series Counterflow Induced Draft Coil Products rigging and assembly manual for suggested lifting method.
 - 6) The area above the discharge must be unobstructed.
 - 7) Do not support piping from unit connections. All necessary piping supports to be supplied by others.
 - 8) M = Motor location

ORDER NO:

DATE:



BALTIMORE AIRCOIL COMPANY

PFI Closed Circuit Cooling Tower Tabulated Unit Print

DRAWING NUMBER:
UP-PFI-2412