

BAC - ACT Line Performance At 24 Standard Conditions

		CAPACITY IN M ³ /HR																								
Model	Fan kW	EWT LWT	37	37.5	38	40	42	45	37	37.5	38	40	42	45	37	37.5	38	40	42	45	37	37.5	38	40	42	45
			32	32	32	32	32	35	32	32	32	32	32	35	32	32	32	32	32	32	35	32	32	32	32	32
				26	26	26	26	26	26	27	27	27	27	27	27	28	28	28	28	28	28	29	29	29	29	29
ACT-08161-G	2.2		134.5	127.0	120.5	102.0	90.4	124.4	121.6	114.8	109.1	92.8	82.6	117.5	107.4	101.6	96.7	82.8	74.1	110.1	91.8	87.1	83.1	71.8	64.7	102.1
ACT-08161-H	4.0		164.4	155.1	147.2	124.5	110.2	152.0	148.5	140.8	133.2	113.2	100.7	143.5	131.1	124.0	118.0	101.0	90.3	134.4	112.0	106.2	101.4	87.5	78.9	124.6
ACT-08161-J	5.5		181.9	171.6	162.8	137.7	121.9	168.1	164.2	155.1	147.3	125.2	111.3	158.7	145.0	137.2	130.5	111.6	99.8	148.6	123.8	117.4	112.0	96.7	87.1	137.7
ACT-08161-K	7.5		201.5	190.1	180.3	152.4	134.9	186.2	181.9	171.8	163.1	138.6	123.1	175.8	160.5	151.8	144.5	123.5	110.4	164.6	137.0	130.0	124.0	107.0	96.3	152.5
ACT-08161-L	11.0		228.4	215.4	204.3	172.6	152.7	211.0	206.1	194.6	184.8	156.9	139.3	199.1	181.8	172.0	163.6	139.8	124.8	186.4	155.1	147.1	140.3	121.0	108.9	172.7
ACT-08162-H	4.0		181.4	171.2	162.5	137.6	121.9	167.8	163.9	154.8	147.1	125.2	111.3	158.4	144.8	137.0	130.4	111.7	99.9	148.4	123.8	117.5	112.1	96.9	87.3	137.6
ACT-08162-J	5.5		200.9	189.6	179.9	152.3	134.9	185.8	181.5	171.4	162.9	138.5	123.2	175.4	160.3	151.7	144.4	123.6	110.5	164.3	137.0	130.0	124.1	107.2	96.6	152.3
ACT-08162-K	7.5		222.4	209.9	199.2	168.6	149.3	205.7	200.9	189.8	180.3	153.3	136.3	194.2	177.5	167.9	159.8	136.7	122.3	181.9	151.6	143.9	137.3	118.6	106.8	168.6
ACT-08162-L	11.0		252.2	238.0	225.8	191.0	169.1	233.2	227.8	215.1	204.4	173.7	154.4	220.1	201.1	190.3	181.1	154.9	138.5	206.1	171.8	163.0	155.5	134.3	121.0	191.1
ACT-08162-M	15.0		280.1	264.2	250.7	212.0	187.6	258.9	252.9	238.8	226.8	192.7	171.3	244.4	223.2	211.1	200.9	171.8	153.5	228.8	190.6	180.8	172.5	148.9	134.1	212.0
ACT-09172-J	5.5		232.9	219.9	208.8	176.9	156.8	215.5	210.6	199.0	189.1	161.0	143.3	203.6	186.2	176.2	167.8	143.7	128.6	190.8	159.3	151.2	144.3	124.8	112.5	177.0
ACT-09172-K	7.5		257.4	243.0	230.7	195.5	173.2	238.2	232.7	219.9	209.0	177.9	158.3	225.0	205.7	194.7	185.4	158.8	142.1	210.8	175.9	167.0	159.4	137.8	124.3	195.5
ACT-09172-L	11.0		291.1	274.8	260.9	221.0	195.8	269.3	263.1	248.6	236.3	201.1	178.9	254.4	232.6	220.1	209.6	179.5	160.6	238.3	198.9	188.8	180.2	155.7	140.4	221.0
ACT-09172-M	15.0		322.8	304.7	289.3	245.0	217.1	298.6	291.8	275.7	262.0	222.9	198.3	282.0	257.8	244.0	232.3	198.9	178.0	264.2	220.5	209.2	199.7	172.6	155.6	245.0
ACT-09172-N	18.5		345.4	326.0	309.5	262.0	232.1	319.5	312.1	294.9	280.2	238.4	212.0	301.7	275.8	261.0	248.4	212.7	190.3	282.6	235.8	223.7	213.5	184.5	166.3	262.1
ACT-09173-K	7.5		272.0	256.8	243.9	206.9	183.5	251.7	246.0	232.5	221.1	188.4	167.8	237.9	217.6	206.1	196.3	168.3	150.7	223.0	186.4	176.9	168.9	146.2	131.9	206.9
ACT-09173-L	11.0		308.4	291.3	276.6	234.7	208.2	285.5	279.0	263.8	250.8	213.7	190.3	269.8	246.9	233.7	222.6	190.9	171.0	252.9	211.4	200.7	191.6	165.9	149.7	234.7
ACT-09173-M	15.0		340.9	321.9	305.7	259.4	230.1	315.5	308.4	291.5	277.2	236.2	210.4	298.2	272.8	258.3	246.0	211.0	189.0	279.5	233.6	221.8	211.8	183.3	165.4	259.4
ACT-09173-N	18.5		365.2	344.9	327.6	277.9	246.5	338.1	330.4	312.3	297.0	253.0	225.4	319.5	292.3	276.8	263.6	226.1	202.5	299.5	250.3	237.7	226.9	196.4	177.2	277.9
ACT-09173-O	22.0		385.6	364.1	345.8	293.3	260.2	356.9	348.8	329.7	313.5	267.1	237.9	337.2	308.6	292.2	278.3	238.6	213.7	316.1	264.2	250.9	239.5	207.3	187.1	293.4
ACT-09174-L	11.0		332.9	314.4	298.6	253.2	224.6	308.2	301.1	284.7	270.6	230.6	205.3	291.2	266.4	252.2	240.2	205.9	184.4	272.9	228.1	216.5	206.7	178.9	161.4	253.3
ACT-09174-M	15.0		368.3	347.8	330.3	280.2	248.5	340.9	333.2	315.0	299.4	255.1	227.3	322.1	294.8	279.1	265.8	227.9	204.1	302.0	252.4	239.6	228.8	198.0	178.7	280.3
ACT-09174-N	18.5		393.6	371.7	353.0	299.5	265.7	364.3	356.0	330.0	312.7	272.2	242.9	344.3	315.0	298.3	284.1	243.7	218.2	322.7	269.8	256.2	244.6	211.7	191.1	299.5
ACT-09174-O	22.0		416.8	393.6	373.9	317.2	281.4	385.8	377.1	356.3	339.0	288.9	257.3	364.6	333.7	316.0	300.9	258.1	231.2	341.8	285.8	271.3	259.1	224.3	202.4	317.3
ACT-09174-P	30.0		460.3	434.7	412.9	350.4	310.9	426.1	416.5	393.7	374.4	319.1	284.3	402.7	368.5	349.0	332.4	285.1	255.4	377.6	315.7	299.7	286.2	247.8	223.6	350.5
ACT-10184-KM	7.5		327.1	309.0	293.5	249.2	221.2	302.9	296.0	279.9	266.2	227.0	202.3	286.3	262.1	248.2	236.4	202.9	181.8	268.5	224.6	213.3	203.7	176.4	159.3	249.2
ACT-10184-LM	11.0		370.3	349.9	332.4	282.3	250.6	343.0	335.2	317.0	301.5	257.2	229.3	324.2	296.8	281.2	267.9	230.0	206.1	304.1	254.5	241.7	230.8	200.0	180.6	282.3
ACT-10184-M	15.0		409.4	386.9	367.6	312.3	277.3	379.3	370.7	350.6	333.5	284.6	253.8	358.6	328.3	311.1	296.4	254.5	228.2	336.3	281.6	267.5	255.5	221.4	200.0	312.3
ACT-10184-N	18.5		438.5	414.4	393.7	334.6	297.1	406.2	397.1	375.6	357.3	305.0	272.0	384.1	351.8	333.3	317.6	272.8	244.6	360.3	301.7	286.6	273.8	237.3	214.4	334.7
ACT-10184-O	22.0		463.6	438.1	416.3	353.8	314.3	429.5	419.8	397.1	377.8	322.5	287.6	406.1	372.0	352.4	335.8	288.5	258.7	381.0	319.1	303.1	289.6	251.1	226.8	353.9
ACT-10184-P	30.0		511.6	483.6	459.6	390.7	347.1	474.1	463.5	438.5	417.1	356.2	317.8	448.3	410.7	389.2	370.9	318.7	285.9	420.7	352.4	334.9	319.9	277.4	250.7	390.8
ACT-10184-Q	37.0		547.7	517.7	492.0	418.4	371.8	507.6	496.2	469.5	446.7	381.5	340.4	480.0	439.8	416.8	397.2	341.4	306.2	450.4	377.5	358.6	342.7	297.2	268.6	418.5
ACT-10185-LM	11.0		409.1	386.5	367.3	312.2	277.3	379.0	370.5	350.4	333.4	284.6	253.8	358.3	328.2	311.0	296.3	254.6	228.3	336.2	281.5	267.5	255.5	221.5	200.1	312.3
ACT-10185-MM	15.0		451.9	427.1	405.9	345.2	306.7	418.8	409.4	387.3	368.5	314.7	280.8	396.0	362.8	343.9	327.7	281.7	252.7	371.6	311.4	295.9	282.7	245.2	221.6	345.3
ACT-10185-N	18.5		482.7	456.3	433.7	369.0	327.9	447.4	437.4	413.9	393.8	336.5	300.3	423.2	387.3	367.5	350.3	301.2	270.3	397.1	332.9	316.4	302.3	262.3	237.1	369.0
ACT-10185-O	22.0		510.5	482.6	458.8	390.4	347.1	473.3	462.7	437.9	416.7	356.1	317.9	447.7	410.3	388.9	370.8	318.9	286.2	420.2	352.4	334.9	320.1	277.8	251.1	390.5
ACT-10185-P	30.0		564.1	533.4	507.2	431.8	384.1	523.1	511.4	484.1	460.8	394.0	351.9	494.9	453.7	430.2	410.1	352.9	316.9	464.6	389.9	370.6	354.3	307.6	278.2	431.9
ACT-10185-Q	37.0		602.7	570.0	542.0	461.7	410.8	559.0	546.6	517.4	492.6	421.4	376.4	529.0	485.1	459.9	438.6	377.5	339.1	496.7	417.0	396.4	379.0	329.2	297.8	461.8
ACT-10185-R	45.0		641.3	606.5	576.9	491.6	437.5	594.8	581.7	550.7	524.3	448.8	401.0	563.0	516.4	489.7	460.7	402.2	361.3	528.7	444.1	422.2	407.3	350.8	317.4	491.7
ACT-11205-LM	11.0		453.3	428.5	407.4	346.6	308.1	420.2	410.8	388.7	369.9	316.1	282.2	397.4	364.2	345.2	329.1	283.0	254.0	373.0	312.8	297.3	284.1	246.5	222.8	346.7
ACT-11205-MM	15.0		499.9	472.6	449.4	382.6	340.3	463.5	453.2	428.9	408.3	349.1	311.7	438.5	402.0	381.1	363.4	312.6	280.7	411.7	345.4	328.3	313.8	275.2	246.4	382.7
ACT-11205-NM	18.5		535.5	506.4	481.6	410.2	364.9	496.6	485.6	459.7	437.6	374.3	334.4	469.9	430.9	408.6	389.6	335.4	301.2	441.2	370.4	352.2	336.6	292.4	264.5	410.3
ACT-11205-O	22.0		565.1	534.4	508.3	433.1	385.4	524.1	512.5	485.3	462.0	395.4	353.3	496.1	455.0	431.5	411.5	354.3	318.3	465.8	391.3	372.0	355.7	309.0	279.6	433.2
ACT-11205-P	30.0		624.2																							