


TrilliumSeries™ Condenser

ENGINEERING DATA



Model	Fan Qty	Base Heat Rejection (MBH) ⁽¹⁾	Base Tons	Motor HP	Airflow (CFM)	Total Unit FLA at 460V	Unit Length (L)	Unit Width (W)	Unit Height (H)	F	Shipping Weight (lbs)	Operating Weight (lbs)
TSDC-033-3	1	391 ⁽¹⁾	33	3.0	14,890	4.7	5'-3"	4'-2"	7'-0"	4'-0"	1,280	1,500
TSDC-058-6.2	2	702 ⁽¹⁾	59	6.2	28,000	8.7	7'-11"	4'-2"	7'-0"	4'-0"	1,740	2,000
TSDC-085-9.6	3	1,026 ⁽¹⁾	86	9.6	41,400	12.6	11'-1"	4'-2"	7'-0"	4'-0"	2,300	2,600
TSDC-116-12.4	4	1,405 ⁽¹⁾	117	12.4	56,000	16.6	15'-7"	4'-4"	7'-1/2"	4'-0"	3,200	3,570
TSDC-TF-033-3	1	391 ⁽¹⁾	33	3.0	14,890	4.7	5'-3"	5'-7"	7'-1/2"	4'-0"	1,740	1,990
TSDC-TF-058-6.2	2	702 ⁽¹⁾	59	6.2	28,000	8.7	7'-11"	5'-7"	7'-1/2"	4'-0"	2,400	2,690
TSDC-TF-085-9.6	3	1,026 ⁽¹⁾	86	9.6	41,400	12.6	11'-1"	5'-7"	7'-1/2"	4'-0"	3,150	3,500
TSDC-TF-116-12.4	4	1,405 ⁽¹⁾	117	12.4	56,000	16.6	15'-7"	5'-7"	7'-1/2"	4'-0"	4,140	4,560
TSDC-C02-044-3	1	530 ⁽²⁾	44	3.0	15,200	4.7	5'-3"	5'-7"	7'-1/2"	4'-0"	1,650	1,890
TSDC-C02-077-6.2	2	828 ⁽²⁾	77	6.0	28,800	8.7	7'-11"	5'-7"	7'-1/2"	4'-0"	2,300	2,580
TSDC-C02-112-9.6	3	1,344 ⁽²⁾	112	9.6	42,600	12.6	11'-1"	5'-7"	7'-1/2"	4'-0"	2,970	3,300
TSDC-C02-152-12.4	4	1,828 ⁽²⁾	152	12.0	57,500	16.6	15'-7"	5'-7"	7'-1/2"	4'-0"	3,940	4,340



NOTES:

1. Base Heat Rejection (MBH) is based on R-134a 90°F dry-bulb/76°F wet-bulb and 105°F condensing temperature.
2. The water make-up connection is 3/4". The water drain connection is 1 1/4". The water overflow connection is 1 1/2".
3. The Pump HP is .33

Do not use for construction. Refer to factory certified dimensions. This catalog includes data current at the time of publication, which should be reconfirmed at the time of purchase. Up-to-date engineering data, free product selection software, and more can be found at www.BaltimoreAircoil.com.