



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0406N-3D1DS-G1	Water	232.9	1.87	4"x1	186.4	1.24	4"x1	279.5	2.62	4"x1
PFI-0406N-3D1ES-H1	Water	232.9	1.87	4"x1	186.4	1.24	4"x1	279.5	2.62	4"x1
PFI-0406N-4D1DS-H1	Water	232.9	2.31	4"x1	186.4	1.53	4"x1	279.5	3.24	4"x1
PFI-0406N-6D1ES-G1	Water	232.9	3.21	4"x1	186.4	2.13	4"x1	279.5	4.49	4"x1
PFI-0406N-6D1ES-H1	Water	232.9	3.21	4"x1	186.4	2.13	4"x1	279.5	4.49	4"x1
PFI-0406N-6D2DS-J1	Water	237.3	2.75	4"x1	189.9	1.82	4"x1	284.8	3.85	4"x1
PFI-0406N-2D3BS-G1	Water	219.9	1.02	4"x1	176.0	0.67	4"x1	263.9	1.42	4"x1
PFI-0406N-2D4BS-H1	Water	219.9	0.92	4"x1	176.0	0.61	4"x1	263.9	1.29	4"x1
PFI-0406N-3D2BS-G1	Water	237.3	1.65	4"x1	189.9	1.09	4"x1	284.8	2.30	4"x1
PFI-0406N-3D3BS-H1	Water	240.6	1.52	4"x1	192.5	1.01	4"x1	288.8	2.13	4"x1
PFI-0406N-4D4BS-G1	Water	245.0	1.68	4"x1	196.0	1.11	4"x1	294.0	2.35	4"x1
PFI-0406N-4D3BS-H1	Water	240.6	1.85	4"x1	192.5	1.22	4"x1	288.8	2.59	4"x1
PFI-0406N-4D4BS-J1	Water	245.0	1.68	4"x1	196.0	1.11	4"x1	294.0	2.35	4"x1
PFI-0406N-5D2BS-G1	Water	237.3	2.38	4"x1	189.9	1.58	4"x1	284.8	3.34	4"x1
PFI-0406N-5D4BS-H1	Water	245.0	1.96	4"x1	196.0	1.30	4"x1	294.0	2.74	4"x1
PFI-0406N-5D4BS-J1	Water	245.0	1.96	4"x1	196.0	1.30	4"x1	294.0	2.74	4"x1
PFI-0406N-6D1BS-H1	Water	232.9	3.21	4"x1	186.4	2.13	4"x1	279.5	4.49	4"x1
PFI-0406N-3D1DZ-G1	Water	108.2	2.47	4"x1	86.6	1.64	4"x1	129.9	3.47	4"x1
PFI-0406N-3D1EZ-H1	Water	108.2	2.48	4"x1	86.6	1.64	4"x1	129.9	3.47	4"x1
PFI-0406N-4D1DZ-H1	Water	108.2	3.25	4"x1	86.6	2.15	4"x1	129.9	4.55	4"x1
PFI-0406N-6D1EZ-G1	Water	108.2	4.79	4"x1	86.6	3.18	4"x1	129.9	6.72	4"x1
PFI-0406N-6D1EZ-H1	Water	108.2	4.79	4"x1	86.6	3.18	4"x1	129.9	6.72	4"x1
PFI-0406N-6D2DZ-J1	Water	109.3	3.90	4"x1	87.5	2.59	4"x1	131.2	5.47	4"x1
PFI-0406N-2D3BT-G1	Water	110.0	1.29	4"x1	88.0	0.85	4"x1	132.0	1.80	4"x1
PFI-0406N-2D4BT-H1	Water	110.0	1.09	4"x1	88.0	0.72	4"x1	132.0	1.52	4"x1
PFI-0406N-3D2BT-G1	Water	109.3	2.02	4"x1	87.5	1.34	4"x1	131.2	2.83	4"x1
PFI-0406N-3D3BT-H1	Water	110.4	1.87	4"x1	88.3	1.24	4"x1	132.5	2.61	4"x1
PFI-0406N-4D4BT-G1	Water	111.5	2.07	4"x1	89.2	1.37	4"x1	133.8	2.90	4"x1
PFI-0406N-4D3BT-H1	Water	110.4	2.44	4"x1	88.3	1.61	4"x1	132.5	3.41	4"x1
PFI-0406N-4D4BT-J1	Water	111.5	2.07	4"x1	89.2	1.37	4"x1	133.8	2.90	4"x1
PFI-0406N-5D2BT-G1	Water	109.3	3.26	4"x1	87.5	2.16	4"x1	131.2	4.58	4"x1
PFI-0406N-5D4BT-H1	Water	111.5	2.55	4"x1	89.2	1.69	4"x1	133.8	3.57	4"x1
PFI-0406N-5D4BT-J1	Water	111.5	2.55	4"x1	89.2	1.69	4"x1	133.8	3.57	4"x1
PFI-0406N-6D1BT-H1	Water	108.2	4.78	4"x1	86.6	3.16	4"x1	129.9	6.70	4"x1
PFI-0412N-2D1DS-G2	Water	232.9	2.06	4"x1	186.4	1.37	4"x1	279.5	2.88	4"x1
PFI-0412N-2D4DS-G2	Water	245.0	1.52	4"x1	196.0	1.01	4"x1	294.0	2.13	4"x1
PFI-0412N-3D1DS-G2	Water	232.9	2.83	4"x1	186.4	1.87	4"x1	279.5	3.96	4"x1
PFI-0412N-3D2DS-H2	Water	237.3	2.44	4"x1	189.9	1.61	4"x1	284.8	3.41	4"x1
PFI-0412N-4D1DS-H2	Water	232.9	3.59	4"x1	186.4	2.38	4"x1	279.5	5.03	4"x1
PFI-0412N-4D3DS-H2	Water	240.6	2.78	4"x1	192.5	1.84	4"x1	288.8	3.89	4"x1
PFI-0412N-4D2ES-J2	Water	237.3	3.07	4"x1	189.9	2.03	4"x1	284.8	4.30	4"x1



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0412N-5D1ES-J2	Water	232.9	4.36	4"x1	186.4	2.89	4"x1	279.5	6.10	4"x1
PFI-0412N-6D1ES-H2	Water	232.9	5.12	4"x1	186.4	3.40	4"x1	279.5	7.18	4"x1
PFI-0412N-6D1ES-J2	Water	232.9	5.12	4"x1	186.4	3.40	4"x1	279.5	7.18	4"x1
PFI-0412N-3D4BS-G2	Water	245.0	2.00	4"x1	196.0	1.32	4"x1	294.0	2.80	4"x1
PFI-0412N-3D4BS-H2	Water	245.0	2.00	4"x1	196.0	1.32	4"x1	294.0	2.80	4"x1
PFI-0412N-3D3BS-J2	Water	240.6	2.22	4"x1	192.5	1.47	4"x1	288.8	3.11	4"x1
PFI-0412N-4D4BS-G2	Water	245.0	2.48	4"x1	196.0	1.64	4"x1	294.0	3.47	4"x1
PFI-0412N-4D2BS-H2	Water	237.3	3.07	4"x1	189.9	2.03	4"x1	284.8	4.30	4"x1
PFI-0412N-4D3BS-H2	Water	240.6	2.78	4"x1	192.5	1.84	4"x1	288.8	3.89	4"x1
PFI-0412N-4D3BS-J2	Water	240.6	2.78	4"x1	192.5	1.84	4"x1	288.8	3.89	4"x1
PFI-0412N-5D2BS-G2	Water	237.3	3.70	4"x1	189.9	2.45	4"x1	284.8	5.18	4"x1
PFI-0412N-6D2BS-G2	Water	237.3	4.33	4"x1	189.9	2.87	4"x1	284.8	6.07	4"x1
PFI-0412N-6D1BS-H2	Water	232.9	5.12	4"x1	186.4	3.40	4"x1	279.5	7.18	4"x1
PFI-0412N-6D2BS-J2	Water	237.3	4.33	4"x1	189.9	2.87	4"x1	284.8	6.07	4"x1
PFI-0412N-2D1DZ-G2	Water	108.2	2.80	4"x1	86.6	1.86	4"x1	129.9	3.93	4"x1
PFI-0412N-2D4DZ-G2	Water	111.5	1.81	4"x1	89.2	1.20	4"x1	133.8	2.53	4"x1
PFI-0412N-3D1DZ-G2	Water	108.2	4.12	4"x1	86.6	2.73	4"x1	129.9	5.78	4"x1
PFI-0412N-3D2DZ-H2	Water	109.3	3.36	4"x1	87.5	2.23	4"x1	131.2	4.71	4"x1
PFI-0412N-4D1DZ-H2	Water	108.2	5.44	4"x1	86.6	3.61	4"x1	129.9	7.63	4"x1
PFI-0412N-4D3DZ-H2	Water	110.4	4.07	4"x1	88.3	2.70	4"x1	132.5	5.71	4"x1
PFI-0412N-4D2EZ-J2	Water	109.3	4.43	4"x1	87.5	2.94	4"x1	131.2	6.21	4"x1
PFI-0412N-5D1EZ-J2	Water	108.2	6.77	4"x1	86.6	4.48	4"x1	129.9	9.49	4"x1
PFI-0412N-6D1EZ-H2	Water	108.2	8.09	4"x1	86.6	5.36	4"x1	129.9	11.34	4"x1
PFI-0412N-6D1EZ-J2	Water	108.2	8.09	4"x1	86.6	5.36	4"x1	129.9	11.34	4"x1
PFI-0412N-3D4BT-G2	Water	111.5	2.62	4"x1	89.2	1.74	4"x1	133.8	3.67	4"x1
PFI-0412N-3D4BT-H2	Water	111.5	2.62	4"x1	89.2	1.74	4"x1	133.8	3.67	4"x1
PFI-0412N-3D3BT-J2	Water	110.4	3.09	4"x1	88.3	2.04	4"x1	132.5	4.33	4"x1
PFI-0412N-4D4BT-G2	Water	111.5	3.44	4"x1	89.2	2.28	4"x1	133.8	4.82	4"x1
PFI-0412N-4D3BT-H2	Water	110.4	4.06	4"x1	88.3	2.69	4"x1	132.5	5.70	4"x1
PFI-0412N-4D3BT-J2	Water	110.4	4.06	4"x1	88.3	2.69	4"x1	132.5	5.70	4"x1
PFI-0412N-5D2BT-G2	Water	109.3	5.49	4"x1	87.5	3.64	4"x1	131.2	7.69	4"x1
PFI-0412N-6D2BT-G2	Water	109.3	6.55	4"x1	87.5	4.34	4"x1	131.2	9.18	4"x1
PFI-0412N-6D1BT-H2	Water	108.2	8.07	4"x1	86.6	5.35	4"x1	129.9	11.32	4"x1
PFI-0412N-6D2BT-J2	Water	109.3	6.55	4"x1	87.5	4.34	4"x1	131.2	9.18	4"x1
PFI-0709N-2D3DS-H1	Water	474.7	1.54	4"x2	379.7	1.02	4"x2	569.6	2.15	4"x2
PFI-0709N-3D1DS-H1	Water	461.5	2.54	4"x2	369.2	1.68	4"x2	553.8	3.56	4"x2
PFI-0709N-3D1DS-J1	Water	461.5	2.54	4"x2	369.2	1.68	4"x2	553.8	3.56	4"x2
PFI-0709N-3D3DS-J1	Water	474.7	2.03	4"x2	379.7	1.35	4"x2	569.6	2.85	4"x2
PFI-0709N-3D1ES-J1	Water	461.5	2.54	4"x2	369.2	1.68	4"x2	553.8	3.56	4"x2
PFI-0709N-3D2ES-J1	Water	468.1	2.25	4"x2	374.5	1.49	4"x2	561.7	3.15	4"x2
PFI-0709N-3D1DS-K1	Water	461.5	2.54	4"x2	369.2	1.68	4"x2	553.8	3.56	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-3D2DS-K1	Water	468.1	2.25	4"x2	374.5	1.49	4"x2	561.7	3.15	4"x2
PFI-0709N-3D2ES-L1	Water	468.1	2.25	4"x2	374.5	1.49	4"x2	561.7	3.15	4"x2
PFI-0709N-4D4DS-J1	Water	481.3	2.31	4"x2	385.0	1.53	4"x2	577.5	3.23	4"x2
PFI-0709N-4D2DS-K1	Water	468.1	2.83	4"x2	374.5	1.87	4"x2	561.7	3.96	4"x2
PFI-0709N-4D1DS-L1	Water	461.5	3.21	4"x2	369.2	2.13	4"x2	553.8	4.50	4"x2
PFI-0709N-5D4DS-K1	Water	481.3	2.74	4"x2	385.0	1.82	4"x2	577.5	3.84	4"x2
PFI-0709N-5D1DS-L1	Water	461.5	3.89	4"x2	369.2	2.57	4"x2	553.8	5.44	4"x2
PFI-0709N-5D2DS-L1	Water	468.1	3.40	4"x2	374.5	2.25	4"x2	561.7	4.76	4"x2
PFI-0709N-5D3ES-L1	Water	474.7	3.03	4"x2	379.7	2.01	4"x2	569.6	4.25	4"x2
PFI-0709N-6D1ES-H1	Water	461.5	4.56	4"x2	369.2	3.02	4"x2	553.8	6.39	4"x2
PFI-0709N-6D1ES-J1	Water	461.5	4.56	4"x2	369.2	3.02	4"x2	553.8	6.39	4"x2
PFI-0709N-6D1ES-K1	Water	461.5	4.56	4"x2	369.2	3.02	4"x2	553.8	6.39	4"x2
PFI-0709N-6D2ES-L1	Water	468.1	3.98	4"x2	374.5	2.63	4"x2	561.7	5.57	4"x2
PFI-0709N-6D1ES-M1	Water	461.5	4.56	4"x2	369.2	3.02	4"x2	553.8	6.39	4"x2
PFI-0709N-3D4BS-J1	Water	481.3	1.87	4"x2	385.0	1.24	4"x2	577.5	2.61	4"x2
PFI-0709N-3D4BS-K1	Water	481.3	1.87	4"x2	385.0	1.24	4"x2	577.5	2.61	4"x2
PFI-0709N-3D4BS-M1	Water	481.3	1.87	4"x2	385.0	1.24	4"x2	577.5	2.61	4"x2
PFI-0709N-4D2BS-H1	Water	468.1	2.83	4"x2	374.5	1.87	4"x2	561.7	3.96	4"x2
PFI-0709N-4D2BS-J1	Water	468.1	2.83	4"x2	374.5	1.87	4"x2	561.7	3.96	4"x2
PFI-0709N-4D3BS-K1	Water	474.7	2.53	4"x2	379.7	1.68	4"x2	569.6	3.55	4"x2
PFI-0709N-4D3BS-L1	Water	474.7	2.53	4"x2	379.7	1.68	4"x2	569.6	3.55	4"x2
PFI-0709N-4D4BS-M1	Water	481.3	2.31	4"x2	385.0	1.53	4"x2	577.5	3.23	4"x2
PFI-0709N-5D4BS-H1	Water	481.3	2.74	4"x2	385.0	1.82	4"x2	577.5	3.84	4"x2
PFI-0709N-5D3BS-J1	Water	474.7	3.03	4"x2	379.7	2.01	4"x2	569.6	4.25	4"x2
PFI-0709N-5D4BS-K1	Water	481.3	2.74	4"x2	385.0	1.82	4"x2	577.5	3.84	4"x2
PFI-0709N-5D4BS-L1	Water	481.3	2.74	4"x2	385.0	1.82	4"x2	577.5	3.84	4"x2
PFI-0709N-5D4BS-M1	Water	481.3	2.74	4"x2	385.0	1.82	4"x2	577.5	3.84	4"x2
PFI-0709N-6D1BS-H1	Water	461.5	4.56	4"x2	369.2	3.02	4"x2	553.8	6.39	4"x2
PFI-0709N-6D1BS-J1	Water	461.5	4.56	4"x2	369.2	3.02	4"x2	553.8	6.39	4"x2
PFI-0709N-6D1BS-K1	Water	461.5	4.56	4"x2	369.2	3.02	4"x2	553.8	6.39	4"x2
PFI-0709N-6D2BS-L1	Water	468.1	3.98	4"x2	374.5	2.63	4"x2	561.7	5.57	4"x2
PFI-0709N-6D2BS-M1	Water	468.1	3.98	4"x2	374.5	2.63	4"x2	561.7	5.57	4"x2
PFI-0709N-2D3DZ-H1	Water	218.6	2.24	4"x2	174.9	1.48	4"x2	262.4	3.14	4"x2
PFI-0709N-3D1DZ-H1	Water	215.3	4.07	4"x2	172.3	2.70	4"x2	258.4	5.71	4"x2
PFI-0709N-3D1DZ-J1	Water	215.3	4.07	4"x2	172.3	2.70	4"x2	258.4	5.71	4"x2
PFI-0709N-3D3DZ-J1	Water	218.6	3.10	4"x2	174.9	2.05	4"x2	262.4	4.34	4"x2
PFI-0709N-3D1EZ-J1	Water	215.3	4.08	4"x2	172.3	2.70	4"x2	258.4	5.72	4"x2
PFI-0709N-3D2EZ-J1	Water	217.0	3.53	4"x2	173.6	2.34	4"x2	260.4	4.94	4"x2
PFI-0709N-3D1DZ-K1	Water	215.3	4.07	4"x2	172.3	2.70	4"x2	258.4	5.71	4"x2
PFI-0709N-3D2DZ-K1	Water	217.0	3.52	4"x2	173.6	2.33	4"x2	260.4	4.93	4"x2
PFI-0709N-3D2EZ-L1	Water	217.0	3.53	4"x2	173.6	2.34	4"x2	260.4	4.94	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-4D4DZ-J1	Water	220.3	3.52	4"x2	176.2	2.33	4"x2	264.3	4.93	4"x2
PFI-0709N-4D2DZ-K1	Water	217.0	4.52	4"x2	173.6	2.99	4"x2	260.4	6.34	4"x2
PFI-0709N-4D1DZ-L1	Water	215.3	5.26	4"x2	172.3	3.49	4"x2	258.4	7.37	4"x2
PFI-0709N-5D4DZ-K1	Water	220.3	4.27	4"x2	176.2	2.83	4"x2	264.3	5.98	4"x2
PFI-0709N-5D1DZ-L1	Water	215.3	6.45	4"x2	172.3	4.27	4"x2	258.4	9.04	4"x2
PFI-0709N-5D2DZ-L1	Water	217.0	5.53	4"x2	173.6	3.66	4"x2	260.4	7.74	4"x2
PFI-0709N-5D3EZ-L1	Water	218.6	4.83	4"x2	174.9	3.20	4"x2	262.4	6.77	4"x2
PFI-0709N-6D1EZ-H1	Water	215.3	7.65	4"x2	172.3	5.07	4"x2	258.4	10.72	4"x2
PFI-0709N-6D1EZ-J1	Water	215.3	7.65	4"x2	172.3	5.07	4"x2	258.4	10.72	4"x2
PFI-0709N-6D1EZ-K1	Water	215.3	7.65	4"x2	172.3	5.07	4"x2	258.4	10.72	4"x2
PFI-0709N-6D2EZ-L1	Water	217.0	6.54	4"x2	173.6	4.33	4"x2	260.4	9.17	4"x2
PFI-0709N-6D1EZ-M1	Water	215.3	7.65	4"x2	172.3	5.07	4"x2	258.4	10.72	4"x2
PFI-0709N-3D4BT-J1	Water	220.3	2.75	4"x2	176.2	1.82	4"x2	264.3	3.85	4"x2
PFI-0709N-3D4BT-K1	Water	220.3	2.75	4"x2	176.2	1.82	4"x2	264.3	3.85	4"x2
PFI-0709N-3D4BT-M1	Water	220.3	2.75	4"x2	176.2	1.82	4"x2	264.3	3.85	4"x2
PFI-0709N-4D2BT-H1	Water	217.0	4.50	4"x2	173.6	2.98	4"x2	260.4	6.30	4"x2
PFI-0709N-4D2BT-J1	Water	217.0	4.50	4"x2	173.6	2.98	4"x2	260.4	6.30	4"x2
PFI-0709N-4D3BT-K1	Water	218.6	3.93	4"x2	174.9	2.60	4"x2	262.4	5.51	4"x2
PFI-0709N-4D3BT-L1	Water	218.6	3.93	4"x2	174.9	2.60	4"x2	262.4	5.51	4"x2
PFI-0709N-4D4BT-M1	Water	220.3	3.49	4"x2	176.2	2.31	4"x2	264.3	4.89	4"x2
PFI-0709N-5D4BT-H1	Water	220.3	4.24	4"x2	176.2	2.81	4"x2	264.3	5.94	4"x2
PFI-0709N-5D3BT-J1	Water	218.6	4.79	4"x2	174.9	3.17	4"x2	262.4	6.71	4"x2
PFI-0709N-5D4BT-K1	Water	220.3	4.24	4"x2	176.2	2.81	4"x2	264.3	5.94	4"x2
PFI-0709N-5D4BT-L1	Water	220.3	4.24	4"x2	176.2	2.81	4"x2	264.3	5.94	4"x2
PFI-0709N-5D4BT-M1	Water	220.3	4.24	4"x2	176.2	2.81	4"x2	264.3	5.94	4"x2
PFI-0709N-6D1BT-H1	Water	215.3	7.60	4"x2	172.3	5.04	4"x2	258.4	10.66	4"x2
PFI-0709N-6D1BT-J1	Water	215.3	7.60	4"x2	172.3	5.04	4"x2	258.4	10.66	4"x2
PFI-0709N-6D1BT-K1	Water	215.3	7.60	4"x2	172.3	5.04	4"x2	258.4	10.66	4"x2
PFI-0709N-6D1BT-L1	Water	215.3	7.60	4"x2	172.3	5.04	4"x2	258.4	10.66	4"x2
PFI-0709N-6D2BT-M1	Water	217.0	6.49	4"x2	173.6	4.30	4"x2	260.4	9.10	4"x2
PFI-0718N-2D2DS-J2	Water	468.1	2.60	4"x2	374.5	1.72	4"x2	561.7	3.65	4"x2
PFI-0718N-2D3DS-K2	Water	474.7	2.34	4"x2	379.7	1.55	4"x2	569.6	3.28	4"x2
PFI-0718N-3D1DS-H2	Water	461.5	4.17	4"x2	369.2	2.76	4"x2	553.8	5.84	4"x2
PFI-0718N-3D1DS-J2	Water	461.5	4.17	4"x2	369.2	2.76	4"x2	553.8	5.84	4"x2
PFI-0718N-3D2DS-J2	Water	468.1	3.64	4"x2	374.5	2.41	4"x2	561.7	5.10	4"x2
PFI-0718N-3D2DS-K2	Water	468.1	3.64	4"x2	374.5	2.41	4"x2	561.7	5.10	4"x2
PFI-0718N-3D3DS-L2	Water	474.7	3.24	4"x2	379.7	2.15	4"x2	569.6	4.54	4"x2
PFI-0718N-3D4DS-M2	Water	481.3	2.93	4"x2	385.0	1.94	4"x2	577.5	4.10	4"x2
PFI-0718N-4D1ES-H2	Water	461.5	5.38	4"x2	369.2	3.56	4"x2	553.8	7.54	4"x2
PFI-0718N-4D2DS-J2	Water	468.1	4.68	4"x2	374.5	3.10	4"x2	561.7	6.55	4"x2
PFI-0718N-4D3DS-K2	Water	474.7	4.14	4"x2	379.7	2.74	4"x2	569.6	5.80	4"x2



## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0718N-4D2DS-L2	Water	468.1	4.68	4"x2	374.5	3.10	4"x2	561.7	6.55	4"x2
PFI-0718N-4D2ES-L2	Water	468.1	4.68	4"x2	374.5	3.10	4"x2	561.7	6.55	4"x2
PFI-0718N-4D3DS-M2	Water	474.7	4.14	4"x2	379.7	2.74	4"x2	569.6	5.80	4"x2
PFI-0718N-4D2ES-M2	Water	468.1	4.68	4"x2	374.5	3.10	4"x2	561.7	6.55	4"x2
PFI-0718N-5D1ES-J2	Water	461.5	6.60	4"x2	369.2	4.37	4"x2	553.8	9.24	4"x2
PFI-0718N-5D1ES-M2	Water	461.5	6.60	4"x2	369.2	4.37	4"x2	553.8	9.24	4"x2
PFI-0718N-6D1ES-H2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-6D1ES-J2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-6D1ES-K2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-6D1ES-L2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-6D2ES-M2	Water	468.1	6.75	4"x2	374.5	4.47	4"x2	561.7	9.46	4"x2
PFI-0718N-3D4BS-H2	Water	481.3	2.93	4"x2	385.0	1.94	4"x2	577.5	4.10	4"x2
PFI-0718N-3D4BS-J2	Water	481.3	2.93	4"x2	385.0	1.94	4"x2	577.5	4.10	4"x2
PFI-0718N-3D4BS-K2	Water	481.3	2.93	4"x2	385.0	1.94	4"x2	577.5	4.10	4"x2
PFI-0718N-3D4BS-L2	Water	481.3	2.93	4"x2	385.0	1.94	4"x2	577.5	4.10	4"x2
PFI-0718N-3D4BS-M2	Water	481.3	2.93	4"x2	385.0	1.94	4"x2	577.5	4.10	4"x2
PFI-0718N-4D2BS-H2	Water	468.1	4.68	4"x2	374.5	3.10	4"x2	561.7	6.55	4"x2
PFI-0718N-4D4BS-J2	Water	481.3	3.72	4"x2	385.0	2.46	4"x2	577.5	5.21	4"x2
PFI-0718N-4D4BS-K2	Water	481.3	3.72	4"x2	385.0	2.46	4"x2	577.5	5.21	4"x2
PFI-0718N-4D4BS-L2	Water	481.3	3.72	4"x2	385.0	2.46	4"x2	577.5	5.21	4"x2
PFI-0718N-4D4BS-M2	Water	481.3	3.72	4"x2	385.0	2.46	4"x2	577.5	5.21	4"x2
PFI-0718N-5D3BS-H2	Water	474.7	5.04	4"x2	379.7	3.34	4"x2	569.6	7.06	4"x2
PFI-0718N-5D3BS-J2	Water	474.7	5.04	4"x2	379.7	3.34	4"x2	569.6	7.06	4"x2
PFI-0718N-5D3BS-K2	Water	474.7	5.04	4"x2	379.7	3.34	4"x2	569.6	7.06	4"x2
PFI-0718N-5D4BS-L2	Water	481.3	4.51	4"x2	385.0	2.99	4"x2	577.5	6.32	4"x2
PFI-0718N-5D4BS-M2	Water	481.3	4.51	4"x2	385.0	2.99	4"x2	577.5	6.32	4"x2
PFI-0718N-6D1BS-H2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-6D1BS-J2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-6D1BS-K2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-6D1BS-L2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-6D1BS-M2	Water	461.5	7.81	4"x2	369.2	5.17	4"x2	553.8	10.94	4"x2
PFI-0718N-2D2DZ-J2	Water	217.0	4.13	4"x2	173.6	2.73	4"x2	260.4	5.78	4"x2
PFI-0718N-2D3DZ-K2	Water	218.6	3.62	4"x2	174.9	2.40	4"x2	262.4	5.07	4"x2
PFI-0718N-3D1DZ-H2	Water	215.3	6.93	4"x2	172.3	4.59	4"x2	258.4	9.72	4"x2
PFI-0718N-3D1DZ-J2	Water	215.3	6.93	4"x2	172.3	4.59	4"x2	258.4	9.72	4"x2
PFI-0718N-3D2DZ-J2	Water	217.0	5.93	4"x2	173.6	3.93	4"x2	260.4	8.31	4"x2
PFI-0718N-3D2DZ-K2	Water	217.0	5.93	4"x2	173.6	3.93	4"x2	260.4	8.31	4"x2
PFI-0718N-3D3DZ-L2	Water	218.6	5.16	4"x2	174.9	3.42	4"x2	262.4	7.24	4"x2
PFI-0718N-3D4DZ-M2	Water	220.3	4.57	4"x2	176.2	3.02	4"x2	264.3	6.40	4"x2
PFI-0718N-4D1EZ-H2	Water	215.3	9.09	4"x2	172.3	6.02	4"x2	258.4	12.74	4"x2
PFI-0718N-4D2DZ-J2	Water	217.0	7.74	4"x2	173.6	5.12	4"x2	260.4	10.84	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0718N-4D3DZ-K2	Water	218.6	6.72	4"x2	174.9	4.45	4"x2	262.4	9.42	4"x2
PFI-0718N-4D2DZ-L2	Water	217.0	7.74	4"x2	173.6	5.12	4"x2	260.4	10.84	4"x2
PFI-0718N-4D2EZ-L2	Water	217.0	7.75	4"x2	173.6	5.13	4"x2	260.4	10.86	4"x2
PFI-0718N-4D3DZ-M2	Water	218.6	6.72	4"x2	174.9	4.45	4"x2	262.4	9.42	4"x2
PFI-0718N-4D2EZ-M2	Water	217.0	7.75	4"x2	173.6	5.13	4"x2	260.4	10.86	4"x2
PFI-0718N-5D1EZ-J2	Water	215.3	11.23	4"x2	172.3	7.44	4"x2	258.4	15.74	4"x2
PFI-0718N-5D1EZ-M2	Water	215.3	11.23	4"x2	172.3	7.44	4"x2	258.4	15.74	4"x2
PFI-0718N-6D1EZ-H2	Water	215.3	13.37	4"x2	172.3	8.86	4"x2	258.4	18.74	4"x2
PFI-0718N-6D1EZ-J2	Water	215.3	13.37	4"x2	172.3	8.86	4"x2	258.4	18.74	4"x2
PFI-0718N-6D1EZ-K2	Water	215.3	13.37	4"x2	172.3	8.86	4"x2	258.4	18.74	4"x2
PFI-0718N-6D1EZ-L2	Water	215.3	13.37	4"x2	172.3	8.86	4"x2	258.4	18.74	4"x2
PFI-0718N-6D2EZ-M2	Water	217.0	11.37	4"x2	173.6	7.52	4"x2	260.4	15.93	4"x2
PFI-0718N-3D4BT-H2	Water	220.3	4.55	4"x2	176.2	3.01	4"x2	264.3	6.37	4"x2
PFI-0718N-3D4BT-J2	Water	220.3	4.55	4"x2	176.2	3.01	4"x2	264.3	6.37	4"x2
PFI-0718N-3D4BT-K2	Water	220.3	4.55	4"x2	176.2	3.01	4"x2	264.3	6.37	4"x2
PFI-0718N-3D4BT-L2	Water	220.3	4.55	4"x2	176.2	3.01	4"x2	264.3	6.37	4"x2
PFI-0718N-3D4BT-M2	Water	220.3	4.55	4"x2	176.2	3.01	4"x2	264.3	6.37	4"x2
PFI-0718N-4D2BT-H2	Water	217.0	7.72	4"x2	173.6	5.11	4"x2	260.4	10.81	4"x2
PFI-0718N-4D4BT-J2	Water	220.3	5.90	4"x2	176.2	3.90	4"x2	264.3	8.26	4"x2
PFI-0718N-4D4BT-K2	Water	220.3	5.90	4"x2	176.2	3.90	4"x2	264.3	8.26	4"x2
PFI-0718N-4D4BT-L2	Water	220.3	5.90	4"x2	176.2	3.90	4"x2	264.3	8.26	4"x2
PFI-0718N-4D4BT-M2	Water	220.3	5.90	4"x2	176.2	3.90	4"x2	264.3	8.26	4"x2
PFI-0718N-5D3BT-H2	Water	218.6	8.24	4"x2	174.9	5.45	4"x2	262.4	11.55	4"x2
PFI-0718N-5D3BT-J2	Water	218.6	8.24	4"x2	174.9	5.45	4"x2	262.4	11.55	4"x2
PFI-0718N-5D3BT-K2	Water	218.6	8.24	4"x2	174.9	5.45	4"x2	262.4	11.55	4"x2
PFI-0718N-5D4BT-L2	Water	220.3	7.24	4"x2	176.2	4.79	4"x2	264.3	10.14	4"x2
PFI-0718N-5D4BT-M2	Water	220.3	7.24	4"x2	176.2	4.79	4"x2	264.3	10.14	4"x2
PFI-0718N-6D1BT-H2	Water	215.3	13.33	4"x2	172.3	8.83	4"x2	258.4	18.68	4"x2
PFI-0718N-6D1BT-J2	Water	215.3	13.33	4"x2	172.3	8.83	4"x2	258.4	18.68	4"x2
PFI-0718N-6D1BT-K2	Water	215.3	13.33	4"x2	172.3	8.83	4"x2	258.4	18.68	4"x2
PFI-0718N-6D1BT-L2	Water	215.3	13.33	4"x2	172.3	8.83	4"x2	258.4	18.68	4"x2
PFI-0718N-6D1BT-M2	Water	215.3	13.33	4"x2	172.3	8.83	4"x2	258.4	18.68	4"x2
PFI-1012N-2D2DS-J1	Water	494.5	1.46	4"x2	395.6	0.97	4"x2	593.4	2.05	4"x2
PFI-1012N-2D4ES-K1	Water	514.3	1.29	4"x2	411.4	0.86	4"x2	617.1	1.81	4"x2
PFI-1012N-2D2ES-L1	Water	494.5	1.46	4"x2	395.6	0.97	4"x2	593.4	2.05	4"x2
PFI-1012N-2D4ES-M1	Water	514.3	1.29	4"x2	411.4	0.86	4"x2	617.1	1.81	4"x2
PFI-1012N-2D4ES-N1	Water	514.3	1.29	4"x2	411.4	0.86	4"x2	617.1	1.81	4"x2
PFI-1012N-3D1DS-K1	Water	485.7	2.10	4"x2	388.5	1.39	4"x2	582.8	2.94	4"x2
PFI-1012N-3D1DS-L1	Water	485.7	2.10	4"x2	388.5	1.39	4"x2	582.8	2.94	4"x2
PFI-1012N-3D4DS-L1	Water	514.3	1.63	4"x2	411.4	1.08	4"x2	617.1	2.29	4"x2
PFI-1012N-3D2ES-M1	Water	494.5	1.91	4"x2	395.6	1.27	4"x2	593.4	2.68	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-3D1DS-N1	Water	485.7	2.10	4"x2	388.5	1.39	4"x2	582.8	2.94	4"x2
PFI-1012N-3D3DS-N1	Water	505.5	1.74	4"x2	404.4	1.15	4"x2	606.6	2.43	4"x2
PFI-1012N-3D1DS-O1	Water	485.7	2.10	4"x2	388.5	1.39	4"x2	582.8	2.94	4"x2
PFI-1012N-3D4ES-O1	Water	514.3	1.63	4"x2	411.4	1.08	4"x2	617.1	2.29	4"x2
PFI-1012N-4D4ES-J1	Water	514.3	1.98	4"x2	411.4	1.31	4"x2	617.1	2.77	4"x2
PFI-1012N-4D2DS-K1	Water	494.5	2.36	4"x2	395.6	1.56	4"x2	593.4	3.30	4"x2
PFI-1012N-4D3DS-L1	Water	505.5	2.12	4"x2	404.4	1.40	4"x2	606.6	2.97	4"x2
PFI-1012N-4D1DS-M1	Water	485.7	2.62	4"x2	388.5	1.73	4"x2	582.8	3.66	4"x2
PFI-1012N-4D2ES-N1	Water	494.5	2.36	4"x2	395.6	1.56	4"x2	593.4	3.30	4"x2
PFI-1012N-4D1DS-O1	Water	485.7	2.62	4"x2	388.5	1.73	4"x2	582.8	3.66	4"x2
PFI-1012N-5D1DS-L1	Water	485.7	3.13	4"x2	388.5	2.07	4"x2	582.8	4.39	4"x2
PFI-1012N-5D2DS-M1	Water	494.5	2.81	4"x2	395.6	1.86	4"x2	593.4	3.93	4"x2
PFI-1012N-5D2DS-O1	Water	494.5	2.81	4"x2	395.6	1.86	4"x2	593.4	3.93	4"x2
PFI-1012N-6D1ES-J1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1ES-K1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1DS-L1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1ES-L1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1ES-M1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1DS-N1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1ES-O1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-3D3BS-K1	Water	505.5	1.74	4"x2	404.4	1.15	4"x2	606.6	2.43	4"x2
PFI-1012N-3D4BS-L1	Water	514.3	1.63	4"x2	411.4	1.08	4"x2	617.1	2.29	4"x2
PFI-1012N-3D4BS-M1	Water	514.3	1.63	4"x2	411.4	1.08	4"x2	617.1	2.29	4"x2
PFI-1012N-3D4BS-N1	Water	514.3	1.63	4"x2	411.4	1.08	4"x2	617.1	2.29	4"x2
PFI-1012N-3D4BS-O1	Water	514.3	1.63	4"x2	411.4	1.08	4"x2	617.1	2.29	4"x2
PFI-1012N-4D4BS-J1	Water	514.3	1.98	4"x2	411.4	1.31	4"x2	617.1	2.77	4"x2
PFI-1012N-4D4BS-K1	Water	514.3	1.98	4"x2	411.4	1.31	4"x2	617.1	2.77	4"x2
PFI-1012N-4D3BS-L1	Water	505.5	2.12	4"x2	404.4	1.40	4"x2	606.6	2.97	4"x2
PFI-1012N-4D4BS-M1	Water	514.3	1.98	4"x2	411.4	1.31	4"x2	617.1	2.77	4"x2
PFI-1012N-4D3BS-N1	Water	505.5	2.12	4"x2	404.4	1.40	4"x2	606.6	2.97	4"x2
PFI-1012N-4D4BS-O1	Water	514.3	1.98	4"x2	411.4	1.31	4"x2	617.1	2.77	4"x2
PFI-1012N-5D4BS-J1	Water	514.3	2.32	4"x2	411.4	1.53	4"x2	617.1	3.24	4"x2
PFI-1012N-5D4BS-K1	Water	514.3	2.32	4"x2	411.4	1.53	4"x2	617.1	3.24	4"x2
PFI-1012N-5D4BS-L1	Water	514.3	2.32	4"x2	411.4	1.53	4"x2	617.1	3.24	4"x2
PFI-1012N-5D2BS-M1	Water	494.5	2.81	4"x2	395.6	1.86	4"x2	593.4	3.93	4"x2
PFI-1012N-5D4BS-N1	Water	514.3	2.32	4"x2	411.4	1.53	4"x2	617.1	3.24	4"x2
PFI-1012N-5D2BS-O1	Water	494.5	2.81	4"x2	395.6	1.86	4"x2	593.4	3.93	4"x2
PFI-1012N-6D1BS-J1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1BS-K1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1BS-L1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1BS-M1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-6D1BS-N1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-6D1BS-O1	Water	485.7	3.65	4"x2	388.5	2.41	4"x2	582.8	5.11	4"x2
PFI-1012N-2D2DZ-J1	Water	223.6	2.03	4"x2	178.9	1.35	4"x2	268.3	2.85	4"x2
PFI-1012N-2D4EZ-K1	Water	228.5	1.67	4"x2	182.8	1.11	4"x2	274.2	2.34	4"x2
PFI-1012N-2D2EZ-L1	Water	223.6	2.04	4"x2	178.9	1.35	4"x2	268.3	2.86	4"x2
PFI-1012N-2D4EZ-M1	Water	228.5	1.67	4"x2	182.8	1.11	4"x2	274.2	2.34	4"x2
PFI-1012N-2D4EZ-N1	Water	228.5	1.67	4"x2	182.8	1.11	4"x2	274.2	2.34	4"x2
PFI-1012N-3D1DZ-K1	Water	221.4	3.15	4"x2	177.1	2.08	4"x2	265.7	4.41	4"x2
PFI-1012N-3D1DZ-L1	Water	221.4	3.15	4"x2	177.1	2.08	4"x2	265.7	4.41	4"x2
PFI-1012N-3D4DZ-L1	Water	228.5	2.22	4"x2	182.8	1.47	4"x2	274.2	3.11	4"x2
PFI-1012N-3D2EZ-M1	Water	223.6	2.79	4"x2	178.9	1.85	4"x2	268.3	3.90	4"x2
PFI-1012N-3D1DZ-N1	Water	221.4	3.15	4"x2	177.1	2.08	4"x2	265.7	4.41	4"x2
PFI-1012N-3D3DZ-N1	Water	226.3	2.43	4"x2	181.1	1.61	4"x2	271.6	3.40	4"x2
PFI-1012N-3D1DZ-O1	Water	221.4	3.15	4"x2	177.1	2.08	4"x2	265.7	4.41	4"x2
PFI-1012N-3D4EZ-O1	Water	228.5	2.23	4"x2	182.8	1.48	4"x2	274.2	3.12	4"x2
PFI-1012N-4D4EZ-J1	Water	228.5	2.78	4"x2	182.8	1.84	4"x2	274.2	3.90	4"x2
PFI-1012N-4D2DZ-K1	Water	223.6	3.52	4"x2	178.9	2.33	4"x2	268.3	4.94	4"x2
PFI-1012N-4D3DZ-L1	Water	226.3	3.06	4"x2	181.1	2.03	4"x2	271.6	4.28	4"x2
PFI-1012N-4D1DZ-M1	Water	221.4	4.02	4"x2	177.1	2.66	4"x2	265.7	5.64	4"x2
PFI-1012N-4D2EZ-N1	Water	223.6	3.53	4"x2	178.9	2.34	4"x2	268.3	4.95	4"x2
PFI-1012N-4D1DZ-O1	Water	221.4	4.02	4"x2	177.1	2.66	4"x2	265.7	5.64	4"x2
PFI-1012N-5D1DZ-L1	Water	221.4	4.90	4"x2	177.1	3.24	4"x2	265.7	6.86	4"x2
PFI-1012N-5D2DZ-M1	Water	223.6	4.27	4"x2	178.9	2.83	4"x2	268.3	5.98	4"x2
PFI-1012N-5D2DZ-O1	Water	223.6	4.27	4"x2	178.9	2.83	4"x2	268.3	5.98	4"x2
PFI-1012N-6D1EZ-J1	Water	221.4	5.78	4"x2	177.1	3.83	4"x2	265.7	8.10	4"x2
PFI-1012N-6D1EZ-K1	Water	221.4	5.78	4"x2	177.1	3.83	4"x2	265.7	8.10	4"x2
PFI-1012N-6D1DZ-L1	Water	221.4	5.77	4"x2	177.1	3.82	4"x2	265.7	8.09	4"x2
PFI-1012N-6D1EZ-L1	Water	221.4	5.78	4"x2	177.1	3.83	4"x2	265.7	8.10	4"x2
PFI-1012N-6D1EZ-M1	Water	221.4	5.78	4"x2	177.1	3.83	4"x2	265.7	8.10	4"x2
PFI-1012N-6D1DZ-N1	Water	221.4	5.77	4"x2	177.1	3.82	4"x2	265.7	8.09	4"x2
PFI-1012N-6D1EZ-O1	Water	221.4	5.78	4"x2	177.1	3.83	4"x2	265.7	8.10	4"x2
PFI-1012N-3D3BT-K1	Water	226.3	2.41	4"x2	181.1	1.60	4"x2	271.6	3.38	4"x2
PFI-1012N-3D4BT-L1	Water	228.5	2.20	4"x2	182.8	1.46	4"x2	274.2	3.08	4"x2
PFI-1012N-3D4BT-M1	Water	228.5	2.20	4"x2	182.8	1.46	4"x2	274.2	3.08	4"x2
PFI-1012N-3D4BT-N1	Water	228.5	2.20	4"x2	182.8	1.46	4"x2	274.2	3.08	4"x2
PFI-1012N-3D4BT-O1	Water	228.5	2.20	4"x2	182.8	1.46	4"x2	274.2	3.08	4"x2
PFI-1012N-4D4BT-J1	Water	228.5	2.75	4"x2	182.8	1.82	4"x2	274.2	3.85	4"x2
PFI-1012N-4D4BT-K1	Water	228.5	2.75	4"x2	182.8	1.82	4"x2	274.2	3.85	4"x2
PFI-1012N-4D3BT-L1	Water	226.3	3.03	4"x2	181.1	2.01	4"x2	271.6	4.25	4"x2
PFI-1012N-4D4BT-M1	Water	228.5	2.75	4"x2	182.8	1.82	4"x2	274.2	3.85	4"x2
PFI-1012N-4D3BT-N1	Water	226.3	3.03	4"x2	181.1	2.01	4"x2	271.6	4.25	4"x2





## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-4D4BT-O1	Water	228.5	2.75	4"x2	182.8	1.82	4"x2	274.2	3.85	4"x2
PFI-1012N-5D4BT-J1	Water	228.5	3.30	4"x2	182.8	2.18	4"x2	274.2	4.62	4"x2
PFI-1012N-5D4BT-K1	Water	228.5	3.30	4"x2	182.8	2.18	4"x2	274.2	4.62	4"x2
PFI-1012N-5D4BT-L1	Water	228.5	3.30	4"x2	182.8	2.18	4"x2	274.2	4.62	4"x2
PFI-1012N-5D2BT-M1	Water	223.6	4.24	4"x2	178.9	2.81	4"x2	268.3	5.95	4"x2
PFI-1012N-5D4BT-N1	Water	228.5	3.30	4"x2	182.8	2.18	4"x2	274.2	4.62	4"x2
PFI-1012N-5D2BT-O1	Water	223.6	4.24	4"x2	178.9	2.81	4"x2	268.3	5.95	4"x2
PFI-1012N-6D1BT-J1	Water	221.4	5.74	4"x2	177.1	3.80	4"x2	265.7	8.04	4"x2
PFI-1012N-6D1BT-K1	Water	221.4	5.74	4"x2	177.1	3.80	4"x2	265.7	8.04	4"x2
PFI-1012N-6D1BT-L1	Water	221.4	5.74	4"x2	177.1	3.80	4"x2	265.7	8.04	4"x2
PFI-1012N-6D2BT-M1	Water	223.6	4.99	4"x2	178.9	3.30	4"x2	268.3	6.99	4"x2
PFI-1012N-6D1BT-N1	Water	221.4	5.74	4"x2	177.1	3.80	4"x2	265.7	8.04	4"x2
PFI-1012N-6D1BT-O1	Water	221.4	5.74	4"x2	177.1	3.80	4"x2	265.7	8.04	4"x2
PFI-1024N-2D2DS-J2	Water	989.0	1.46	4"x4	791.2	0.97	4"x4	1186.7	2.05	4"x4
PFI-1024N-2D4ES-K2	Water	1028.6	1.29	4"x4	822.8	0.86	4"x4	1234.3	1.81	4"x4
PFI-1024N-2D2ES-L2	Water	989.0	1.46	4"x4	791.2	0.97	4"x4	1186.7	2.05	4"x4
PFI-1024N-2D4ES-M2	Water	1028.6	1.29	4"x4	822.8	0.86	4"x4	1234.3	1.81	4"x4
PFI-1024N-2D4ES-N2	Water	1028.6	1.29	4"x4	822.8	0.86	4"x4	1234.3	1.81	4"x4
PFI-1024N-3D1DS-K2	Water	971.4	2.10	4"x4	777.1	1.39	4"x4	1165.6	2.94	4"x4
PFI-1024N-3D1DS-L2	Water	971.4	2.10	4"x4	777.1	1.39	4"x4	1165.6	2.94	4"x4
PFI-1024N-3D4DS-L2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-1024N-3D2ES-M2	Water	989.0	1.91	4"x4	791.2	1.27	4"x4	1186.7	2.68	4"x4
PFI-1024N-3D1DS-N2	Water	971.4	2.10	4"x4	777.1	1.39	4"x4	1165.6	2.94	4"x4
PFI-1024N-3D3DS-N2	Water	1011.0	1.74	4"x4	808.8	1.15	4"x4	1213.1	2.43	4"x4
PFI-1024N-3D1DS-O2	Water	971.4	2.10	4"x4	777.1	1.39	4"x4	1165.6	2.94	4"x4
PFI-1024N-3D4ES-O2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-1024N-4D4ES-J2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-1024N-4D2DS-K2	Water	989.0	2.36	4"x4	791.2	1.56	4"x4	1186.7	3.30	4"x4
PFI-1024N-4D3DS-L2	Water	1011.0	2.12	4"x4	808.8	1.40	4"x4	1213.1	2.97	4"x4
PFI-1024N-4D1DS-M2	Water	971.4	2.62	4"x4	777.1	1.73	4"x4	1165.6	3.66	4"x4
PFI-1024N-4D2ES-N2	Water	989.0	2.36	4"x4	791.2	1.56	4"x4	1186.7	3.30	4"x4
PFI-1024N-4D1DS-O2	Water	971.4	2.62	4"x4	777.1	1.73	4"x4	1165.6	3.66	4"x4
PFI-1024N-5D1DS-L2	Water	971.4	3.13	4"x4	777.1	2.07	4"x4	1165.6	4.39	4"x4
PFI-1024N-5D2DS-M2	Water	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.93	4"x4
PFI-1024N-5D2DS-O2	Water	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.93	4"x4
PFI-1024N-6D1ES-J2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1ES-K2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1DS-L2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1ES-L2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1ES-M2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1DS-N2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4



# PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-6D1ES-O2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-3D3BS-K2	Water	1011.0	1.74	4"x4	808.8	1.15	4"x4	1213.1	2.43	4"x4
PFI-1024N-3D4BS-L2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-1024N-3D4BS-M2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-1024N-3D4BS-N2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-1024N-3D4BS-O2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-1024N-4D4BS-J2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-1024N-4D4BS-K2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-1024N-4D3BS-L2	Water	1011.0	2.12	4"x4	808.8	1.40	4"x4	1213.1	2.97	4"x4
PFI-1024N-4D4BS-M2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-1024N-4D3BS-N2	Water	1011.0	2.12	4"x4	808.8	1.40	4"x4	1213.1	2.97	4"x4
PFI-1024N-4D4BS-O2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-1024N-5D4BS-J2	Water	1028.6	2.32	4"x4	822.8	1.53	4"x4	1234.3	3.24	4"x4
PFI-1024N-5D4BS-K2	Water	1028.6	2.32	4"x4	822.8	1.53	4"x4	1234.3	3.24	4"x4
PFI-1024N-5D4BS-L2	Water	1028.6	2.32	4"x4	822.8	1.53	4"x4	1234.3	3.24	4"x4
PFI-1024N-5D2BS-M2	Water	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.93	4"x4
PFI-1024N-5D4BS-N2	Water	1028.6	2.32	4"x4	822.8	1.53	4"x4	1234.3	3.24	4"x4
PFI-1024N-5D2BS-O2	Water	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.93	4"x4
PFI-1024N-6D1BS-J2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1BS-K2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1BS-L2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1BS-M2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1BS-N2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-6D1BS-O2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-1024N-2D2DZ-J2	Water	447.2	2.03	4"x4	357.7	1.35	4"x4	536.6	2.85	4"x4
PFI-1024N-2D4EZ-K2	Water	457.1	1.67	4"x4	365.7	1.11	4"x4	548.5	2.34	4"x4
PFI-1024N-2D2EZ-L2	Water	447.2	2.04	4"x4	357.7	1.35	4"x4	536.6	2.86	4"x4
PFI-1024N-2D4EZ-M2	Water	457.1	1.67	4"x4	365.7	1.11	4"x4	548.5	2.34	4"x4
PFI-1024N-2D4EZ-N2	Water	457.1	1.67	4"x4	365.7	1.11	4"x4	548.5	2.34	4"x4
PFI-1024N-3D1DZ-K2	Water	442.8	3.15	4"x4	354.2	2.08	4"x4	531.3	4.41	4"x4
PFI-1024N-3D1DZ-L2	Water	442.8	3.15	4"x4	354.2	2.08	4"x4	531.3	4.41	4"x4
PFI-1024N-3D4DZ-L2	Water	457.1	2.22	4"x4	365.7	1.47	4"x4	548.5	3.11	4"x4
PFI-1024N-3D2EZ-M2	Water	447.2	2.79	4"x4	357.7	1.84	4"x4	536.6	3.90	4"x4
PFI-1024N-3D1DZ-N2	Water	442.8	3.15	4"x4	354.2	2.08	4"x4	531.3	4.41	4"x4
PFI-1024N-3D3DZ-N2	Water	452.7	2.43	4"x4	362.1	1.61	4"x4	543.2	3.40	4"x4
PFI-1024N-3D1DZ-O2	Water	442.8	3.15	4"x4	354.2	2.08	4"x4	531.3	4.41	4"x4
PFI-1024N-3D4EZ-O2	Water	457.1	2.23	4"x4	365.7	1.48	4"x4	548.5	3.12	4"x4
PFI-1024N-4D4EZ-J2	Water	457.1	2.78	4"x4	365.7	1.84	4"x4	548.5	3.90	4"x4
PFI-1024N-4D2DZ-K2	Water	447.2	3.52	4"x4	357.7	2.33	4"x4	536.6	4.94	4"x4
PFI-1024N-4D3DZ-L2	Water	452.7	3.06	4"x4	362.1	2.02	4"x4	543.2	4.28	4"x4
PFI-1024N-4D1DZ-M2	Water	442.8	4.02	4"x4	354.2	2.66	4"x4	531.3	5.63	4"x4



## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-4D2EZ-N2	Water	447.2	3.53	4"x4	357.7	2.34	4"x4	536.6	4.95	4"x4
PFI-1024N-4D1DZ-O2	Water	442.8	4.02	4"x4	354.2	2.66	4"x4	531.3	5.63	4"x4
PFI-1024N-5D1DZ-L2	Water	442.8	4.90	4"x4	354.2	3.24	4"x4	531.3	6.86	4"x4
PFI-1024N-5D2DZ-M2	Water	447.2	4.27	4"x4	357.7	2.83	4"x4	536.6	5.98	4"x4
PFI-1024N-5D2DZ-O2	Water	447.2	4.27	4"x4	357.7	2.83	4"x4	536.6	5.98	4"x4
PFI-1024N-6D1EZ-J2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-1024N-6D1EZ-K2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-1024N-6D1DZ-L2	Water	442.8	5.77	4"x4	354.2	3.82	4"x4	531.3	8.08	4"x4
PFI-1024N-6D1EZ-L2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-1024N-6D1EZ-M2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-1024N-6D1DZ-N2	Water	442.8	5.77	4"x4	354.2	3.82	4"x4	531.3	8.08	4"x4
PFI-1024N-6D1EZ-O2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-1024N-3D3BT-K2	Water	452.7	2.41	4"x4	362.1	1.60	4"x4	543.2	3.38	4"x4
PFI-1024N-3D4BT-L2	Water	457.1	2.20	4"x4	365.7	1.46	4"x4	548.5	3.08	4"x4
PFI-1024N-3D4BT-M2	Water	457.1	2.20	4"x4	365.7	1.46	4"x4	548.5	3.08	4"x4
PFI-1024N-3D4BT-N2	Water	457.1	2.20	4"x4	365.7	1.46	4"x4	548.5	3.08	4"x4
PFI-1024N-3D4BT-O2	Water	457.1	2.20	4"x4	365.7	1.46	4"x4	548.5	3.08	4"x4
PFI-1024N-4D4BT-J2	Water	457.1	2.75	4"x4	365.7	1.82	4"x4	548.5	3.85	4"x4
PFI-1024N-4D4BT-K2	Water	457.1	2.75	4"x4	365.7	1.82	4"x4	548.5	3.85	4"x4
PFI-1024N-4D3BT-L2	Water	452.7	3.04	4"x4	362.1	2.01	4"x4	543.2	4.25	4"x4
PFI-1024N-4D4BT-M2	Water	457.1	2.75	4"x4	365.7	1.82	4"x4	548.5	3.85	4"x4
PFI-1024N-4D3BT-N2	Water	452.7	3.04	4"x4	362.1	2.01	4"x4	543.2	4.25	4"x4
PFI-1024N-4D4BT-O2	Water	457.1	2.75	4"x4	365.7	1.82	4"x4	548.5	3.85	4"x4
PFI-1024N-5D4BT-J2	Water	457.1	3.30	4"x4	365.7	2.19	4"x4	548.5	4.62	4"x4
PFI-1024N-5D4BT-K2	Water	457.1	3.30	4"x4	365.7	2.19	4"x4	548.5	4.62	4"x4
PFI-1024N-5D4BT-L2	Water	457.1	3.30	4"x4	365.7	2.19	4"x4	548.5	4.62	4"x4
PFI-1024N-5D2BT-M2	Water	447.2	4.24	4"x4	357.7	2.81	4"x4	536.6	5.95	4"x4
PFI-1024N-5D4BT-N2	Water	457.1	3.30	4"x4	365.7	2.19	4"x4	548.5	4.62	4"x4
PFI-1024N-5D2BT-O2	Water	447.2	4.24	4"x4	357.7	2.81	4"x4	536.6	5.95	4"x4
PFI-1024N-6D1BT-J2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-1024N-6D1BT-K2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-1024N-6D1BT-L2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-1024N-6D2BT-M2	Water	447.2	4.99	4"x4	357.7	3.30	4"x4	536.6	6.99	4"x4
PFI-1024N-6D1BT-N2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-1024N-6D1BT-O2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-2012N-2D2DS-J2	Water	989.0	1.46	4"x4	791.2	0.97	4"x4	1186.7	2.05	4"x4
PFI-2012N-2D4ES-K2	Water	1028.6	1.29	4"x4	822.8	0.86	4"x4	1234.3	1.81	4"x4
PFI-2012N-2D2ES-L2	Water	989.0	1.46	4"x4	791.2	0.97	4"x4	1186.7	2.05	4"x4
PFI-2012N-2D4ES-M2	Water	1028.6	1.29	4"x4	822.8	0.86	4"x4	1234.3	1.81	4"x4
PFI-2012N-2D4ES-N2	Water	1028.6	1.29	4"x4	822.8	0.86	4"x4	1234.3	1.81	4"x4
PFI-2012N-3D1DS-K2	Water	971.4	2.10	4"x4	777.1	1.39	4"x4	1165.6	2.94	4"x4



## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-3D1DS-L2	Water	971.4	2.10	4"x4	777.1	1.39	4"x4	1165.6	2.94	4"x4
PFI-2012N-3D4DS-L2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-2012N-3D2ES-M2	Water	989.0	1.91	4"x4	791.2	1.27	4"x4	1186.7	2.68	4"x4
PFI-2012N-3D1DS-N2	Water	971.4	2.10	4"x4	777.1	1.39	4"x4	1165.6	2.94	4"x4
PFI-2012N-3D3DS-N2	Water	1011.0	1.74	4"x4	808.8	1.15	4"x4	1213.1	2.43	4"x4
PFI-2012N-3D1DS-O2	Water	971.4	2.10	4"x4	777.1	1.39	4"x4	1165.6	2.94	4"x4
PFI-2012N-3D4ES-O2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-2012N-4D4ES-J2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-2012N-4D2DS-K2	Water	989.0	2.36	4"x4	791.2	1.56	4"x4	1186.7	3.30	4"x4
PFI-2012N-4D3DS-L2	Water	1011.0	2.12	4"x4	808.8	1.40	4"x4	1213.1	2.97	4"x4
PFI-2012N-4D1DS-M2	Water	971.4	2.62	4"x4	777.1	1.73	4"x4	1165.6	3.66	4"x4
PFI-2012N-4D2ES-N2	Water	989.0	2.36	4"x4	791.2	1.56	4"x4	1186.7	3.30	4"x4
PFI-2012N-4D1DS-O2	Water	971.4	2.62	4"x4	777.1	1.73	4"x4	1165.6	3.66	4"x4
PFI-2012N-5D1DS-L2	Water	971.4	3.13	4"x4	777.1	2.07	4"x4	1165.6	4.39	4"x4
PFI-2012N-5D2DS-M2	Water	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.93	4"x4
PFI-2012N-5D2DS-O2	Water	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.93	4"x4
PFI-2012N-6D1ES-J2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1ES-K2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1DS-L2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1ES-L2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1ES-M2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1DS-N2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1ES-O2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-3D3BS-K2	Water	1011.0	1.74	4"x4	808.8	1.15	4"x4	1213.1	2.43	4"x4
PFI-2012N-3D4BS-L2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-2012N-3D4BS-M2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-2012N-3D4BS-N2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-2012N-3D4BS-O2	Water	1028.6	1.63	4"x4	822.8	1.08	4"x4	1234.3	2.29	4"x4
PFI-2012N-4D4BS-J2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-2012N-4D4BS-K2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-2012N-4D3BS-L2	Water	1011.0	2.12	4"x4	808.8	1.40	4"x4	1213.1	2.97	4"x4
PFI-2012N-4D4BS-M2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-2012N-4D3BS-N2	Water	1011.0	2.12	4"x4	808.8	1.40	4"x4	1213.1	2.97	4"x4
PFI-2012N-4D4BS-O2	Water	1028.6	1.98	4"x4	822.8	1.31	4"x4	1234.3	2.77	4"x4
PFI-2012N-5D4BS-J2	Water	1028.6	2.32	4"x4	822.8	1.53	4"x4	1234.3	3.24	4"x4
PFI-2012N-5D4BS-K2	Water	1028.6	2.32	4"x4	822.8	1.53	4"x4	1234.3	3.24	4"x4
PFI-2012N-5D4BS-L2	Water	1028.6	2.32	4"x4	822.8	1.53	4"x4	1234.3	3.24	4"x4
PFI-2012N-5D2BS-M2	Water	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.93	4"x4
PFI-2012N-5D4BS-N2	Water	1028.6	2.32	4"x4	822.8	1.53	4"x4	1234.3	3.24	4"x4
PFI-2012N-5D2BS-O2	Water	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.93	4"x4
PFI-2012N-6D1BS-J2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-6D1BS-K2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1BS-L2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1BS-M2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1BS-N2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-6D1BS-O2	Water	971.4	3.65	4"x4	777.1	2.42	4"x4	1165.6	5.11	4"x4
PFI-2012N-2D2DZ-J2	Water	447.2	2.03	4"x4	357.7	1.35	4"x4	536.6	2.85	4"x4
PFI-2012N-2D4EZ-K2	Water	457.1	1.67	4"x4	365.7	1.11	4"x4	548.5	2.34	4"x4
PFI-2012N-2D2EZ-L2	Water	447.2	2.04	4"x4	357.7	1.35	4"x4	536.6	2.86	4"x4
PFI-2012N-2D4EZ-M2	Water	457.1	1.67	4"x4	365.7	1.11	4"x4	548.5	2.34	4"x4
PFI-2012N-2D4EZ-N2	Water	457.1	1.67	4"x4	365.7	1.11	4"x4	548.5	2.34	4"x4
PFI-2012N-3D1DZ-K2	Water	442.8	3.15	4"x4	354.2	2.08	4"x4	531.3	4.41	4"x4
PFI-2012N-3D1DZ-L2	Water	442.8	3.15	4"x4	354.2	2.08	4"x4	531.3	4.41	4"x4
PFI-2012N-3D4DZ-L2	Water	457.1	2.22	4"x4	365.7	1.47	4"x4	548.5	3.11	4"x4
PFI-2012N-3D2EZ-M2	Water	447.2	2.79	4"x4	357.7	1.84	4"x4	536.6	3.90	4"x4
PFI-2012N-3D1DZ-N2	Water	442.8	3.15	4"x4	354.2	2.08	4"x4	531.3	4.41	4"x4
PFI-2012N-3D3DZ-N2	Water	452.7	2.43	4"x4	362.1	1.61	4"x4	543.2	3.40	4"x4
PFI-2012N-3D1DZ-O2	Water	442.8	3.15	4"x4	354.2	2.08	4"x4	531.3	4.41	4"x4
PFI-2012N-3D4EZ-O2	Water	457.1	2.23	4"x4	365.7	1.48	4"x4	548.5	3.12	4"x4
PFI-2012N-4D4EZ-J2	Water	457.1	2.78	4"x4	365.7	1.84	4"x4	548.5	3.90	4"x4
PFI-2012N-4D2DZ-K2	Water	447.2	3.52	4"x4	357.7	2.33	4"x4	536.6	4.94	4"x4
PFI-2012N-4D3DZ-L2	Water	452.7	3.06	4"x4	362.1	2.02	4"x4	543.2	4.28	4"x4
PFI-2012N-4D1DZ-M2	Water	442.8	4.02	4"x4	354.2	2.66	4"x4	531.3	5.63	4"x4
PFI-2012N-4D2EZ-N2	Water	447.2	3.53	4"x4	357.7	2.34	4"x4	536.6	4.95	4"x4
PFI-2012N-4D1DZ-O2	Water	442.8	4.02	4"x4	354.2	2.66	4"x4	531.3	5.63	4"x4
PFI-2012N-5D1DZ-L2	Water	442.8	4.90	4"x4	354.2	3.24	4"x4	531.3	6.86	4"x4
PFI-2012N-5D2DZ-M2	Water	447.2	4.27	4"x4	357.7	2.83	4"x4	536.6	5.98	4"x4
PFI-2012N-5D2DZ-O2	Water	447.2	4.27	4"x4	357.7	2.83	4"x4	536.6	5.98	4"x4
PFI-2012N-6D1EZ-J2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-2012N-6D1EZ-K2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-2012N-6D1DZ-L2	Water	442.8	5.77	4"x4	354.2	3.82	4"x4	531.3	8.08	4"x4
PFI-2012N-6D1EZ-L2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-2012N-6D1EZ-M2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-2012N-6D1DZ-N2	Water	442.8	5.77	4"x4	354.2	3.82	4"x4	531.3	8.08	4"x4
PFI-2012N-6D1EZ-O2	Water	442.8	5.78	4"x4	354.2	3.83	4"x4	531.3	8.10	4"x4
PFI-2012N-3D3BT-K2	Water	452.7	2.41	4"x4	362.1	1.60	4"x4	543.2	3.38	4"x4
PFI-2012N-3D4BT-L2	Water	457.1	2.20	4"x4	365.7	1.46	4"x4	548.5	3.08	4"x4
PFI-2012N-3D4BT-M2	Water	457.1	2.20	4"x4	365.7	1.46	4"x4	548.5	3.08	4"x4
PFI-2012N-3D4BT-N2	Water	457.1	2.20	4"x4	365.7	1.46	4"x4	548.5	3.08	4"x4
PFI-2012N-3D4BT-O2	Water	457.1	2.20	4"x4	365.7	1.46	4"x4	548.5	3.08	4"x4
PFI-2012N-4D4BT-J2	Water	457.1	2.75	4"x4	365.7	1.82	4"x4	548.5	3.85	4"x4
PFI-2012N-4D4BT-K2	Water	457.1	2.75	4"x4	365.7	1.82	4"x4	548.5	3.85	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-4D3BT-L2	Water	452.7	3.04	4"x4	362.1	2.01	4"x4	543.2	4.25	4"x4
PFI-2012N-4D4BT-M2	Water	457.1	2.75	4"x4	365.7	1.82	4"x4	548.5	3.85	4"x4
PFI-2012N-4D3BT-N2	Water	452.7	3.04	4"x4	362.1	2.01	4"x4	543.2	4.25	4"x4
PFI-2012N-4D4BT-O2	Water	457.1	2.75	4"x4	365.7	1.82	4"x4	548.5	3.85	4"x4
PFI-2012N-5D4BT-J2	Water	457.1	3.30	4"x4	365.7	2.19	4"x4	548.5	4.62	4"x4
PFI-2012N-5D4BT-K2	Water	457.1	3.30	4"x4	365.7	2.19	4"x4	548.5	4.62	4"x4
PFI-2012N-5D4BT-L2	Water	457.1	3.30	4"x4	365.7	2.19	4"x4	548.5	4.62	4"x4
PFI-2012N-5D2BT-M2	Water	447.2	4.24	4"x4	357.7	2.81	4"x4	536.6	5.95	4"x4
PFI-2012N-5D4BT-N2	Water	457.1	3.30	4"x4	365.7	2.19	4"x4	548.5	4.62	4"x4
PFI-2012N-5D2BT-O2	Water	447.2	4.24	4"x4	357.7	2.81	4"x4	536.6	5.95	4"x4
PFI-2012N-6D1BT-J2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-2012N-6D1BT-K2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-2012N-6D1BT-L2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-2012N-6D2BT-M2	Water	447.2	4.99	4"x4	357.7	3.30	4"x4	536.6	6.99	4"x4
PFI-2012N-6D1BT-N2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-2012N-6D1BT-O2	Water	442.8	5.74	4"x4	354.2	3.80	4"x4	531.3	8.04	4"x4
PFI-1212N-2D4DS-K1	Water	540.7	1.18	4"x2	432.5	0.78	4"x2	648.8	1.65	4"x2
PFI-1212N-2D3ES-L1	Water	527.5	1.22	4"x2	422.0	0.81	4"x2	633.0	1.71	4"x2
PFI-1212N-2D4DS-M1	Water	540.7	1.18	4"x2	432.5	0.78	4"x2	648.8	1.65	4"x2
PFI-1212N-2D4ES-M1	Water	540.7	1.18	4"x2	432.5	0.78	4"x2	648.8	1.65	4"x2
PFI-1212N-2D4ES-N1	Water	540.7	1.18	4"x2	432.5	0.78	4"x2	648.8	1.65	4"x2
PFI-1212N-2D4ES-O1	Water	540.7	1.18	4"x2	432.5	0.78	4"x2	648.8	1.65	4"x2
PFI-1212N-3D2DS-L1	Water	516.5	1.61	4"x2	413.2	1.07	4"x2	619.8	2.26	4"x2
PFI-1212N-3D3DS-M1	Water	527.5	1.52	4"x2	422.0	1.01	4"x2	633.0	2.13	4"x2
PFI-1212N-3D2ES-M1	Water	516.5	1.61	4"x2	413.2	1.07	4"x2	619.8	2.26	4"x2
PFI-1212N-3D2DS-N1	Water	516.5	1.61	4"x2	413.2	1.07	4"x2	619.8	2.26	4"x2
PFI-1212N-3D2ES-N1	Water	516.5	1.61	4"x2	413.2	1.07	4"x2	619.8	2.26	4"x2
PFI-1212N-3D4ES-O1	Water	540.7	1.44	4"x2	432.5	0.95	4"x2	648.8	2.01	4"x2
PFI-1212N-3D1DS-P1	Water	505.5	1.74	4"x2	404.4	1.15	4"x2	606.6	2.43	4"x2
PFI-1212N-4D1ES-K1	Water	505.5	2.12	4"x2	404.4	1.40	4"x2	606.6	2.97	4"x2
PFI-1212N-4D3ES-M1	Water	527.5	1.81	4"x2	422.0	1.20	4"x2	633.0	2.54	4"x2
PFI-1212N-4D2DS-N1	Water	516.5	1.94	4"x2	413.2	1.29	4"x2	619.8	2.72	4"x2
PFI-1212N-4D3DS-P1	Water	527.5	1.81	4"x2	422.0	1.20	4"x2	633.0	2.54	4"x2
PFI-1212N-5D2ES-K1	Water	516.5	2.28	4"x2	413.2	1.51	4"x2	619.8	3.19	4"x2
PFI-1212N-5D2ES-L1	Water	516.5	2.28	4"x2	413.2	1.51	4"x2	619.8	3.19	4"x2
PFI-1212N-5D2DS-N1	Water	516.5	2.28	4"x2	413.2	1.51	4"x2	619.8	3.19	4"x2
PFI-1212N-5D1DS-O1	Water	505.5	2.50	4"x2	404.4	1.66	4"x2	606.6	3.50	4"x2
PFI-1212N-5D4DS-O1	Water	540.7	1.96	4"x2	432.5	1.30	4"x2	648.8	2.74	4"x2
PFI-1212N-5D2ES-P1	Water	516.5	2.28	4"x2	413.2	1.51	4"x2	619.8	3.19	4"x2
PFI-1212N-6D1ES-L1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-6D1ES-M1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2



## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-6D1ES-N1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-6D1ES-O1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-6D1ES-P1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-3D3BS-L1	Water	527.5	1.52	4"x2	422.0	1.01	4"x2	633.0	2.13	4"x2
PFI-1212N-3D4BS-N1	Water	540.7	1.44	4"x2	432.5	0.95	4"x2	648.8	2.01	4"x2
PFI-1212N-3D4BS-O1	Water	540.7	1.44	4"x2	432.5	0.95	4"x2	648.8	2.01	4"x2
PFI-1212N-4D4BS-K1	Water	540.7	1.70	4"x2	432.5	1.12	4"x2	648.8	2.38	4"x2
PFI-1212N-4D3BS-L1	Water	527.5	1.81	4"x2	422.0	1.20	4"x2	633.0	2.54	4"x2
PFI-1212N-4D4BS-M1	Water	540.7	1.70	4"x2	432.5	1.12	4"x2	648.8	2.38	4"x2
PFI-1212N-4D3BS-N1	Water	527.5	1.81	4"x2	422.0	1.20	4"x2	633.0	2.54	4"x2
PFI-1212N-4D4BS-O1	Water	540.7	1.70	4"x2	432.5	1.12	4"x2	648.8	2.38	4"x2
PFI-1212N-4D4BS-P1	Water	540.7	1.70	4"x2	432.5	1.12	4"x2	648.8	2.38	4"x2
PFI-1212N-5D2BS-K1	Water	516.5	2.28	4"x2	413.2	1.51	4"x2	619.8	3.19	4"x2
PFI-1212N-5D3BS-L1	Water	527.5	2.11	4"x2	422.0	1.40	4"x2	633.0	2.95	4"x2
PFI-1212N-5D2BS-M1	Water	516.5	2.28	4"x2	413.2	1.51	4"x2	619.8	3.19	4"x2
PFI-1212N-5D2BS-N1	Water	516.5	2.28	4"x2	413.2	1.51	4"x2	619.8	3.19	4"x2
PFI-1212N-5D3BS-O1	Water	527.5	2.11	4"x2	422.0	1.40	4"x2	633.0	2.95	4"x2
PFI-1212N-5D2BS-P1	Water	516.5	2.28	4"x2	413.2	1.51	4"x2	619.8	3.19	4"x2
PFI-1212N-6D1BS-K1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-6D1BS-L1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-6D1BS-M1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-6D1BS-N1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-6D1BS-O1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-6D1BS-P1	Water	505.5	2.88	4"x2	404.4	1.91	4"x2	606.6	4.04	4"x2
PFI-1212N-2D4DZ-K1	Water	235.1	1.41	4"x2	188.1	0.93	4"x2	282.2	1.97	4"x2
PFI-1212N-2D3EZ-L1	Water	231.8	1.53	4"x2	185.5	1.01	4"x2	278.2	2.14	4"x2
PFI-1212N-2D4DZ-M1	Water	235.1	1.41	4"x2	188.1	0.93	4"x2	282.2	1.97	4"x2
PFI-1212N-2D4EZ-M1	Water	235.1	1.41	4"x2	188.1	0.93	4"x2	282.2	1.98	4"x2
PFI-1212N-2D4EZ-N1	Water	235.1	1.41	4"x2	188.1	0.93	4"x2	282.2	1.98	4"x2
PFI-1212N-2D4EZ-O1	Water	235.1	1.41	4"x2	188.1	0.93	4"x2	282.2	1.98	4"x2
PFI-1212N-3D2DZ-L1	Water	229.1	2.18	4"x2	183.3	1.45	4"x2	274.9	3.06	4"x2
PFI-1212N-3D3DZ-M1	Water	231.8	1.99	4"x2	185.5	1.32	4"x2	278.2	2.78	4"x2
PFI-1212N-3D2EZ-M1	Water	229.1	2.19	4"x2	183.3	1.45	4"x2	274.9	3.07	4"x2
PFI-1212N-3D2DZ-N1	Water	229.1	2.18	4"x2	183.3	1.45	4"x2	274.9	3.06	4"x2
PFI-1212N-3D2EZ-N1	Water	229.1	2.19	4"x2	183.3	1.45	4"x2	274.9	3.07	4"x2
PFI-1212N-3D4EZ-O1	Water	235.1	1.82	4"x2	188.1	1.20	4"x2	282.2	2.55	4"x2
PFI-1212N-3D1DZ-P1	Water	226.3	2.44	4"x2	181.1	1.62	4"x2	271.6	3.42	4"x2
PFI-1212N-4D1EZ-K1	Water	226.3	3.08	4"x2	181.1	2.04	4"x2	271.6	4.31	4"x2
PFI-1212N-4D3EZ-M1	Water	231.8	2.47	4"x2	185.5	1.63	4"x2	278.2	3.45	4"x2
PFI-1212N-4D2DZ-N1	Water	229.1	2.72	4"x2	183.3	1.80	4"x2	274.9	3.81	4"x2
PFI-1212N-4D3DZ-P1	Water	231.8	2.45	4"x2	185.5	1.63	4"x2	278.2	3.44	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-5D2EZ-K1	Water	229.1	3.27	4"x2	183.3	2.16	4"x2	274.9	4.58	4"x2
PFI-1212N-5D2EZ-L1	Water	229.1	3.27	4"x2	183.3	2.16	4"x2	274.9	4.58	4"x2
PFI-1212N-5D2DZ-N1	Water	229.1	3.26	4"x2	183.3	2.16	4"x2	274.9	4.57	4"x2
PFI-1212N-5D1DZ-O1	Water	226.3	3.69	4"x2	181.1	2.45	4"x2	271.6	5.18	4"x2
PFI-1212N-5D4DZ-O1	Water	235.1	2.62	4"x2	188.1	1.73	4"x2	282.2	3.67	4"x2
PFI-1212N-5D2EZ-P1	Water	229.1	3.27	4"x2	183.3	2.16	4"x2	274.9	4.58	4"x2
PFI-1212N-6D1EZ-L1	Water	226.3	4.33	4"x2	181.1	2.87	4"x2	271.6	6.07	4"x2
PFI-1212N-6D1EZ-M1	Water	226.3	4.33	4"x2	181.1	2.87	4"x2	271.6	6.07	4"x2
PFI-1212N-6D1EZ-N1	Water	226.3	4.33	4"x2	181.1	2.87	4"x2	271.6	6.07	4"x2
PFI-1212N-6D1EZ-O1	Water	226.3	4.33	4"x2	181.1	2.87	4"x2	271.6	6.07	4"x2
PFI-1212N-6D1EZ-P1	Water	426.3	13.99	4"x2	341.0	9.25	4"x2	511.5	19.61	4"x2
PFI-1212N-3D3BT-L1	Water	231.8	1.97	4"x2	185.5	1.31	4"x2	278.2	2.76	4"x2
PFI-1212N-3D4BT-N1	Water	235.1	1.79	4"x2	188.1	1.19	4"x2	282.2	2.51	4"x2
PFI-1212N-3D4BT-O1	Water	235.1	1.79	4"x2	188.1	1.19	4"x2	282.2	2.51	4"x2
PFI-1212N-4D4BT-K1	Water	235.1	2.19	4"x2	188.1	1.45	4"x2	282.2	3.07	4"x2
PFI-1212N-4D3BT-L1	Water	231.8	2.43	4"x2	185.5	1.61	4"x2	278.2	3.41	4"x2
PFI-1212N-4D4BT-M1	Water	235.1	2.19	4"x2	188.1	1.45	4"x2	282.2	3.07	4"x2
PFI-1212N-4D3BT-N1	Water	231.8	2.43	4"x2	185.5	1.61	4"x2	278.2	3.41	4"x2
PFI-1212N-4D4BT-O1	Water	235.1	2.19	4"x2	188.1	1.45	4"x2	282.2	3.07	4"x2
PFI-1212N-4D4BT-P1	Water	235.1	2.19	4"x2	188.1	1.45	4"x2	282.2	3.07	4"x2
PFI-1212N-5D2BT-K1	Water	229.1	3.23	4"x2	183.3	2.14	4"x2	274.9	4.53	4"x2
PFI-1212N-5D3BT-L1	Water	231.8	2.90	4"x2	185.5	1.92	4"x2	278.2	4.06	4"x2
PFI-1212N-5D2BT-M1	Water	229.1	3.23	4"x2	183.3	2.14	4"x2	274.9	4.53	4"x2
PFI-1212N-5D2BT-N1	Water	229.1	3.23	4"x2	183.3	2.14	4"x2	274.9	4.53	4"x2
PFI-1212N-5D3BT-O1	Water	231.8	2.90	4"x2	185.5	1.92	4"x2	278.2	4.06	4"x2
PFI-1212N-5D2BT-P1	Water	229.1	3.23	4"x2	183.3	2.14	4"x2	274.9	4.53	4"x2
PFI-1212N-6D1BT-K1	Water	226.3	4.29	4"x2	181.1	2.84	4"x2	271.6	6.02	4"x2
PFI-1212N-6D1BT-L1	Water	226.3	4.29	4"x2	181.1	2.84	4"x2	271.6	6.02	4"x2
PFI-1212N-6D1BT-M1	Water	226.3	4.29	4"x2	181.1	2.84	4"x2	271.6	6.02	4"x2
PFI-1212N-6D1BT-N1	Water	226.3	4.29	4"x2	181.1	2.84	4"x2	271.6	6.02	4"x2
PFI-1212N-6D1BT-O1	Water	226.3	4.29	4"x2	181.1	2.84	4"x2	271.6	6.02	4"x2
PFI-1212N-6D1BT-P1	Water	226.3	4.29	4"x2	181.1	2.84	4"x2	271.6	6.02	4"x2
PFI-1224N-2D4DS-K2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-1224N-2D3ES-L2	Water	1055.0	1.22	4"x4	844.0	0.81	4"x4	1265.9	1.71	4"x4
PFI-1224N-2D4DS-M2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-1224N-2D4ES-M2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-1224N-2D4ES-N2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-1224N-2D4ES-O2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-1224N-3D2DS-L2	Water	1033.0	1.61	4"x4	826.4	1.07	4"x4	1239.5	2.26	4"x4
PFI-1224N-3D3DS-M2	Water	1055.0	1.52	4"x4	844.0	1.01	4"x4	1265.9	2.13	4"x4
PFI-1224N-3D2ES-M2	Water	1033.0	1.61	4"x4	826.4	1.07	4"x4	1239.5	2.26	4"x4





## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-3D2DS-N2	Water	1033.0	1.61	4"x4	826.4	1.07	4"x4	1239.5	2.26	4"x4
PFI-1224N-3D2ES-N2	Water	1033.0	1.61	4"x4	826.4	1.07	4"x4	1239.5	2.26	4"x4
PFI-1224N-3D4ES-O2	Water	1081.4	1.44	4"x4	865.1	0.95	4"x4	1297.6	2.01	4"x4
PFI-1224N-3D1DS-P2	Water	1011.0	1.74	4"x4	808.8	1.15	4"x4	1213.1	2.43	4"x4
PFI-1224N-4D1ES-K2	Water	1011.0	2.12	4"x4	808.8	1.40	4"x4	1213.1	2.97	4"x4
PFI-1224N-4D3ES-M2	Water	1055.0	1.81	4"x4	844.0	1.20	4"x4	1265.9	2.54	4"x4
PFI-1224N-4D2DS-N2	Water	1033.0	1.94	4"x4	826.4	1.29	4"x4	1239.5	2.72	4"x4
PFI-1224N-4D3DS-P2	Water	1055.0	1.81	4"x4	844.0	1.20	4"x4	1265.9	2.54	4"x4
PFI-1224N-5D2ES-K2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-1224N-5D2ES-L2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-1224N-5D2DS-N2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-1224N-5D1DS-O2	Water	1011.0	2.50	4"x4	808.8	1.66	4"x4	1213.1	3.50	4"x4
PFI-1224N-5D4DS-O2	Water	1081.4	1.96	4"x4	865.1	1.30	4"x4	1297.6	2.74	4"x4
PFI-1224N-5D2ES-P2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-1224N-6D1ES-L2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1ES-M2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1ES-N2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1ES-O2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1ES-P2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-3D3BS-L2	Water	1055.0	1.52	4"x4	844.0	1.01	4"x4	1265.9	2.13	4"x4
PFI-1224N-3D4BS-N2	Water	1081.4	1.44	4"x4	865.1	0.95	4"x4	1297.6	2.01	4"x4
PFI-1224N-3D4BS-O2	Water	1081.4	1.44	4"x4	865.1	0.95	4"x4	1297.6	2.01	4"x4
PFI-1224N-4D4BS-K2	Water	1081.4	1.70	4"x4	865.1	1.13	4"x4	1297.6	2.38	4"x4
PFI-1224N-4D3BS-L2	Water	1055.0	1.81	4"x4	844.0	1.20	4"x4	1265.9	2.54	4"x4
PFI-1224N-4D4BS-M2	Water	1081.4	1.70	4"x4	865.1	1.13	4"x4	1297.6	2.38	4"x4
PFI-1224N-4D3BS-N2	Water	1055.0	1.81	4"x4	844.0	1.20	4"x4	1265.9	2.54	4"x4
PFI-1224N-4D4BS-O2	Water	1081.4	1.70	4"x4	865.1	1.13	4"x4	1297.6	2.38	4"x4
PFI-1224N-4D4BS-P2	Water	1081.4	1.70	4"x4	865.1	1.13	4"x4	1297.6	2.38	4"x4
PFI-1224N-5D2BS-K2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-1224N-5D3BS-L2	Water	1055.0	2.11	4"x4	844.0	1.40	4"x4	1265.9	2.95	4"x4
PFI-1224N-5D2BS-M2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-1224N-5D2BS-N2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-1224N-5D3BS-O2	Water	1055.0	2.11	4"x4	844.0	1.40	4"x4	1265.9	2.95	4"x4
PFI-1224N-5D2BS-P2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-1224N-6D1BS-K2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1BS-L2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1BS-M2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1BS-N2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1BS-O2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-6D1BS-P2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-1224N-2D4DZ-K2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.97	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-2D3EZ-L2	Water	463.7	1.53	4"x4	370.9	1.01	4"x4	556.4	2.14	4"x4
PFI-1224N-2D4DZ-M2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.97	4"x4
PFI-1224N-2D4EZ-M2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.98	4"x4
PFI-1224N-2D4EZ-N2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.98	4"x4
PFI-1224N-2D4EZ-O2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.98	4"x4
PFI-1224N-3D2DZ-L2	Water	458.2	2.18	4"x4	366.5	1.44	4"x4	549.8	3.06	4"x4
PFI-1224N-3D3DZ-M2	Water	463.7	1.99	4"x4	370.9	1.31	4"x4	556.4	2.78	4"x4
PFI-1224N-3D2EZ-M2	Water	458.2	2.19	4"x4	366.5	1.45	4"x4	549.8	3.07	4"x4
PFI-1224N-3D2DZ-N2	Water	458.2	2.18	4"x4	366.5	1.44	4"x4	549.8	3.06	4"x4
PFI-1224N-3D2EZ-N2	Water	458.2	2.19	4"x4	366.5	1.45	4"x4	549.8	3.07	4"x4
PFI-1224N-3D4EZ-O2	Water	470.3	1.82	4"x4	376.2	1.20	4"x4	564.3	2.55	4"x4
PFI-1224N-3D1DZ-P2	Water	452.7	2.44	4"x4	362.1	1.62	4"x4	543.2	3.42	4"x4
PFI-1224N-4D1EZ-K2	Water	452.7	3.08	4"x4	362.1	2.04	4"x4	543.2	4.31	4"x4
PFI-1224N-4D3EZ-M2	Water	463.7	2.47	4"x4	370.9	1.63	4"x4	556.4	3.45	4"x4
PFI-1224N-4D2DZ-N2	Water	458.2	2.72	4"x4	366.5	1.80	4"x4	549.8	3.81	4"x4
PFI-1224N-4D3DZ-P2	Water	463.7	2.46	4"x4	370.9	1.63	4"x4	556.4	3.44	4"x4
PFI-1224N-5D2EZ-K2	Water	458.2	3.27	4"x4	366.5	2.16	4"x4	549.8	4.58	4"x4
PFI-1224N-5D2EZ-L2	Water	458.2	3.27	4"x4	366.5	2.16	4"x4	549.8	4.58	4"x4
PFI-1224N-5D2DZ-N2	Water	458.2	3.26	4"x4	366.5	2.16	4"x4	549.8	4.57	4"x4
PFI-1224N-5D1DZ-O2	Water	452.7	3.70	4"x4	362.1	2.45	4"x4	543.2	5.18	4"x4
PFI-1224N-5D4DZ-O2	Water	470.3	2.62	4"x4	376.2	1.73	4"x4	564.3	3.67	4"x4
PFI-1224N-5D2EZ-P2	Water	458.2	3.27	4"x4	366.5	2.16	4"x4	549.8	4.58	4"x4
PFI-1224N-6D1EZ-L2	Water	452.7	4.33	4"x4	362.1	2.87	4"x4	543.2	6.07	4"x4
PFI-1224N-6D1EZ-M2	Water	452.7	4.33	4"x4	362.1	2.87	4"x4	543.2	6.07	4"x4
PFI-1224N-6D1EZ-N2	Water	452.7	4.33	4"x4	362.1	2.87	4"x4	543.2	6.07	4"x4
PFI-1224N-6D1EZ-O2	Water	452.7	4.33	4"x4	362.1	2.87	4"x4	543.2	6.07	4"x4
PFI-1224N-6D1EZ-P2	Water	852.6	13.99	4"x4	682.0	9.25	4"x4	1023.1	19.61	4"x4
PFI-1224N-3D3BT-L2	Water	463.7	1.97	4"x4	370.9	1.30	4"x4	556.4	2.76	4"x4
PFI-1224N-3D4BT-N2	Water	470.3	1.79	4"x4	376.2	1.19	4"x4	564.3	2.51	4"x4
PFI-1224N-3D4BT-O2	Water	470.3	1.79	4"x4	376.2	1.19	4"x4	564.3	2.51	4"x4
PFI-1224N-4D4BT-K2	Water	470.3	2.19	4"x4	376.2	1.45	4"x4	564.3	3.07	4"x4
PFI-1224N-4D3BT-L2	Water	463.7	2.44	4"x4	370.9	1.61	4"x4	556.4	3.41	4"x4
PFI-1224N-4D4BT-M2	Water	470.3	2.19	4"x4	376.2	1.45	4"x4	564.3	3.07	4"x4
PFI-1224N-4D3BT-N2	Water	463.7	2.44	4"x4	370.9	1.61	4"x4	556.4	3.41	4"x4
PFI-1224N-4D4BT-O2	Water	470.3	2.19	4"x4	376.2	1.45	4"x4	564.3	3.07	4"x4
PFI-1224N-4D4BT-P2	Water	470.3	2.19	4"x4	376.2	1.45	4"x4	564.3	3.07	4"x4
PFI-1224N-5D2BT-K2	Water	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.53	4"x4
PFI-1224N-5D3BT-L2	Water	463.7	2.90	4"x4	370.9	1.92	4"x4	556.4	4.06	4"x4
PFI-1224N-5D2BT-M2	Water	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.53	4"x4
PFI-1224N-5D2BT-N2	Water	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.53	4"x4
PFI-1224N-5D3BT-O2	Water	463.7	2.90	4"x4	370.9	1.92	4"x4	556.4	4.06	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-5D2BT-P2	Water	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.53	4"x4
PFI-1224N-6D1BT-K2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-1224N-6D1BT-L2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-1224N-6D1BT-M2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-1224N-6D1BT-N2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-1224N-6D1BT-O2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-1224N-6D1BT-P2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-2412N-2D4DS-K2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-2412N-2D3ES-L2	Water	1055.0	1.22	4"x4	844.0	0.81	4"x4	1265.9	1.71	4"x4
PFI-2412N-2D4DS-M2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-2412N-2D4ES-M2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-2412N-2D4ES-N2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-2412N-2D4ES-O2	Water	1081.4	1.18	4"x4	865.1	0.78	4"x4	1297.6	1.65	4"x4
PFI-2412N-3D2DS-L2	Water	1033.0	1.61	4"x4	826.4	1.07	4"x4	1239.5	2.26	4"x4
PFI-2412N-3D3DS-M2	Water	1055.0	1.52	4"x4	844.0	1.01	4"x4	1265.9	2.13	4"x4
PFI-2412N-3D2ES-M2	Water	1033.0	1.61	4"x4	826.4	1.07	4"x4	1239.5	2.26	4"x4
PFI-2412N-3D2DS-N2	Water	1033.0	1.61	4"x4	826.4	1.07	4"x4	1239.5	2.26	4"x4
PFI-2412N-3D2ES-N2	Water	1033.0	1.61	4"x4	826.4	1.07	4"x4	1239.5	2.26	4"x4
PFI-2412N-3D4ES-O2	Water	1081.4	1.44	4"x4	865.1	0.95	4"x4	1297.6	2.01	4"x4
PFI-2412N-3D1DS-P2	Water	1011.0	1.74	4"x4	808.8	1.15	4"x4	1213.1	2.43	4"x4
PFI-2412N-4D1ES-K2	Water	1011.0	2.12	4"x4	808.8	1.40	4"x4	1213.1	2.97	4"x4
PFI-2412N-4D3ES-M2	Water	1055.0	1.81	4"x4	844.0	1.20	4"x4	1265.9	2.54	4"x4
PFI-2412N-4D2DS-N2	Water	1033.0	1.94	4"x4	826.4	1.29	4"x4	1239.5	2.72	4"x4
PFI-2412N-4D3DS-P2	Water	1055.0	1.81	4"x4	844.0	1.20	4"x4	1265.9	2.54	4"x4
PFI-2412N-5D2ES-K2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-2412N-5D2ES-L2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-2412N-5D2DS-N2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-2412N-5D1DS-O2	Water	1011.0	2.50	4"x4	808.8	1.66	4"x4	1213.1	3.50	4"x4
PFI-2412N-5D4DS-O2	Water	1081.4	1.96	4"x4	865.1	1.30	4"x4	1297.6	2.74	4"x4
PFI-2412N-5D2ES-P2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-2412N-6D1ES-L2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1ES-M2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1ES-N2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1ES-O2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1ES-P2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-3D3BS-L2	Water	1055.0	1.52	4"x4	844.0	1.01	4"x4	1265.9	2.13	4"x4
PFI-2412N-3D4BS-N2	Water	1081.4	1.44	4"x4	865.1	0.95	4"x4	1297.6	2.01	4"x4
PFI-2412N-3D4BS-O2	Water	1081.4	1.44	4"x4	865.1	0.95	4"x4	1297.6	2.01	4"x4
PFI-2412N-4D4BS-K2	Water	1081.4	1.70	4"x4	865.1	1.13	4"x4	1297.6	2.38	4"x4
PFI-2412N-4D3BS-L2	Water	1055.0	1.81	4"x4	844.0	1.20	4"x4	1265.9	2.54	4"x4
PFI-2412N-4D4BS-M2	Water	1081.4	1.70	4"x4	865.1	1.13	4"x4	1297.6	2.38	4"x4



## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-4D3BS-N2	Water	1055.0	1.81	4"x4	844.0	1.20	4"x4	1265.9	2.54	4"x4
PFI-2412N-4D4BS-O2	Water	1081.4	1.70	4"x4	865.1	1.13	4"x4	1297.6	2.38	4"x4
PFI-2412N-4D4BS-P2	Water	1081.4	1.70	4"x4	865.1	1.13	4"x4	1297.6	2.38	4"x4
PFI-2412N-5D2BS-K2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-2412N-5D3BS-L2	Water	1055.0	2.11	4"x4	844.0	1.40	4"x4	1265.9	2.95	4"x4
PFI-2412N-5D2BS-M2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-2412N-5D2BS-N2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-2412N-5D3BS-O2	Water	1055.0	2.11	4"x4	844.0	1.40	4"x4	1265.9	2.95	4"x4
PFI-2412N-5D2BS-P2	Water	1033.0	2.28	4"x4	826.4	1.51	4"x4	1239.5	3.19	4"x4
PFI-2412N-6D1BS-K2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1BS-L2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1BS-M2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1BS-N2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1BS-O2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-6D1BS-P2	Water	1011.0	2.88	4"x4	808.8	1.91	4"x4	1213.1	4.04	4"x4
PFI-2412N-2D4DZ-K2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.97	4"x4
PFI-2412N-2D3EZ-L2	Water	463.7	1.53	4"x4	370.9	1.01	4"x4	556.4	2.14	4"x4
PFI-2412N-2D4DZ-M2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.97	4"x4
PFI-2412N-2D4EZ-M2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.98	4"x4
PFI-2412N-2D4EZ-N2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.98	4"x4
PFI-2412N-2D4EZ-O2	Water	470.3	1.41	4"x4	376.2	0.93	4"x4	564.3	1.98	4"x4
PFI-2412N-3D2DZ-L2	Water	458.2	2.18	4"x4	366.5	1.44	4"x4	549.8	3.06	4"x4
PFI-2412N-3D3DZ-M2	Water	463.7	1.99	4"x4	370.9	1.31	4"x4	556.4	2.78	4"x4
PFI-2412N-3D2EZ-M2	Water	458.2	2.19	4"x4	366.5	1.45	4"x4	549.8	3.07	4"x4
PFI-2412N-3D2DZ-N2	Water	458.2	2.18	4"x4	366.5	1.44	4"x4	549.8	3.06	4"x4
PFI-2412N-3D2EZ-N2	Water	458.2	2.19	4"x4	366.5	1.45	4"x4	549.8	3.07	4"x4
PFI-2412N-3D4EZ-O2	Water	470.3	1.82	4"x4	376.2	1.20	4"x4	564.3	2.55	4"x4
PFI-2412N-3D1DZ-P2	Water	452.7	2.44	4"x4	362.1	1.62	4"x4	543.2	3.42	4"x4
PFI-2412N-4D1EZ-K2	Water	452.7	3.08	4"x4	362.1	2.04	4"x4	543.2	4.31	4"x4
PFI-2412N-4D3EZ-M2	Water	463.7	2.47	4"x4	370.9	1.63	4"x4	556.4	3.45	4"x4
PFI-2412N-4D2DZ-N2	Water	458.2	2.72	4"x4	366.5	1.80	4"x4	549.8	3.81	4"x4
PFI-2412N-4D3DZ-P2	Water	463.7	2.46	4"x4	370.9	1.63	4"x4	556.4	3.44	4"x4
PFI-2412N-5D2EZ-K2	Water	458.2	3.27	4"x4	366.5	2.16	4"x4	549.8	4.58	4"x4
PFI-2412N-5D2EZ-L2	Water	458.2	3.27	4"x4	366.5	2.16	4"x4	549.8	4.58	4"x4
PFI-2412N-5D2DZ-N2	Water	458.2	3.26	4"x4	366.5	2.16	4"x4	549.8	4.57	4"x4
PFI-2412N-5D1DZ-O2	Water	452.7	3.70	4"x4	362.1	2.45	4"x4	543.2	5.18	4"x4
PFI-2412N-5D4DZ-O2	Water	470.3	2.62	4"x4	376.2	1.73	4"x4	564.3	3.67	4"x4
PFI-2412N-5D2EZ-P2	Water	458.2	3.27	4"x4	366.5	2.16	4"x4	549.8	4.58	4"x4
PFI-2412N-6D1EZ-L2	Water	452.7	4.33	4"x4	362.1	2.87	4"x4	543.2	6.07	4"x4
PFI-2412N-6D1EZ-M2	Water	452.7	4.33	4"x4	362.1	2.87	4"x4	543.2	6.07	4"x4
PFI-2412N-6D1EZ-N2	Water	452.7	4.33	4"x4	362.1	2.87	4"x4	543.2	6.07	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-6D1EZ-O2	Water	452.7	4.33	4"x4	362.1	2.87	4"x4	543.2	6.07	4"x4
PFI-2412N-6D1EZ-P2	Water	852.6	13.99	4"x4	682.0	9.25	4"x4	1023.1	19.61	4"x4
PFI-2412N-3D3BT-L2	Water	463.7	1.97	4"x4	370.9	1.30	4"x4	556.4	2.76	4"x4
PFI-2412N-3D4BT-N2	Water	470.3	1.79	4"x4	376.2	1.19	4"x4	564.3	2.51	4"x4
PFI-2412N-3D4BT-O2	Water	470.3	1.79	4"x4	376.2	1.19	4"x4	564.3	2.51	4"x4
PFI-2412N-4D4BT-K2	Water	470.3	2.19	4"x4	376.2	1.45	4"x4	564.3	3.07	4"x4
PFI-2412N-4D3BT-L2	Water	463.7	2.44	4"x4	370.9	1.61	4"x4	556.4	3.41	4"x4
PFI-2412N-4D4BT-M2	Water	470.3	2.19	4"x4	376.2	1.45	4"x4	564.3	3.07	4"x4
PFI-2412N-4D3BT-N2	Water	463.7	2.44	4"x4	370.9	1.61	4"x4	556.4	3.41	4"x4
PFI-2412N-4D4BT-O2	Water	470.3	2.19	4"x4	376.2	1.45	4"x4	564.3	3.07	4"x4
PFI-2412N-4D4BT-P2	Water	470.3	2.19	4"x4	376.2	1.45	4"x4	564.3	3.07	4"x4
PFI-2412N-5D2BT-K2	Water	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.53	4"x4
PFI-2412N-5D3BT-L2	Water	463.7	2.90	4"x4	370.9	1.92	4"x4	556.4	4.06	4"x4
PFI-2412N-5D2BT-M2	Water	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.53	4"x4
PFI-2412N-5D2BT-N2	Water	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.53	4"x4
PFI-2412N-5D3BT-O2	Water	463.7	2.90	4"x4	370.9	1.92	4"x4	556.4	4.06	4"x4
PFI-2412N-5D2BT-P2	Water	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.53	4"x4
PFI-2412N-6D1BT-K2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-2412N-6D1BT-L2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-2412N-6D1BT-M2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-2412N-6D1BT-N2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-2412N-6D1BT-O2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-2412N-6D1BT-P2	Water	452.7	4.29	4"x4	362.1	2.84	4"x4	543.2	6.02	4"x4
PFI-2424N-2D4DS-K4	Water	2162.7	1.18	4"x8	1730.2	0.78	4"x8	2595.2	1.65	4"x8
PFI-2424N-2D3ES-L4	Water	2109.9	1.22	4"x8	1687.9	0.81	4"x8	2531.9	1.71	4"x8
PFI-2424N-2D4DS-M4	Water	2162.7	1.18	4"x8	1730.2	0.78	4"x8	2595.2	1.65	4"x8
PFI-2424N-2D4ES-M4	Water	2162.7	1.18	4"x8	1730.2	0.78	4"x8	2595.2	1.65	4"x8
PFI-2424N-2D4ES-N4	Water	2162.7	1.18	4"x8	1730.2	0.78	4"x8	2595.2	1.65	4"x8
PFI-2424N-2D4ES-O4	Water	2162.7	1.18	4"x8	1730.2	0.78	4"x8	2595.2	1.65	4"x8
PFI-2424N-3D2DS-L4	Water	2065.9	1.61	4"x8	1652.7	1.07	4"x8	2479.1	2.26	4"x8
PFI-2424N-3D3DS-M4	Water	2109.9	1.52	4"x8	1687.9	1.01	4"x8	2531.9	2.13	4"x8
PFI-2424N-3D2ES-M4	Water	2065.9	1.61	4"x8	1652.7	1.07	4"x8	2479.1	2.26	4"x8
PFI-2424N-3D2DS-N4	Water	2065.9	1.61	4"x8	1652.7	1.07	4"x8	2479.1	2.26	4"x8
PFI-2424N-3D2ES-N4	Water	2065.9	1.61	4"x8	1652.7	1.07	4"x8	2479.1	2.26	4"x8
PFI-2424N-3D4ES-O4	Water	2162.7	1.44	4"x8	1730.2	0.95	4"x8	2595.2	2.01	4"x8
PFI-2424N-3D1DS-P4	Water	2021.9	1.74	4"x8	1617.5	1.15	4"x8	2426.3	2.43	4"x8
PFI-2424N-4D1ES-K4	Water	2021.9	2.12	4"x8	1617.5	1.40	4"x8	2426.3	2.97	4"x8
PFI-2424N-4D3ES-M4	Water	2109.9	1.81	4"x8	1687.9	1.20	4"x8	2531.9	2.54	4"x8
PFI-2424N-4D2DS-N4	Water	2065.9	1.94	4"x8	1652.7	1.29	4"x8	2479.1	2.72	4"x8
PFI-2424N-4D3DS-P4	Water	2109.9	1.81	4"x8	1687.9	1.20	4"x8	2531.9	2.54	4"x8
PFI-2424N-5D2ES-K4	Water	2065.9	2.28	4"x8	1652.7	1.51	4"x8	2479.1	3.19	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-5D2ES-L4	Water	2065.9	2.28	4"x8	1652.7	1.51	4"x8	2479.1	3.19	4"x8
PFI-2424N-5D2DS-N4	Water	2065.9	2.28	4"x8	1652.7	1.51	4"x8	2479.1	3.19	4"x8
PFI-2424N-5D1DS-O4	Water	2021.9	2.50	4"x8	1617.5	1.66	4"x8	2426.3	3.50	4"x8
PFI-2424N-5D4DS-O4	Water	2162.7	1.96	4"x8	1730.2	1.30	4"x8	2595.2	2.74	4"x8
PFI-2424N-5D2ES-P4	Water	2065.9	2.28	4"x8	1652.7	1.51	4"x8	2479.1	3.19	4"x8
PFI-2424N-6D1ES-L4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1ES-M4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1ES-N4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1ES-O4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1ES-P4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-3D3BS-L4	Water	2109.9	1.52	4"x8	1687.9	1.01	4"x8	2531.9	2.13	4"x8
PFI-2424N-3D4BS-N4	Water	2162.7	1.44	4"x8	1730.2	0.95	4"x8	2595.2	2.01	4"x8
PFI-2424N-3D4BS-O4	Water	2162.7	1.44	4"x8	1730.2	0.95	4"x8	2595.2	2.01	4"x8
PFI-2424N-4D4BS-K4	Water	2162.7	1.70	4"x8	1730.2	1.13	4"x8	2595.2	2.38	4"x8
PFI-2424N-4D3BS-L4	Water	2109.9	1.81	4"x8	1687.9	1.20	4"x8	2531.9	2.54	4"x8
PFI-2424N-4D4BS-M4	Water	2162.7	1.70	4"x8	1730.2	1.13	4"x8	2595.2	2.38	4"x8
PFI-2424N-4D3BS-N4	Water	2109.9	1.81	4"x8	1687.9	1.20	4"x8	2531.9	2.54	4"x8
PFI-2424N-4D4BS-O4	Water	2162.7	1.70	4"x8	1730.2	1.13	4"x8	2595.2	2.38	4"x8
PFI-2424N-4D4BS-P4	Water	2162.7	1.70	4"x8	1730.2	1.13	4"x8	2595.2	2.38	4"x8
PFI-2424N-5D2BS-K4	Water	2065.9	2.28	4"x8	1652.7	1.51	4"x8	2479.1	3.19	4"x8
PFI-2424N-5D3BS-L4	Water	2109.9	2.11	4"x8	1687.9	1.40	4"x8	2531.9	2.95	4"x8
PFI-2424N-5D2BS-M4	Water	2065.9	2.28	4"x8	1652.7	1.51	4"x8	2479.1	3.19	4"x8
PFI-2424N-5D2BS-N4	Water	2065.9	2.28	4"x8	1652.7	1.51	4"x8	2479.1	3.19	4"x8
PFI-2424N-5D3BS-O4	Water	2109.9	2.11	4"x8	1687.9	1.40	4"x8	2531.9	2.95	4"x8
PFI-2424N-5D2BS-P4	Water	2065.9	2.28	4"x8	1652.7	1.51	4"x8	2479.1	3.19	4"x8
PFI-2424N-6D1BS-K4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1BS-L4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1BS-M4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1BS-N4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1BS-O4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-6D1BS-P4	Water	2021.9	2.88	4"x8	1617.5	1.91	4"x8	2426.3	4.04	4"x8
PFI-2424N-2D4DZ-K4	Water	940.6	1.41	4"x8	752.4	0.93	4"x8	1128.7	1.97	4"x8
PFI-2424N-2D3EZ-L4	Water	927.4	1.53	4"x8	741.9	1.01	4"x8	1112.8	2.14	4"x8
PFI-2424N-2D4DZ-M4	Water	940.6	1.41	4"x8	752.4	0.93	4"x8	1128.7	1.97	4"x8
PFI-2424N-2D4EZ-M4	Water	940.6	1.41	4"x8	752.4	0.93	4"x8	1128.7	1.98	4"x8
PFI-2424N-2D4EZ-N4	Water	940.6	1.41	4"x8	752.4	0.93	4"x8	1128.7	1.98	4"x8
PFI-2424N-2D4EZ-O4	Water	940.6	1.41	4"x8	752.4	0.93	4"x8	1128.7	1.98	4"x8
PFI-2424N-3D2DZ-L4	Water	916.4	2.18	4"x8	733.1	1.45	4"x8	1099.6	3.06	4"x8
PFI-2424N-3D3DZ-M4	Water	927.4	1.99	4"x8	741.9	1.32	4"x8	1112.8	2.78	4"x8
PFI-2424N-3D2EZ-M4	Water	916.4	2.19	4"x8	733.1	1.45	4"x8	1099.6	3.07	4"x8
PFI-2424N-3D2DZ-N4	Water	916.4	2.18	4"x8	733.1	1.45	4"x8	1099.6	3.06	4"x8



## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-3D2EZ-N4	Water	916.4	2.19	4"x8	733.1	1.45	4"x8	1099.6	3.07	4"x8
PFI-2424N-3D4EZ-O4	Water	940.6	1.82	4"x8	752.4	1.20	4"x8	1128.7	2.55	4"x8
PFI-2424N-3D1DZ-P4	Water	905.4	2.44	4"x8	724.3	1.62	4"x8	1086.4	3.42	4"x8
PFI-2424N-4D1EZ-K4	Water	905.4	3.08	4"x8	724.3	2.04	4"x8	1086.4	4.31	4"x8
PFI-2424N-4D3EZ-M4	Water	927.4	2.47	4"x8	741.9	1.63	4"x8	1112.8	3.45	4"x8
PFI-2424N-4D2DZ-N4	Water	916.4	2.72	4"x8	733.1	1.80	4"x8	1099.6	3.81	4"x8
PFI-2424N-4D3DZ-P4	Water	927.4	2.46	4"x8	741.9	1.63	4"x8	1112.8	3.44	4"x8
PFI-2424N-5D2EZ-K4	Water	916.4	3.27	4"x8	733.1	2.16	4"x8	1099.6	4.58	4"x8
PFI-2424N-5D2EZ-L4	Water	916.4	3.27	4"x8	733.1	2.16	4"x8	1099.6	4.58	4"x8
PFI-2424N-5D2DZ-N4	Water	916.4	3.26	4"x8	733.1	2.16	4"x8	1099.6	4.57	4"x8
PFI-2424N-5D1DZ-O4	Water	905.4	3.70	4"x8	724.3	2.45	4"x8	1086.4	5.18	4"x8
PFI-2424N-5D4DZ-O4	Water	940.6	2.62	4"x8	752.4	1.73	4"x8	1128.7	3.67	4"x8
PFI-2424N-5D2EZ-P4	Water	916.4	3.27	4"x8	733.1	2.16	4"x8	1099.6	4.58	4"x8
PFI-2424N-6D1EZ-L4	Water	905.4	4.33	4"x8	724.3	2.87	4"x8	1086.4	6.07	4"x8
PFI-2424N-6D1EZ-M4	Water	905.4	4.33	4"x8	724.3	2.87	4"x8	1086.4	6.07	4"x8
PFI-2424N-6D1EZ-N4	Water	905.4	4.33	4"x8	724.3	2.87	4"x8	1086.4	6.07	4"x8
PFI-2424N-6D1EZ-O4	Water	905.4	4.33	4"x8	724.3	2.87	4"x8	1086.4	6.07	4"x8
PFI-2424N-6D1EZ-P4	Water	1705.1	13.99	4"x8	1364.1	9.25	4"x8	2046.1	19.61	4"x8
PFI-2424N-3D3BT-L4	Water	927.4	1.97	4"x8	741.9	1.30	4"x8	1112.8	2.76	4"x8
PFI-2424N-3D4BT-N4	Water	940.6	1.79	4"x8	752.4	1.19	4"x8	1128.7	2.51	4"x8
PFI-2424N-3D4BT-O4	Water	940.6	1.79	4"x8	752.4	1.19	4"x8	1128.7	2.51	4"x8
PFI-2424N-4D4BT-K4	Water	940.6	2.19	4"x8	752.4	1.45	4"x8	1128.7	3.07	4"x8
PFI-2424N-4D3BT-L4	Water	927.4	2.44	4"x8	741.9	1.61	4"x8	1112.8	3.41	4"x8
PFI-2424N-4D4BT-M4	Water	940.6	2.19	4"x8	752.4	1.45	4"x8	1128.7	3.07	4"x8
PFI-2424N-4D3BT-N4	Water	927.4	2.44	4"x8	741.9	1.61	4"x8	1112.8	3.41	4"x8
PFI-2424N-4D4BT-O4	Water	940.6	2.19	4"x8	752.4	1.45	4"x8	1128.7	3.07	4"x8
PFI-2424N-4D4BT-P4	Water	940.6	2.19	4"x8	752.4	1.45	4"x8	1128.7	3.07	4"x8
PFI-2424N-5D2BT-K4	Water	916.4	3.23	4"x8	733.1	2.14	4"x8	1099.6	4.53	4"x8
PFI-2424N-5D3BT-L4	Water	927.4	2.90	4"x8	741.9	1.92	4"x8	1112.8	4.06	4"x8
PFI-2424N-5D2BT-M4	Water	916.4	3.23	4"x8	733.1	2.14	4"x8	1099.6	4.53	4"x8
PFI-2424N-5D2BT-N4	Water	916.4	3.23	4"x8	733.1	2.14	4"x8	1099.6	4.53	4"x8
PFI-2424N-5D3BT-O4	Water	927.4	2.90	4"x8	741.9	1.92	4"x8	1112.8	4.06	4"x8
PFI-2424N-5D2BT-P4	Water	916.4	3.23	4"x8	733.1	2.14	4"x8	1099.6	4.53	4"x8
PFI-2424N-6D1BT-K4	Water	905.4	4.29	4"x8	724.3	2.84	4"x8	1086.4	6.02	4"x8
PFI-2424N-6D1BT-L4	Water	905.4	4.29	4"x8	724.3	2.84	4"x8	1086.4	6.02	4"x8
PFI-2424N-6D1BT-M4	Water	905.4	4.29	4"x8	724.3	2.84	4"x8	1086.4	6.02	4"x8
PFI-2424N-6D1BT-N4	Water	905.4	4.29	4"x8	724.3	2.84	4"x8	1086.4	6.02	4"x8
PFI-2424N-6D1BT-O4	Water	905.4	4.29	4"x8	724.3	2.84	4"x8	1086.4	6.02	4"x8
PFI-2424N-6D1BT-P4	Water	905.4	4.29	4"x8	724.3	2.84	4"x8	1086.4	6.02	4"x8
PFI-1218N-2D1DS-M1	Water	505.5	1.68	4"x2	404.4	1.11	4"x2	606.6	2.35	4"x2
PFI-1218N-2D4ES-M1	Water	540.7	1.40	4"x2	432.5	0.93	4"x2	648.8	1.96	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-2D1DS-N1	Water	505.5	1.68	4"x2	404.4	1.11	4"x2	606.6	2.35	4"x2
PFI-1218N-2D2DS-N1	Water	516.5	1.56	4"x2	413.2	1.03	4"x2	619.8	2.18	4"x2
PFI-1218N-2D3ES-N1	Water	527.5	1.47	4"x2	422.0	0.98	4"x2	633.0	2.06	4"x2
PFI-1218N-2D2DS-O1	Water	516.5	1.56	4"x2	413.2	1.03	4"x2	619.8	2.18	4"x2
PFI-1218N-2D3ES-O1	Water	527.5	1.47	4"x2	422.0	0.98	4"x2	633.0	2.06	4"x2
PFI-1218N-2D4DS-P1	Water	540.7	1.40	4"x2	432.5	0.93	4"x2	648.8	1.96	4"x2
PFI-1218N-3D1ES-K1	Water	505.5	2.22	4"x2	404.4	1.47	4"x2	606.6	3.11	4"x2
PFI-1218N-3D1ES-L1	Water	505.5	2.22	4"x2	404.4	1.47	4"x2	606.6	3.11	4"x2
PFI-1218N-3D4ES-M1	Water	940.6	3.67	4"x4	752.4	3.25	4"x2	1128.7	5.14	4"x4
PFI-1218N-3D1DS-N1	Water	505.5	2.22	4"x2	404.4	1.47	4"x2	606.6	3.11	4"x2
PFI-1218N-3D1ES-N1	Water	505.5	2.22	4"x2	404.4	1.47	4"x2	606.6	3.11	4"x2
PFI-1218N-3D1DS-O1	Water	505.5	2.22	4"x2	404.4	1.47	4"x2	606.6	3.11	4"x2
PFI-1218N-3D2DS-O1	Water	516.5	2.03	4"x2	413.2	1.35	4"x2	619.8	2.85	4"x2
PFI-1218N-3D1ES-O1	Water	905.4	6.52	4"x2	724.3	4.32	4"x2	1086.4	7.22	4"x4
PFI-1218N-3D2DS-P1	Water	916.4	5.87	4"x2	733.1	3.88	4"x2	1099.6	6.26	4"x4
PFI-1218N-3D2ES-P1	Water	916.4	5.87	4"x2	733.1	3.88	4"x2	1099.6	6.26	4"x4
PFI-1218N-3D2DS-Q1	Water	916.4	5.87	4"x2	733.1	3.88	4"x2	1099.6	6.26	4"x4
PFI-1218N-3D4DS-Q1	Water	940.6	3.67	4"x4	752.4	3.25	4"x2	1128.7	5.14	4"x4
PFI-1218N-3D4ES-Q1	Water	940.6	3.67	4"x4	752.4	3.25	4"x2	1128.7	5.14	4"x4
PFI-1218N-3D1ES-R1	Water	905.4	6.52	4"x2	724.3	4.32	4"x2	1086.4	7.22	4"x4
PFI-1218N-3D4ES-R1	Water	940.6	3.67	4"x4	752.4	3.25	4"x2	1128.7	5.14	4"x4
PFI-1218N-4D1DS-K1	Water	505.5	2.77	4"x2	404.4	1.83	4"x2	606.6	3.87	4"x2
PFI-1218N-4D1ES-L1	Water	905.4	8.12	4"x2	724.3	5.38	4"x2	1086.4	9.38	4"x4
PFI-1218N-4D2ES-M1	Water	916.4	7.24	4"x2	733.1	4.79	4"x2	1099.6	8.10	4"x4
PFI-1218N-4D2DS-N1	Water	916.4	7.24	4"x2	733.1	4.79	4"x2	1099.6	8.10	4"x4
PFI-1218N-4D1ES-N1	Water	905.4	8.12	4"x2	724.3	5.38	4"x2	1086.4	9.38	4"x4
PFI-1218N-4D3DS-O1	Water	927.4	6.56	4"x2	741.9	4.34	4"x2	1112.8	7.14	4"x4
PFI-1218N-4D1ES-O1	Water	905.4	8.12	4"x2	724.3	5.38	4"x2	1086.4	9.38	4"x4
PFI-1218N-4D1ES-P1	Water	905.4	8.12	4"x2	724.3	5.38	4"x2	1086.4	9.38	4"x4
PFI-1218N-4D1DS-Q1	Water	905.4	8.12	4"x2	724.3	5.38	4"x2	1086.4	9.38	4"x4
PFI-1218N-4D2ES-Q1	Water	916.4	7.24	4"x2	733.1	4.79	4"x2	1099.6	8.10	4"x4
PFI-1218N-4D4ES-Q1	Water	940.6	4.45	4"x4	752.4	3.93	4"x2	1128.7	6.24	4"x4
PFI-1218N-4D2ES-R1	Water	916.4	7.24	4"x2	733.1	4.79	4"x2	1099.6	8.10	4"x4
PFI-1218N-4D4ES-R1	Water	940.6	4.45	4"x4	752.4	3.93	4"x2	1128.7	6.24	4"x4
PFI-1218N-5D1DS-K1	Water	505.5	3.31	4"x2	404.4	2.19	4"x2	606.6	4.64	4"x2
PFI-1218N-5D1ES-O1	Water	905.4	9.72	4"x2	724.3	6.43	4"x2	1086.4	11.54	4"x4
PFI-1218N-5D2ES-P1	Water	916.4	8.61	4"x2	733.1	5.70	4"x2	1099.6	9.94	4"x4
PFI-1218N-6D2DS-M1	Water	916.4	9.98	4"x2	733.1	6.60	4"x2	1099.6	11.78	4"x4
PFI-1218N-6D1DS-N1	Water	905.4	11.32	4"x2	724.3	7.49	4"x2	1086.4	13.70	4"x4
PFI-1218N-6D1DS-R1	Water	905.4	11.32	4"x2	724.3	7.49	4"x2	1086.4	13.70	4"x4
PFI-1218N-6D1ES-R1	Water	905.4	11.32	4"x2	724.3	7.49	4"x2	1086.4	13.70	4"x4





## PFi Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-6D3ES-R1	Water	927.4	8.94	4"x2	741.9	5.92	4"x2	1112.8	10.33	4"x4
PFI-1218N-3D4BS-K1	Water	540.7	1.77	4"x2	432.5	1.17	4"x2	648.8	2.47	4"x2
PFI-1218N-3D4BS-L1	Water	540.7	1.77	4"x2	432.5	1.17	4"x2	648.8	2.47	4"x2
PFI-1218N-3D4BS-N1	Water	540.7	1.77	4"x2	432.5	1.17	4"x2	648.8	2.47	4"x2
PFI-1218N-3D4BS-O1	Water	540.7	1.77	4"x2	432.5	1.17	4"x2	648.8	2.47	4"x2
PFI-1218N-3D4BS-P1	Water	540.7	1.77	4"x2	432.5	1.17	4"x2	648.8	2.47	4"x2
PFI-1218N-4D4BS-K1	Water	540.7	2.14	4"x2	432.5	1.42	4"x2	648.8	2.99	4"x2
PFI-1218N-4D4BS-L1	Water	540.7	2.14	4"x2	432.5	1.42	4"x2	648.8	2.99	4"x2
PFI-1218N-4D3BS-M1	Water	527.5	2.31	4"x2	422.0	1.53	4"x2	633.0	3.24	4"x2
PFI-1218N-4D3BS-N1	Water	527.5	2.31	4"x2	422.0	1.53	4"x2	633.0	3.24	4"x2
PFI-1218N-4D3BS-O1	Water	527.5	2.31	4"x2	422.0	1.53	4"x2	633.0	3.24	4"x2
PFI-1218N-4D4BS-P1	Water	940.6	4.45	4"x4	752.4	3.93	4"x2	1128.7	6.24	4"x4
PFI-1218N-4D3BS-Q1	Water	927.4	6.56	4"x2	741.9	4.34	4"x2	1112.8	7.14	4"x4
PFI-1218N-5D2BS-K1	Water	516.5	2.98	4"x2	413.2	1.98	4"x2	619.8	4.18	4"x2
PFI-1218N-5D2BS-L1	Water	516.5	2.98	4"x2	413.2	1.98	4"x2	619.8	4.18	4"x2
PFI-1218N-5D2BS-M1	Water	516.5	2.98	4"x2	413.2	1.98	4"x2	619.8	4.18	4"x2
PFI-1218N-5D2BS-N1	Water	516.5	2.98	4"x2	413.2	1.98	4"x2	619.8	4.18	4"x2
PFI-1218N-5D3BS-O1	Water	527.5	2.73	4"x2	422.0	1.81	4"x2	633.0	3.83	4"x2
PFI-1218N-5D2BS-P1	Water	916.4	8.61	4"x2	733.1	5.70	4"x2	1099.6	9.94	4"x4
PFI-1218N-5D3BS-Q1	Water	927.4	7.75	4"x2	741.9	5.13	4"x2	1112.8	8.74	4"x4
PFI-1218N-6D1BS-K1	Water	505.5	3.85	4"x2	404.4	2.55	4"x2	606.6	5.40	4"x2
PFI-1218N-6D1BS-L1	Water	505.5	3.85	4"x2	404.4	2.55	4"x2	606.6	5.40	4"x2
PFI-1218N-6D1BS-M1	Water	505.5	3.85	4"x2	404.4	2.55	4"x2	606.6	5.40	4"x2
PFI-1218N-6D1BS-N1	Water	505.5	3.85	4"x2	404.4	2.55	4"x2	606.6	5.40	4"x2
PFI-1218N-6D1BS-O1	Water	905.4	11.32	4"x2	724.3	7.49	4"x2	1086.4	13.70	4"x4
PFI-1218N-6D1BS-P1	Water	905.4	11.32	4"x2	724.3	7.49	4"x2	1086.4	13.70	4"x4
PFI-1218N-6D1BS-Q1	Water	905.4	11.32	4"x2	724.3	7.49	4"x2	1086.4	13.70	4"x4
PFI-1218N-6D2BS-R1	Water	916.4	9.98	4"x2	733.1	6.60	4"x2	1099.6	11.78	4"x4
PFI-1218N-2D1DZ-M1	Water	226.3	2.34	4"x2	181.1	1.55	4"x2	271.6	3.28	4"x2
PFI-1218N-2D4EZ-M1	Water	235.1	1.75	4"x2	188.1	1.16	4"x2	282.2	2.45	4"x2
PFI-1218N-2D1DZ-N1	Water	226.3	2.34	4"x2	181.1	1.55	4"x2	271.6	3.28	4"x2
PFI-1218N-2D2DZ-N1	Water	229.1	2.10	4"x2	183.3	1.39	4"x2	274.9	2.94	4"x2
PFI-1218N-2D3EZ-N1	Water	231.8	1.92	4"x2	185.5	1.27	4"x2	278.2	2.69	4"x2
PFI-1218N-2D2DZ-O1	Water	229.1	2.10	4"x2	183.3	1.39	4"x2	274.9	2.94	4"x2
PFI-1218N-2D3EZ-O1	Water	231.8	1.92	4"x2	185.5	1.27	4"x2	278.2	2.69	4"x2
PFI-1218N-2D4DZ-P1	Water	235.1	1.75	4"x2	188.1	1.16	4"x2	282.2	2.45	4"x2
PFI-1218N-3D1EZ-K1	Water	226.3	3.24	4"x2	181.1	2.15	4"x2	271.6	4.54	4"x2
PFI-1218N-3D1EZ-L1	Water	226.3	3.24	4"x2	181.1	2.15	4"x2	271.6	4.54	4"x2
PFI-1218N-3D4EZ-M1	Water	435.1	7.18	4"x2	348.1	4.75	4"x2	522.1	10.07	4"x2
PFI-1218N-3D1DZ-N1	Water	226.3	3.23	4"x2	181.1	2.14	4"x2	271.6	4.53	4"x2
PFI-1218N-3D1EZ-N1	Water	426.3	10.46	4"x2	341.0	6.92	4"x2	511.5	14.66	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-3D1DZ-O1	Water	226.3	3.23	4"x2	181.1	2.14	4"x2	271.6	4.53	4"x2
PFI-1218N-3D2DZ-O1	Water	429.0	9.04	4"x2	343.2	5.98	4"x2	514.8	12.67	4"x2
PFI-1218N-3D1EZ-O1	Water	426.3	10.46	4"x2	341.0	6.92	4"x2	511.5	14.66	4"x2
PFI-1218N-3D2DZ-P1	Water	429.0	9.04	4"x2	343.2	5.98	4"x2	514.8	12.67	4"x2
PFI-1218N-3D2EZ-P1	Water	429.0	9.08	4"x2	343.2	6.01	4"x2	514.8	12.73	4"x2
PFI-1218N-3D2DZ-Q1	Water	429.0	9.04	4"x2	343.2	5.98	4"x2	514.8	12.67	4"x2
PFI-1218N-3D4DZ-Q1	Water	435.1	7.14	4"x2	348.1	4.72	4"x2	522.1	10.00	4"x2
PFI-1218N-3D4EZ-Q1	Water	435.1	7.18	4"x2	348.1	4.75	4"x2	522.1	10.07	4"x2
PFI-1218N-3D1EZ-R1	Water	426.3	10.46	4"x2	341.0	6.92	4"x2	511.5	14.66	4"x2
PFI-1218N-3D4EZ-R1	Water	435.1	7.18	4"x2	348.1	4.75	4"x2	522.1	10.07	4"x2
PFI-1218N-4D1DZ-K1	Water	226.3	4.12	4"x2	181.1	2.73	4"x2	271.6	5.78	4"x2
PFI-1218N-4D1EZ-L1	Water	426.3	13.26	4"x2	341.0	8.77	4"x2	511.5	18.58	4"x2
PFI-1218N-4D2EZ-M1	Water	429.0	11.53	4"x2	343.2	7.63	4"x2	514.8	16.16	4"x2
PFI-1218N-4D2DZ-N1	Water	429.0	11.49	4"x2	343.2	7.60	4"x2	514.8	16.10	4"x2
PFI-1218N-4D1EZ-N1	Water	426.3	13.26	4"x2	341.0	8.77	4"x2	511.5	18.58	4"x2
PFI-1218N-4D3DZ-O1	Water	431.8	10.16	4"x2	345.4	6.72	4"x2	518.1	14.24	4"x2
PFI-1218N-4D1EZ-O1	Water	426.3	13.26	4"x2	341.0	8.77	4"x2	511.5	18.58	4"x2
PFI-1218N-4D1EZ-P1	Water	426.3	13.26	4"x2	341.0	8.77	4"x2	511.5	18.58	4"x2
PFI-1218N-4D1DZ-Q1	Water	426.3	13.30	4"x2	341.0	8.80	4"x2	511.5	18.64	4"x2
PFI-1218N-4D2EZ-Q1	Water	429.0	11.53	4"x2	343.2	7.63	4"x2	514.8	16.16	4"x2
PFI-1218N-4D4EZ-Q1	Water	435.1	8.99	4"x2	348.1	5.95	4"x2	522.1	12.60	4"x2
PFI-1218N-4D2EZ-R1	Water	429.0	11.53	4"x2	343.2	7.63	4"x2	514.8	16.16	4"x2
PFI-1218N-4D4EZ-R1	Water	435.1	8.99	4"x2	348.1	5.95	4"x2	522.1	12.60	4"x2
PFI-1218N-5D1DZ-K1	Water	226.3	5.01	4"x2	181.1	3.32	4"x2	271.6	7.03	4"x2
PFI-1218N-5D1EZ-O1	Water	426.3	16.10	4"x2	341.0	10.65	4"x2	511.5	22.56	4"x2
PFI-1218N-5D2EZ-P1	Water	429.0	13.98	4"x2	343.2	9.25	4"x2	514.8	19.59	4"x2
PFI-1218N-6D2DZ-M1	Water	429.0	16.38	4"x2	343.2	10.84	4"x2	514.8	22.96	4"x2
PFI-1218N-6D1DZ-N1	Water	426.3	18.99	4"x2	341.0	12.56	4"x2	511.5	26.60	4"x2
PFI-1218N-6D1DZ-R1	Water	426.3	18.99	4"x2	341.0	12.56	4"x2	511.5	26.60	4"x2
PFI-1218N-6D1EZ-R1	Water	426.3	19.03	4"x2	341.0	12.59	4"x2	511.5	26.66	4"x2
PFI-1218N-3D4BT-K1	Water	235.1	2.30	4"x2	188.1	1.52	4"x2	282.2	3.22	4"x2
PFI-1218N-3D4BT-L1	Water	235.1	2.30	4"x2	188.1	1.52	4"x2	282.2	3.22	4"x2
PFI-1218N-3D4BT-N1	Water	235.1	2.30	4"x2	188.1	1.52	4"x2	282.2	3.22	4"x2
PFI-1218N-3D4BT-O1	Water	235.1	2.30	4"x2	188.1	1.52	4"x2	282.2	3.22	4"x2
PFI-1218N-3D4BT-P1	Water	235.1	2.30	4"x2	188.1	1.52	4"x2	282.2	3.22	4"x2
PFI-1218N-4D4BT-K1	Water	235.1	2.87	4"x2	188.1	1.90	4"x2	282.2	4.02	4"x2
PFI-1218N-4D4BT-L1	Water	235.1	2.87	4"x2	188.1	1.90	4"x2	282.2	4.02	4"x2
PFI-1218N-4D3BT-M1	Water	231.8	3.22	4"x2	185.5	2.13	4"x2	278.2	4.51	4"x2
PFI-1218N-4D3BT-N1	Water	231.8	3.22	4"x2	185.5	2.13	4"x2	278.2	4.51	4"x2
PFI-1218N-4D3BT-O1	Water	231.8	3.22	4"x2	185.5	2.13	4"x2	278.2	4.51	4"x2
PFI-1218N-4D4BT-P1	Water	435.1	8.96	4"x2	348.1	5.93	4"x2	522.1	12.56	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-4D3BT-Q1	Water	431.8	10.18	4"x2	345.4	6.74	4"x2	518.1	14.27	4"x2
PFI-1218N-5D2BT-K1	Water	229.1	4.36	4"x2	183.3	2.89	4"x2	274.9	6.11	4"x2
PFI-1218N-5D2BT-L1	Water	229.1	4.36	4"x2	183.3	2.89	4"x2	274.9	6.11	4"x2
PFI-1218N-5D2BT-M1	Water	229.1	4.36	4"x2	183.3	2.89	4"x2	274.9	6.11	4"x2
PFI-1218N-5D2BT-N1	Water	229.1	4.36	4"x2	183.3	2.89	4"x2	274.9	6.11	4"x2
PFI-1218N-5D3BT-O1	Water	431.8	12.14	4"x2	345.4	8.03	4"x2	518.1	17.01	4"x2
PFI-1218N-5D2BT-P1	Water	429.0	13.93	4"x2	343.2	9.22	4"x2	514.8	19.53	4"x2
PFI-1218N-5D3BT-Q1	Water	431.8	12.14	4"x2	345.4	8.03	4"x2	518.1	17.01	4"x2
PFI-1218N-6D1BT-K1	Water	226.3	5.88	4"x2	181.1	3.89	4"x2	271.6	8.23	4"x2
PFI-1218N-6D1BT-L1	Water	226.3	5.88	4"x2	181.1	3.89	4"x2	271.6	8.23	4"x2
PFI-1218N-6D1BT-M1	Water	226.3	5.88	4"x2	181.1	3.89	4"x2	271.6	8.23	4"x2
PFI-1218N-6D1BT-N1	Water	426.3	18.96	4"x2	341.0	12.54	4"x2	511.5	26.57	4"x2
PFI-1218N-6D1BT-O1	Water	426.3	18.96	4"x2	341.0	12.54	4"x2	511.5	26.57	4"x2
PFI-1218N-6D1BT-P1	Water	426.3	18.96	4"x2	341.0	12.54	4"x2	511.5	26.57	4"x2
PFI-1218N-6D1BT-Q1	Water	426.3	18.96	4"x2	341.0	12.54	4"x2	511.5	26.57	4"x2
PFI-1236N-2D1DS-M2	Water	1011.0	1.68	4"x4	808.8	1.11	4"x4	1213.1	2.35	4"x4
PFI-1236N-2D4ES-M2	Water	1081.4	1.40	4"x4	865.1	0.93	4"x4	1297.6	1.96	4"x4
PFI-1236N-2D1DS-N2	Water	1011.0	1.68	4"x4	808.8	1.11	4"x4	1213.1	2.35	4"x4
PFI-1236N-2D2DS-N2	Water	1033.0	1.56	4"x4	826.4	1.03	4"x4	1239.5	2.18	4"x4
PFI-1236N-2D3ES-N2	Water	1055.0	1.47	4"x4	844.0	0.98	4"x4	1265.9	2.06	4"x4
PFI-1236N-2D2DS-O2	Water	1033.0	1.56	4"x4	826.4	1.03	4"x4	1239.5	2.18	4"x4
PFI-1236N-2D3ES-O2	Water	1055.0	1.47	4"x4	844.0	0.98	4"x4	1265.9	2.06	4"x4
PFI-1236N-2D4DS-P2	Water	1081.4	1.40	4"x4	865.1	0.93	4"x4	1297.6	1.96	4"x4
PFI-1236N-3D1ES-K2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-1236N-3D1ES-L2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-1236N-3D4ES-M2	Water	1881.1	3.67	4"x8	1504.9	3.25	4"x4	2257.3	5.14	4"x8
PFI-1236N-3D1DS-N2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-1236N-3D1ES-N2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-1236N-3D1DS-O2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-1236N-3D2DS-O2	Water	1033.0	2.03	4"x4	826.4	1.35	4"x4	1239.5	2.85	4"x4
PFI-1236N-3D1ES-O2	Water	1810.7	6.52	4"x4	1448.6	4.32	4"x4	2172.8	7.22	4"x8
PFI-1236N-3D2DS-P2	Water	1832.7	5.87	4"x4	1466.2	3.88	4"x4	2199.2	6.26	4"x8
PFI-1236N-3D2ES-P2	Water	1832.7	5.87	4"x4	1466.2	3.88	4"x4	2199.2	6.26	4"x8
PFI-1236N-3D2DS-Q2	Water	1832.7	5.87	4"x4	1466.2	3.88	4"x4	2199.2	6.26	4"x8
PFI-1236N-3D4DS-Q2	Water	1881.1	3.67	4"x8	1504.9	3.25	4"x4	2257.3	5.14	4"x8
PFI-1236N-3D4ES-Q2	Water	1881.1	3.67	4"x8	1504.9	3.25	4"x4	2257.3	5.14	4"x8
PFI-1236N-3D1ES-R2	Water	1810.7	6.52	4"x4	1448.6	4.32	4"x4	2172.8	7.22	4"x8
PFI-1236N-3D4ES-R2	Water	1881.1	3.67	4"x8	1504.9	3.25	4"x4	2257.3	5.14	4"x8
PFI-1236N-4D1DS-K2	Water	1011.0	2.77	4"x4	808.8	1.83	4"x4	1213.1	3.87	4"x4
PFI-1236N-4D1ES-L2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-1236N-4D2ES-M2	Water	1832.7	7.24	4"x4	1466.2	4.79	4"x4	2199.2	8.10	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-4D2DS-N2	Water	1832.7	7.24	4"x4	1466.2	4.79	4"x4	2199.2	8.10	4"x8
PFI-1236N-4D1ES-N2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-1236N-4D3DS-O2	Water	1854.7	6.56	4"x4	1483.8	4.34	4"x4	2225.6	7.14	4"x8
PFI-1236N-4D1ES-O2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-1236N-4D1ES-P2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-1236N-4D1DS-Q2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-1236N-4D2ES-Q2	Water	1832.7	7.24	4"x4	1466.2	4.79	4"x4	2199.2	8.10	4"x8
PFI-1236N-4D4ES-Q2	Water	1881.1	4.45	4"x8	1504.9	3.93	4"x4	2257.3	6.24	4"x8
PFI-1236N-4D2ES-R2	Water	1832.7	7.24	4"x4	1466.2	4.79	4"x4	2199.2	8.10	4"x8
PFI-1236N-4D4ES-R2	Water	1881.1	4.45	4"x8	1504.9	3.93	4"x4	2257.3	6.24	4"x8
PFI-1236N-5D1DS-K2	Water	1011.0	3.31	4"x4	808.8	2.19	4"x4	1213.1	4.64	4"x4
PFI-1236N-5D1ES-O2	Water	1810.7	9.72	4"x4	1448.6	6.43	4"x4	2172.8	11.54	4"x8
PFI-1236N-5D2ES-P2	Water	1832.7	8.61	4"x4	1466.2	5.70	4"x4	2199.2	9.94	4"x8
PFI-1236N-6D2DS-M2	Water	1832.7	9.97	4"x4	1466.2	6.60	4"x4	2199.2	11.78	4"x8
PFI-1236N-6D1DS-N2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-1236N-6D1DS-R2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-1236N-6D1ES-R2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-1236N-3D4BS-K2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-1236N-3D4BS-L2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-1236N-3D4BS-N2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-1236N-3D4BS-O2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-1236N-3D4BS-P2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-1236N-4D4BS-K2	Water	1081.4	2.14	4"x4	865.1	1.42	4"x4	1297.6	2.99	4"x4
PFI-1236N-4D4BS-L2	Water	1081.4	2.14	4"x4	865.1	1.42	4"x4	1297.6	2.99	4"x4
PFI-1236N-4D3BS-M2	Water	1055.0	2.31	4"x4	844.0	1.53	4"x4	1265.9	3.24	4"x4
PFI-1236N-4D3BS-N2	Water	1055.0	2.31	4"x4	844.0	1.53	4"x4	1265.9	3.24	4"x4
PFI-1236N-4D3BS-O2	Water	1055.0	2.31	4"x4	844.0	1.53	4"x4	1265.9	3.24	4"x4
PFI-1236N-4D4BS-P2	Water	1881.1	4.45	4"x8	1504.9	3.93	4"x4	2257.3	6.24	4"x8
PFI-1236N-4D3BS-Q2	Water	1854.7	6.56	4"x4	1483.8	4.34	4"x4	2225.6	7.14	4"x8
PFI-1236N-5D2BS-K2	Water	1033.0	2.98	4"x4	826.4	1.98	4"x4	1239.5	4.18	4"x4
PFI-1236N-5D2BS-L2	Water	1033.0	2.98	4"x4	826.4	1.98	4"x4	1239.5	4.18	4"x4
PFI-1236N-5D2BS-M2	Water	1033.0	2.98	4"x4	826.4	1.98	4"x4	1239.5	4.18	4"x4
PFI-1236N-5D2BS-N2	Water	1033.0	2.98	4"x4	826.4	1.98	4"x4	1239.5	4.18	4"x4
PFI-1236N-5D3BS-O2	Water	1055.0	2.73	4"x4	844.0	1.81	4"x4	1265.9	3.83	4"x4
PFI-1236N-5D2BS-P2	Water	1832.7	8.61	4"x4	1466.2	5.70	4"x4	2199.2	9.94	4"x8
PFI-1236N-5D3BS-Q2	Water	1854.7	7.75	4"x4	1483.8	5.13	4"x4	2225.6	8.74	4"x8
PFI-1236N-6D1BS-K2	Water	1011.0	3.85	4"x4	808.8	2.55	4"x4	1213.1	5.40	4"x4
PFI-1236N-6D1BS-L2	Water	1011.0	3.85	4"x4	808.8	2.55	4"x4	1213.1	5.40	4"x4
PFI-1236N-6D1BS-M2	Water	1011.0	3.85	4"x4	808.8	2.55	4"x4	1213.1	5.40	4"x4
PFI-1236N-6D1BS-N2	Water	1011.0	3.85	4"x4	808.8	2.55	4"x4	1213.1	5.40	4"x4
PFI-1236N-6D1BS-O2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-6D1BS-P2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-1236N-6D1BS-Q2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-1236N-6D2BS-R2	Water	1832.7	9.97	4"x4	1466.2	6.60	4"x4	2199.2	11.78	4"x8
PFI-1236N-2D1DZ-M2	Water	452.7	2.34	4"x4	362.1	1.55	4"x4	543.2	3.28	4"x4
PFI-1236N-2D4EZ-M2	Water	470.3	1.75	4"x4	376.2	1.16	4"x4	564.3	2.45	4"x4
PFI-1236N-2D1DZ-N2	Water	452.7	2.34	4"x4	362.1	1.55	4"x4	543.2	3.28	4"x4
PFI-1236N-2D2DZ-N2	Water	458.2	2.10	4"x4	366.5	1.39	4"x4	549.8	2.94	4"x4
PFI-1236N-2D3EZ-N2	Water	463.7	1.92	4"x4	370.9	1.27	4"x4	556.4	2.69	4"x4
PFI-1236N-2D2DZ-O2	Water	458.2	2.10	4"x4	366.5	1.39	4"x4	549.8	2.94	4"x4
PFI-1236N-2D3EZ-O2	Water	463.7	1.92	4"x4	370.9	1.27	4"x4	556.4	2.69	4"x4
PFI-1236N-2D4DZ-P2	Water	470.3	1.75	4"x4	376.2	1.16	4"x4	564.3	2.45	4"x4
PFI-1236N-3D1EZ-K2	Water	452.7	3.24	4"x4	362.1	2.14	4"x4	543.2	4.54	4"x4
PFI-1236N-3D1EZ-L2	Water	452.7	3.24	4"x4	362.1	2.14	4"x4	543.2	4.54	4"x4
PFI-1236N-3D4EZ-M2	Water	870.2	7.18	4"x4	696.1	4.75	4"x4	1044.2	10.07	4"x4
PFI-1236N-3D1DZ-N2	Water	452.7	3.23	4"x4	362.1	2.14	4"x4	543.2	4.53	4"x4
PFI-1236N-3D1EZ-N2	Water	852.6	10.46	4"x4	682.0	6.92	4"x4	1023.1	14.66	4"x4
PFI-1236N-3D1DZ-O2	Water	452.7	3.23	4"x4	362.1	2.14	4"x4	543.2	4.53	4"x4
PFI-1236N-3D2DZ-O2	Water	858.1	9.04	4"x4	686.4	5.98	4"x4	1029.7	12.67	4"x4
PFI-1236N-3D1EZ-O2	Water	852.6	10.46	4"x4	682.0	6.92	4"x4	1023.1	14.66	4"x4
PFI-1236N-3D2DZ-P2	Water	858.1	9.04	4"x4	686.4	5.98	4"x4	1029.7	12.67	4"x4
PFI-1236N-3D2EZ-P2	Water	858.1	9.09	4"x4	686.4	6.01	4"x4	1029.7	12.73	4"x4
PFI-1236N-3D2DZ-Q2	Water	858.1	9.04	4"x4	686.4	5.98	4"x4	1029.7	12.67	4"x4
PFI-1236N-3D4DZ-Q2	Water	870.2	7.14	4"x4	696.1	4.72	4"x4	1044.2	10.00	4"x4
PFI-1236N-3D4EZ-Q2	Water	870.2	7.18	4"x4	696.1	4.75	4"x4	1044.2	10.07	4"x4
PFI-1236N-3D1EZ-R2	Water	852.6	10.46	4"x4	682.0	6.92	4"x4	1023.1	14.66	4"x4
PFI-1236N-3D4EZ-R2	Water	870.2	7.18	4"x4	696.1	4.75	4"x4	1044.2	10.07	4"x4
PFI-1236N-4D1DZ-K2	Water	452.7	4.12	4"x4	362.1	2.73	4"x4	543.2	5.78	4"x4
PFI-1236N-4D1EZ-L2	Water	852.6	13.26	4"x4	682.0	8.77	4"x4	1023.1	18.59	4"x4
PFI-1236N-4D2EZ-M2	Water	858.1	11.53	4"x4	686.4	7.63	4"x4	1029.7	16.17	4"x4
PFI-1236N-4D2DZ-N2	Water	858.1	11.49	4"x4	686.4	7.60	4"x4	1029.7	16.10	4"x4
PFI-1236N-4D1EZ-N2	Water	852.6	13.26	4"x4	682.0	8.77	4"x4	1023.1	18.59	4"x4
PFI-1236N-4D3DZ-O2	Water	863.6	10.16	4"x4	690.8	6.72	4"x4	1036.3	14.24	4"x4
PFI-1236N-4D1EZ-O2	Water	852.6	13.26	4"x4	682.0	8.77	4"x4	1023.1	18.59	4"x4
PFI-1236N-4D1EZ-P2	Water	852.6	13.26	4"x4	682.0	8.77	4"x4	1023.1	18.59	4"x4
PFI-1236N-4D1DZ-Q2	Water	852.6	13.30	4"x4	682.0	8.80	4"x4	1023.1	18.65	4"x4
PFI-1236N-4D2EZ-Q2	Water	858.1	11.53	4"x4	686.4	7.63	4"x4	1029.7	16.17	4"x4
PFI-1236N-4D4EZ-Q2	Water	870.2	8.99	4"x4	696.1	5.94	4"x4	1044.2	12.60	4"x4
PFI-1236N-4D2EZ-R2	Water	858.1	11.53	4"x4	686.4	7.63	4"x4	1029.7	16.17	4"x4
PFI-1236N-4D4EZ-R2	Water	870.2	8.99	4"x4	696.1	5.94	4"x4	1044.2	12.60	4"x4
PFI-1236N-5D1DZ-K2	Water	452.7	5.01	4"x4	362.1	3.32	4"x4	543.2	7.03	4"x4
PFI-1236N-5D1EZ-O2	Water	852.6	16.10	4"x4	682.0	10.65	4"x4	1023.1	22.56	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-5D2EZ-P2	Water	858.1	13.98	4"x4	686.4	9.25	4"x4	1029.7	19.59	4"x4
PFI-1236N-6D2DZ-M2	Water	858.1	16.39	4"x4	686.4	10.84	4"x4	1029.7	22.96	4"x4
PFI-1236N-6D1DZ-N2	Water	852.6	18.99	4"x4	682.0	12.56	4"x4	1023.1	26.61	4"x4
PFI-1236N-6D1DZ-R2	Water	852.6	18.99	4"x4	682.0	12.56	4"x4	1023.1	26.61	4"x4
PFI-1236N-6D1EZ-R2	Water	852.6	19.03	4"x4	682.0	12.59	4"x4	1023.1	26.67	4"x4
PFI-1236N-3D4BT-K2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-1236N-3D4BT-L2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-1236N-3D4BT-N2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-1236N-3D4BT-O2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-1236N-3D4BT-P2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-1236N-4D4BT-K2	Water	470.3	2.87	4"x4	376.2	1.90	4"x4	564.3	4.02	4"x4
PFI-1236N-4D4BT-L2	Water	470.3	2.87	4"x4	376.2	1.90	4"x4	564.3	4.02	4"x4
PFI-1236N-4D3BT-M2	Water	463.7	3.22	4"x4	370.9	2.13	4"x4	556.4	4.51	4"x4
PFI-1236N-4D3BT-N2	Water	463.7	3.22	4"x4	370.9	2.13	4"x4	556.4	4.51	4"x4
PFI-1236N-4D3BT-O2	Water	463.7	3.22	4"x4	370.9	2.13	4"x4	556.4	4.51	4"x4
PFI-1236N-4D4BT-P2	Water	870.2	8.96	4"x4	696.1	5.93	4"x4	1044.2	12.56	4"x4
PFI-1236N-4D3BT-Q2	Water	863.6	10.18	4"x4	690.8	6.74	4"x4	1036.3	14.27	4"x4
PFI-1236N-5D2BT-K2	Water	458.2	4.36	4"x4	366.5	2.89	4"x4	549.8	6.11	4"x4
PFI-1236N-5D2BT-L2	Water	458.2	4.36	4"x4	366.5	2.89	4"x4	549.8	6.11	4"x4
PFI-1236N-5D2BT-M2	Water	458.2	4.36	4"x4	366.5	2.89	4"x4	549.8	6.11	4"x4
PFI-1236N-5D2BT-N2	Water	458.2	4.36	4"x4	366.5	2.89	4"x4	549.8	6.11	4"x4
PFI-1236N-5D3BT-O2	Water	863.6	12.14	4"x4	690.8	8.03	4"x4	1036.3	17.01	4"x4
PFI-1236N-5D2BT-P2	Water	858.1	13.94	4"x4	686.4	9.22	4"x4	1029.7	19.53	4"x4
PFI-1236N-5D3BT-Q2	Water	863.6	12.14	4"x4	690.8	8.03	4"x4	1036.3	17.01	4"x4
PFI-1236N-6D1BT-K2	Water	452.7	5.88	4"x4	362.1	3.89	4"x4	543.2	8.23	4"x4
PFI-1236N-6D1BT-L2	Water	452.7	5.88	4"x4	362.1	3.89	4"x4	543.2	8.23	4"x4
PFI-1236N-6D1BT-M2	Water	452.7	5.88	4"x4	362.1	3.89	4"x4	543.2	8.23	4"x4
PFI-1236N-6D1BT-N2	Water	852.6	18.96	4"x4	682.0	12.54	4"x4	1023.1	26.57	4"x4
PFI-1236N-6D1BT-O2	Water	852.6	18.96	4"x4	682.0	12.54	4"x4	1023.1	26.57	4"x4
PFI-1236N-6D1BT-P2	Water	852.6	18.96	4"x4	682.0	12.54	4"x4	1023.1	26.57	4"x4
PFI-1236N-6D1BT-Q2	Water	852.6	18.96	4"x4	682.0	12.54	4"x4	1023.1	26.57	4"x4
PFI-2418N-2D1DS-M2	Water	1011.0	1.68	4"x4	808.8	1.11	4"x4	1213.1	2.35	4"x4
PFI-2418N-2D4ES-M2	Water	1081.4	1.40	4"x4	865.1	0.93	4"x4	1297.6	1.96	4"x4
PFI-2418N-2D1DS-N2	Water	1011.0	1.68	4"x4	808.8	1.11	4"x4	1213.1	2.35	4"x4
PFI-2418N-2D2DS-N2	Water	1033.0	1.56	4"x4	826.4	1.03	4"x4	1239.5	2.18	4"x4
PFI-2418N-2D3ES-N2	Water	1055.0	1.47	4"x4	844.0	0.98	4"x4	1265.9	2.06	4"x4
PFI-2418N-2D2DS-O2	Water	1033.0	1.56	4"x4	826.4	1.03	4"x4	1239.5	2.18	4"x4
PFI-2418N-2D3ES-O2	Water	1055.0	1.47	4"x4	844.0	0.98	4"x4	1265.9	2.06	4"x4
PFI-2418N-2D4DS-P2	Water	1081.4	1.40	4"x4	865.1	0.93	4"x4	1297.6	1.96	4"x4
PFI-2418N-3D1ES-K2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-2418N-3D1ES-L2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-3D4ES-M2	Water	1881.1	3.67	4"x8	1504.9	3.25	4"x4	2257.3	5.14	4"x8
PFI-2418N-3D1DS-N2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-2418N-3D1ES-N2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-2418N-3D1DS-O2	Water	1011.0	2.22	4"x4	808.8	1.47	4"x4	1213.1	3.11	4"x4
PFI-2418N-3D2DS-O2	Water	1033.0	2.03	4"x4	826.4	1.35	4"x4	1239.5	2.85	4"x4
PFI-2418N-3D1ES-O2	Water	1810.7	6.52	4"x4	1448.6	4.32	4"x4	2172.8	7.22	4"x8
PFI-2418N-3D2DS-P2	Water	1832.7	5.87	4"x4	1466.2	3.88	4"x4	2199.2	6.26	4"x8
PFI-2418N-3D2ES-P2	Water	1832.7	5.87	4"x4	1466.2	3.88	4"x4	2199.2	6.26	4"x8
PFI-2418N-3D2DS-Q2	Water	1832.7	5.87	4"x4	1466.2	3.88	4"x4	2199.2	6.26	4"x8
PFI-2418N-3D4DS-Q2	Water	1881.1	3.67	4"x8	1504.9	3.25	4"x4	2257.3	5.14	4"x8
PFI-2418N-3D4ES-Q2	Water	1881.1	3.67	4"x8	1504.9	3.25	4"x4	2257.3	5.14	4"x8
PFI-2418N-3D1ES-R2	Water	1810.7	6.52	4"x4	1448.6	4.32	4"x4	2172.8	7.22	4"x8
PFI-2418N-3D4ES-R2	Water	1881.1	3.67	4"x8	1504.9	3.25	4"x4	2257.3	5.14	4"x8
PFI-2418N-4D1DS-K2	Water	1011.0	2.77	4"x4	808.8	1.83	4"x4	1213.1	3.87	4"x4
PFI-2418N-4D1ES-L2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-2418N-4D2ES-M2	Water	1832.7	7.24	4"x4	1466.2	4.79	4"x4	2199.2	8.10	4"x8
PFI-2418N-4D2DS-N2	Water	1832.7	7.24	4"x4	1466.2	4.79	4"x4	2199.2	8.10	4"x8
PFI-2418N-4D1ES-N2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-2418N-4D3DS-O2	Water	1854.7	6.56	4"x4	1483.8	4.34	4"x4	2225.6	7.14	4"x8
PFI-2418N-4D1ES-O2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-2418N-4D1ES-P2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-2418N-4D1DS-Q2	Water	1810.7	8.12	4"x4	1448.6	5.38	4"x4	2172.8	9.38	4"x8
PFI-2418N-4D2ES-Q2	Water	1832.7	7.24	4"x4	1466.2	4.79	4"x4	2199.2	8.10	4"x8
PFI-2418N-4D4ES-Q2	Water	1881.1	4.45	4"x8	1504.9	3.93	4"x4	2257.3	6.24	4"x8
PFI-2418N-4D2ES-R2	Water	1832.7	7.24	4"x4	1466.2	4.79	4"x4	2199.2	8.10	4"x8
PFI-2418N-4D4ES-R2	Water	1881.1	4.45	4"x8	1504.9	3.93	4"x4	2257.3	6.24	4"x8
PFI-2418N-5D1DS-K2	Water	1011.0	3.31	4"x4	808.8	2.19	4"x4	1213.1	4.64	4"x4
PFI-2418N-5D1ES-O2	Water	1810.7	9.72	4"x4	1448.6	6.43	4"x4	2172.8	11.54	4"x8
PFI-2418N-5D2ES-P2	Water	1832.7	8.61	4"x4	1466.2	5.70	4"x4	2199.2	9.94	4"x8
PFI-2418N-6D2DS-M2	Water	1832.7	9.97	4"x4	1466.2	6.60	4"x4	2199.2	11.78	4"x8
PFI-2418N-6D1DS-N2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-2418N-6D1DS-R2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-2418N-6D1ES-R2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-2418N-3D4BS-K2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-2418N-3D4BS-L2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-2418N-3D4BS-N2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-2418N-3D4BS-O2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-2418N-3D4BS-P2	Water	1081.4	1.77	4"x4	865.1	1.17	4"x4	1297.6	2.47	4"x4
PFI-2418N-4D4BS-K2	Water	1081.4	2.14	4"x4	865.1	1.42	4"x4	1297.6	2.99	4"x4
PFI-2418N-4D4BS-L2	Water	1081.4	2.14	4"x4	865.1	1.42	4"x4	1297.6	2.99	4"x4
PFI-2418N-4D3BS-M2	Water	1055.0	2.31	4"x4	844.0	1.53	4"x4	1265.9	3.24	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-4D3BS-N2	Water	1055.0	2.31	4"x4	844.0	1.53	4"x4	1265.9	3.24	4"x4
PFI-2418N-4D3BS-O2	Water	1055.0	2.31	4"x4	844.0	1.53	4"x4	1265.9	3.24	4"x4
PFI-2418N-4D4BS-P2	Water	1881.1	4.45	4"x8	1504.9	3.93	4"x4	2257.3	6.24	4"x8
PFI-2418N-4D3BS-Q2	Water	1854.7	6.56	4"x4	1483.8	4.34	4"x4	2225.6	7.14	4"x8
PFI-2418N-5D2BS-K2	Water	1033.0	2.98	4"x4	826.4	1.98	4"x4	1239.5	4.18	4"x4
PFI-2418N-5D2BS-L2	Water	1033.0	2.98	4"x4	826.4	1.98	4"x4	1239.5	4.18	4"x4
PFI-2418N-5D2BS-M2	Water	1033.0	2.98	4"x4	826.4	1.98	4"x4	1239.5	4.18	4"x4
PFI-2418N-5D2BS-N2	Water	1033.0	2.98	4"x4	826.4	1.98	4"x4	1239.5	4.18	4"x4
PFI-2418N-5D3BS-O2	Water	1055.0	2.73	4"x4	844.0	1.81	4"x4	1265.9	3.83	4"x4
PFI-2418N-5D2BS-P2	Water	1832.7	8.61	4"x4	1466.2	5.70	4"x4	2199.2	9.94	4"x8
PFI-2418N-5D3BS-Q2	Water	1854.7	7.75	4"x4	1483.8	5.13	4"x4	2225.6	8.74	4"x8
PFI-2418N-6D1BS-K2	Water	1011.0	3.85	4"x4	808.8	2.55	4"x4	1213.1	5.40	4"x4
PFI-2418N-6D1BS-L2	Water	1011.0	3.85	4"x4	808.8	2.55	4"x4	1213.1	5.40	4"x4
PFI-2418N-6D1BS-M2	Water	1011.0	3.85	4"x4	808.8	2.55	4"x4	1213.1	5.40	4"x4
PFI-2418N-6D1BS-N2	Water	1011.0	3.85	4"x4	808.8	2.55	4"x4	1213.1	5.40	4"x4
PFI-2418N-6D1BS-O2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-2418N-6D1BS-P2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-2418N-6D1BS-Q2	Water	1810.7	11.32	4"x4	1448.6	7.49	4"x4	2172.8	13.70	4"x8
PFI-2418N-6D2BS-R2	Water	1832.7	9.97	4"x4	1466.2	6.60	4"x4	2199.2	11.78	4"x8
PFI-2418N-2D1DZ-M2	Water	452.7	2.34	4"x4	362.1	1.55	4"x4	543.2	3.28	4"x4
PFI-2418N-2D4EZ-M2	Water	470.3	1.75	4"x4	376.2	1.16	4"x4	564.3	2.45	4"x4
PFI-2418N-2D1DZ-N2	Water	452.7	2.34	4"x4	362.1	1.55	4"x4	543.2	3.28	4"x4
PFI-2418N-2D2DZ-N2	Water	458.2	2.10	4"x4	366.5	1.39	4"x4	549.8	2.94	4"x4
PFI-2418N-2D3EZ-N2	Water	463.7	1.92	4"x4	370.9	1.27	4"x4	556.4	2.69	4"x4
PFI-2418N-2D2DZ-O2	Water	458.2	2.10	4"x4	366.5	1.39	4"x4	549.8	2.94	4"x4
PFI-2418N-2D3EZ-O2	Water	463.7	1.92	4"x4	370.9	1.27	4"x4	556.4	2.69	4"x4
PFI-2418N-2D4DZ-P2	Water	470.3	1.75	4"x4	376.2	1.16	4"x4	564.3	2.45	4"x4
PFI-2418N-3D1EZ-K2	Water	452.7	3.24	4"x4	362.1	2.14	4"x4	543.2	4.54	4"x4
PFI-2418N-3D1EZ-L2	Water	452.7	3.24	4"x4	362.1	2.14	4"x4	543.2	4.54	4"x4
PFI-2418N-3D4EZ-M2	Water	870.2	7.18	4"x4	696.1	4.75	4"x4	1044.2	10.07	4"x4
PFI-2418N-3D1DZ-N2	Water	452.7	3.23	4"x4	362.1	2.14	4"x4	543.2	4.53	4"x4
PFI-2418N-3D1EZ-N2	Water	852.6	10.46	4"x4	682.0	6.92	4"x4	1023.1	14.66	4"x4
PFI-2418N-3D1DZ-O2	Water	452.7	3.23	4"x4	362.1	2.14	4"x4	543.2	4.53	4"x4
PFI-2418N-3D2DZ-O2	Water	858.1	9.04	4"x4	686.4	5.98	4"x4	1029.7	12.67	4"x4
PFI-2418N-3D1EZ-O2	Water	852.6	10.46	4"x4	682.0	6.92	4"x4	1023.1	14.66	4"x4
PFI-2418N-3D2DZ-P2	Water	858.1	9.04	4"x4	686.4	5.98	4"x4	1029.7	12.67	4"x4
PFI-2418N-3D2EZ-P2	Water	858.1	9.09	4"x4	686.4	6.01	4"x4	1029.7	12.73	4"x4
PFI-2418N-3D2DZ-Q2	Water	858.1	9.04	4"x4	686.4	5.98	4"x4	1029.7	12.67	4"x4
PFI-2418N-3D4DZ-Q2	Water	870.2	7.14	4"x4	696.1	4.72	4"x4	1044.2	10.00	4"x4
PFI-2418N-3D4EZ-Q2	Water	870.2	7.18	4"x4	696.1	4.75	4"x4	1044.2	10.07	4"x4
PFI-2418N-3D1EZ-R2	Water	852.6	10.46	4"x4	682.0	6.92	4"x4	1023.1	14.66	4"x4





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-3D4EZ-R2	Water	870.2	7.18	4"x4	696.1	4.75	4"x4	1044.2	10.07	4"x4
PFI-2418N-4D1DZ-K2	Water	452.7	4.12	4"x4	362.1	2.73	4"x4	543.2	5.78	4"x4
PFI-2418N-4D1EZ-L2	Water	852.6	13.26	4"x4	682.0	8.77	4"x4	1023.1	18.59	4"x4
PFI-2418N-4D2EZ-M2	Water	858.1	11.53	4"x4	686.4	7.63	4"x4	1029.7	16.17	4"x4
PFI-2418N-4D2DZ-N2	Water	858.1	11.49	4"x4	686.4	7.60	4"x4	1029.7	16.10	4"x4
PFI-2418N-4D1EZ-N2	Water	852.6	13.26	4"x4	682.0	8.77	4"x4	1023.1	18.59	4"x4
PFI-2418N-4D3DZ-O2	Water	863.6	10.16	4"x4	690.8	6.72	4"x4	1036.3	14.24	4"x4
PFI-2418N-4D1EZ-O2	Water	852.6	13.26	4"x4	682.0	8.77	4"x4	1023.1	18.59	4"x4
PFI-2418N-4D1EZ-P2	Water	852.6	13.26	4"x4	682.0	8.77	4"x4	1023.1	18.59	4"x4
PFI-2418N-4D1DZ-Q2	Water	852.6	13.30	4"x4	682.0	8.80	4"x4	1023.1	18.65	4"x4
PFI-2418N-4D2EZ-Q2	Water	858.1	11.53	4"x4	686.4	7.63	4"x4	1029.7	16.17	4"x4
PFI-2418N-4D4EZ-Q2	Water	870.2	8.99	4"x4	696.1	5.94	4"x4	1044.2	12.60	4"x4
PFI-2418N-4D2EZ-R2	Water	858.1	11.53	4"x4	686.4	7.63	4"x4	1029.7	16.17	4"x4
PFI-2418N-4D4EZ-R2	Water	870.2	8.99	4"x4	696.1	5.94	4"x4	1044.2	12.60	4"x4
PFI-2418N-5D1DZ-K2	Water	452.7	5.01	4"x4	362.1	3.32	4"x4	543.2	7.03	4"x4
PFI-2418N-5D1EZ-O2	Water	852.6	16.10	4"x4	682.0	10.65	4"x4	1023.1	22.56	4"x4
PFI-2418N-5D2EZ-P2	Water	858.1	13.98	4"x4	686.4	9.25	4"x4	1029.7	19.59	4"x4
PFI-2418N-6D2DZ-M2	Water	858.1	16.39	4"x4	686.4	10.84	4"x4	1029.7	22.96	4"x4
PFI-2418N-6D1DZ-N2	Water	852.6	18.99	4"x4	682.0	12.56	4"x4	1023.1	26.61	4"x4
PFI-2418N-6D1DZ-R2	Water	852.6	18.99	4"x4	682.0	12.56	4"x4	1023.1	26.61	4"x4
PFI-2418N-6D1EZ-R2	Water	852.6	19.03	4"x4	682.0	12.59	4"x4	1023.1	26.67	4"x4
PFI-2418N-3D4BT-K2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-2418N-3D4BT-L2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-2418N-3D4BT-N2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-2418N-3D4BT-O2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-2418N-3D4BT-P2	Water	470.3	2.30	4"x4	376.2	1.52	4"x4	564.3	3.22	4"x4
PFI-2418N-4D4BT-K2	Water	470.3	2.87	4"x4	376.2	1.90	4"x4	564.3	4.02	4"x4
PFI-2418N-4D4BT-L2	Water	470.3	2.87	4"x4	376.2	1.90	4"x4	564.3	4.02	4"x4
PFI-2418N-4D3BT-M2	Water	463.7	3.22	4"x4	370.9	2.13	4"x4	556.4	4.51	4"x4
PFI-2418N-4D3BT-N2	Water	463.7	3.22	4"x4	370.9	2.13	4"x4	556.4	4.51	4"x4
PFI-2418N-4D3BT-O2	Water	463.7	3.22	4"x4	370.9	2.13	4"x4	556.4	4.51	4"x4
PFI-2418N-4D4BT-P2	Water	870.2	8.96	4"x4	696.1	5.93	4"x4	1044.2	12.56	4"x4
PFI-2418N-4D3BT-Q2	Water	863.6	10.18	4"x4	690.8	6.74	4"x4	1036.3	14.27	4"x4
PFI-2418N-5D2BT-K2	Water	458.2	4.36	4"x4	366.5	2.89	4"x4	549.8	6.11	4"x4
PFI-2418N-5D2BT-L2	Water	458.2	4.36	4"x4	366.5	2.89	4"x4	549.8	6.11	4"x4
PFI-2418N-5D2BT-M2	Water	458.2	4.36	4"x4	366.5	2.89	4"x4	549.8	6.11	4"x4
PFI-2418N-5D2BT-N2	Water	458.2	4.36	4"x4	366.5	2.89	4"x4	549.8	6.11	4"x4
PFI-2418N-5D3BT-O2	Water	863.6	12.14	4"x4	690.8	8.03	4"x4	1036.3	17.01	4"x4
PFI-2418N-5D2BT-P2	Water	858.1	13.94	4"x4	686.4	9.22	4"x4	1029.7	19.53	4"x4
PFI-2418N-5D3BT-Q2	Water	863.6	12.14	4"x4	690.8	8.03	4"x4	1036.3	17.01	4"x4
PFI-2418N-6D1BT-K2	Water	452.7	5.88	4"x4	362.1	3.89	4"x4	543.2	8.23	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-6D1BT-L2	Water	452.7	5.88	4"x4	362.1	3.89	4"x4	543.2	8.23	4"x4
PFI-2418N-6D1BT-M2	Water	452.7	5.88	4"x4	362.1	3.89	4"x4	543.2	8.23	4"x4
PFI-2418N-6D1BT-N2	Water	852.6	18.96	4"x4	682.0	12.54	4"x4	1023.1	26.57	4"x4
PFI-2418N-6D1BT-O2	Water	852.6	18.96	4"x4	682.0	12.54	4"x4	1023.1	26.57	4"x4
PFI-2418N-6D1BT-P2	Water	852.6	18.96	4"x4	682.0	12.54	4"x4	1023.1	26.57	4"x4
PFI-2418N-6D1BT-Q2	Water	852.6	18.96	4"x4	682.0	12.54	4"x4	1023.1	26.57	4"x4
PFI-2436N-2D1DS-M4	Water	2021.9	1.68	4"x8	1617.5	1.11	4"x8	2426.3	2.35	4"x8
PFI-2436N-2D4ES-M4	Water	2162.7	1.40	4"x8	1730.2	0.93	4"x8	2595.2	1.96	4"x8
PFI-2436N-2D1DS-N4	Water	2021.9	1.68	4"x8	1617.5	1.11	4"x8	2426.3	2.35	4"x8
PFI-2436N-2D2DS-N4	Water	2065.9	1.56	4"x8	1652.7	1.03	4"x8	2479.1	2.18	4"x8
PFI-2436N-2D3ES-N4	Water	2109.9	1.47	4"x8	1687.9	0.98	4"x8	2531.9	2.06	4"x8
PFI-2436N-2D2DS-O4	Water	2065.9	1.56	4"x8	1652.7	1.03	4"x8	2479.1	2.18	4"x8
PFI-2436N-2D3ES-O4	Water	2109.9	1.47	4"x8	1687.9	0.98	4"x8	2531.9	2.06	4"x8
PFI-2436N-2D4DS-P4	Water	2162.7	1.40	4"x8	1730.2	0.93	4"x8	2595.2	1.96	4"x8
PFI-2436N-3D1ES-K4	Water	2021.9	2.22	4"x8	1617.5	1.47	4"x8	2426.3	3.11	4"x8
PFI-2436N-3D1ES-L4	Water	2021.9	2.22	4"x8	1617.5	1.47	4"x8	2426.3	3.11	4"x8
PFI-2436N-3D4ES-M4	Water	2162.7	1.77	4"x8	1730.2	1.17	4"x8	2595.2	2.47	4"x8
PFI-2436N-3D1DS-N4	Water	2021.9	2.22	4"x8	1617.5	1.47	4"x8	2426.3	3.11	4"x8
PFI-2436N-3D1ES-N4	Water	2021.9	2.22	4"x8	1617.5	1.47	4"x8	2426.3	3.11	4"x8
PFI-2436N-3D1DS-O4	Water	2021.9	2.22	4"x8	1617.5	1.47	4"x8	2426.3	3.11	4"x8
PFI-2436N-3D2DS-O4	Water	2065.9	2.03	4"x8	1652.7	1.35	4"x8	2479.1	2.85	4"x8
PFI-2436N-3D1ES-O4	Water	3621.4	6.52	4"x8	2897.1	4.32	4"x8	4345.7	7.22	4"x16
PFI-2436N-3D2DS-P4	Water	3665.4	5.87	4"x8	2932.3	3.88	4"x8	4398.5	6.26	4"x16
PFI-2436N-3D2ES-P4	Water	3665.4	5.87	4"x8	2932.3	3.88	4"x8	4398.5	6.26	4"x16
PFI-2436N-3D2DS-Q4	Water	3665.4	5.87	4"x8	2932.3	3.88	4"x8	4398.5	6.26	4"x16
PFI-2436N-3D4DS-Q4	Water	3762.2	3.67	4"x16	3009.8	3.25	4"x8	4514.7	5.14	4"x16
PFI-2436N-3D4ES-Q4	Water	3762.2	3.67	4"x16	3009.8	3.25	4"x8	4514.7	5.14	4"x16
PFI-2436N-3D1ES-R4	Water	3621.4	6.52	4"x8	2897.1	4.32	4"x8	4345.7	7.22	4"x16
PFI-2436N-3D4ES-R4	Water	3762.2	3.67	4"x16	3009.8	3.25	4"x8	4514.7	5.14	4"x16
PFI-2436N-4D1DS-K4	Water	2021.9	2.77	4"x8	1617.5	1.83	4"x8	2426.3	3.87	4"x8
PFI-2436N-4D1ES-L4	Water	2021.9	2.77	4"x8	1617.5	1.83	4"x8	2426.3	3.87	4"x8
PFI-2436N-4D2ES-M4	Water	3665.4	7.24	4"x8	2932.3	4.79	4"x8	4398.5	8.10	4"x16
PFI-2436N-4D2DS-N4	Water	3665.4	7.24	4"x8	2932.3	4.79	4"x8	4398.5	8.10	4"x16
PFI-2436N-4D1ES-N4	Water	3621.4	8.12	4"x8	2897.1	5.38	4"x8	4345.7	9.38	4"x16
PFI-2436N-4D3DS-O4	Water	3709.4	6.56	4"x8	2967.5	4.34	4"x8	4451.3	7.14	4"x16
PFI-2436N-4D1ES-O4	Water	3621.4	8.12	4"x8	2897.1	5.38	4"x8	4345.7	9.38	4"x16
PFI-2436N-4D1ES-P4	Water	3621.4	8.12	4"x8	2897.1	5.38	4"x8	4345.7	9.38	4"x16
PFI-2436N-4D1DS-Q4	Water	3621.4	8.12	4"x8	2897.1	5.38	4"x8	4345.7	9.38	4"x16
PFI-2436N-4D2ES-Q4	Water	3665.4	7.24	4"x8	2932.3	4.79	4"x8	4398.5	8.10	4"x16
PFI-2436N-4D4ES-Q4	Water	3762.2	4.45	4"x16	3009.8	3.93	4"x8	4514.7	6.24	4"x16
PFI-2436N-4D2ES-R4	Water	3665.4	7.24	4"x8	2932.3	4.79	4"x8	4398.5	8.10	4"x16



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-4D4ES-R4	Water	3762.2	4.45	4"x16	3009.8	3.93	4"x8	4514.7	6.24	4"x16
PFI-2436N-5D1DS-K4	Water	2021.9	3.31	4"x8	1617.5	2.19	4"x8	2426.3	4.64	4"x8
PFI-2436N-5D1ES-O4	Water	3621.4	9.72	4"x8	2897.1	6.43	4"x8	4345.7	11.54	4"x16
PFI-2436N-5D2ES-P4	Water	3665.4	8.61	4"x8	2932.3	5.70	4"x8	4398.5	9.94	4"x16
PFI-2436N-6D2DS-M4	Water	3665.4	9.97	4"x8	2932.3	6.60	4"x8	4398.5	11.78	4"x16
PFI-2436N-6D1DS-N4	Water	3621.4	11.32	4"x8	2897.1	7.49	4"x8	4345.7	13.70	4"x16
PFI-2436N-6D1DS-R4	Water	3621.4	11.32	4"x8	2897.1	7.49	4"x8	4345.7	13.70	4"x16
PFI-2436N-6D1ES-R4	Water	3621.4	11.32	4"x8	2897.1	7.49	4"x8	4345.7	13.70	4"x16
PFI-2436N-3D4BS-K4	Water	2162.7	1.77	4"x8	1730.2	1.17	4"x8	2595.2	2.47	4"x8
PFI-2436N-3D4BS-L4	Water	2162.7	1.77	4"x8	1730.2	1.17	4"x8	2595.2	2.47	4"x8
PFI-2436N-3D4BS-N4	Water	2162.7	1.77	4"x8	1730.2	1.17	4"x8	2595.2	2.47	4"x8
PFI-2436N-3D4BS-O4	Water	2162.7	1.77	4"x8	1730.2	1.17	4"x8	2595.2	2.47	4"x8
PFI-2436N-3D4BS-P4	Water	2162.7	1.77	4"x8	1730.2	1.17	4"x8	2595.2	2.47	4"x8
PFI-2436N-4D4BS-K4	Water	2162.7	2.14	4"x8	1730.2	1.42	4"x8	2595.2	2.99	4"x8
PFI-2436N-4D4BS-L4	Water	2162.7	2.14	4"x8	1730.2	1.42	4"x8	2595.2	2.99	4"x8
PFI-2436N-4D3BS-M4	Water	2109.9	2.31	4"x8	1687.9	1.53	4"x8	2531.9	3.24	4"x8
PFI-2436N-4D3BS-N4	Water	2109.9	2.31	4"x8	1687.9	1.53	4"x8	2531.9	3.24	4"x8
PFI-2436N-4D3BS-O4	Water	2109.9	2.31	4"x8	1687.9	1.53	4"x8	2531.9	3.24	4"x8
PFI-2436N-4D4BS-P4	Water	3762.2	4.45	4"x16	3009.8	3.93	4"x8	4514.7	6.24	4"x16
PFI-2436N-4D3BS-Q4	Water	3709.4	6.56	4"x8	2967.5	4.34	4"x8	4451.3	7.14	4"x16
PFI-2436N-5D2BS-K4	Water	2065.9	2.98	4"x8	1652.7	1.98	4"x8	2479.1	4.18	4"x8
PFI-2436N-5D2BS-L4	Water	2065.9	2.98	4"x8	1652.7	1.98	4"x8	2479.1	4.18	4"x8
PFI-2436N-5D2BS-M4	Water	2065.9	2.98	4"x8	1652.7	1.98	4"x8	2479.1	4.18	4"x8
PFI-2436N-5D2BS-N4	Water	2065.9	2.98	4"x8	1652.7	1.98	4"x8	2479.1	4.18	4"x8
PFI-2436N-5D3BS-O4	Water	2109.9	2.73	4"x8	1687.9	1.81	4"x8	2531.9	3.83	4"x8
PFI-2436N-5D2BS-P4	Water	2065.9	2.98	4"x8	1652.7	1.98	4"x8	2479.1	4.18	4"x8
PFI-2436N-5D3BS-Q4	Water	3709.4	7.75	4"x8	2967.5	5.13	4"x8	4451.3	8.74	4"x16
PFI-2436N-6D1BS-K4	Water	2021.9	3.85	4"x8	1617.5	2.55	4"x8	2426.3	5.40	4"x8
PFI-2436N-6D1BS-L4	Water	2021.9	3.85	4"x8	1617.5	2.55	4"x8	2426.3	5.40	4"x8
PFI-2436N-6D1BS-M4	Water	2021.9	3.85	4"x8	1617.5	2.55	4"x8	2426.3	5.40	4"x8
PFI-2436N-6D1BS-N4	Water	2021.9	3.85	4"x8	1617.5	2.55	4"x8	2426.3	5.40	4"x8
PFI-2436N-6D1BS-O4	Water	3621.4	11.32	4"x8	2897.1	7.49	4"x8	4345.7	13.70	4"x16
PFI-2436N-6D1BS-P4	Water	3621.4	11.32	4"x8	2897.1	7.49	4"x8	4345.7	13.70	4"x16
PFI-2436N-6D1BS-Q4	Water	3621.4	11.32	4"x8	2897.1	7.49	4"x8	4345.7	13.70	4"x16
PFI-2436N-6D2BS-R4	Water	3665.4	9.97	4"x8	2932.3	6.60	4"x8	4398.5	11.78	4"x16
PFI-2436N-2D1DZ-M4	Water	905.4	2.34	4"x8	724.3	1.55	4"x8	1086.4	3.28	4"x8
PFI-2436N-2D4EZ-M4	Water	940.6	1.75	4"x8	752.4	1.16	4"x8	1128.7	2.45	4"x8
PFI-2436N-2D1DZ-N4	Water	905.4	2.34	4"x8	724.3	1.55	4"x8	1086.4	3.28	4"x8
PFI-2436N-2D2DZ-N4	Water	916.4	2.10	4"x8	733.1	1.39	4"x8	1099.6	2.94	4"x8
PFI-2436N-2D3EZ-N4	Water	927.4	1.92	4"x8	741.9	1.27	4"x8	1112.8	2.69	4"x8
PFI-2436N-2D2DZ-O4	Water	916.4	2.10	4"x8	733.1	1.39	4"x8	1099.6	2.94	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-2D3EZ-O4	Water	927.4	1.92	4"x8	741.9	1.27	4"x8	1112.8	2.69	4"x8
PFI-2436N-2D4DZ-P4	Water	940.6	1.75	4"x8	752.4	1.16	4"x8	1128.7	2.45	4"x8
PFI-2436N-3D1EZ-K4	Water	905.4	3.24	4"x8	724.3	2.15	4"x8	1086.4	4.54	4"x8
PFI-2436N-3D1EZ-L4	Water	905.4	3.24	4"x8	724.3	2.15	4"x8	1086.4	4.54	4"x8
PFI-2436N-3D4EZ-M4	Water	1740.3	7.18	4"x8	1392.2	4.75	4"x8	2088.4	10.07	4"x8
PFI-2436N-3D1DZ-N4	Water	905.4	3.23	4"x8	724.3	2.14	4"x8	1086.4	4.53	4"x8
PFI-2436N-3D1EZ-N4	Water	1705.1	10.46	4"x8	1364.1	6.92	4"x8	2046.1	14.66	4"x8
PFI-2436N-3D1DZ-O4	Water	905.4	3.23	4"x8	724.3	2.14	4"x8	1086.4	4.53	4"x8
PFI-2436N-3D2DZ-O4	Water	1716.1	9.04	4"x8	1372.9	5.98	4"x8	2059.3	12.67	4"x8
PFI-2436N-3D1EZ-O4	Water	1705.1	10.46	4"x8	1364.1	6.92	4"x8	2046.1	14.66	4"x8
PFI-2436N-3D2DZ-P4	Water	1716.1	9.04	4"x8	1372.9	5.98	4"x8	2059.3	12.67	4"x8
PFI-2436N-3D2EZ-P4	Water	1716.1	9.08	4"x8	1372.9	6.01	4"x8	2059.3	12.73	4"x8
PFI-2436N-3D2DZ-Q4	Water	1716.1	9.04	4"x8	1372.9	5.98	4"x8	2059.3	12.67	4"x8
PFI-2436N-3D4DZ-Q4	Water	1740.3	7.14	4"x8	1392.2	4.72	4"x8	2088.4	10.00	4"x8
PFI-2436N-3D4EZ-Q4	Water	1740.3	7.18	4"x8	1392.2	4.75	4"x8	2088.4	10.07	4"x8
PFI-2436N-3D1EZ-R4	Water	1705.1	10.46	4"x8	1364.1	6.92	4"x8	2046.1	14.66	4"x8
PFI-2436N-3D4EZ-R4	Water	1740.3	7.18	4"x8	1392.2	4.75	4"x8	2088.4	10.07	4"x8
PFI-2436N-4D1DZ-K4	Water	905.4	4.12	4"x8	724.3	2.73	4"x8	1086.4	5.78	4"x8
PFI-2436N-4D1EZ-L4	Water	1705.1	13.26	4"x8	1364.1	8.77	4"x8	2046.1	18.59	4"x8
PFI-2436N-4D2EZ-M4	Water	1716.1	11.53	4"x8	1372.9	7.63	4"x8	2059.3	16.16	4"x8
PFI-2436N-4D2DZ-N4	Water	1716.1	11.49	4"x8	1372.9	7.60	4"x8	2059.3	16.10	4"x8
PFI-2436N-4D1EZ-N4	Water	1705.1	13.26	4"x8	1364.1	8.77	4"x8	2046.1	18.59	4"x8
PFI-2436N-4D3DZ-O4	Water	1727.1	10.16	4"x8	1381.7	6.72	4"x8	2072.5	14.24	4"x8
PFI-2436N-4D1EZ-O4	Water	1705.1	13.26	4"x8	1364.1	8.77	4"x8	2046.1	18.59	4"x8
PFI-2436N-4D1EZ-P4	Water	1705.1	13.26	4"x8	1364.1	8.77	4"x8	2046.1	18.59	4"x8
PFI-2436N-4D1DZ-Q4	Water	1705.1	13.30	4"x8	1364.1	8.80	4"x8	2046.1	18.65	4"x8
PFI-2436N-4D2EZ-Q4	Water	1716.1	11.53	4"x8	1372.9	7.63	4"x8	2059.3	16.16	4"x8
PFI-2436N-4D4EZ-Q4	Water	1740.3	8.98	4"x8	1392.2	5.94	4"x8	2088.4	12.60	4"x8
PFI-2436N-4D2EZ-R4	Water	1716.1	11.53	4"x8	1372.9	7.63	4"x8	2059.3	16.16	4"x8
PFI-2436N-4D4EZ-R4	Water	1740.3	8.98	4"x8	1392.2	5.94	4"x8	2088.4	12.60	4"x8
PFI-2436N-5D1DZ-K4	Water	905.4	5.01	4"x8	724.3	3.32	4"x8	1086.4	7.03	4"x8
PFI-2436N-5D1EZ-O4	Water	1705.1	16.10	4"x8	1364.1	10.65	4"x8	2046.1	22.56	4"x8
PFI-2436N-5D2EZ-P4	Water	1716.1	13.98	4"x8	1372.9	9.25	4"x8	2059.3	19.59	4"x8
PFI-2436N-6D2DZ-M4	Water	1716.1	16.38	4"x8	1372.9	10.84	4"x8	2059.3	22.96	4"x8
PFI-2436N-6D1DZ-N4	Water	1705.1	18.98	4"x8	1364.1	12.56	4"x8	2046.1	26.60	4"x8
PFI-2436N-6D1DZ-R4	Water	1705.1	18.98	4"x8	1364.1	12.56	4"x8	2046.1	26.60	4"x8
PFI-2436N-6D1EZ-R4	Water	1705.1	19.03	4"x8	1364.1	12.59	4"x8	2046.1	26.67	4"x8
PFI-2436N-3D4BT-K4	Water	940.6	2.30	4"x8	752.4	1.52	4"x8	1128.7	3.22	4"x8
PFI-2436N-3D4BT-L4	Water	940.6	2.30	4"x8	752.4	1.52	4"x8	1128.7	3.22	4"x8
PFI-2436N-3D4BT-N4	Water	940.6	2.30	4"x8	752.4	1.52	4"x8	1128.7	3.22	4"x8
PFI-2436N-3D4BT-O4	Water	940.6	2.30	4"x8	752.4	1.52	4"x8	1128.7	3.22	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-3D4BT-P4	Water	940.6	2.30	4"x8	752.4	1.52	4"x8	1128.7	3.22	4"x8
PFI-2436N-4D4BT-K4	Water	940.6	2.87	4"x8	752.4	1.90	4"x8	1128.7	4.02	4"x8
PFI-2436N-4D4BT-L4	Water	940.6	2.87	4"x8	752.4	1.90	4"x8	1128.7	4.02	4"x8
PFI-2436N-4D3BT-M4	Water	927.4	3.22	4"x8	741.9	2.13	4"x8	1112.8	4.51	4"x8
PFI-2436N-4D3BT-N4	Water	927.4	3.22	4"x8	741.9	2.13	4"x8	1112.8	4.51	4"x8
PFI-2436N-4D3BT-O4	Water	927.4	3.22	4"x8	741.9	2.13	4"x8	1112.8	4.51	4"x8
PFI-2436N-4D4BT-P4	Water	1740.3	8.96	4"x8	1392.2	5.93	4"x8	2088.4	12.56	4"x8
PFI-2436N-4D3BT-Q4	Water	1727.1	10.18	4"x8	1381.7	6.74	4"x8	2072.5	14.27	4"x8
PFI-2436N-5D2BT-K4	Water	916.4	4.36	4"x8	733.1	2.89	4"x8	1099.6	6.11	4"x8
PFI-2436N-5D2BT-L4	Water	916.4	4.36	4"x8	733.1	2.89	4"x8	1099.6	6.11	4"x8
PFI-2436N-5D2BT-M4	Water	916.4	4.36	4"x8	733.1	2.89	4"x8	1099.6	6.11	4"x8
PFI-2436N-5D2BT-N4	Water	916.4	4.36	4"x8	733.1	2.89	4"x8	1099.6	6.11	4"x8
PFI-2436N-5D3BT-O4	Water	927.4	3.84	4"x8	741.9	2.55	4"x8	1112.8	5.38	4"x8
PFI-2436N-5D2BT-P4	Water	1716.1	13.93	4"x8	1372.9	9.22	4"x8	2059.3	19.53	4"x8
PFI-2436N-5D3BT-Q4	Water	1727.1	12.14	4"x8	1381.7	8.03	4"x8	2072.5	17.01	4"x8
PFI-2436N-6D1BT-K4	Water	905.4	5.88	4"x8	724.3	3.89	4"x8	1086.4	8.23	4"x8
PFI-2436N-6D1BT-L4	Water	905.4	5.88	4"x8	724.3	3.89	4"x8	1086.4	8.23	4"x8
PFI-2436N-6D1BT-M4	Water	905.4	5.88	4"x8	724.3	3.89	4"x8	1086.4	8.23	4"x8
PFI-2436N-6D1BT-N4	Water	1705.1	18.96	4"x8	1364.1	12.55	4"x8	2046.1	26.57	4"x8
PFI-2436N-6D1BT-O4	Water	1705.1	18.96	4"x8	1364.1	12.55	4"x8	2046.1	26.57	4"x8
PFI-2436N-6D1BT-P4	Water	1705.1	18.96	4"x8	1364.1	12.55	4"x8	2046.1	26.57	4"x8
PFI-2436N-6D1BT-Q4	Water	1705.1	18.96	4"x8	1364.1	12.55	4"x8	2046.1	26.57	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0406N-3D1DS-G1	Ethylene Glycol	232.9	2.12	4"x1	186.4	1.4	4"x1	279.5	2.96	4"x1
PFI-0406N-3D1ES-H1	Ethylene Glycol	232.9	2.12	4"x1	186.4	1.4	4"x1	279.5	2.96	4"x1
PFI-0406N-4D1DS-H1	Ethylene Glycol	232.9	2.62	4"x1	186.4	1.74	4"x1	279.5	3.67	4"x1
PFI-0406N-6D1ES-G1	Ethylene Glycol	232.9	3.64	4"x1	186.4	2.41	4"x1	279.5	5.09	4"x1
PFI-0406N-6D1ES-H1	Ethylene Glycol	232.9	3.64	4"x1	186.4	2.41	4"x1	279.5	5.09	4"x1
PFI-0406N-6D2DS-J1	Ethylene Glycol	237.3	3.12	4"x1	189.9	2.07	4"x1	284.8	4.37	4"x1
PFI-0406N-2D3BS-G1	Ethylene Glycol	219.9	1.15	4"x1	176.0	0.76	4"x1	263.9	1.61	4"x1
PFI-0406N-2D4BS-H1	Ethylene Glycol	219.9	1.04	4"x1	176.0	0.69	4"x1	263.9	1.46	4"x1
PFI-0406N-3D2BS-G1	Ethylene Glycol	237.3	1.86	4"x1	189.9	1.24	4"x1	284.8	2.61	4"x1
PFI-0406N-3D3BS-H1	Ethylene Glycol	240.6	1.73	4"x1	192.5	1.14	4"x1	288.8	2.42	4"x1
PFI-0406N-4D4BS-G1	Ethylene Glycol	245.0	1.9	4"x1	196.0	1.26	4"x1	294.0	2.66	4"x1
PFI-0406N-4D3BS-H1	Ethylene Glycol	240.6	2.09	4"x1	192.5	1.39	4"x1	288.8	2.93	4"x1
PFI-0406N-4D4BS-J1	Ethylene Glycol	245.0	1.9	4"x1	196.0	1.26	4"x1	294.0	2.66	4"x1
PFI-0406N-5D2BS-G1	Ethylene Glycol	237.3	2.7	4"x1	189.9	1.79	4"x1	284.8	3.78	4"x1
PFI-0406N-5D4BS-H1	Ethylene Glycol	245.0	2.22	4"x1	196.0	1.47	4"x1	294.0	3.11	4"x1
PFI-0406N-5D4BS-J1	Ethylene Glycol	245.0	2.22	4"x1	196.0	1.47	4"x1	294.0	3.11	4"x1
PFI-0406N-6D1BS-H1	Ethylene Glycol	232.9	3.64	4"x1	186.4	2.41	4"x1	279.5	5.09	4"x1
PFI-0406N-3D1DZ-G1	Ethylene Glycol	108.2	2.8	4"x1	86.6	1.86	4"x1	129.9	3.93	4"x1
PFI-0406N-3D1EZ-H1	Ethylene Glycol	108.2	2.8	4"x1	86.6	1.86	4"x1	129.9	3.93	4"x1
PFI-0406N-4D1DZ-H1	Ethylene Glycol	108.2	3.68	4"x1	86.6	2.44	4"x1	129.9	5.15	4"x1
PFI-0406N-6D1EZ-G1	Ethylene Glycol	108.2	5.43	4"x1	86.6	3.6	4"x1	129.9	7.61	4"x1
PFI-0406N-6D1EZ-H1	Ethylene Glycol	108.2	5.43	4"x1	86.6	3.6	4"x1	129.9	7.61	4"x1
PFI-0406N-6D2DZ-J1	Ethylene Glycol	109.3	4.42	4"x1	87.5	2.93	4"x1	131.2	6.19	4"x1
PFI-0406N-2D3BT-G1	Ethylene Glycol	110.0	1.46	4"x1	88.0	0.97	4"x1	132.0	2.04	4"x1
PFI-0406N-2D4BT-H1	Ethylene Glycol	110.0	1.23	4"x1	88.0	0.82	4"x1	132.0	1.72	4"x1



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0406N-3D2BT-G1	Ethylene Glycol	109.3	2.29	4"x1	87.5	1.52	4"x1	131.2	3.21	4"x1
PFI-0406N-3D3BT-H1	Ethylene Glycol	110.4	2.11	4"x1	88.3	1.4	4"x1	132.5	2.96	4"x1
PFI-0406N-4D4BT-G1	Ethylene Glycol	111.5	2.35	4"x1	89.2	1.55	4"x1	133.8	3.29	4"x1
PFI-0406N-4D3BT-H1	Ethylene Glycol	110.4	2.76	4"x1	88.3	1.83	4"x1	132.5	3.87	4"x1
PFI-0406N-4D4BT-J1	Ethylene Glycol	111.5	2.35	4"x1	89.2	1.55	4"x1	133.8	3.29	4"x1
PFI-0406N-5D2BT-G1	Ethylene Glycol	109.3	3.7	4"x1	87.5	2.45	4"x1	131.2	5.18	4"x1
PFI-0406N-5D4BT-H1	Ethylene Glycol	111.5	2.89	4"x1	89.2	1.91	4"x1	133.8	4.05	4"x1
PFI-0406N-5D4BT-J1	Ethylene Glycol	111.5	2.89	4"x1	89.2	1.91	4"x1	133.8	4.05	4"x1
PFI-0406N-6D1BT-H1	Ethylene Glycol	108.2	5.41	4"x1	86.6	3.59	4"x1	129.9	7.59	4"x1
PFI-0412N-2D1DS-G2	Ethylene Glycol	232.9	2.33	4"x1	186.4	1.55	4"x1	279.5	3.27	4"x1
PFI-0412N-2D4DS-G2	Ethylene Glycol	245.0	1.72	4"x1	196.0	1.14	4"x1	294.0	2.41	4"x1
PFI-0412N-3D1DS-G2	Ethylene Glycol	232.9	3.2	4"x1	186.4	2.12	4"x1	279.5	4.48	4"x1
PFI-0412N-3D2DS-H2	Ethylene Glycol	237.3	2.76	4"x1	189.9	1.83	4"x1	284.8	3.87	4"x1
PFI-0412N-4D1DS-H2	Ethylene Glycol	232.9	4.07	4"x1	186.4	2.7	4"x1	279.5	5.7	4"x1
PFI-0412N-4D3DS-H2	Ethylene Glycol	240.6	3.15	4"x1	192.5	2.08	4"x1	288.8	4.41	4"x1
PFI-0412N-4D2ES-J2	Ethylene Glycol	237.3	3.48	4"x1	189.9	2.3	4"x1	284.8	4.87	4"x1
PFI-0412N-5D1ES-J2	Ethylene Glycol	232.9	4.94	4"x1	186.4	3.27	4"x1	279.5	6.92	4"x1
PFI-0412N-6D1ES-H2	Ethylene Glycol	232.9	5.81	4"x1	186.4	3.85	4"x1	279.5	8.13	4"x1
PFI-0412N-6D1ES-J2	Ethylene Glycol	232.9	5.81	4"x1	186.4	3.85	4"x1	279.5	8.13	4"x1
PFI-0412N-3D4BS-G2	Ethylene Glycol	245.0	2.26	4"x1	196.0	1.5	4"x1	294.0	3.17	4"x1
PFI-0412N-3D4BS-H2	Ethylene Glycol	245.0	2.26	4"x1	196.0	1.5	4"x1	294.0	3.17	4"x1
PFI-0412N-3D3BS-J2	Ethylene Glycol	240.6	2.51	4"x1	192.5	1.67	4"x1	288.8	3.52	4"x1
PFI-0412N-4D4BS-G2	Ethylene Glycol	245.0	2.81	4"x1	196.0	1.86	4"x1	294.0	3.93	4"x1
PFI-0412N-4D2BS-H2	Ethylene Glycol	237.3	3.48	4"x1	189.9	2.3	4"x1	284.8	4.87	4"x1
PFI-0412N-4D3BS-H2	Ethylene Glycol	240.6	3.15	4"x1	192.5	2.08	4"x1	288.8	4.41	4"x1



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0412N-4D3BS-J2	Ethylene Glycol	240.6	3.15	4"x1	192.5	2.08	4"x1	288.8	4.41	4"x1
PFI-0412N-5D2BS-G2	Ethylene Glycol	237.3	4.19	4"x1	189.9	2.78	4"x1	284.8	5.87	4"x1
PFI-0412N-6D2BS-G2	Ethylene Glycol	237.3	4.91	4"x1	189.9	3.25	4"x1	284.8	6.88	4"x1
PFI-0412N-6D1BS-H2	Ethylene Glycol	232.9	5.81	4"x1	186.4	3.85	4"x1	279.5	8.13	4"x1
PFI-0412N-6D2BS-J2	Ethylene Glycol	237.3	4.91	4"x1	189.9	3.25	4"x1	284.8	6.88	4"x1
PFI-0412N-2D1DZ-G2	Ethylene Glycol	108.2	3.18	4"x1	86.6	2.1	4"x1	129.9	4.45	4"x1
PFI-0412N-2D4DZ-G2	Ethylene Glycol	111.5	2.04	4"x1	89.2	1.35	4"x1	133.8	2.86	4"x1
PFI-0412N-3D1DZ-G2	Ethylene Glycol	108.2	4.67	4"x1	86.6	3.1	4"x1	129.9	6.55	4"x1
PFI-0412N-3D2DZ-H2	Ethylene Glycol	109.3	3.81	4"x1	87.5	2.52	4"x1	131.2	5.33	4"x1
PFI-0412N-4D1DZ-H2	Ethylene Glycol	108.2	6.17	4"x1	86.6	4.09	4"x1	129.9	8.65	4"x1
PFI-0412N-4D3DZ-H2	Ethylene Glycol	110.4	4.61	4"x1	88.3	3.05	4"x1	132.5	6.47	4"x1
PFI-0412N-4D2EZ-J2	Ethylene Glycol	109.3	5.02	4"x1	87.5	3.33	4"x1	131.2	7.04	4"x1
PFI-0412N-5D1EZ-J2	Ethylene Glycol	108.2	7.67	4"x1	86.6	5.08	4"x1	129.9	10.75	4"x1
PFI-0412N-6D1EZ-H2	Ethylene Glycol	108.2	9.16	4"x1	86.6	6.07	4"x1	129.9	12.85	4"x1
PFI-0412N-6D1EZ-J2	Ethylene Glycol	108.2	9.16	4"x1	86.6	6.07	4"x1	129.9	12.85	4"x1
PFI-0412N-3D4BT-G2	Ethylene Glycol	111.5	2.97	4"x1	89.2	1.97	4"x1	133.8	4.16	4"x1
PFI-0412N-3D4BT-H2	Ethylene Glycol	111.5	2.97	4"x1	89.2	1.97	4"x1	133.8	4.16	4"x1
PFI-0412N-3D3BT-J2	Ethylene Glycol	110.4	3.5	4"x1	88.3	2.32	4"x1	132.5	4.9	4"x1
PFI-0412N-4D4BT-G2	Ethylene Glycol	111.5	3.9	4"x1	89.2	2.58	4"x1	133.8	5.46	4"x1
PFI-0412N-4D3BT-H2	Ethylene Glycol	110.4	4.61	4"x1	88.3	3.05	4"x1	132.5	6.45	4"x1
PFI-0412N-4D3BT-J2	Ethylene Glycol	110.4	4.61	4"x1	88.3	3.05	4"x1	132.5	6.45	4"x1
PFI-0412N-5D2BT-G2	Ethylene Glycol	109.3	6.22	4"x1	87.5	4.12	4"x1	131.2	8.71	4"x1
PFI-0412N-6D2BT-G2	Ethylene Glycol	109.3	7.42	4"x1	87.5	4.92	4"x1	131.2	10.41	4"x1
PFI-0412N-6D1BT-H2	Ethylene Glycol	108.2	9.15	4"x1	86.6	6.06	4"x1	129.9	12.83	4"x1
PFI-0412N-6D2BT-J2	Ethylene Glycol	109.3	7.42	4"x1	87.5	4.92	4"x1	131.2	10.41	4"x1





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-2D3DS-H1	Ethylene Glycol	474.7	1.74	4"x2	379.7	1.15	4"x2	569.6	2.44	4"x2
PFI-0709N-3D1DS-H1	Ethylene Glycol	461.5	2.88	4"x2	369.2	1.91	4"x2	553.8	4.03	4"x2
PFI-0709N-3D1DS-J1	Ethylene Glycol	461.5	2.88	4"x2	369.2	1.91	4"x2	553.8	4.03	4"x2
PFI-0709N-3D3DS-J1	Ethylene Glycol	474.7	2.31	4"x2	379.7	1.53	4"x2	569.6	3.23	4"x2
PFI-0709N-3D1ES-J1	Ethylene Glycol	461.5	2.88	4"x2	369.2	1.91	4"x2	553.8	4.03	4"x2
PFI-0709N-3D2ES-J1	Ethylene Glycol	468.1	2.55	4"x2	374.5	1.69	4"x2	561.7	3.57	4"x2
PFI-0709N-3D1DS-K1	Ethylene Glycol	461.5	2.88	4"x2	369.2	1.91	4"x2	553.8	4.03	4"x2
PFI-0709N-3D2DS-K1	Ethylene Glycol	468.1	2.55	4"x2	374.5	1.69	4"x2	561.7	3.57	4"x2
PFI-0709N-3D2ES-L1	Ethylene Glycol	468.1	2.55	4"x2	374.5	1.69	4"x2	561.7	3.57	4"x2
PFI-0709N-4D4DS-J1	Ethylene Glycol	481.3	2.61	4"x2	385.0	1.73	4"x2	577.5	3.66	4"x2
PFI-0709N-4D2DS-K1	Ethylene Glycol	468.1	3.2	4"x2	374.5	2.12	4"x2	561.7	4.49	4"x2
PFI-0709N-4D1DS-L1	Ethylene Glycol	461.5	3.64	4"x2	369.2	2.41	4"x2	553.8	5.1	4"x2
PFI-0709N-5D4DS-K1	Ethylene Glycol	481.3	3.11	4"x2	385.0	2.06	4"x2	577.5	4.35	4"x2
PFI-0709N-5D1DS-L1	Ethylene Glycol	461.5	4.4	4"x2	369.2	2.92	4"x2	553.8	6.17	4"x2
PFI-0709N-5D2DS-L1	Ethylene Glycol	468.1	3.85	4"x2	374.5	2.55	4"x2	561.7	5.4	4"x2
PFI-0709N-5D3ES-L1	Ethylene Glycol	474.7	3.44	4"x2	379.7	2.27	4"x2	569.6	4.81	4"x2
PFI-0709N-6D1ES-H1	Ethylene Glycol	461.5	5.17	4"x2	369.2	3.42	4"x2	553.8	7.24	4"x2
PFI-0709N-6D1ES-J1	Ethylene Glycol	461.5	5.17	4"x2	369.2	3.42	4"x2	553.8	7.24	4"x2
PFI-0709N-6D1ES-K1	Ethylene Glycol	461.5	5.17	4"x2	369.2	3.42	4"x2	553.8	7.24	4"x2
PFI-0709N-6D2ES-L1	Ethylene Glycol	468.1	4.51	4"x2	374.5	2.98	4"x2	561.7	6.31	4"x2
PFI-0709N-6D1ES-M1	Ethylene Glycol	461.5	5.17	4"x2	369.2	3.42	4"x2	553.8	7.24	4"x2
PFI-0709N-3D4BS-J1	Ethylene Glycol	481.3	2.11	4"x2	385.0	1.4	4"x2	577.5	2.96	4"x2
PFI-0709N-3D4BS-K1	Ethylene Glycol	481.3	2.11	4"x2	385.0	1.4	4"x2	577.5	2.96	4"x2
PFI-0709N-3D4BS-M1	Ethylene Glycol	481.3	2.11	4"x2	385.0	1.4	4"x2	577.5	2.96	4"x2
PFI-0709N-4D2BS-H1	Ethylene Glycol	468.1	3.2	4"x2	374.5	2.12	4"x2	561.7	4.49	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-4D2BS-J1	Ethylene Glycol	468.1	3.2	4"x2	374.5	2.12	4"x2	561.7	4.49	4"x2
PFI-0709N-4D3BS-K1	Ethylene Glycol	474.7	2.87	4"x2	379.7	1.9	4"x2	569.6	4.02	4"x2
PFI-0709N-4D3BS-L1	Ethylene Glycol	474.7	2.87	4"x2	379.7	1.9	4"x2	569.6	4.02	4"x2
PFI-0709N-4D4BS-M1	Ethylene Glycol	481.3	2.61	4"x2	385.0	1.73	4"x2	577.5	3.66	4"x2
PFI-0709N-5D4BS-H1	Ethylene Glycol	481.3	3.11	4"x2	385.0	2.06	4"x2	577.5	4.35	4"x2
PFI-0709N-5D3BS-J1	Ethylene Glycol	474.7	3.44	4"x2	379.7	2.27	4"x2	569.6	4.81	4"x2
PFI-0709N-5D4BS-K1	Ethylene Glycol	481.3	3.11	4"x2	385.0	2.06	4"x2	577.5	4.35	4"x2
PFI-0709N-5D4BS-L1	Ethylene Glycol	481.3	3.11	4"x2	385.0	2.06	4"x2	577.5	4.35	4"x2
PFI-0709N-5D4BS-M1	Ethylene Glycol	481.3	3.11	4"x2	385.0	2.06	4"x2	577.5	4.35	4"x2
PFI-0709N-6D1BS-H1	Ethylene Glycol	461.5	5.17	4"x2	369.2	3.42	4"x2	553.8	7.24	4"x2
PFI-0709N-6D1BS-J1	Ethylene Glycol	461.5	5.17	4"x2	369.2	3.42	4"x2	553.8	7.24	4"x2
PFI-0709N-6D1BS-K1	Ethylene Glycol	461.5	5.17	4"x2	369.2	3.42	4"x2	553.8	7.24	4"x2
PFI-0709N-6D2BS-L1	Ethylene Glycol	468.1	4.51	4"x2	374.5	2.98	4"x2	561.7	6.31	4"x2
PFI-0709N-6D2BS-M1	Ethylene Glycol	468.1	4.51	4"x2	374.5	2.98	4"x2	561.7	6.31	4"x2
PFI-0709N-2D3DZ-H1	Ethylene Glycol	218.6	2.53	4"x2	174.9	1.67	4"x2	262.4	3.54	4"x2
PFI-0709N-3D1DZ-H1	Ethylene Glycol	215.3	4.61	4"x2	172.3	3.05	4"x2	258.4	6.46	4"x2
PFI-0709N-3D1DZ-J1	Ethylene Glycol	215.3	4.61	4"x2	172.3	3.05	4"x2	258.4	6.46	4"x2
PFI-0709N-3D3DZ-J1	Ethylene Glycol	218.6	3.5	4"x2	174.9	2.32	4"x2	262.4	4.9	4"x2
PFI-0709N-3D1EZ-J1	Ethylene Glycol	215.3	4.62	4"x2	172.3	3.06	4"x2	258.4	6.47	4"x2
PFI-0709N-3D2EZ-J1	Ethylene Glycol	217.0	3.99	4"x2	173.6	2.64	4"x2	260.4	5.59	4"x2
PFI-0709N-3D1DZ-K1	Ethylene Glycol	215.3	4.61	4"x2	172.3	3.05	4"x2	258.4	6.46	4"x2
PFI-0709N-3D2DZ-K1	Ethylene Glycol	217.0	3.98	4"x2	173.6	2.63	4"x2	260.4	5.57	4"x2
PFI-0709N-3D2EZ-L1	Ethylene Glycol	217.0	3.99	4"x2	173.6	2.64	4"x2	260.4	5.59	4"x2
PFI-0709N-4D4DZ-J1	Ethylene Glycol	220.3	3.98	4"x2	176.2	2.63	4"x2	264.3	5.57	4"x2
PFI-0709N-4D2DZ-K1	Ethylene Glycol	217.0	5.12	4"x2	173.6	3.39	4"x2	260.4	7.17	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-4D1DZ-L1	Ethylene Glycol	215.3	5.95	4"x2	172.3	3.94	4"x2	258.4	8.34	4"x2
PFI-0709N-5D4DZ-K1	Ethylene Glycol	220.3	4.83	4"x2	176.2	3.2	4"x2	264.3	6.76	4"x2
PFI-0709N-5D1DZ-L1	Ethylene Glycol	215.3	7.3	4"x2	172.3	4.84	4"x2	258.4	10.23	4"x2
PFI-0709N-5D2DZ-L1	Ethylene Glycol	217.0	6.25	4"x2	173.6	4.14	4"x2	260.4	8.76	4"x2
PFI-0709N-5D3EZ-L1	Ethylene Glycol	218.6	5.46	4"x2	174.9	3.62	4"x2	262.4	7.66	4"x2
PFI-0709N-6D1EZ-H1	Ethylene Glycol	215.3	8.66	4"x2	172.3	5.74	4"x2	258.4	12.14	4"x2
PFI-0709N-6D1EZ-J1	Ethylene Glycol	215.3	8.66	4"x2	172.3	5.74	4"x2	258.4	12.14	4"x2
PFI-0709N-6D1EZ-K1	Ethylene Glycol	215.3	8.66	4"x2	172.3	5.74	4"x2	258.4	12.14	4"x2
PFI-0709N-6D2EZ-L1	Ethylene Glycol	217.0	7.4	4"x2	173.6	4.9	4"x2	260.4	10.37	4"x2
PFI-0709N-6D1EZ-M1	Ethylene Glycol	215.3	8.66	4"x2	172.3	5.74	4"x2	258.4	12.14	4"x2
PFI-0709N-3D4BT-J1	Ethylene Glycol	220.3	3.11	4"x2	176.2	2.06	4"x2	264.3	4.35	4"x2
PFI-0709N-3D4BT-K1	Ethylene Glycol	220.3	3.11	4"x2	176.2	2.06	4"x2	264.3	4.35	4"x2
PFI-0709N-3D4BT-M1	Ethylene Glycol	220.3	3.11	4"x2	176.2	2.06	4"x2	264.3	4.35	4"x2
PFI-0709N-4D2BT-H1	Ethylene Glycol	217.0	5.09	4"x2	173.6	3.37	4"x2	260.4	7.13	4"x2
PFI-0709N-4D2BT-J1	Ethylene Glycol	217.0	5.09	4"x2	173.6	3.37	4"x2	260.4	7.13	4"x2
PFI-0709N-4D3BT-K1	Ethylene Glycol	218.6	4.45	4"x2	174.9	2.95	4"x2	262.4	6.24	4"x2
PFI-0709N-4D3BT-L1	Ethylene Glycol	218.6	4.45	4"x2	174.9	2.95	4"x2	262.4	6.24	4"x2
PFI-0709N-4D4BT-M1	Ethylene Glycol	220.3	3.95	4"x2	176.2	2.62	4"x2	264.3	5.53	4"x2
PFI-0709N-5D4BT-H1	Ethylene Glycol	220.3	4.8	4"x2	176.2	3.17	4"x2	264.3	6.72	4"x2
PFI-0709N-5D3BT-J1	Ethylene Glycol	218.6	5.42	4"x2	174.9	3.59	4"x2	262.4	7.6	4"x2
PFI-0709N-5D4BT-K1	Ethylene Glycol	220.3	4.8	4"x2	176.2	3.17	4"x2	264.3	6.72	4"x2
PFI-0709N-5D4BT-L1	Ethylene Glycol	220.3	4.8	4"x2	176.2	3.17	4"x2	264.3	6.72	4"x2
PFI-0709N-5D4BT-M1	Ethylene Glycol	220.3	4.8	4"x2	176.2	3.17	4"x2	264.3	6.72	4"x2
PFI-0709N-6D1BT-H1	Ethylene Glycol	215.3	8.61	4"x2	172.3	5.7	4"x2	258.4	12.07	4"x2
PFI-0709N-6D1BT-J1	Ethylene Glycol	215.3	8.61	4"x2	172.3	5.7	4"x2	258.4	12.07	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-6D1BT-K1	Ethylene Glycol	215.3	8.61	4"x2	172.3	5.7	4"x2	258.4	12.07	4"x2
PFI-0709N-6D1BT-L1	Ethylene Glycol	215.3	8.61	4"x2	172.3	5.7	4"x2	258.4	12.07	4"x2
PFI-0709N-6D2BT-M1	Ethylene Glycol	217.0	7.35	4"x2	173.6	4.87	4"x2	260.4	10.3	4"x2
PFI-0718N-2D2DS-J2	Ethylene Glycol	468.1	2.95	4"x2	374.5	1.95	4"x2	561.7	4.13	4"x2
PFI-0718N-2D3DS-K2	Ethylene Glycol	474.7	2.65	4"x2	379.7	1.76	4"x2	569.6	3.71	4"x2
PFI-0718N-3D1DS-H2	Ethylene Glycol	461.5	4.72	4"x2	369.2	3.13	4"x2	553.8	6.61	4"x2
PFI-0718N-3D1DS-J2	Ethylene Glycol	461.5	4.72	4"x2	369.2	3.13	4"x2	553.8	6.61	4"x2
PFI-0718N-3D2DS-J2	Ethylene Glycol	468.1	4.13	4"x2	374.5	2.73	4"x2	561.7	5.78	4"x2
PFI-0718N-3D2DS-K2	Ethylene Glycol	468.1	4.13	4"x2	374.5	2.73	4"x2	561.7	5.78	4"x2
PFI-0718N-3D3DS-L2	Ethylene Glycol	474.7	3.67	4"x2	379.7	2.43	4"x2	569.6	5.14	4"x2
PFI-0718N-3D4DS-M2	Ethylene Glycol	481.3	3.32	4"x2	385.0	2.2	4"x2	577.5	4.64	4"x2
PFI-0718N-4D1ES-H2	Ethylene Glycol	461.5	6.1	4"x2	369.2	4.04	4"x2	553.8	8.54	4"x2
PFI-0718N-4D2DS-J2	Ethylene Glycol	468.1	5.3	4"x2	374.5	3.51	4"x2	561.7	7.42	4"x2
PFI-0718N-4D3DS-K2	Ethylene Glycol	474.7	4.69	4"x2	379.7	3.11	4"x2	569.6	6.57	4"x2
PFI-0718N-4D2DS-L2	Ethylene Glycol	468.1	5.3	4"x2	374.5	3.51	4"x2	561.7	7.42	4"x2
PFI-0718N-4D2ES-L2	Ethylene Glycol	468.1	5.3	4"x2	374.5	3.51	4"x2	561.7	7.42	4"x2
PFI-0718N-4D3DS-M2	Ethylene Glycol	474.7	4.69	4"x2	379.7	3.11	4"x2	569.6	6.57	4"x2
PFI-0718N-4D2ES-M2	Ethylene Glycol	468.1	5.3	4"x2	374.5	3.51	4"x2	561.7	7.42	4"x2
PFI-0718N-5D1ES-J2	Ethylene Glycol	461.5	7.48	4"x2	369.2	4.95	4"x2	553.8	10.47	4"x2
PFI-0718N-5D1ES-M2	Ethylene Glycol	461.5	7.48	4"x2	369.2	4.95	4"x2	553.8	10.47	4"x2
PFI-0718N-6D1ES-H2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-6D1ES-J2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-6D1ES-K2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-6D1ES-L2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-6D2ES-M2	Ethylene Glycol	468.1	7.65	4"x2	374.5	5.07	4"x2	561.7	10.72	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0718N-3D4BS-H2	Ethylene Glycol	481.3	3.32	4"x2	385.0	2.2	4"x2	577.5	4.64	4"x2
PFI-0718N-3D4BS-J2	Ethylene Glycol	481.3	3.32	4"x2	385.0	2.2	4"x2	577.5	4.64	4"x2
PFI-0718N-3D4BS-K2	Ethylene Glycol	481.3	3.32	4"x2	385.0	2.2	4"x2	577.5	4.64	4"x2
PFI-0718N-3D4BS-L2	Ethylene Glycol	481.3	3.32	4"x2	385.0	2.2	4"x2	577.5	4.64	4"x2
PFI-0718N-3D4BS-M2	Ethylene Glycol	481.3	3.32	4"x2	385.0	2.2	4"x2	577.5	4.64	4"x2
PFI-0718N-4D2BS-H2	Ethylene Glycol	468.1	5.3	4"x2	374.5	3.51	4"x2	561.7	7.42	4"x2
PFI-0718N-4D4BS-J2	Ethylene Glycol	481.3	4.22	4"x2	385.0	2.79	4"x2	577.5	5.9	4"x2
PFI-0718N-4D4BS-K2	Ethylene Glycol	481.3	4.22	4"x2	385.0	2.79	4"x2	577.5	5.9	4"x2
PFI-0718N-4D4BS-L2	Ethylene Glycol	481.3	4.22	4"x2	385.0	2.79	4"x2	577.5	5.9	4"x2
PFI-0718N-4D4BS-M2	Ethylene Glycol	481.3	4.22	4"x2	385.0	2.79	4"x2	577.5	5.9	4"x2
PFI-0718N-5D3BS-H2	Ethylene Glycol	474.7	5.71	4"x2	379.7	3.78	4"x2	569.6	8	4"x2
PFI-0718N-5D3BS-J2	Ethylene Glycol	474.7	5.71	4"x2	379.7	3.78	4"x2	569.6	8	4"x2
PFI-0718N-5D3BS-K2	Ethylene Glycol	474.7	5.71	4"x2	379.7	3.78	4"x2	569.6	8	4"x2
PFI-0718N-5D4BS-L2	Ethylene Glycol	481.3	5.11	4"x2	385.0	3.39	4"x2	577.5	7.16	4"x2
PFI-0718N-5D4BS-M2	Ethylene Glycol	481.3	5.11	4"x2	385.0	3.39	4"x2	577.5	7.16	4"x2
PFI-0718N-6D1BS-H2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-6D1BS-J2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-6D1BS-K2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-6D1BS-L2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-6D1BS-M2	Ethylene Glycol	461.5	8.85	4"x2	369.2	5.86	4"x2	553.8	12.4	4"x2
PFI-0718N-2D2DZ-J2	Ethylene Glycol	217.0	4.67	4"x2	173.6	3.09	4"x2	260.4	6.54	4"x2
PFI-0718N-2D3DZ-K2	Ethylene Glycol	218.6	4.09	4"x2	174.9	2.71	4"x2	262.4	5.74	4"x2
PFI-0718N-3D1DZ-H2	Ethylene Glycol	215.3	7.85	4"x2	172.3	5.2	4"x2	258.4	11	4"x2
PFI-0718N-3D1DZ-J2	Ethylene Glycol	215.3	7.85	4"x2	172.3	5.2	4"x2	258.4	11	4"x2
PFI-0718N-3D2DZ-J2	Ethylene Glycol	217.0	6.71	4"x2	173.6	4.44	4"x2	260.4	9.41	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0718N-3D2DZ-K2	Ethylene Glycol	217.0	6.71	4"x2	173.6	4.44	4"x2	260.4	9.41	4"x2
PFI-0718N-3D3DZ-L2	Ethylene Glycol	218.6	5.84	4"x2	174.9	3.87	4"x2	262.4	8.19	4"x2
PFI-0718N-3D4DZ-M2	Ethylene Glycol	220.3	5.17	4"x2	176.2	3.42	4"x2	264.3	7.24	4"x2
PFI-0718N-4D1EZ-H2	Ethylene Glycol	215.3	10.29	4"x2	172.3	6.81	4"x2	258.4	14.42	4"x2
PFI-0718N-4D2DZ-J2	Ethylene Glycol	217.0	8.76	4"x2	173.6	5.8	4"x2	260.4	12.28	4"x2
PFI-0718N-4D3DZ-K2	Ethylene Glycol	218.6	7.6	4"x2	174.9	5.03	4"x2	262.4	10.66	4"x2
PFI-0718N-4D2DZ-L2	Ethylene Glycol	217.0	8.76	4"x2	173.6	5.8	4"x2	260.4	12.28	4"x2
PFI-0718N-4D2EZ-L2	Ethylene Glycol	217.0	8.77	4"x2	173.6	5.81	4"x2	260.4	12.29	4"x2
PFI-0718N-4D3DZ-M2	Ethylene Glycol	218.6	7.6	4"x2	174.9	5.03	4"x2	262.4	10.66	4"x2
PFI-0718N-4D2EZ-M2	Ethylene Glycol	217.0	8.77	4"x2	173.6	5.81	4"x2	260.4	12.29	4"x2
PFI-0718N-5D1EZ-J2	Ethylene Glycol	215.3	12.72	4"x2	172.3	8.42	4"x2	258.4	17.82	4"x2
PFI-0718N-5D1EZ-M2	Ethylene Glycol	215.3	12.72	4"x2	172.3	8.42	4"x2	258.4	17.82	4"x2
PFI-0718N-6D1EZ-H2	Ethylene Glycol	215.3	15.14	4"x2	172.3	10.03	4"x2	258.4	21.23	4"x2
PFI-0718N-6D1EZ-J2	Ethylene Glycol	215.3	15.14	4"x2	172.3	10.03	4"x2	258.4	21.23	4"x2
PFI-0718N-6D1EZ-K2	Ethylene Glycol	215.3	15.14	4"x2	172.3	10.03	4"x2	258.4	21.23	4"x2
PFI-0718N-6D1EZ-L2	Ethylene Glycol	215.3	15.14	4"x2	172.3	10.03	4"x2	258.4	21.23	4"x2
PFI-0718N-6D2EZ-M2	Ethylene Glycol	217.0	12.87	4"x2	173.6	8.52	4"x2	260.4	18.04	4"x2
PFI-0718N-3D4BT-H2	Ethylene Glycol	220.3	5.15	4"x2	176.2	3.41	4"x2	264.3	7.21	4"x2
PFI-0718N-3D4BT-J2	Ethylene Glycol	220.3	5.15	4"x2	176.2	3.41	4"x2	264.3	7.21	4"x2
PFI-0718N-3D4BT-K2	Ethylene Glycol	220.3	5.15	4"x2	176.2	3.41	4"x2	264.3	7.21	4"x2
PFI-0718N-3D4BT-L2	Ethylene Glycol	220.3	5.15	4"x2	176.2	3.41	4"x2	264.3	7.21	4"x2
PFI-0718N-3D4BT-M2	Ethylene Glycol	220.3	5.15	4"x2	176.2	3.41	4"x2	264.3	7.21	4"x2
PFI-0718N-4D2BT-H2	Ethylene Glycol	217.0	8.74	4"x2	173.6	5.78	4"x2	260.4	12.24	4"x2
PFI-0718N-4D4BT-J2	Ethylene Glycol	220.3	6.68	4"x2	176.2	4.42	4"x2	264.3	9.35	4"x2
PFI-0718N-4D4BT-K2	Ethylene Glycol	220.3	6.68	4"x2	176.2	4.42	4"x2	264.3	9.35	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0718N-4D4BT-L2	Ethylene Glycol	220.3	6.68	4"x2	176.2	4.42	4"x2	264.3	9.35	4"x2
PFI-0718N-4D4BT-M2	Ethylene Glycol	220.3	6.68	4"x2	176.2	4.42	4"x2	264.3	9.35	4"x2
PFI-0718N-5D3BT-H2	Ethylene Glycol	218.6	9.33	4"x2	174.9	6.18	4"x2	262.4	13.08	4"x2
PFI-0718N-5D3BT-J2	Ethylene Glycol	218.6	9.33	4"x2	174.9	6.18	4"x2	262.4	13.08	4"x2
PFI-0718N-5D3BT-K2	Ethylene Glycol	218.6	9.33	4"x2	174.9	6.18	4"x2	262.4	13.08	4"x2
PFI-0718N-5D4BT-L2	Ethylene Glycol	220.3	8.2	4"x2	176.2	5.43	4"x2	264.3	11.49	4"x2
PFI-0718N-5D4BT-M2	Ethylene Glycol	220.3	8.2	4"x2	176.2	5.43	4"x2	264.3	11.49	4"x2
PFI-0718N-6D1BT-H2	Ethylene Glycol	215.3	15.1	4"x2	172.3	10	4"x2	258.4	21.16	4"x2
PFI-0718N-6D1BT-J2	Ethylene Glycol	215.3	15.1	4"x2	172.3	10	4"x2	258.4	21.16	4"x2
PFI-0718N-6D1BT-K2	Ethylene Glycol	215.3	15.1	4"x2	172.3	10	4"x2	258.4	21.16	4"x2
PFI-0718N-6D1BT-L2	Ethylene Glycol	215.3	15.1	4"x2	172.3	10	4"x2	258.4	21.16	4"x2
PFI-0718N-6D1BT-M2	Ethylene Glycol	215.3	15.1	4"x2	172.3	10	4"x2	258.4	21.16	4"x2
PFI-1012N-2D2DS-J1	Ethylene Glycol	494.5	1.66	4"x2	395.6	1.1	4"x2	593.4	2.32	4"x2
PFI-1012N-2D4ES-K1	Ethylene Glycol	514.3	1.46	4"x2	411.4	0.97	4"x2	617.1	2.05	4"x2
PFI-1012N-2D2ES-L1	Ethylene Glycol	494.5	1.66	4"x2	395.6	1.1	4"x2	593.4	2.32	4"x2
PFI-1012N-2D4ES-M1	Ethylene Glycol	514.3	1.46	4"x2	411.4	0.97	4"x2	617.1	2.05	4"x2
PFI-1012N-2D4ES-N1	Ethylene Glycol	514.3	1.46	4"x2	411.4	0.97	4"x2	617.1	2.05	4"x2
PFI-1012N-3D1DS-K1	Ethylene Glycol	485.7	2.38	4"x2	388.5	1.58	4"x2	582.8	3.33	4"x2
PFI-1012N-3D1DS-L1	Ethylene Glycol	485.7	2.38	4"x2	388.5	1.58	4"x2	582.8	3.33	4"x2
PFI-1012N-3D4DS-L1	Ethylene Glycol	514.3	1.85	4"x2	411.4	1.23	4"x2	617.1	2.59	4"x2
PFI-1012N-3D2ES-M1	Ethylene Glycol	494.5	2.17	4"x2	395.6	1.43	4"x2	593.4	3.03	4"x2
PFI-1012N-3D1DS-N1	Ethylene Glycol	485.7	2.38	4"x2	388.5	1.58	4"x2	582.8	3.33	4"x2
PFI-1012N-3D3DS-N1	Ethylene Glycol	505.5	1.97	4"x2	404.4	1.3	4"x2	606.6	2.76	4"x2
PFI-1012N-3D1DS-O1	Ethylene Glycol	485.7	2.38	4"x2	388.5	1.58	4"x2	582.8	3.33	4"x2
PFI-1012N-3D4ES-O1	Ethylene Glycol	514.3	1.85	4"x2	411.4	1.23	4"x2	617.1	2.59	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-4D4ES-J1	Ethylene Glycol	514.3	2.24	4"x2	411.4	1.48	4"x2	617.1	3.13	4"x2
PFI-1012N-4D2DS-K1	Ethylene Glycol	494.5	2.67	4"x2	395.6	1.77	4"x2	593.4	3.74	4"x2
PFI-1012N-4D3DS-L1	Ethylene Glycol	505.5	2.4	4"x2	404.4	1.59	4"x2	606.6	3.36	4"x2
PFI-1012N-4D1DS-M1	Ethylene Glycol	485.7	2.97	4"x2	388.5	1.96	4"x2	582.8	4.15	4"x2
PFI-1012N-4D2ES-N1	Ethylene Glycol	494.5	2.67	4"x2	395.6	1.77	4"x2	593.4	3.74	4"x2
PFI-1012N-4D1DS-O1	Ethylene Glycol	485.7	2.97	4"x2	388.5	1.96	4"x2	582.8	4.15	4"x2
PFI-1012N-5D1DS-L1	Ethylene Glycol	485.7	3.55	4"x2	388.5	2.35	4"x2	582.8	4.97	4"x2
PFI-1012N-5D2DS-M1	Ethylene Glycol	494.5	3.18	4"x2	395.6	2.11	4"x2	593.4	4.45	4"x2
PFI-1012N-5D2DS-O1	Ethylene Glycol	494.5	3.18	4"x2	395.6	2.11	4"x2	593.4	4.45	4"x2
PFI-1012N-6D1ES-J1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1ES-K1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1DS-L1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1ES-L1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1ES-M1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1DS-N1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1ES-O1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-3D3BS-K1	Ethylene Glycol	505.5	1.97	4"x2	404.4	1.3	4"x2	606.6	2.76	4"x2
PFI-1012N-3D4BS-L1	Ethylene Glycol	514.3	1.85	4"x2	411.4	1.23	4"x2	617.1	2.59	4"x2
PFI-1012N-3D4BS-M1	Ethylene Glycol	514.3	1.85	4"x2	411.4	1.23	4"x2	617.1	2.59	4"x2
PFI-1012N-3D4BS-N1	Ethylene Glycol	514.3	1.85	4"x2	411.4	1.23	4"x2	617.1	2.59	4"x2
PFI-1012N-3D4BS-O1	Ethylene Glycol	514.3	1.85	4"x2	411.4	1.23	4"x2	617.1	2.59	4"x2
PFI-1012N-4D4BS-J1	Ethylene Glycol	514.3	2.24	4"x2	411.4	1.48	4"x2	617.1	3.13	4"x2
PFI-1012N-4D4BS-K1	Ethylene Glycol	514.3	2.24	4"x2	411.4	1.48	4"x2	617.1	3.13	4"x2
PFI-1012N-4D3BS-L1	Ethylene Glycol	505.5	2.4	4"x2	404.4	1.59	4"x2	606.6	3.36	4"x2
PFI-1012N-4D4BS-M1	Ethylene Glycol	514.3	2.24	4"x2	411.4	1.48	4"x2	617.1	3.13	4"x2





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-4D3BS-N1	Ethylene Glycol	505.5	2.4	4"x2	404.4	1.59	4"x2	606.6	3.36	4"x2
PFI-1012N-4D4BS-O1	Ethylene Glycol	514.3	2.24	4"x2	411.4	1.48	4"x2	617.1	3.13	4"x2
PFI-1012N-5D4BS-J1	Ethylene Glycol	514.3	2.63	4"x2	411.4	1.74	4"x2	617.1	3.68	4"x2
PFI-1012N-5D4BS-K1	Ethylene Glycol	514.3	2.63	4"x2	411.4	1.74	4"x2	617.1	3.68	4"x2
PFI-1012N-5D4BS-L1	Ethylene Glycol	514.3	2.63	4"x2	411.4	1.74	4"x2	617.1	3.68	4"x2
PFI-1012N-5D2BS-M1	Ethylene Glycol	494.5	3.18	4"x2	395.6	2.11	4"x2	593.4	4.45	4"x2
PFI-1012N-5D4BS-N1	Ethylene Glycol	514.3	2.63	4"x2	411.4	1.74	4"x2	617.1	3.68	4"x2
PFI-1012N-5D2BS-O1	Ethylene Glycol	494.5	3.18	4"x2	395.6	2.11	4"x2	593.4	4.45	4"x2
PFI-1012N-6D1BS-J1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1BS-K1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1BS-L1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1BS-M1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1BS-N1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-6D1BS-O1	Ethylene Glycol	485.7	4.13	4"x2	388.5	2.74	4"x2	582.8	5.79	4"x2
PFI-1012N-2D2DZ-J1	Ethylene Glycol	223.6	2.3	4"x2	178.9	1.52	4"x2	268.3	3.22	4"x2
PFI-1012N-2D4EZ-K1	Ethylene Glycol	228.5	1.88	4"x2	182.8	1.25	4"x2	274.2	2.64	4"x2
PFI-1012N-2D2EZ-L1	Ethylene Glycol	223.6	2.3	4"x2	178.9	1.52	4"x2	268.3	3.22	4"x2
PFI-1012N-2D4EZ-M1	Ethylene Glycol	228.5	1.88	4"x2	182.8	1.25	4"x2	274.2	2.64	4"x2
PFI-1012N-2D4EZ-N1	Ethylene Glycol	228.5	1.88	4"x2	182.8	1.25	4"x2	274.2	2.64	4"x2
PFI-1012N-3D1DZ-K1	Ethylene Glycol	221.4	3.56	4"x2	177.1	2.36	4"x2	265.7	4.99	4"x2
PFI-1012N-3D1DZ-L1	Ethylene Glycol	221.4	3.56	4"x2	177.1	2.36	4"x2	265.7	4.99	4"x2
PFI-1012N-3D4DZ-L1	Ethylene Glycol	228.5	2.5	4"x2	182.8	1.66	4"x2	274.2	3.51	4"x2
PFI-1012N-3D2EZ-M1	Ethylene Glycol	223.6	3.15	4"x2	178.9	2.08	4"x2	268.3	4.41	4"x2
PFI-1012N-3D1DZ-N1	Ethylene Glycol	221.4	3.56	4"x2	177.1	2.36	4"x2	265.7	4.99	4"x2
PFI-1012N-3D3DZ-N1	Ethylene Glycol	226.3	2.74	4"x2	181.1	1.82	4"x2	271.6	3.84	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-3D1DZ-O1	Ethylene Glycol	221.4	3.56	4"x2	177.1	2.36	4"x2	265.7	4.99	4"x2
PFI-1012N-3D4EZ-O1	Ethylene Glycol	228.5	2.51	4"x2	182.8	1.66	4"x2	274.2	3.52	4"x2
PFI-1012N-4D4EZ-J1	Ethylene Glycol	228.5	3.14	4"x2	182.8	2.08	4"x2	274.2	4.4	4"x2
PFI-1012N-4D2DZ-K1	Ethylene Glycol	223.6	3.98	4"x2	178.9	2.64	4"x2	268.3	5.58	4"x2
PFI-1012N-4D3DZ-L1	Ethylene Glycol	226.3	3.45	4"x2	181.1	2.29	4"x2	271.6	4.84	4"x2
PFI-1012N-4D1DZ-M1	Ethylene Glycol	221.4	4.55	4"x2	177.1	3.01	4"x2	265.7	6.37	4"x2
PFI-1012N-4D2EZ-N1	Ethylene Glycol	223.6	3.99	4"x2	178.9	2.64	4"x2	268.3	5.59	4"x2
PFI-1012N-4D1DZ-O1	Ethylene Glycol	221.4	4.55	4"x2	177.1	3.01	4"x2	265.7	6.37	4"x2
PFI-1012N-5D1DZ-L1	Ethylene Glycol	221.4	5.54	4"x2	177.1	3.66	4"x2	265.7	7.76	4"x2
PFI-1012N-5D2DZ-M1	Ethylene Glycol	223.6	4.83	4"x2	178.9	3.2	4"x2	268.3	6.76	4"x2
PFI-1012N-5D2DZ-O1	Ethylene Glycol	223.6	4.83	4"x2	178.9	3.2	4"x2	268.3	6.76	4"x2
PFI-1012N-6D1EZ-J1	Ethylene Glycol	221.4	6.54	4"x2	177.1	4.33	4"x2	265.7	9.16	4"x2
PFI-1012N-6D1EZ-K1	Ethylene Glycol	221.4	6.54	4"x2	177.1	4.33	4"x2	265.7	9.16	4"x2
PFI-1012N-6D1DZ-L1	Ethylene Glycol	221.4	6.53	4"x2	177.1	4.32	4"x2	265.7	9.15	4"x2
PFI-1012N-6D1EZ-L1	Ethylene Glycol	221.4	6.54	4"x2	177.1	4.33	4"x2	265.7	9.16	4"x2
PFI-1012N-6D1EZ-M1	Ethylene Glycol	221.4	6.54	4"x2	177.1	4.33	4"x2	265.7	9.16	4"x2
PFI-1012N-6D1DZ-N1	Ethylene Glycol	221.4	6.53	4"x2	177.1	4.32	4"x2	265.7	9.15	4"x2
PFI-1012N-6D1EZ-O1	Ethylene Glycol	221.4	6.54	4"x2	177.1	4.33	4"x2	265.7	9.16	4"x2
PFI-1012N-3D3BT-K1	Ethylene Glycol	226.3	2.72	4"x2	181.1	1.81	4"x2	271.6	3.82	4"x2
PFI-1012N-3D4BT-L1	Ethylene Glycol	228.5	2.48	4"x2	182.8	1.65	4"x2	274.2	3.48	4"x2
PFI-1012N-3D4BT-M1	Ethylene Glycol	228.5	2.48	4"x2	182.8	1.65	4"x2	274.2	3.48	4"x2
PFI-1012N-3D4BT-N1	Ethylene Glycol	228.5	2.48	4"x2	182.8	1.65	4"x2	274.2	3.48	4"x2
PFI-1012N-3D4BT-O1	Ethylene Glycol	228.5	2.48	4"x2	182.8	1.65	4"x2	274.2	3.48	4"x2
PFI-1012N-4D4BT-J1	Ethylene Glycol	228.5	3.11	4"x2	182.8	2.06	4"x2	274.2	4.35	4"x2
PFI-1012N-4D4BT-K1	Ethylene Glycol	228.5	3.11	4"x2	182.8	2.06	4"x2	274.2	4.35	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-4D3BT-L1	Ethylene Glycol	226.3	3.43	4"x2	181.1	2.27	4"x2	271.6	4.81	4"x2
PFI-1012N-4D4BT-M1	Ethylene Glycol	228.5	3.11	4"x2	182.8	2.06	4"x2	274.2	4.35	4"x2
PFI-1012N-4D3BT-N1	Ethylene Glycol	226.3	3.43	4"x2	181.1	2.27	4"x2	271.6	4.81	4"x2
PFI-1012N-4D4BT-O1	Ethylene Glycol	228.5	3.11	4"x2	182.8	2.06	4"x2	274.2	4.35	4"x2
PFI-1012N-5D4BT-J1	Ethylene Glycol	228.5	3.73	4"x2	182.8	2.47	4"x2	274.2	5.23	4"x2
PFI-1012N-5D4BT-K1	Ethylene Glycol	228.5	3.73	4"x2	182.8	2.47	4"x2	274.2	5.23	4"x2
PFI-1012N-5D4BT-L1	Ethylene Glycol	228.5	3.73	4"x2	182.8	2.47	4"x2	274.2	5.23	4"x2
PFI-1012N-5D2BT-M1	Ethylene Glycol	223.6	4.8	4"x2	178.9	3.18	4"x2	268.3	6.73	4"x2
PFI-1012N-5D4BT-N1	Ethylene Glycol	228.5	3.73	4"x2	182.8	2.47	4"x2	274.2	5.23	4"x2
PFI-1012N-5D2BT-O1	Ethylene Glycol	223.6	4.8	4"x2	178.9	3.18	4"x2	268.3	6.73	4"x2
PFI-1012N-6D1BT-J1	Ethylene Glycol	221.4	6.5	4"x2	177.1	4.3	4"x2	265.7	9.1	4"x2
PFI-1012N-6D1BT-K1	Ethylene Glycol	221.4	6.5	4"x2	177.1	4.3	4"x2	265.7	9.1	4"x2
PFI-1012N-6D1BT-L1	Ethylene Glycol	221.4	6.5	4"x2	177.1	4.3	4"x2	265.7	9.1	4"x2
PFI-1012N-6D2BT-M1	Ethylene Glycol	223.6	5.64	4"x2	178.9	3.74	4"x2	268.3	7.9	4"x2
PFI-1012N-6D1BT-N1	Ethylene Glycol	221.4	6.5	4"x2	177.1	4.3	4"x2	265.7	9.1	4"x2
PFI-1012N-6D1BT-O1	Ethylene Glycol	221.4	6.5	4"x2	177.1	4.3	4"x2	265.7	9.1	4"x2
PFI-1024N-2D2DS-J2	Ethylene Glycol	989.0	1.66	4"x4	791.2	1.1	4"x4	1186.7	2.32	4"x4
PFI-1024N-2D4ES-K2	Ethylene Glycol	1028.6	1.46	4"x4	822.8	0.97	4"x4	1234.3	2.05	4"x4
PFI-1024N-2D2ES-L2	Ethylene Glycol	989.0	1.66	4"x4	791.2	1.1	4"x4	1186.7	2.32	4"x4
PFI-1024N-2D4ES-M2	Ethylene Glycol	1028.6	1.46	4"x4	822.8	0.97	4"x4	1234.3	2.05	4"x4
PFI-1024N-2D4ES-N2	Ethylene Glycol	1028.6	1.46	4"x4	822.8	0.97	4"x4	1234.3	2.05	4"x4
PFI-1024N-3D1DS-K2	Ethylene Glycol	971.4	2.38	4"x4	777.1	1.58	4"x4	1165.6	3.33	4"x4
PFI-1024N-3D1DS-L2	Ethylene Glycol	971.4	2.38	4"x4	777.1	1.58	4"x4	1165.6	3.33	4"x4
PFI-1024N-3D4DS-L2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-1024N-3D2ES-M2	Ethylene Glycol	989.0	2.17	4"x4	791.2	1.43	4"x4	1186.7	3.03	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-3D1DS-N2	Ethylene Glycol	971.4	2.38	4"x4	777.1	1.58	4"x4	1165.6	3.33	4"x4
PFI-1024N-3D3DS-N2	Ethylene Glycol	1011.0	1.97	4"x4	808.8	1.3	4"x4	1213.1	2.76	4"x4
PFI-1024N-3D1DS-O2	Ethylene Glycol	971.4	2.38	4"x4	777.1	1.58	4"x4	1165.6	3.33	4"x4
PFI-1024N-3D4ES-O2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-1024N-4D4ES-J2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-1024N-4D2DS-K2	Ethylene Glycol	989.0	2.67	4"x4	791.2	1.77	4"x4	1186.7	3.74	4"x4
PFI-1024N-4D3DS-L2	Ethylene Glycol	1011.0	2.4	4"x4	808.8	1.59	4"x4	1213.1	3.36	4"x4
PFI-1024N-4D1DS-M2	Ethylene Glycol	971.4	2.97	4"x4	777.1	1.96	4"x4	1165.6	4.15	4"x4
PFI-1024N-4D2ES-N2	Ethylene Glycol	989.0	2.67	4"x4	791.2	1.77	4"x4	1186.7	3.74	4"x4
PFI-1024N-4D1DS-O2	Ethylene Glycol	971.4	2.97	4"x4	777.1	1.96	4"x4	1165.6	4.15	4"x4
PFI-1024N-5D1DS-L2	Ethylene Glycol	971.4	3.55	4"x4	777.1	2.35	4"x4	1165.6	4.97	4"x4
PFI-1024N-5D2DS-M2	Ethylene Glycol	989.0	3.18	4"x4	791.2	2.11	4"x4	1186.7	4.45	4"x4
PFI-1024N-5D2DS-O2	Ethylene Glycol	989.0	3.18	4"x4	791.2	2.11	4"x4	1186.7	4.45	4"x4
PFI-1024N-6D1ES-J2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1ES-K2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1DS-L2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1ES-L2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1ES-M2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1DS-N2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1ES-O2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-3D3BS-K2	Ethylene Glycol	1011.0	1.97	4"x4	808.8	1.3	4"x4	1213.1	2.76	4"x4
PFI-1024N-3D4BS-L2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-1024N-3D4BS-M2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-1024N-3D4BS-N2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-1024N-3D4BS-O2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-4D4BS-J2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-1024N-4D4BS-K2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-1024N-4D3BS-L2	Ethylene Glycol	1011.0	2.4	4"x4	808.8	1.59	4"x4	1213.1	3.36	4"x4
PFI-1024N-4D4BS-M2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-1024N-4D3BS-N2	Ethylene Glycol	1011.0	2.4	4"x4	808.8	1.59	4"x4	1213.1	3.36	4"x4
PFI-1024N-4D4BS-O2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-1024N-5D4BS-J2	Ethylene Glycol	1028.6	2.63	4"x4	822.8	1.74	4"x4	1234.3	3.68	4"x4
PFI-1024N-5D4BS-K2	Ethylene Glycol	1028.6	2.63	4"x4	822.8	1.74	4"x4	1234.3	3.68	4"x4
PFI-1024N-5D4BS-L2	Ethylene Glycol	1028.6	2.63	4"x4	822.8	1.74	4"x4	1234.3	3.68	4"x4
PFI-1024N-5D2BS-M2	Ethylene Glycol	989.0	3.18	4"x4	791.2	2.11	4"x4	1186.7	4.45	4"x4
PFI-1024N-5D4BS-N2	Ethylene Glycol	1028.6	2.63	4"x4	822.8	1.74	4"x4	1234.3	3.68	4"x4
PFI-1024N-5D2BS-O2	Ethylene Glycol	989.0	3.18	4"x4	791.2	2.11	4"x4	1186.7	4.45	4"x4
PFI-1024N-6D1BS-J2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1BS-K2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1BS-L2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1BS-M2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1BS-N2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-6D1BS-O2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-1024N-2D2DZ-J2	Ethylene Glycol	447.2	2.3	4"x4	357.7	1.52	4"x4	536.6	3.22	4"x4
PFI-1024N-2D4EZ-K2	Ethylene Glycol	457.1	1.88	4"x4	365.7	1.25	4"x4	548.5	2.64	4"x4
PFI-1024N-2D2EZ-L2	Ethylene Glycol	447.2	2.3	4"x4	357.7	1.52	4"x4	536.6	3.22	4"x4
PFI-1024N-2D4EZ-M2	Ethylene Glycol	457.1	1.88	4"x4	365.7	1.25	4"x4	548.5	2.64	4"x4
PFI-1024N-2D4EZ-N2	Ethylene Glycol	457.1	1.88	4"x4	365.7	1.25	4"x4	548.5	2.64	4"x4
PFI-1024N-3D1DZ-K2	Ethylene Glycol	442.8	3.56	4"x4	354.2	2.36	4"x4	531.3	4.98	4"x4
PFI-1024N-3D1DZ-L2	Ethylene Glycol	442.8	3.56	4"x4	354.2	2.36	4"x4	531.3	4.98	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-3D4DZ-L2	Ethylene Glycol	457.1	2.5	4"x4	365.7	1.66	4"x4	548.5	3.51	4"x4
PFI-1024N-3D2EZ-M2	Ethylene Glycol	447.2	3.15	4"x4	357.7	2.08	4"x4	536.6	4.41	4"x4
PFI-1024N-3D1DZ-N2	Ethylene Glycol	442.8	3.56	4"x4	354.2	2.36	4"x4	531.3	4.98	4"x4
PFI-1024N-3D3DZ-N2	Ethylene Glycol	452.7	2.74	4"x4	362.1	1.82	4"x4	543.2	3.84	4"x4
PFI-1024N-3D1DZ-O2	Ethylene Glycol	442.8	3.56	4"x4	354.2	2.36	4"x4	531.3	4.98	4"x4
PFI-1024N-3D4EZ-O2	Ethylene Glycol	457.1	2.51	4"x4	365.7	1.66	4"x4	548.5	3.52	4"x4
PFI-1024N-4D4EZ-J2	Ethylene Glycol	457.1	3.14	4"x4	365.7	2.08	4"x4	548.5	4.4	4"x4
PFI-1024N-4D2DZ-K2	Ethylene Glycol	447.2	3.98	4"x4	357.7	2.64	4"x4	536.6	5.58	4"x4
PFI-1024N-4D3DZ-L2	Ethylene Glycol	452.7	3.45	4"x4	362.1	2.29	4"x4	543.2	4.84	4"x4
PFI-1024N-4D1DZ-M2	Ethylene Glycol	442.8	4.55	4"x4	354.2	3.01	4"x4	531.3	6.37	4"x4
PFI-1024N-4D2EZ-N2	Ethylene Glycol	447.2	3.99	4"x4	357.7	2.64	4"x4	536.6	5.59	4"x4
PFI-1024N-4D1DZ-O2	Ethylene Glycol	442.8	4.55	4"x4	354.2	3.01	4"x4	531.3	6.37	4"x4
PFI-1024N-5D1DZ-L2	Ethylene Glycol	442.8	5.54	4"x4	354.2	3.66	4"x4	531.3	7.76	4"x4
PFI-1024N-5D2DZ-M2	Ethylene Glycol	447.2	4.83	4"x4	357.7	3.2	4"x4	536.6	6.76	4"x4
PFI-1024N-5D2DZ-O2	Ethylene Glycol	447.2	4.83	4"x4	357.7	3.2	4"x4	536.6	6.76	4"x4
PFI-1024N-6D1EZ-J2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-1024N-6D1EZ-K2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-1024N-6D1DZ-L2	Ethylene Glycol	442.8	6.53	4"x4	354.2	4.32	4"x4	531.3	9.14	4"x4
PFI-1024N-6D1EZ-L2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-1024N-6D1EZ-M2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-1024N-6D1DZ-N2	Ethylene Glycol	442.8	6.53	4"x4	354.2	4.32	4"x4	531.3	9.14	4"x4
PFI-1024N-6D1EZ-O2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-1024N-3D3BT-K2	Ethylene Glycol	452.7	2.73	4"x4	362.1	1.8	4"x4	543.2	3.82	4"x4
PFI-1024N-3D4BT-L2	Ethylene Glycol	457.1	2.49	4"x4	365.7	1.65	4"x4	548.5	3.48	4"x4
PFI-1024N-3D4BT-M2	Ethylene Glycol	457.1	2.49	4"x4	365.7	1.65	4"x4	548.5	3.48	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-3D4BT-N2	Ethylene Glycol	457.1	2.49	4"x4	365.7	1.65	4"x4	548.5	3.48	4"x4
PFI-1024N-3D4BT-O2	Ethylene Glycol	457.1	2.49	4"x4	365.7	1.65	4"x4	548.5	3.48	4"x4
PFI-1024N-4D4BT-J2	Ethylene Glycol	457.1	3.11	4"x4	365.7	2.06	4"x4	548.5	4.35	4"x4
PFI-1024N-4D4BT-K2	Ethylene Glycol	457.1	3.11	4"x4	365.7	2.06	4"x4	548.5	4.35	4"x4
PFI-1024N-4D3BT-L2	Ethylene Glycol	452.7	3.43	4"x4	362.1	2.27	4"x4	543.2	4.81	4"x4
PFI-1024N-4D4BT-M2	Ethylene Glycol	457.1	3.11	4"x4	365.7	2.06	4"x4	548.5	4.35	4"x4
PFI-1024N-4D3BT-N2	Ethylene Glycol	452.7	3.43	4"x4	362.1	2.27	4"x4	543.2	4.81	4"x4
PFI-1024N-4D4BT-O2	Ethylene Glycol	457.1	3.11	4"x4	365.7	2.06	4"x4	548.5	4.35	4"x4
PFI-1024N-5D4BT-J2	Ethylene Glycol	457.1	3.73	4"x4	365.7	2.47	4"x4	548.5	5.23	4"x4
PFI-1024N-5D4BT-K2	Ethylene Glycol	457.1	3.73	4"x4	365.7	2.47	4"x4	548.5	5.23	4"x4
PFI-1024N-5D4BT-L2	Ethylene Glycol	457.1	3.73	4"x4	365.7	2.47	4"x4	548.5	5.23	4"x4
PFI-1024N-5D2BT-M2	Ethylene Glycol	447.2	4.8	4"x4	357.7	3.18	4"x4	536.6	6.73	4"x4
PFI-1024N-5D4BT-N2	Ethylene Glycol	457.1	3.73	4"x4	365.7	2.47	4"x4	548.5	5.23	4"x4
PFI-1024N-5D2BT-O2	Ethylene Glycol	447.2	4.8	4"x4	357.7	3.18	4"x4	536.6	6.73	4"x4
PFI-1024N-6D1BT-J2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-1024N-6D1BT-K2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-1024N-6D1BT-L2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-1024N-6D2BT-M2	Ethylene Glycol	447.2	5.64	4"x4	357.7	3.73	4"x4	536.6	7.9	4"x4
PFI-1024N-6D1BT-N2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-1024N-6D1BT-O2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-2012N-2D2DS-J2	Ethylene Glycol	989.0	1.66	4"x4	791.2	1.1	4"x4	1186.7	2.32	4"x4
PFI-2012N-2D4ES-K2	Ethylene Glycol	1028.6	1.46	4"x4	822.8	0.97	4"x4	1234.3	2.05	4"x4
PFI-2012N-2D2ES-L2	Ethylene Glycol	989.0	1.66	4"x4	791.2	1.1	4"x4	1186.7	2.32	4"x4
PFI-2012N-2D4ES-M2	Ethylene Glycol	1028.6	1.46	4"x4	822.8	0.97	4"x4	1234.3	2.05	4"x4
PFI-2012N-2D4ES-N2	Ethylene Glycol	1028.6	1.46	4"x4	822.8	0.97	4"x4	1234.3	2.05	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-3D1DS-K2	Ethylene Glycol	971.4	2.38	4"x4	777.1	1.58	4"x4	1165.6	3.33	4"x4
PFI-2012N-3D1DS-L2	Ethylene Glycol	971.4	2.38	4"x4	777.1	1.58	4"x4	1165.6	3.33	4"x4
PFI-2012N-3D4DS-L2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-2012N-3D2ES-M2	Ethylene Glycol	989.0	2.17	4"x4	791.2	1.43	4"x4	1186.7	3.03	4"x4
PFI-2012N-3D1DS-N2	Ethylene Glycol	971.4	2.38	4"x4	777.1	1.58	4"x4	1165.6	3.33	4"x4
PFI-2012N-3D3DS-N2	Ethylene Glycol	1011.0	1.97	4"x4	808.8	1.3	4"x4	1213.1	2.76	4"x4
PFI-2012N-3D1DS-O2	Ethylene Glycol	971.4	2.38	4"x4	777.1	1.58	4"x4	1165.6	3.33	4"x4
PFI-2012N-3D4ES-O2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-2012N-4D4ES-J2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-2012N-4D2DS-K2	Ethylene Glycol	989.0	2.67	4"x4	791.2	1.77	4"x4	1186.7	3.74	4"x4
PFI-2012N-4D3DS-L2	Ethylene Glycol	1011.0	2.4	4"x4	808.8	1.59	4"x4	1213.1	3.36	4"x4
PFI-2012N-4D1DS-M2	Ethylene Glycol	971.4	2.97	4"x4	777.1	1.96	4"x4	1165.6	4.15	4"x4
PFI-2012N-4D2ES-N2	Ethylene Glycol	989.0	2.67	4"x4	791.2	1.77	4"x4	1186.7	3.74	4"x4
PFI-2012N-4D1DS-O2	Ethylene Glycol	971.4	2.97	4"x4	777.1	1.96	4"x4	1165.6	4.15	4"x4
PFI-2012N-5D1DS-L2	Ethylene Glycol	971.4	3.55	4"x4	777.1	2.35	4"x4	1165.6	4.97	4"x4
PFI-2012N-5D2DS-M2	Ethylene Glycol	989.0	3.18	4"x4	791.2	2.11	4"x4	1186.7	4.45	4"x4
PFI-2012N-5D2DS-O2	Ethylene Glycol	989.0	3.18	4"x4	791.2	2.11	4"x4	1186.7	4.45	4"x4
PFI-2012N-6D1ES-J2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1ES-K2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1DS-L2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1ES-L2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1ES-M2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1DS-N2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1ES-O2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-3D3BS-K2	Ethylene Glycol	1011.0	1.97	4"x4	808.8	1.3	4"x4	1213.1	2.76	4"x4





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-3D4BS-L2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-2012N-3D4BS-M2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-2012N-3D4BS-N2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-2012N-3D4BS-O2	Ethylene Glycol	1028.6	1.85	4"x4	822.8	1.23	4"x4	1234.3	2.59	4"x4
PFI-2012N-4D4BS-J2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-2012N-4D4BS-K2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-2012N-4D3BS-L2	Ethylene Glycol	1011.0	2.4	4"x4	808.8	1.59	4"x4	1213.1	3.36	4"x4
PFI-2012N-4D4BS-M2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-2012N-4D3BS-N2	Ethylene Glycol	1011.0	2.4	4"x4	808.8	1.59	4"x4	1213.1	3.36	4"x4
PFI-2012N-4D4BS-O2	Ethylene Glycol	1028.6	2.24	4"x4	822.8	1.48	4"x4	1234.3	3.13	4"x4
PFI-2012N-5D4BS-J2	Ethylene Glycol	1028.6	2.63	4"x4	822.8	1.74	4"x4	1234.3	3.68	4"x4
PFI-2012N-5D4BS-K2	Ethylene Glycol	1028.6	2.63	4"x4	822.8	1.74	4"x4	1234.3	3.68	4"x4
PFI-2012N-5D4BS-L2	Ethylene Glycol	1028.6	2.63	4"x4	822.8	1.74	4"x4	1234.3	3.68	4"x4
PFI-2012N-5D2BS-M2	Ethylene Glycol	989.0	3.18	4"x4	791.2	2.11	4"x4	1186.7	4.45	4"x4
PFI-2012N-5D4BS-N2	Ethylene Glycol	1028.6	2.63	4"x4	822.8	1.74	4"x4	1234.3	3.68	4"x4
PFI-2012N-5D2BS-O2	Ethylene Glycol	989.0	3.18	4"x4	791.2	2.11	4"x4	1186.7	4.45	4"x4
PFI-2012N-6D1BS-J2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1BS-K2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1BS-L2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1BS-M2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1BS-N2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-6D1BS-O2	Ethylene Glycol	971.4	4.13	4"x4	777.1	2.74	4"x4	1165.6	5.79	4"x4
PFI-2012N-2D2DZ-J2	Ethylene Glycol	447.2	2.3	4"x4	357.7	1.52	4"x4	536.6	3.22	4"x4
PFI-2012N-2D4EZ-K2	Ethylene Glycol	457.1	1.88	4"x4	365.7	1.25	4"x4	548.5	2.64	4"x4
PFI-2012N-2D2EZ-L2	Ethylene Glycol	447.2	2.3	4"x4	357.7	1.52	4"x4	536.6	3.22	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-2D4EZ-M2	Ethylene Glycol	457.1	1.88	4"x4	365.7	1.25	4"x4	548.5	2.64	4"x4
PFI-2012N-2D4EZ-N2	Ethylene Glycol	457.1	1.88	4"x4	365.7	1.25	4"x4	548.5	2.64	4"x4
PFI-2012N-3D1DZ-K2	Ethylene Glycol	442.8	3.56	4"x4	354.2	2.36	4"x4	531.3	4.98	4"x4
PFI-2012N-3D1DZ-L2	Ethylene Glycol	442.8	3.56	4"x4	354.2	2.36	4"x4	531.3	4.98	4"x4
PFI-2012N-3D4DZ-L2	Ethylene Glycol	457.1	2.5	4"x4	365.7	1.66	4"x4	548.5	3.51	4"x4
PFI-2012N-3D2EZ-M2	Ethylene Glycol	447.2	3.15	4"x4	357.7	2.08	4"x4	536.6	4.41	4"x4
PFI-2012N-3D1DZ-N2	Ethylene Glycol	442.8	3.56	4"x4	354.2	2.36	4"x4	531.3	4.98	4"x4
PFI-2012N-3D3DZ-N2	Ethylene Glycol	452.7	2.74	4"x4	362.1	1.82	4"x4	543.2	3.84	4"x4
PFI-2012N-3D1DZ-O2	Ethylene Glycol	442.8	3.56	4"x4	354.2	2.36	4"x4	531.3	4.98	4"x4
PFI-2012N-3D4EZ-O2	Ethylene Glycol	457.1	2.51	4"x4	365.7	1.66	4"x4	548.5	3.52	4"x4
PFI-2012N-4D4EZ-J2	Ethylene Glycol	457.1	3.14	4"x4	365.7	2.08	4"x4	548.5	4.4	4"x4
PFI-2012N-4D2DZ-K2	Ethylene Glycol	447.2	3.98	4"x4	357.7	2.64	4"x4	536.6	5.58	4"x4
PFI-2012N-4D3DZ-L2	Ethylene Glycol	452.7	3.45	4"x4	362.1	2.29	4"x4	543.2	4.84	4"x4
PFI-2012N-4D1DZ-M2	Ethylene Glycol	442.8	4.55	4"x4	354.2	3.01	4"x4	531.3	6.37	4"x4
PFI-2012N-4D2EZ-N2	Ethylene Glycol	447.2	3.99	4"x4	357.7	2.64	4"x4	536.6	5.59	4"x4
PFI-2012N-4D1DZ-O2	Ethylene Glycol	442.8	4.55	4"x4	354.2	3.01	4"x4	531.3	6.37	4"x4
PFI-2012N-5D1DZ-L2	Ethylene Glycol	442.8	5.54	4"x4	354.2	3.66	4"x4	531.3	7.76	4"x4
PFI-2012N-5D2DZ-M2	Ethylene Glycol	447.2	4.83	4"x4	357.7	3.2	4"x4	536.6	6.76	4"x4
PFI-2012N-5D2DZ-O2	Ethylene Glycol	447.2	4.83	4"x4	357.7	3.2	4"x4	536.6	6.76	4"x4
PFI-2012N-6D1EZ-J2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-2012N-6D1EZ-K2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-2012N-6D1DZ-L2	Ethylene Glycol	442.8	6.53	4"x4	354.2	4.32	4"x4	531.3	9.14	4"x4
PFI-2012N-6D1EZ-L2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-2012N-6D1EZ-M2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-2012N-6D1DZ-N2	Ethylene Glycol	442.8	6.53	4"x4	354.2	4.32	4"x4	531.3	9.14	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-6D1EZ-O2	Ethylene Glycol	442.8	6.54	4"x4	354.2	4.33	4"x4	531.3	9.16	4"x4
PFI-2012N-3D3BT-K2	Ethylene Glycol	452.7	2.73	4"x4	362.1	1.8	4"x4	543.2	3.82	4"x4
PFI-2012N-3D4BT-L2	Ethylene Glycol	457.1	2.49	4"x4	365.7	1.65	4"x4	548.5	3.48	4"x4
PFI-2012N-3D4BT-M2	Ethylene Glycol	457.1	2.49	4"x4	365.7	1.65	4"x4	548.5	3.48	4"x4
PFI-2012N-3D4BT-N2	Ethylene Glycol	457.1	2.49	4"x4	365.7	1.65	4"x4	548.5	3.48	4"x4
PFI-2012N-3D4BT-O2	Ethylene Glycol	457.1	2.49	4"x4	365.7	1.65	4"x4	548.5	3.48	4"x4
PFI-2012N-4D4BT-J2	Ethylene Glycol	457.1	3.11	4"x4	365.7	2.06	4"x4	548.5	4.35	4"x4
PFI-2012N-4D4BT-K2	Ethylene Glycol	457.1	3.11	4"x4	365.7	2.06	4"x4	548.5	4.35	4"x4
PFI-2012N-4D3BT-L2	Ethylene Glycol	452.7	3.43	4"x4	362.1	2.27	4"x4	543.2	4.81	4"x4
PFI-2012N-4D4BT-M2	Ethylene Glycol	457.1	3.11	4"x4	365.7	2.06	4"x4	548.5	4.35	4"x4
PFI-2012N-4D3BT-N2	Ethylene Glycol	452.7	3.43	4"x4	362.1	2.27	4"x4	543.2	4.81	4"x4
PFI-2012N-4D4BT-O2	Ethylene Glycol	457.1	3.11	4"x4	365.7	2.06	4"x4	548.5	4.35	4"x4
PFI-2012N-5D4BT-J2	Ethylene Glycol	457.1	3.73	4"x4	365.7	2.47	4"x4	548.5	5.23	4"x4
PFI-2012N-5D4BT-K2	Ethylene Glycol	457.1	3.73	4"x4	365.7	2.47	4"x4	548.5	5.23	4"x4
PFI-2012N-5D4BT-L2	Ethylene Glycol	457.1	3.73	4"x4	365.7	2.47	4"x4	548.5	5.23	4"x4
PFI-2012N-5D2BT-M2	Ethylene Glycol	447.2	4.8	4"x4	357.7	3.18	4"x4	536.6	6.73	4"x4
PFI-2012N-5D4BT-N2	Ethylene Glycol	457.1	3.73	4"x4	365.7	2.47	4"x4	548.5	5.23	4"x4
PFI-2012N-5D2BT-O2	Ethylene Glycol	447.2	4.8	4"x4	357.7	3.18	4"x4	536.6	6.73	4"x4
PFI-2012N-6D1BT-J2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-2012N-6D1BT-K2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-2012N-6D1BT-L2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-2012N-6D2BT-M2	Ethylene Glycol	447.2	5.64	4"x4	357.7	3.73	4"x4	536.6	7.9	4"x4
PFI-2012N-6D1BT-N2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-2012N-6D1BT-O2	Ethylene Glycol	442.8	6.5	4"x4	354.2	4.3	4"x4	531.3	9.1	4"x4
PFI-1212N-2D4DS-K1	Ethylene Glycol	540.7	1.34	4"x2	432.5	0.89	4"x2	648.8	1.87	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-2D3ES-L1	Ethylene Glycol	527.5	1.39	4"x2	422.0	0.92	4"x2	633.0	1.94	4"x2
PFI-1212N-2D4DS-M1	Ethylene Glycol	540.7	1.34	4"x2	432.5	0.89	4"x2	648.8	1.87	4"x2
PFI-1212N-2D4ES-M1	Ethylene Glycol	540.7	1.34	4"x2	432.5	0.89	4"x2	648.8	1.87	4"x2
PFI-1212N-2D4ES-N1	Ethylene Glycol	540.7	1.34	4"x2	432.5	0.89	4"x2	648.8	1.87	4"x2
PFI-1212N-2D4ES-O1	Ethylene Glycol	540.7	1.34	4"x2	432.5	0.89	4"x2	648.8	1.87	4"x2
PFI-1212N-3D2DS-L1	Ethylene Glycol	516.5	1.83	4"x2	413.2	1.21	4"x2	619.8	2.56	4"x2
PFI-1212N-3D3DS-M1	Ethylene Glycol	527.5	1.72	4"x2	422.0	1.14	4"x2	633.0	2.41	4"x2
PFI-1212N-3D2ES-M1	Ethylene Glycol	516.5	1.83	4"x2	413.2	1.21	4"x2	619.8	2.56	4"x2
PFI-1212N-3D2DS-N1	Ethylene Glycol	516.5	1.83	4"x2	413.2	1.21	4"x2	619.8	2.56	4"x2
PFI-1212N-3D2ES-N1	Ethylene Glycol	516.5	1.83	4"x2	413.2	1.21	4"x2	619.8	2.56	4"x2
PFI-1212N-3D4ES-O1	Ethylene Glycol	540.7	1.63	4"x2	432.5	1.08	4"x2	648.8	2.28	4"x2
PFI-1212N-3D1DS-P1	Ethylene Glycol	505.5	1.97	4"x2	404.4	1.3	4"x2	606.6	2.76	4"x2
PFI-1212N-4D1ES-K1	Ethylene Glycol	505.5	2.4	4"x2	404.4	1.59	4"x2	606.6	3.36	4"x2
PFI-1212N-4D3ES-M1	Ethylene Glycol	527.5	2.05	4"x2	422.0	1.36	4"x2	633.0	2.88	4"x2
PFI-1212N-4D2DS-N1	Ethylene Glycol	516.5	2.2	4"x2	413.2	1.46	4"x2	619.8	3.08	4"x2
PFI-1212N-4D3DS-P1	Ethylene Glycol	527.5	2.05	4"x2	422.0	1.36	4"x2	633.0	2.88	4"x2
PFI-1212N-5D2ES-K1	Ethylene Glycol	516.5	2.58	4"x2	413.2	1.71	4"x2	619.8	3.61	4"x2
PFI-1212N-5D2ES-L1	Ethylene Glycol	516.5	2.58	4"x2	413.2	1.71	4"x2	619.8	3.61	4"x2
PFI-1212N-5D2DS-N1	Ethylene Glycol	516.5	2.58	4"x2	413.2	1.71	4"x2	619.8	3.61	4"x2
PFI-1212N-5D1DS-O1	Ethylene Glycol	505.5	2.83	4"x2	404.4	1.88	4"x2	606.6	3.97	4"x2
PFI-1212N-5D4DS-O1	Ethylene Glycol	540.7	2.22	4"x2	432.5	1.47	4"x2	648.8	3.1	4"x2
PFI-1212N-5D2ES-P1	Ethylene Glycol	516.5	2.58	4"x2	413.2	1.71	4"x2	619.8	3.61	4"x2
PFI-1212N-6D1ES-L1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-6D1ES-M1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-6D1ES-N1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-6D1ES-O1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-6D1ES-P1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-3D3BS-L1	Ethylene Glycol	527.5	1.72	4"x2	422.0	1.14	4"x2	633.0	2.41	4"x2
PFI-1212N-3D4BS-N1	Ethylene Glycol	540.7	1.63	4"x2	432.5	1.08	4"x2	648.8	2.28	4"x2
PFI-1212N-3D4BS-O1	Ethylene Glycol	540.7	1.63	4"x2	432.5	1.08	4"x2	648.8	2.28	4"x2
PFI-1212N-4D4BS-K1	Ethylene Glycol	540.7	1.92	4"x2	432.5	1.27	4"x2	648.8	2.69	4"x2
PFI-1212N-4D3BS-L1	Ethylene Glycol	527.5	2.05	4"x2	422.0	1.36	4"x2	633.0	2.88	4"x2
PFI-1212N-4D4BS-M1	Ethylene Glycol	540.7	1.92	4"x2	432.5	1.27	4"x2	648.8	2.69	4"x2
PFI-1212N-4D3BS-N1	Ethylene Glycol	527.5	2.05	4"x2	422.0	1.36	4"x2	633.0	2.88	4"x2
PFI-1212N-4D4BS-O1	Ethylene Glycol	540.7	1.92	4"x2	432.5	1.27	4"x2	648.8	2.69	4"x2
PFI-1212N-4D4BS-P1	Ethylene Glycol	540.7	1.92	4"x2	432.5	1.27	4"x2	648.8	2.69	4"x2
PFI-1212N-5D2BS-K1	Ethylene Glycol	516.5	2.58	4"x2	413.2	1.71	4"x2	619.8	3.61	4"x2
PFI-1212N-5D3BS-L1	Ethylene Glycol	527.5	2.39	4"x2	422.0	1.58	4"x2	633.0	3.35	4"x2
PFI-1212N-5D2BS-M1	Ethylene Glycol	516.5	2.58	4"x2	413.2	1.71	4"x2	619.8	3.61	4"x2
PFI-1212N-5D2BS-N1	Ethylene Glycol	516.5	2.58	4"x2	413.2	1.71	4"x2	619.8	3.61	4"x2
PFI-1212N-5D3BS-O1	Ethylene Glycol	527.5	2.39	4"x2	422.0	1.58	4"x2	633.0	3.35	4"x2
PFI-1212N-5D2BS-P1	Ethylene Glycol	516.5	2.58	4"x2	413.2	1.71	4"x2	619.8	3.61	4"x2
PFI-1212N-6D1BS-K1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-6D1BS-L1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-6D1BS-M1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-6D1BS-N1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-6D1BS-O1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-6D1BS-P1	Ethylene Glycol	505.5	3.27	4"x2	404.4	2.16	4"x2	606.6	4.58	4"x2
PFI-1212N-2D4DZ-K1	Ethylene Glycol	235.1	1.58	4"x2	188.1	1.05	4"x2	282.2	2.22	4"x2
PFI-1212N-2D3EZ-L1	Ethylene Glycol	231.8	1.72	4"x2	185.5	1.14	4"x2	278.2	2.4	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-2D4DZ-M1	Ethylene Glycol	235.1	1.58	4"x2	188.1	1.05	4"x2	282.2	2.22	4"x2
PFI-1212N-2D4EZ-M1	Ethylene Glycol	235.1	1.59	4"x2	188.1	1.05	4"x2	282.2	2.22	4"x2
PFI-1212N-2D4EZ-N1	Ethylene Glycol	235.1	1.59	4"x2	188.1	1.05	4"x2	282.2	2.22	4"x2
PFI-1212N-2D4EZ-O1	Ethylene Glycol	235.1	1.59	4"x2	188.1	1.05	4"x2	282.2	2.22	4"x2
PFI-1212N-3D2DZ-L1	Ethylene Glycol	229.1	2.46	4"x2	183.3	1.63	4"x2	274.9	3.45	4"x2
PFI-1212N-3D3DZ-M1	Ethylene Glycol	231.8	2.24	4"x2	185.5	1.48	4"x2	278.2	3.14	4"x2
PFI-1212N-3D2EZ-M1	Ethylene Glycol	229.1	2.47	4"x2	183.3	1.64	4"x2	274.9	3.46	4"x2
PFI-1212N-3D2DZ-N1	Ethylene Glycol	229.1	2.46	4"x2	183.3	1.63	4"x2	274.9	3.45	4"x2
PFI-1212N-3D2EZ-N1	Ethylene Glycol	229.1	2.47	4"x2	183.3	1.64	4"x2	274.9	3.46	4"x2
PFI-1212N-3D4EZ-O1	Ethylene Glycol	235.1	2.04	4"x2	188.1	1.35	4"x2	282.2	2.87	4"x2
PFI-1212N-3D1DZ-P1	Ethylene Glycol	226.3	2.75	4"x2	181.1	1.82	4"x2	271.6	3.86	4"x2
PFI-1212N-4D1EZ-K1	Ethylene Glycol	226.3	3.47	4"x2	181.1	2.3	4"x2	271.6	4.87	4"x2
PFI-1212N-4D3EZ-M1	Ethylene Glycol	231.8	2.78	4"x2	185.5	1.84	4"x2	278.2	3.89	4"x2
PFI-1212N-4D2DZ-N1	Ethylene Glycol	229.1	3.07	4"x2	183.3	2.03	4"x2	274.9	4.3	4"x2
PFI-1212N-4D3DZ-P1	Ethylene Glycol	231.8	2.77	4"x2	185.5	1.83	4"x2	278.2	3.88	4"x2
PFI-1212N-5D2EZ-K1	Ethylene Glycol	229.1	3.69	4"x2	183.3	2.44	4"x2	274.9	5.17	4"x2
PFI-1212N-5D2EZ-L1	Ethylene Glycol	229.1	3.69	4"x2	183.3	2.44	4"x2	274.9	5.17	4"x2
PFI-1212N-5D2DZ-N1	Ethylene Glycol	229.1	3.68	4"x2	183.3	2.44	4"x2	274.9	5.16	4"x2
PFI-1212N-5D1DZ-O1	Ethylene Glycol	226.3	4.17	4"x2	181.1	2.76	4"x2	271.6	5.85	4"x2
PFI-1212N-5D4DZ-O1	Ethylene Glycol	235.1	2.95	4"x2	188.1	1.95	4"x2	282.2	4.14	4"x2
PFI-1212N-5D2EZ-P1	Ethylene Glycol	229.1	3.69	4"x2	183.3	2.44	4"x2	274.9	5.17	4"x2
PFI-1212N-6D1EZ-L1	Ethylene Glycol	226.3	4.89	4"x2	181.1	3.24	4"x2	271.6	6.86	4"x2
PFI-1212N-6D1EZ-M1	Ethylene Glycol	226.3	4.89	4"x2	181.1	3.24	4"x2	271.6	6.86	4"x2
PFI-1212N-6D1EZ-N1	Ethylene Glycol	226.3	4.89	4"x2	181.1	3.24	4"x2	271.6	6.86	4"x2
PFI-1212N-6D1EZ-O1	Ethylene Glycol	226.3	4.89	4"x2	181.1	3.24	4"x2	271.6	6.86	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-6D1EZ-P1	Ethylene Glycol	426.3	15.8	4"x2	341.0	10.45	4"x2	511.5	22.15	4"x2
PFI-1212N-3D3BT-L1	Ethylene Glycol	231.8	2.22	4"x2	185.5	1.47	4"x2	278.2	3.11	4"x2
PFI-1212N-3D4BT-N1	Ethylene Glycol	235.1	2.02	4"x2	188.1	1.34	4"x2	282.2	2.83	4"x2
PFI-1212N-3D4BT-O1	Ethylene Glycol	235.1	2.02	4"x2	188.1	1.34	4"x2	282.2	2.83	4"x2
PFI-1212N-4D4BT-K1	Ethylene Glycol	235.1	2.47	4"x2	188.1	1.64	4"x2	282.2	3.46	4"x2
PFI-1212N-4D3BT-L1	Ethylene Glycol	231.8	2.75	4"x2	185.5	1.82	4"x2	278.2	3.85	4"x2
PFI-1212N-4D4BT-M1	Ethylene Glycol	235.1	2.47	4"x2	188.1	1.64	4"x2	282.2	3.46	4"x2
PFI-1212N-4D3BT-N1	Ethylene Glycol	231.8	2.75	4"x2	185.5	1.82	4"x2	278.2	3.85	4"x2
PFI-1212N-4D4BT-O1	Ethylene Glycol	235.1	2.47	4"x2	188.1	1.64	4"x2	282.2	3.46	4"x2
PFI-1212N-4D4BT-P1	Ethylene Glycol	235.1	2.47	4"x2	188.1	1.64	4"x2	282.2	3.46	4"x2
PFI-1212N-5D2BT-K1	Ethylene Glycol	229.1	3.66	4"x2	183.3	2.42	4"x2	274.9	5.12	4"x2
PFI-1212N-5D3BT-L1	Ethylene Glycol	231.8	3.27	4"x2	185.5	2.17	4"x2	278.2	4.59	4"x2
PFI-1212N-5D2BT-M1	Ethylene Glycol	229.1	3.66	4"x2	183.3	2.42	4"x2	274.9	5.12	4"x2
PFI-1212N-5D2BT-N1	Ethylene Glycol	229.1	3.66	4"x2	183.3	2.42	4"x2	274.9	5.12	4"x2
PFI-1212N-5D3BT-O1	Ethylene Glycol	231.8	3.27	4"x2	185.5	2.17	4"x2	278.2	4.59	4"x2
PFI-1212N-5D2BT-P1	Ethylene Glycol	229.1	3.66	4"x2	183.3	2.42	4"x2	274.9	5.12	4"x2
PFI-1212N-6D1BT-K1	Ethylene Glycol	226.3	4.86	4"x2	181.1	3.22	4"x2	271.6	6.8	4"x2
PFI-1212N-6D1BT-L1	Ethylene Glycol	226.3	4.86	4"x2	181.1	3.22	4"x2	271.6	6.8	4"x2
PFI-1212N-6D1BT-M1	Ethylene Glycol	226.3	4.86	4"x2	181.1	3.22	4"x2	271.6	6.8	4"x2
PFI-1212N-6D1BT-N1	Ethylene Glycol	226.3	4.86	4"x2	181.1	3.22	4"x2	271.6	6.8	4"x2
PFI-1212N-6D1BT-O1	Ethylene Glycol	226.3	4.86	4"x2	181.1	3.22	4"x2	271.6	6.8	4"x2
PFI-1212N-6D1BT-P1	Ethylene Glycol	226.3	4.86	4"x2	181.1	3.22	4"x2	271.6	6.8	4"x2
PFI-1224N-2D4DS-K2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4
PFI-1224N-2D3ES-L2	Ethylene Glycol	1055.0	1.39	4"x4	844.0	0.92	4"x4	1265.9	1.94	4"x4
PFI-1224N-2D4DS-M2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-2D4ES-M2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4
PFI-1224N-2D4ES-N2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4
PFI-1224N-2D4ES-O2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4
PFI-1224N-3D2DS-L2	Ethylene Glycol	1033.0	1.83	4"x4	826.4	1.21	4"x4	1239.5	2.56	4"x4
PFI-1224N-3D3DS-M2	Ethylene Glycol	1055.0	1.72	4"x4	844.0	1.14	4"x4	1265.9	2.41	4"x4
PFI-1224N-3D2ES-M2	Ethylene Glycol	1033.0	1.83	4"x4	826.4	1.21	4"x4	1239.5	2.56	4"x4
PFI-1224N-3D2DS-N2	Ethylene Glycol	1033.0	1.83	4"x4	826.4	1.21	4"x4	1239.5	2.56	4"x4
PFI-1224N-3D2ES-N2	Ethylene Glycol	1033.0	1.83	4"x4	826.4	1.21	4"x4	1239.5	2.56	4"x4
PFI-1224N-3D4ES-O2	Ethylene Glycol	1081.4	1.63	4"x4	865.1	1.08	4"x4	1297.6	2.28	4"x4
PFI-1224N-3D1DS-P2	Ethylene Glycol	1011.0	1.97	4"x4	808.8	1.3	4"x4	1213.1	2.76	4"x4
PFI-1224N-4D1ES-K2	Ethylene Glycol	1011.0	2.4	4"x4	808.8	1.59	4"x4	1213.1	3.36	4"x4
PFI-1224N-4D3ES-M2	Ethylene Glycol	1055.0	2.05	4"x4	844.0	1.36	4"x4	1265.9	2.88	4"x4
PFI-1224N-4D2DS-N2	Ethylene Glycol	1033.0	2.2	4"x4	826.4	1.46	4"x4	1239.5	3.08	4"x4
PFI-1224N-4D3DS-P2	Ethylene Glycol	1055.0	2.05	4"x4	844.0	1.36	4"x4	1265.9	2.88	4"x4
PFI-1224N-5D2ES-K2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-1224N-5D2ES-L2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-1224N-5D2DS-N2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-1224N-5D1DS-O2	Ethylene Glycol	1011.0	2.83	4"x4	808.8	1.88	4"x4	1213.1	3.97	4"x4
PFI-1224N-5D4DS-O2	Ethylene Glycol	1081.4	2.22	4"x4	865.1	1.47	4"x4	1297.6	3.1	4"x4
PFI-1224N-5D2ES-P2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-1224N-6D1ES-L2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1ES-M2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1ES-N2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1ES-O2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1ES-P2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-3D3BS-L2	Ethylene Glycol	1055.0	1.72	4"x4	844.0	1.14	4"x4	1265.9	2.41	4"x4
PFI-1224N-3D4BS-N2	Ethylene Glycol	1081.4	1.63	4"x4	865.1	1.08	4"x4	1297.6	2.28	4"x4
PFI-1224N-3D4BS-O2	Ethylene Glycol	1081.4	1.63	4"x4	865.1	1.08	4"x4	1297.6	2.28	4"x4
PFI-1224N-4D4BS-K2	Ethylene Glycol	1081.4	1.92	4"x4	865.1	1.27	4"x4	1297.6	2.69	4"x4
PFI-1224N-4D3BS-L2	Ethylene Glycol	1055.0	2.05	4"x4	844.0	1.36	4"x4	1265.9	2.88	4"x4
PFI-1224N-4D4BS-M2	Ethylene Glycol	1081.4	1.92	4"x4	865.1	1.27	4"x4	1297.6	2.69	4"x4
PFI-1224N-4D3BS-N2	Ethylene Glycol	1055.0	2.05	4"x4	844.0	1.36	4"x4	1265.9	2.88	4"x4
PFI-1224N-4D4BS-O2	Ethylene Glycol	1081.4	1.92	4"x4	865.1	1.27	4"x4	1297.6	2.69	4"x4
PFI-1224N-4D4BS-P2	Ethylene Glycol	1081.4	1.92	4"x4	865.1	1.27	4"x4	1297.6	2.69	4"x4
PFI-1224N-5D2BS-K2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-1224N-5D3BS-L2	Ethylene Glycol	1055.0	2.39	4"x4	844.0	1.58	4"x4	1265.9	3.34	4"x4
PFI-1224N-5D2BS-M2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-1224N-5D2BS-N2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-1224N-5D3BS-O2	Ethylene Glycol	1055.0	2.39	4"x4	844.0	1.58	4"x4	1265.9	3.34	4"x4
PFI-1224N-5D2BS-P2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-1224N-6D1BS-K2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1BS-L2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1BS-M2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1BS-N2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1BS-O2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-6D1BS-P2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-1224N-2D4DZ-K2	Ethylene Glycol	470.3	1.58	4"x4	376.2	1.05	4"x4	564.3	2.21	4"x4
PFI-1224N-2D3EZ-L2	Ethylene Glycol	463.7	1.72	4"x4	370.9	1.14	4"x4	556.4	2.4	4"x4
PFI-1224N-2D4DZ-M2	Ethylene Glycol	470.3	1.58	4"x4	376.2	1.05	4"x4	564.3	2.21	4"x4
PFI-1224N-2D4EZ-M2	Ethylene Glycol	470.3	1.59	4"x4	376.2	1.05	4"x4	564.3	2.22	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-2D4EZ-N2	Ethylene Glycol	470.3	1.59	4"x4	376.2	1.05	4"x4	564.3	2.22	4"x4
PFI-1224N-2D4EZ-O2	Ethylene Glycol	470.3	1.59	4"x4	376.2	1.05	4"x4	564.3	2.22	4"x4
PFI-1224N-3D2DZ-L2	Ethylene Glycol	458.2	2.46	4"x4	366.5	1.63	4"x4	549.8	3.45	4"x4
PFI-1224N-3D3DZ-M2	Ethylene Glycol	463.7	2.24	4"x4	370.9	1.48	4"x4	556.4	3.14	4"x4
PFI-1224N-3D2EZ-M2	Ethylene Glycol	458.2	2.47	4"x4	366.5	1.64	4"x4	549.8	3.46	4"x4
PFI-1224N-3D2DZ-N2	Ethylene Glycol	458.2	2.46	4"x4	366.5	1.63	4"x4	549.8	3.45	4"x4
PFI-1224N-3D2EZ-N2	Ethylene Glycol	458.2	2.47	4"x4	366.5	1.64	4"x4	549.8	3.46	4"x4
PFI-1224N-3D4EZ-O2	Ethylene Glycol	470.3	2.04	4"x4	376.2	1.35	4"x4	564.3	2.86	4"x4
PFI-1224N-3D1DZ-P2	Ethylene Glycol	452.7	2.75	4"x4	362.1	1.82	4"x4	543.2	3.86	4"x4
PFI-1224N-4D1EZ-K2	Ethylene Glycol	452.7	3.47	4"x4	362.1	2.3	4"x4	543.2	4.87	4"x4
PFI-1224N-4D3EZ-M2	Ethylene Glycol	463.7	2.78	4"x4	370.9	1.84	4"x4	556.4	3.89	4"x4
PFI-1224N-4D2DZ-N2	Ethylene Glycol	458.2	3.07	4"x4	366.5	2.03	4"x4	549.8	4.3	4"x4
PFI-1224N-4D3DZ-P2	Ethylene Glycol	463.7	2.77	4"x4	370.9	1.83	4"x4	556.4	3.88	4"x4
PFI-1224N-5D2EZ-K2	Ethylene Glycol	458.2	3.69	4"x4	366.5	2.44	4"x4	549.8	5.17	4"x4
PFI-1224N-5D2EZ-L2	Ethylene Glycol	458.2	3.69	4"x4	366.5	2.44	4"x4	549.8	5.17	4"x4
PFI-1224N-5D2DZ-N2	Ethylene Glycol	458.2	3.68	4"x4	366.5	2.44	4"x4	549.8	5.16	4"x4
PFI-1224N-5D1DZ-O2	Ethylene Glycol	452.7	4.17	4"x4	362.1	2.76	4"x4	543.2	5.85	4"x4
PFI-1224N-5D4DZ-O2	Ethylene Glycol	470.3	2.95	4"x4	376.2	1.95	4"x4	564.3	4.14	4"x4
PFI-1224N-5D2EZ-P2	Ethylene Glycol	458.2	3.69	4"x4	366.5	2.44	4"x4	549.8	5.17	4"x4
PFI-1224N-6D1EZ-L2	Ethylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-1224N-6D1EZ-M2	Ethylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-1224N-6D1EZ-N2	Ethylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-1224N-6D1EZ-O2	Ethylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-1224N-6D1EZ-P2	Ethylene Glycol	852.6	15.8	4"x4	682.0	10.45	4"x4	1023.1	22.15	4"x4
PFI-1224N-3D3BT-L2	Ethylene Glycol	463.7	2.22	4"x4	370.9	1.47	4"x4	556.4	3.11	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-3D4BT-N2	Ethylene Glycol	470.3	2.02	4"x4	376.2	1.34	4"x4	564.3	2.83	4"x4
PFI-1224N-3D4BT-O2	Ethylene Glycol	470.3	2.02	4"x4	376.2	1.34	4"x4	564.3	2.83	4"x4
PFI-1224N-4D4BT-K2	Ethylene Glycol	470.3	2.47	4"x4	376.2	1.64	4"x4	564.3	3.46	4"x4
PFI-1224N-4D3BT-L2	Ethylene Glycol	463.7	2.75	4"x4	370.9	1.82	4"x4	556.4	3.85	4"x4
PFI-1224N-4D4BT-M2	Ethylene Glycol	470.3	2.47	4"x4	376.2	1.64	4"x4	564.3	3.46	4"x4
PFI-1224N-4D3BT-N2	Ethylene Glycol	463.7	2.75	4"x4	370.9	1.82	4"x4	556.4	3.85	4"x4
PFI-1224N-4D4BT-O2	Ethylene Glycol	470.3	2.47	4"x4	376.2	1.64	4"x4	564.3	3.46	4"x4
PFI-1224N-4D4BT-P2	Ethylene Glycol	470.3	2.47	4"x4	376.2	1.64	4"x4	564.3	3.46	4"x4
PFI-1224N-5D2BT-K2	Ethylene Glycol	458.2	3.66	4"x4	366.5	2.42	4"x4	549.8	5.12	4"x4
PFI-1224N-5D3BT-L2	Ethylene Glycol	463.7	3.28	4"x4	370.9	2.17	4"x4	556.4	4.59	4"x4
PFI-1224N-5D2BT-M2	Ethylene Glycol	458.2	3.66	4"x4	366.5	2.42	4"x4	549.8	5.12	4"x4
PFI-1224N-5D2BT-N2	Ethylene Glycol	458.2	3.66	4"x4	366.5	2.42	4"x4	549.8	5.12	4"x4
PFI-1224N-5D3BT-O2	Ethylene Glycol	463.7	3.28	4"x4	370.9	2.17	4"x4	556.4	4.59	4"x4
PFI-1224N-5D2BT-P2	Ethylene Glycol	458.2	3.66	4"x4	366.5	2.42	4"x4	549.8	5.12	4"x4
PFI-1224N-6D1BT-K2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-1224N-6D1BT-L2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-1224N-6D1BT-M2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-1224N-6D1BT-N2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-1224N-6D1BT-O2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-1224N-6D1BT-P2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-2412N-2D4DS-K2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4
PFI-2412N-2D3ES-L2	Ethylene Glycol	1055.0	1.39	4"x4	844.0	0.92	4"x4	1265.9	1.94	4"x4
PFI-2412N-2D4DS-M2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4
PFI-2412N-2D4ES-M2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4
PFI-2412N-2D4ES-N2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-2D4ES-O2	Ethylene Glycol	1081.4	1.34	4"x4	865.1	0.89	4"x4	1297.6	1.87	4"x4
PFI-2412N-3D2DS-L2	Ethylene Glycol	1033.0	1.83	4"x4	826.4	1.21	4"x4	1239.5	2.56	4"x4
PFI-2412N-3D3DS-M2	Ethylene Glycol	1055.0	1.72	4"x4	844.0	1.14	4"x4	1265.9	2.41	4"x4
PFI-2412N-3D2ES-M2	Ethylene Glycol	1033.0	1.83	4"x4	826.4	1.21	4"x4	1239.5	2.56	4"x4
PFI-2412N-3D2DS-N2	Ethylene Glycol	1033.0	1.83	4"x4	826.4	1.21	4"x4	1239.5	2.56	4"x4
PFI-2412N-3D2ES-N2	Ethylene Glycol	1033.0	1.83	4"x4	826.4	1.21	4"x4	1239.5	2.56	4"x4
PFI-2412N-3D4ES-O2	Ethylene Glycol	1081.4	1.63	4"x4	865.1	1.08	4"x4	1297.6	2.28	4"x4
PFI-2412N-3D1DS-P2	Ethylene Glycol	1011.0	1.97	4"x4	808.8	1.3	4"x4	1213.1	2.76	4"x4
PFI-2412N-4D1ES-K2	Ethylene Glycol	1011.0	2.4	4"x4	808.8	1.59	4"x4	1213.1	3.36	4"x4
PFI-2412N-4D3ES-M2	Ethylene Glycol	1055.0	2.05	4"x4	844.0	1.36	4"x4	1265.9	2.88	4"x4
PFI-2412N-4D2DS-N2	Ethylene Glycol	1033.0	2.2	4"x4	826.4	1.46	4"x4	1239.5	3.08	4"x4
PFI-2412N-4D3DS-P2	Ethylene Glycol	1055.0	2.05	4"x4	844.0	1.36	4"x4	1265.9	2.88	4"x4
PFI-2412N-5D2ES-K2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-2412N-5D2ES-L2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-2412N-5D2DS-N2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-2412N-5D1DS-O2	Ethylene Glycol	1011.0	2.83	4"x4	808.8	1.88	4"x4	1213.1	3.97	4"x4
PFI-2412N-5D4DS-O2	Ethylene Glycol	1081.4	2.22	4"x4	865.1	1.47	4"x4	1297.6	3.1	4"x4
PFI-2412N-5D2ES-P2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-2412N-6D1ES-L2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1ES-M2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1ES-N2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1ES-O2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1ES-P2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-3D3BS-L2	Ethylene Glycol	1055.0	1.72	4"x4	844.0	1.14	4"x4	1265.9	2.41	4"x4
PFI-2412N-3D4BS-N2	Ethylene Glycol	1081.4	1.63	4"x4	865.1	1.08	4"x4	1297.6	2.28	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-3D4BS-O2	Ethylene Glycol	1081.4	1.63	4"x4	865.1	1.08	4"x4	1297.6	2.28	4"x4
PFI-2412N-4D4BS-K2	Ethylene Glycol	1081.4	1.92	4"x4	865.1	1.27	4"x4	1297.6	2.69	4"x4
PFI-2412N-4D3BS-L2	Ethylene Glycol	1055.0	2.05	4"x4	844.0	1.36	4"x4	1265.9	2.88	4"x4
PFI-2412N-4D4BS-M2	Ethylene Glycol	1081.4	1.92	4"x4	865.1	1.27	4"x4	1297.6	2.69	4"x4
PFI-2412N-4D3BS-N2	Ethylene Glycol	1055.0	2.05	4"x4	844.0	1.36	4"x4	1265.9	2.88	4"x4
PFI-2412N-4D4BS-O2	Ethylene Glycol	1081.4	1.92	4"x4	865.1	1.27	4"x4	1297.6	2.69	4"x4
PFI-2412N-4D4BS-P2	Ethylene Glycol	1081.4	1.92	4"x4	865.1	1.27	4"x4	1297.6	2.69	4"x4
PFI-2412N-5D2BS-K2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-2412N-5D3BS-L2	Ethylene Glycol	1055.0	2.39	4"x4	844.0	1.58	4"x4	1265.9	3.34	4"x4
PFI-2412N-5D2BS-M2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-2412N-5D2BS-N2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-2412N-5D3BS-O2	Ethylene Glycol	1055.0	2.39	4"x4	844.0	1.58	4"x4	1265.9	3.34	4"x4
PFI-2412N-5D2BS-P2	Ethylene Glycol	1033.0	2.58	4"x4	826.4	1.71	4"x4	1239.5	3.61	4"x4
PFI-2412N-6D1BS-K2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1BS-L2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1BS-M2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1BS-N2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1BS-O2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-6D1BS-P2	Ethylene Glycol	1011.0	3.27	4"x4	808.8	2.16	4"x4	1213.1	4.58	4"x4
PFI-2412N-2D4DZ-K2	Ethylene Glycol	470.3	1.58	4"x4	376.2	1.05	4"x4	564.3	2.21	4"x4
PFI-2412N-2D3EZ-L2	Ethylene Glycol	463.7	1.72	4"x4	370.9	1.14	4"x4	556.4	2.4	4"x4
PFI-2412N-2D4DZ-M2	Ethylene Glycol	470.3	1.58	4"x4	376.2	1.05	4"x4	564.3	2.21	4"x4
PFI-2412N-2D4EZ-M2	Ethylene Glycol	470.3	1.59	4"x4	376.2	1.05	4"x4	564.3	2.22	4"x4
PFI-2412N-2D4EZ-N2	Ethylene Glycol	470.3	1.59	4"x4	376.2	1.05	4"x4	564.3	2.22	4"x4
PFI-2412N-2D4EZ-O2	Ethylene Glycol	470.3	1.59	4"x4	376.2	1.05	4"x4	564.3	2.22	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-3D2DZ-L2	Ethylene Glycol	458.2	2.46	4"x4	366.5	1.63	4"x4	549.8	3.45	4"x4
PFI-2412N-3D3DZ-M2	Ethylene Glycol	463.7	2.24	4"x4	370.9	1.48	4"x4	556.4	3.14	4"x4
PFI-2412N-3D2EZ-M2	Ethylene Glycol	458.2	2.47	4"x4	366.5	1.64	4"x4	549.8	3.46	4"x4
PFI-2412N-3D2DZ-N2	Ethylene Glycol	458.2	2.46	4"x4	366.5	1.63	4"x4	549.8	3.45	4"x4
PFI-2412N-3D2EZ-N2	Ethylene Glycol	458.2	2.47	4"x4	366.5	1.64	4"x4	549.8	3.46	4"x4
PFI-2412N-3D4EZ-O2	Ethylene Glycol	470.3	2.04	4"x4	376.2	1.35	4"x4	564.3	2.86	4"x4
PFI-2412N-3D1DZ-P2	Ethylene Glycol	452.7	2.75	4"x4	362.1	1.82	4"x4	543.2	3.86	4"x4
PFI-2412N-4D1EZ-K2	Ethylene Glycol	452.7	3.47	4"x4	362.1	2.3	4"x4	543.2	4.87	4"x4
PFI-2412N-4D3EZ-M2	Ethylene Glycol	463.7	2.78	4"x4	370.9	1.84	4"x4	556.4	3.89	4"x4
PFI-2412N-4D2DZ-N2	Ethylene Glycol	458.2	3.07	4"x4	366.5	2.03	4"x4	549.8	4.3	4"x4
PFI-2412N-4D3DZ-P2	Ethylene Glycol	463.7	2.77	4"x4	370.9	1.83	4"x4	556.4	3.88	4"x4
PFI-2412N-5D2EZ-K2	Ethylene Glycol	458.2	3.69	4"x4	366.5	2.44	4"x4	549.8	5.17	4"x4
PFI-2412N-5D2EZ-L2	Ethylene Glycol	458.2	3.69	4"x4	366.5	2.44	4"x4	549.8	5.17	4"x4
PFI-2412N-5D2DZ-N2	Ethylene Glycol	458.2	3.68	4"x4	366.5	2.44	4"x4	549.8	5.16	4"x4
PFI-2412N-5D1DZ-O2	Ethylene Glycol	452.7	4.17	4"x4	362.1	2.76	4"x4	543.2	5.85	4"x4
PFI-2412N-5D4DZ-O2	Ethylene Glycol	470.3	2.95	4"x4	376.2	1.95	4"x4	564.3	4.14	4"x4
PFI-2412N-5D2EZ-P2	Ethylene Glycol	458.2	3.69	4"x4	366.5	2.44	4"x4	549.8	5.17	4"x4
PFI-2412N-6D1EZ-L2	Ethylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-2412N-6D1EZ-M2	Ethylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-2412N-6D1EZ-N2	Ethylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-2412N-6D1EZ-O2	Ethylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-2412N-6D1EZ-P2	Ethylene Glycol	852.6	15.8	4"x4	682.0	10.45	4"x4	1023.1	22.15	4"x4
PFI-2412N-3D3BT-L2	Ethylene Glycol	463.7	2.22	4"x4	370.9	1.47	4"x4	556.4	3.11	4"x4
PFI-2412N-3D4BT-N2	Ethylene Glycol	470.3	2.02	4"x4	376.2	1.34	4"x4	564.3	2.83	4"x4
PFI-2412N-3D4BT-O2	Ethylene Glycol	470.3	2.02	4"x4	376.2	1.34	4"x4	564.3	2.83	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-4D4BT-K2	Ethylene Glycol	470.3	2.47	4"x4	376.2	1.64	4"x4	564.3	3.46	4"x4
PFI-2412N-4D3BT-L2	Ethylene Glycol	463.7	2.75	4"x4	370.9	1.82	4"x4	556.4	3.85	4"x4
PFI-2412N-4D4BT-M2	Ethylene Glycol	470.3	2.47	4"x4	376.2	1.64	4"x4	564.3	3.46	4"x4
PFI-2412N-4D3BT-N2	Ethylene Glycol	463.7	2.75	4"x4	370.9	1.82	4"x4	556.4	3.85	4"x4
PFI-2412N-4D4BT-O2	Ethylene Glycol	470.3	2.47	4"x4	376.2	1.64	4"x4	564.3	3.46	4"x4
PFI-2412N-4D4BT-P2	Ethylene Glycol	470.3	2.47	4"x4	376.2	1.64	4"x4	564.3	3.46	4"x4
PFI-2412N-5D2BT-K2	Ethylene Glycol	458.2	3.66	4"x4	366.5	2.42	4"x4	549.8	5.12	4"x4
PFI-2412N-5D3BT-L2	Ethylene Glycol	463.7	3.28	4"x4	370.9	2.17	4"x4	556.4	4.59	4"x4
PFI-2412N-5D2BT-M2	Ethylene Glycol	458.2	3.66	4"x4	366.5	2.42	4"x4	549.8	5.12	4"x4
PFI-2412N-5D2BT-N2	Ethylene Glycol	458.2	3.66	4"x4	366.5	2.42	4"x4	549.8	5.12	4"x4
PFI-2412N-5D3BT-O2	Ethylene Glycol	463.7	3.28	4"x4	370.9	2.17	4"x4	556.4	4.59	4"x4
PFI-2412N-5D2BT-P2	Ethylene Glycol	458.2	3.66	4"x4	366.5	2.42	4"x4	549.8	5.12	4"x4
PFI-2412N-6D1BT-K2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-2412N-6D1BT-L2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-2412N-6D1BT-M2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-2412N-6D1BT-N2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-2412N-6D1BT-O2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-2412N-6D1BT-P2	Ethylene Glycol	452.7	4.86	4"x4	362.1	3.21	4"x4	543.2	6.8	4"x4
PFI-2424N-2D4DS-K4	Ethylene Glycol	2162.7	1.34	4"x8	1730.2	0.89	4"x8	2595.2	1.87	4"x8
PFI-2424N-2D3ES-L4	Ethylene Glycol	2109.9	1.39	4"x8	1687.9	0.92	4"x8	2531.9	1.94	4"x8
PFI-2424N-2D4DS-M4	Ethylene Glycol	2162.7	1.34	4"x8	1730.2	0.89	4"x8	2595.2	1.87	4"x8
PFI-2424N-2D4ES-M4	Ethylene Glycol	2162.7	1.34	4"x8	1730.2	0.89	4"x8	2595.2	1.87	4"x8
PFI-2424N-2D4ES-N4	Ethylene Glycol	2162.7	1.34	4"x8	1730.2	0.89	4"x8	2595.2	1.87	4"x8
PFI-2424N-2D4ES-O4	Ethylene Glycol	2162.7	1.34	4"x8	1730.2	0.89	4"x8	2595.2	1.87	4"x8
PFI-2424N-3D2DS-L4	Ethylene Glycol	2065.9	1.83	4"x8	1652.7	1.21	4"x8	2479.1	2.56	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-3D3DS-M4	Ethylene Glycol	2109.9	1.72	4"x8	1687.9	1.14	4"x8	2531.9	2.41	4"x8
PFI-2424N-3D2ES-M4	Ethylene Glycol	2065.9	1.83	4"x8	1652.7	1.21	4"x8	2479.1	2.56	4"x8
PFI-2424N-3D2DS-N4	Ethylene Glycol	2065.9	1.83	4"x8	1652.7	1.21	4"x8	2479.1	2.56	4"x8
PFI-2424N-3D2ES-N4	Ethylene Glycol	2065.9	1.83	4"x8	1652.7	1.21	4"x8	2479.1	2.56	4"x8
PFI-2424N-3D4ES-O4	Ethylene Glycol	2162.7	1.63	4"x8	1730.2	1.08	4"x8	2595.2	2.28	4"x8
PFI-2424N-3D1DS-P4	Ethylene Glycol	2021.9	1.97	4"x8	1617.5	1.3	4"x8	2426.3	2.76	4"x8
PFI-2424N-4D1ES-K4	Ethylene Glycol	2021.9	2.4	4"x8	1617.5	1.59	4"x8	2426.3	3.36	4"x8
PFI-2424N-4D3ES-M4	Ethylene Glycol	2109.9	2.05	4"x8	1687.9	1.36	4"x8	2531.9	2.88	4"x8
PFI-2424N-4D2DS-N4	Ethylene Glycol	2065.9	2.2	4"x8	1652.7	1.46	4"x8	2479.1	3.08	4"x8
PFI-2424N-4D3DS-P4	Ethylene Glycol	2109.9	2.05	4"x8	1687.9	1.36	4"x8	2531.9	2.88	4"x8
PFI-2424N-5D2ES-K4	Ethylene Glycol	2065.9	2.58	4"x8	1652.7	1.71	4"x8	2479.1	3.61	4"x8
PFI-2424N-5D2ES-L4	Ethylene Glycol	2065.9	2.58	4"x8	1652.7	1.71	4"x8	2479.1	3.61	4"x8
PFI-2424N-5D2DS-N4	Ethylene Glycol	2065.9	2.58	4"x8	1652.7	1.71	4"x8	2479.1	3.61	4"x8
PFI-2424N-5D1DS-O4	Ethylene Glycol	2021.9	2.83	4"x8	1617.5	1.88	4"x8	2426.3	3.97	4"x8
PFI-2424N-5D4DS-O4	Ethylene Glycol	2162.7	2.22	4"x8	1730.2	1.47	4"x8	2595.2	3.1	4"x8
PFI-2424N-5D2ES-P4	Ethylene Glycol	2065.9	2.58	4"x8	1652.7	1.71	4"x8	2479.1	3.61	4"x8
PFI-2424N-6D1ES-L4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1ES-M4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1ES-N4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1ES-O4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1ES-P4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-3D3BS-L4	Ethylene Glycol	2109.9	1.72	4"x8	1687.9	1.14	4"x8	2531.9	2.41	4"x8
PFI-2424N-3D4BS-N4	Ethylene Glycol	2162.7	1.63	4"x8	1730.2	1.08	4"x8	2595.2	2.28	4"x8
PFI-2424N-3D4BS-O4	Ethylene Glycol	2162.7	1.63	4"x8	1730.2	1.08	4"x8	2595.2	2.28	4"x8
PFI-2424N-4D4BS-K4	Ethylene Glycol	2162.7	1.92	4"x8	1730.2	1.27	4"x8	2595.2	2.69	4"x8





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-4D3BS-L4	Ethylene Glycol	2109.9	2.05	4"x8	1687.9	1.36	4"x8	2531.9	2.88	4"x8
PFI-2424N-4D4BS-M4	Ethylene Glycol	2162.7	1.92	4"x8	1730.2	1.27	4"x8	2595.2	2.69	4"x8
PFI-2424N-4D3BS-N4	Ethylene Glycol	2109.9	2.05	4"x8	1687.9	1.36	4"x8	2531.9	2.88	4"x8
PFI-2424N-4D4BS-O4	Ethylene Glycol	2162.7	1.92	4"x8	1730.2	1.27	4"x8	2595.2	2.69	4"x8
PFI-2424N-4D4BS-P4	Ethylene Glycol	2162.7	1.92	4"x8	1730.2	1.27	4"x8	2595.2	2.69	4"x8
PFI-2424N-5D2BS-K4	Ethylene Glycol	2065.9	2.58	4"x8	1652.7	1.71	4"x8	2479.1	3.61	4"x8
PFI-2424N-5D3BS-L4	Ethylene Glycol	2109.9	2.39	4"x8	1687.9	1.58	4"x8	2531.9	3.35	4"x8
PFI-2424N-5D2BS-M4	Ethylene Glycol	2065.9	2.58	4"x8	1652.7	1.71	4"x8	2479.1	3.61	4"x8
PFI-2424N-5D2BS-N4	Ethylene Glycol	2065.9	2.58	4"x8	1652.7	1.71	4"x8	2479.1	3.61	4"x8
PFI-2424N-5D3BS-O4	Ethylene Glycol	2109.9	2.39	4"x8	1687.9	1.58	4"x8	2531.9	3.35	4"x8
PFI-2424N-5D2BS-P4	Ethylene Glycol	2065.9	2.58	4"x8	1652.7	1.71	4"x8	2479.1	3.61	4"x8
PFI-2424N-6D1BS-K4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1BS-L4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1BS-M4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1BS-N4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1BS-O4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-6D1BS-P4	Ethylene Glycol	2021.9	3.27	4"x8	1617.5	2.16	4"x8	2426.3	4.58	4"x8
PFI-2424N-2D4DZ-K4	Ethylene Glycol	940.6	1.58	4"x8	752.4	1.05	4"x8	1128.7	2.22	4"x8
PFI-2424N-2D3EZ-L4	Ethylene Glycol	927.4	1.72	4"x8	741.9	1.14	4"x8	1112.8	2.4	4"x8
PFI-2424N-2D4DZ-M4	Ethylene Glycol	940.6	1.58	4"x8	752.4	1.05	4"x8	1128.7	2.22	4"x8
PFI-2424N-2D4EZ-M4	Ethylene Glycol	940.6	1.59	4"x8	752.4	1.05	4"x8	1128.7	2.22	4"x8
PFI-2424N-2D4EZ-N4	Ethylene Glycol	940.6	1.59	4"x8	752.4	1.05	4"x8	1128.7	2.22	4"x8
PFI-2424N-2D4EZ-O4	Ethylene Glycol	940.6	1.59	4"x8	752.4	1.05	4"x8	1128.7	2.22	4"x8
PFI-2424N-3D2DZ-L4	Ethylene Glycol	916.4	2.46	4"x8	733.1	1.63	4"x8	1099.6	3.45	4"x8
PFI-2424N-3D3DZ-M4	Ethylene Glycol	927.4	2.24	4"x8	741.9	1.48	4"x8	1112.8	3.14	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-3D2EZ-M4	Ethylene Glycol	916.4	2.47	4"x8	733.1	1.64	4"x8	1099.6	3.46	4"x8
PFI-2424N-3D2DZ-N4	Ethylene Glycol	916.4	2.46	4"x8	733.1	1.63	4"x8	1099.6	3.45	4"x8
PFI-2424N-3D2EZ-N4	Ethylene Glycol	916.4	2.47	4"x8	733.1	1.64	4"x8	1099.6	3.46	4"x8
PFI-2424N-3D4EZ-O4	Ethylene Glycol	940.6	2.04	4"x8	752.4	1.35	4"x8	1128.7	2.87	4"x8
PFI-2424N-3D1DZ-P4	Ethylene Glycol	905.4	2.75	4"x8	724.3	1.82	4"x8	1086.4	3.86	4"x8
PFI-2424N-4D1EZ-K4	Ethylene Glycol	905.4	3.47	4"x8	724.3	2.3	4"x8	1086.4	4.87	4"x8
PFI-2424N-4D3EZ-M4	Ethylene Glycol	927.4	2.78	4"x8	741.9	1.84	4"x8	1112.8	3.89	4"x8
PFI-2424N-4D2DZ-N4	Ethylene Glycol	916.4	3.07	4"x8	733.1	2.03	4"x8	1099.6	4.3	4"x8
PFI-2424N-4D3DZ-P4	Ethylene Glycol	927.4	2.77	4"x8	741.9	1.83	4"x8	1112.8	3.88	4"x8
PFI-2424N-5D2EZ-K4	Ethylene Glycol	916.4	3.69	4"x8	733.1	2.44	4"x8	1099.6	5.17	4"x8
PFI-2424N-5D2EZ-L4	Ethylene Glycol	916.4	3.69	4"x8	733.1	2.44	4"x8	1099.6	5.17	4"x8
PFI-2424N-5D2DZ-N4	Ethylene Glycol	916.4	3.68	4"x8	733.1	2.44	4"x8	1099.6	5.16	4"x8
PFI-2424N-5D1DZ-O4	Ethylene Glycol	905.4	4.17	4"x8	724.3	2.76	4"x8	1086.4	5.85	4"x8
PFI-2424N-5D4DZ-O4	Ethylene Glycol	940.6	2.95	4"x8	752.4	1.95	4"x8	1128.7	4.14	4"x8
PFI-2424N-5D2EZ-P4	Ethylene Glycol	916.4	3.69	4"x8	733.1	2.44	4"x8	1099.6	5.17	4"x8
PFI-2424N-6D1EZ-L4	Ethylene Glycol	905.4	4.9	4"x8	724.3	3.24	4"x8	1086.4	6.86	4"x8
PFI-2424N-6D1EZ-M4	Ethylene Glycol	905.4	4.9	4"x8	724.3	3.24	4"x8	1086.4	6.86	4"x8
PFI-2424N-6D1EZ-N4	Ethylene Glycol	905.4	4.9	4"x8	724.3	3.24	4"x8	1086.4	6.86	4"x8
PFI-2424N-6D1EZ-O4	Ethylene Glycol	905.4	4.9	4"x8	724.3	3.24	4"x8	1086.4	6.86	4"x8
PFI-2424N-6D1EZ-P4	Ethylene Glycol	1705.1	15.8	4"x8	1364.1	10.45	4"x8	2046.1	22.15	4"x8
PFI-2424N-3D3BT-L4	Ethylene Glycol	927.4	2.22	4"x8	741.9	1.47	4"x8	1112.8	3.11	4"x8
PFI-2424N-3D4BT-N4	Ethylene Glycol	940.6	2.02	4"x8	752.4	1.34	4"x8	1128.7	2.83	4"x8
PFI-2424N-3D4BT-O4	Ethylene Glycol	940.6	2.02	4"x8	752.4	1.34	4"x8	1128.7	2.83	4"x8
PFI-2424N-4D4BT-K4	Ethylene Glycol	940.6	2.47	4"x8	752.4	1.64	4"x8	1128.7	3.46	4"x8
PFI-2424N-4D3BT-L4	Ethylene Glycol	927.4	2.75	4"x8	741.9	1.82	4"x8	1112.8	3.85	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-4D4BT-M4	Ethylene Glycol	940.6	2.47	4"x8	752.4	1.64	4"x8	1128.7	3.46	4"x8
PFI-2424N-4D3BT-N4	Ethylene Glycol	927.4	2.75	4"x8	741.9	1.82	4"x8	1112.8	3.85	4"x8
PFI-2424N-4D4BT-O4	Ethylene Glycol	940.6	2.47	4"x8	752.4	1.64	4"x8	1128.7	3.46	4"x8
PFI-2424N-4D4BT-P4	Ethylene Glycol	940.6	2.47	4"x8	752.4	1.64	4"x8	1128.7	3.46	4"x8
PFI-2424N-5D2BT-K4	Ethylene Glycol	916.4	3.66	4"x8	733.1	2.42	4"x8	1099.6	5.12	4"x8
PFI-2424N-5D3BT-L4	Ethylene Glycol	927.4	3.28	4"x8	741.9	2.17	4"x8	1112.8	4.59	4"x8
PFI-2424N-5D2BT-M4	Ethylene Glycol	916.4	3.66	4"x8	733.1	2.42	4"x8	1099.6	5.12	4"x8
PFI-2424N-5D2BT-N4	Ethylene Glycol	916.4	3.66	4"x8	733.1	2.42	4"x8	1099.6	5.12	4"x8
PFI-2424N-5D3BT-O4	Ethylene Glycol	927.4	3.28	4"x8	741.9	2.17	4"x8	1112.8	4.59	4"x8
PFI-2424N-5D2BT-P4	Ethylene Glycol	916.4	3.66	4"x8	733.1	2.42	4"x8	1099.6	5.12	4"x8
PFI-2424N-6D1BT-K4	Ethylene Glycol	905.4	4.86	4"x8	724.3	3.22	4"x8	1086.4	6.8	4"x8
PFI-2424N-6D1BT-L4	Ethylene Glycol	905.4	4.86	4"x8	724.3	3.22	4"x8	1086.4	6.8	4"x8
PFI-2424N-6D1BT-M4	Ethylene Glycol	905.4	4.86	4"x8	724.3	3.22	4"x8	1086.4	6.8	4"x8
PFI-2424N-6D1BT-N4	Ethylene Glycol	905.4	4.86	4"x8	724.3	3.22	4"x8	1086.4	6.8	4"x8
PFI-2424N-6D1BT-O4	Ethylene Glycol	905.4	4.86	4"x8	724.3	3.22	4"x8	1086.4	6.8	4"x8
PFI-2424N-6D1BT-P4	Ethylene Glycol	905.4	4.86	4"x8	724.3	3.22	4"x8	1086.4	6.8	4"x8
PFI-1218N-2D1DS-M1	Ethylene Glycol	505.5	1.9	4"x2	404.4	1.26	4"x2	606.6	2.66	4"x2
PFI-1218N-2D4ES-M1	Ethylene Glycol	540.7	1.58	4"x2	432.5	1.05	4"x2	648.8	2.22	4"x2
PFI-1218N-2D1DS-N1	Ethylene Glycol	505.5	1.9	4"x2	404.4	1.26	4"x2	606.6	2.66	4"x2
PFI-1218N-2D2DS-N1	Ethylene Glycol	516.5	1.77	4"x2	413.2	1.17	4"x2	619.8	2.47	4"x2
PFI-1218N-2D3ES-N1	Ethylene Glycol	527.5	1.67	4"x2	422.0	1.11	4"x2	633.0	2.34	4"x2
PFI-1218N-2D2DS-O1	Ethylene Glycol	516.5	1.77	4"x2	413.2	1.17	4"x2	619.8	2.47	4"x2
PFI-1218N-2D3ES-O1	Ethylene Glycol	527.5	1.67	4"x2	422.0	1.11	4"x2	633.0	2.34	4"x2
PFI-1218N-2D4DS-P1	Ethylene Glycol	540.7	1.58	4"x2	432.5	1.05	4"x2	648.8	2.22	4"x2
PFI-1218N-3D1ES-K1	Ethylene Glycol	505.5	2.52	4"x2	404.4	1.67	4"x2	606.6	3.53	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-3D1ES-L1	Ethylene Glycol	505.5	2.52	4"x2	404.4	1.67	4"x2	606.6	3.53	4"x2
PFI-1218N-3D4ES-M1	Ethylene Glycol	940.6	4.15	4"x4	752.4	3.69	4"x2	1128.7	5.82	4"x4
PFI-1218N-3D1DS-N1	Ethylene Glycol	505.5	2.52	4"x2	404.4	1.67	4"x2	606.6	3.53	4"x2
PFI-1218N-3D1ES-N1	Ethylene Glycol	505.5	2.52	4"x2	404.4	1.67	4"x2	606.6	3.53	4"x2
PFI-1218N-3D1DS-O1	Ethylene Glycol	505.5	2.52	4"x2	404.4	1.67	4"x2	606.6	3.53	4"x2
PFI-1218N-3D2DS-O1	Ethylene Glycol	516.5	2.3	4"x2	413.2	1.53	4"x2	619.8	3.23	4"x2
PFI-1218N-3D1ES-O1	Ethylene Glycol	905.4	7.39	4"x2	724.3	4.89	4"x2	1086.4	8.18	4"x4
PFI-1218N-3D2DS-P1	Ethylene Glycol	916.4	6.65	4"x2	733.1	4.4	4"x2	1099.6	7.1	4"x4
PFI-1218N-3D2ES-P1	Ethylene Glycol	916.4	6.65	4"x2	733.1	4.4	4"x2	1099.6	7.1	4"x4
PFI-1218N-3D2DS-Q1	Ethylene Glycol	916.4	6.65	4"x2	733.1	4.4	4"x2	1099.6	7.1	4"x4
PFI-1218N-3D4DS-Q1	Ethylene Glycol	940.6	4.15	4"x4	752.4	3.69	4"x2	1128.7	5.82	4"x4
PFI-1218N-3D4ES-Q1	Ethylene Glycol	940.6	4.15	4"x4	752.4	3.69	4"x2	1128.7	5.82	4"x4
PFI-1218N-3D1ES-R1	Ethylene Glycol	905.4	7.39	4"x2	724.3	4.89	4"x2	1086.4	8.18	4"x4
PFI-1218N-3D4ES-R1	Ethylene Glycol	940.6	4.15	4"x4	752.4	3.69	4"x2	1128.7	5.82	4"x4
PFI-1218N-4D1DS-K1	Ethylene Glycol	505.5	3.13	4"x2	404.4	2.08	4"x2	606.6	4.39	4"x2
PFI-1218N-4D1ES-L1	Ethylene Glycol	905.4	9.2	4"x2	724.3	6.09	4"x2	1086.4	10.63	4"x4
PFI-1218N-4D2ES-M1	Ethylene Glycol	916.4	8.2	4"x2	733.1	5.43	4"x2	1099.6	9.18	4"x4
PFI-1218N-4D2DS-N1	Ethylene Glycol	916.4	8.2	4"x2	733.1	5.43	4"x2	1099.6	9.18	4"x4
PFI-1218N-4D1ES-N1	Ethylene Glycol	905.4	9.2	4"x2	724.3	6.09	4"x2	1086.4	10.63	4"x4
PFI-1218N-4D3DS-O1	Ethylene Glycol	927.4	7.43	4"x2	741.9	4.92	4"x2	1112.8	8.09	4"x4
PFI-1218N-4D1ES-O1	Ethylene Glycol	905.4	9.2	4"x2	724.3	6.09	4"x2	1086.4	10.63	4"x4
PFI-1218N-4D1ES-P1	Ethylene Glycol	905.4	9.2	4"x2	724.3	6.09	4"x2	1086.4	10.63	4"x4
PFI-1218N-4D1DS-Q1	Ethylene Glycol	905.4	9.2	4"x2	724.3	6.09	4"x2	1086.4	10.63	4"x4
PFI-1218N-4D2ES-Q1	Ethylene Glycol	916.4	8.2	4"x2	733.1	5.43	4"x2	1099.6	9.18	4"x4
PFI-1218N-4D4ES-Q1	Ethylene Glycol	940.6	5.05	4"x4	752.4	4.46	4"x2	1128.7	7.07	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-4D2ES-R1	Ethylene Glycol	916.4	8.2	4"x2	733.1	5.43	4"x2	1099.6	9.18	4"x4
PFI-1218N-4D4ES-R1	Ethylene Glycol	940.6	5.05	4"x4	752.4	4.46	4"x2	1128.7	7.07	4"x4
PFI-1218N-5D1DS-K1	Ethylene Glycol	505.5	3.75	4"x2	404.4	2.48	4"x2	606.6	5.25	4"x2
PFI-1218N-5D1ES-O1	Ethylene Glycol	905.4	11.02	4"x2	724.3	7.29	4"x2	1086.4	13.08	4"x4
PFI-1218N-5D2ES-P1	Ethylene Glycol	916.4	9.75	4"x2	733.1	6.46	4"x2	1099.6	11.27	4"x4
PFI-1218N-6D2DS-M1	Ethylene Glycol	916.4	11.31	4"x2	733.1	7.48	4"x2	1099.6	13.35	4"x4
PFI-1218N-6D1DS-N1	Ethylene Glycol	905.4	12.83	4"x2	724.3	8.49	4"x2	1086.4	15.53	4"x4
PFI-1218N-6D1DS-R1	Ethylene Glycol	905.4	12.83	4"x2	724.3	8.49	4"x2	1086.4	15.53	4"x4
PFI-1218N-6D1ES-R1	Ethylene Glycol	905.4	12.83	4"x2	724.3	8.49	4"x2	1086.4	15.53	4"x4
PFI-1218N-6D3ES-R1	Ethylene Glycol	927.4	10.14	4"x2	741.9	6.71	4"x2	1112.8	11.71	4"x4
PFI-1218N-3D4BS-K1	Ethylene Glycol	540.7	2	4"x2	432.5	1.33	4"x2	648.8	2.8	4"x2
PFI-1218N-3D4BS-L1	Ethylene Glycol	540.7	2	4"x2	432.5	1.33	4"x2	648.8	2.8	4"x2
PFI-1218N-3D4BS-N1	Ethylene Glycol	540.7	2	4"x2	432.5	1.33	4"x2	648.8	2.8	4"x2
PFI-1218N-3D4BS-O1	Ethylene Glycol	540.7	2	4"x2	432.5	1.33	4"x2	648.8	2.8	4"x2
PFI-1218N-3D4BS-P1	Ethylene Glycol	540.7	2	4"x2	432.5	1.33	4"x2	648.8	2.8	4"x2
PFI-1218N-4D4BS-K1	Ethylene Glycol	540.7	2.42	4"x2	432.5	1.6	4"x2	648.8	3.39	4"x2
PFI-1218N-4D4BS-L1	Ethylene Glycol	540.7	2.42	4"x2	432.5	1.6	4"x2	648.8	3.39	4"x2
PFI-1218N-4D3BS-M1	Ethylene Glycol	527.5	2.62	4"x2	422.0	1.74	4"x2	633.0	3.67	4"x2
PFI-1218N-4D3BS-N1	Ethylene Glycol	527.5	2.62	4"x2	422.0	1.74	4"x2	633.0	3.67	4"x2
PFI-1218N-4D3BS-O1	Ethylene Glycol	527.5	2.62	4"x2	422.0	1.74	4"x2	633.0	3.67	4"x2
PFI-1218N-4D4BS-P1	Ethylene Glycol	940.6	5.05	4"x4	752.4	4.46	4"x2	1128.7	7.07	4"x4
PFI-1218N-4D3BS-Q1	Ethylene Glycol	927.4	7.43	4"x2	741.9	4.92	4"x2	1112.8	8.09	4"x4
PFI-1218N-5D2BS-K1	Ethylene Glycol	516.5	3.38	4"x2	413.2	2.24	4"x2	619.8	4.73	4"x2
PFI-1218N-5D2BS-L1	Ethylene Glycol	516.5	3.38	4"x2	413.2	2.24	4"x2	619.8	4.73	4"x2
PFI-1218N-5D2BS-M1	Ethylene Glycol	516.5	3.38	4"x2	413.2	2.24	4"x2	619.8	4.73	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-5D2BS-N1	Ethylene Glycol	516.5	3.38	4"x2	413.2	2.24	4"x2	619.8	4.73	4"x2
PFI-1218N-5D3BS-O1	Ethylene Glycol	527.5	3.1	4"x2	422.0	2.05	4"x2	633.0	4.34	4"x2
PFI-1218N-5D2BS-P1	Ethylene Glycol	916.4	9.75	4"x2	733.1	6.46	4"x2	1099.6	11.27	4"x4
PFI-1218N-5D3BS-Q1	Ethylene Glycol	927.4	8.79	4"x2	741.9	5.82	4"x2	1112.8	9.9	4"x4
PFI-1218N-6D1BS-K1	Ethylene Glycol	505.5	4.37	4"x2	404.4	2.89	4"x2	606.6	6.12	4"x2
PFI-1218N-6D1BS-L1	Ethylene Glycol	505.5	4.37	4"x2	404.4	2.89	4"x2	606.6	6.12	4"x2
PFI-1218N-6D1BS-M1	Ethylene Glycol	505.5	4.37	4"x2	404.4	2.89	4"x2	606.6	6.12	4"x2
PFI-1218N-6D1BS-N1	Ethylene Glycol	505.5	4.37	4"x2	404.4	2.89	4"x2	606.6	6.12	4"x2
PFI-1218N-6D1BS-O1	Ethylene Glycol	905.4	12.83	4"x2	724.3	8.49	4"x2	1086.4	15.53	4"x4
PFI-1218N-6D1BS-P1	Ethylene Glycol	905.4	12.83	4"x2	724.3	8.49	4"x2	1086.4	15.53	4"x4
PFI-1218N-6D1BS-Q1	Ethylene Glycol	905.4	12.83	4"x2	724.3	8.49	4"x2	1086.4	15.53	4"x4
PFI-1218N-6D2BS-R1	Ethylene Glycol	916.4	11.31	4"x2	733.1	7.48	4"x2	1099.6	13.35	4"x4
PFI-1218N-2D1DZ-M1	Ethylene Glycol	226.3	2.64	4"x2	181.1	1.75	4"x2	271.6	3.7	4"x2
PFI-1218N-2D4EZ-M1	Ethylene Glycol	235.1	1.97	4"x2	188.1	1.3	4"x2	282.2	2.76	4"x2
PFI-1218N-2D1DZ-N1	Ethylene Glycol	226.3	2.64	4"x2	181.1	1.75	4"x2	271.6	3.7	4"x2
PFI-1218N-2D2DZ-N1	Ethylene Glycol	229.1	2.37	4"x2	183.3	1.57	4"x2	274.9	3.32	4"x2
PFI-1218N-2D3EZ-N1	Ethylene Glycol	231.8	2.16	4"x2	185.5	1.43	4"x2	278.2	3.03	4"x2
PFI-1218N-2D2DZ-O1	Ethylene Glycol	229.1	2.37	4"x2	183.3	1.57	4"x2	274.9	3.32	4"x2
PFI-1218N-2D3EZ-O1	Ethylene Glycol	231.8	2.16	4"x2	185.5	1.43	4"x2	278.2	3.03	4"x2
PFI-1218N-2D4DZ-P1	Ethylene Glycol	235.1	1.96	4"x2	188.1	1.3	4"x2	282.2	2.75	4"x2
PFI-1218N-3D1EZ-K1	Ethylene Glycol	226.3	3.66	4"x2	181.1	2.42	4"x2	271.6	5.13	4"x2
PFI-1218N-3D1EZ-L1	Ethylene Glycol	226.3	3.66	4"x2	181.1	2.42	4"x2	271.6	5.13	4"x2
PFI-1218N-3D4EZ-M1	Ethylene Glycol	435.1	8.11	4"x2	348.1	5.36	4"x2	522.1	11.36	4"x2
PFI-1218N-3D1DZ-N1	Ethylene Glycol	226.3	3.65	4"x2	181.1	2.42	4"x2	271.6	5.11	4"x2
PFI-1218N-3D1EZ-N1	Ethylene Glycol	426.3	11.81	4"x2	341.0	7.81	4"x2	511.5	16.55	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-3D1DZ-O1	Ethylene Glycol	226.3	3.65	4"x2	181.1	2.42	4"x2	271.6	5.11	4"x2
PFI-1218N-3D2DZ-O1	Ethylene Glycol	429.0	10.22	4"x2	343.2	6.76	4"x2	514.8	14.32	4"x2
PFI-1218N-3D1EZ-O1	Ethylene Glycol	426.3	11.81	4"x2	341.0	7.81	4"x2	511.5	16.55	4"x2
PFI-1218N-3D2DZ-P1	Ethylene Glycol	429.0	10.22	4"x2	343.2	6.76	4"x2	514.8	14.32	4"x2
PFI-1218N-3D2EZ-P1	Ethylene Glycol	429.0	10.26	4"x2	343.2	6.79	4"x2	514.8	14.38	4"x2
PFI-1218N-3D2DZ-Q1	Ethylene Glycol	429.0	10.22	4"x2	343.2	6.76	4"x2	514.8	14.32	4"x2
PFI-1218N-3D4DZ-Q1	Ethylene Glycol	435.1	8.06	4"x2	348.1	5.33	4"x2	522.1	11.3	4"x2
PFI-1218N-3D4EZ-Q1	Ethylene Glycol	435.1	8.11	4"x2	348.1	5.36	4"x2	522.1	11.36	4"x2
PFI-1218N-3D1EZ-R1	Ethylene Glycol	426.3	11.81	4"x2	341.0	7.81	4"x2	511.5	16.55	4"x2
PFI-1218N-3D4EZ-R1	Ethylene Glycol	435.1	8.11	4"x2	348.1	5.36	4"x2	522.1	11.36	4"x2
PFI-1218N-4D1DZ-K1	Ethylene Glycol	226.3	4.66	4"x2	181.1	3.09	4"x2	271.6	6.53	4"x2
PFI-1218N-4D1EZ-L1	Ethylene Glycol	426.3	14.99	4"x2	341.0	9.92	4"x2	511.5	21.01	4"x2
PFI-1218N-4D2EZ-M1	Ethylene Glycol	429.0	13.03	4"x2	343.2	8.62	4"x2	514.8	18.26	4"x2
PFI-1218N-4D2DZ-N1	Ethylene Glycol	429.0	12.99	4"x2	343.2	8.59	4"x2	514.8	18.2	4"x2
PFI-1218N-4D1EZ-N1	Ethylene Glycol	426.3	14.99	4"x2	341.0	9.92	4"x2	511.5	21.01	4"x2
PFI-1218N-4D3DZ-O1	Ethylene Glycol	431.8	11.49	4"x2	345.4	7.6	4"x2	518.1	16.09	4"x2
PFI-1218N-4D1EZ-O1	Ethylene Glycol	426.3	14.99	4"x2	341.0	9.92	4"x2	511.5	21.01	4"x2
PFI-1218N-4D1EZ-P1	Ethylene Glycol	426.3	14.99	4"x2	341.0	9.92	4"x2	511.5	21.01	4"x2
PFI-1218N-4D1DZ-Q1	Ethylene Glycol	426.3	15.04	4"x2	341.0	9.95	4"x2	511.5	21.07	4"x2
PFI-1218N-4D2EZ-Q1	Ethylene Glycol	429.0	13.03	4"x2	343.2	8.62	4"x2	514.8	18.26	4"x2
PFI-1218N-4D4EZ-Q1	Ethylene Glycol	435.1	10.15	4"x2	348.1	6.71	4"x2	522.1	14.22	4"x2
PFI-1218N-4D2EZ-R1	Ethylene Glycol	429.0	13.03	4"x2	343.2	8.62	4"x2	514.8	18.26	4"x2
PFI-1218N-4D4EZ-R1	Ethylene Glycol	435.1	10.15	4"x2	348.1	6.71	4"x2	522.1	14.22	4"x2
PFI-1218N-5D1DZ-K1	Ethylene Glycol	226.3	5.67	4"x2	181.1	3.75	4"x2	271.6	7.94	4"x2
PFI-1218N-5D1EZ-O1	Ethylene Glycol	426.3	18.21	4"x2	341.0	12.05	4"x2	511.5	25.52	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-5D2EZ-P1	Ethylene Glycol	429.0	15.8	4"x2	343.2	10.45	4"x2	514.8	22.15	4"x2
PFI-1218N-6D2DZ-M1	Ethylene Glycol	429.0	18.53	4"x2	343.2	12.26	4"x2	514.8	25.97	4"x2
PFI-1218N-6D1DZ-N1	Ethylene Glycol	426.3	21.48	4"x2	341.0	14.21	4"x2	511.5	30.1	4"x2
PFI-1218N-6D1DZ-R1	Ethylene Glycol	426.3	21.48	4"x2	341.0	14.21	4"x2	511.5	30.1	4"x2
PFI-1218N-6D1EZ-R1	Ethylene Glycol	426.3	21.52	4"x2	341.0	14.24	4"x2	511.5	30.16	4"x2
PFI-1218N-3D4BT-K1	Ethylene Glycol	235.1	2.59	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1218N-3D4BT-L1	Ethylene Glycol	235.1	2.59	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1218N-3D4BT-N1	Ethylene Glycol	235.1	2.59	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1218N-3D4BT-O1	Ethylene Glycol	235.1	2.59	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1218N-3D4BT-P1	Ethylene Glycol	235.1	2.59	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1218N-4D4BT-K1	Ethylene Glycol	235.1	3.24	4"x2	188.1	2.15	4"x2	282.2	4.54	4"x2
PFI-1218N-4D4BT-L1	Ethylene Glycol	235.1	3.24	4"x2	188.1	2.15	4"x2	282.2	4.54	4"x2
PFI-1218N-4D3BT-M1	Ethylene Glycol	231.8	3.64	4"x2	185.5	2.41	4"x2	278.2	5.1	4"x2
PFI-1218N-4D3BT-N1	Ethylene Glycol	231.8	3.64	4"x2	185.5	2.41	4"x2	278.2	5.1	4"x2
PFI-1218N-4D3BT-O1	Ethylene Glycol	231.8	3.64	4"x2	185.5	2.41	4"x2	278.2	5.1	4"x2
PFI-1218N-4D4BT-P1	Ethylene Glycol	435.1	10.12	4"x2	348.1	6.7	4"x2	522.1	14.19	4"x2
PFI-1218N-4D3BT-Q1	Ethylene Glycol	431.8	11.51	4"x2	345.4	7.61	4"x2	518.1	16.12	4"x2
PFI-1218N-5D2BT-K1	Ethylene Glycol	229.1	4.94	4"x2	183.3	3.27	4"x2	274.9	6.91	4"x2
PFI-1218N-5D2BT-L1	Ethylene Glycol	229.1	4.94	4"x2	183.3	3.27	4"x2	274.9	6.91	4"x2
PFI-1218N-5D2BT-M1	Ethylene Glycol	229.1	4.94	4"x2	183.3	3.27	4"x2	274.9	6.91	4"x2
PFI-1218N-5D2BT-N1	Ethylene Glycol	229.1	4.94	4"x2	183.3	3.27	4"x2	274.9	6.91	4"x2
PFI-1218N-5D3BT-O1	Ethylene Glycol	431.8	13.74	4"x2	345.4	9.09	4"x2	518.1	19.25	4"x2
PFI-1218N-5D2BT-P1	Ethylene Glycol	429.0	15.76	4"x2	343.2	10.43	4"x2	514.8	22.08	4"x2
PFI-1218N-5D3BT-Q1	Ethylene Glycol	431.8	13.74	4"x2	345.4	9.09	4"x2	518.1	19.25	4"x2
PFI-1218N-6D1BT-K1	Ethylene Glycol	226.3	6.65	4"x2	181.1	4.4	4"x2	271.6	9.32	4"x2





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-6D1BT-L1	Ethylene Glycol	226.3	6.65	4"x2	181.1	4.4	4"x2	271.6	9.32	4"x2
PFI-1218N-6D1BT-M1	Ethylene Glycol	226.3	6.65	4"x2	181.1	4.4	4"x2	271.6	9.32	4"x2
PFI-1218N-6D1BT-N1	Ethylene Glycol	426.3	21.46	4"x2	341.0	14.19	4"x2	511.5	30.06	4"x2
PFI-1218N-6D1BT-O1	Ethylene Glycol	426.3	21.46	4"x2	341.0	14.19	4"x2	511.5	30.06	4"x2
PFI-1218N-6D1BT-P1	Ethylene Glycol	426.3	21.46	4"x2	341.0	14.19	4"x2	511.5	30.06	4"x2
PFI-1218N-6D1BT-Q1	Ethylene Glycol	426.3	21.46	4"x2	341.0	14.19	4"x2	511.5	30.06	4"x2
PFI-1236N-2D1DS-M2	Ethylene Glycol	1011.0	1.9	4"x4	808.8	1.26	4"x4	1213.1	2.66	4"x4
PFI-1236N-2D4ES-M2	Ethylene Glycol	1081.4	1.58	4"x4	865.1	1.05	4"x4	1297.6	2.22	4"x4
PFI-1236N-2D1DS-N2	Ethylene Glycol	1011.0	1.9	4"x4	808.8	1.26	4"x4	1213.1	2.66	4"x4
PFI-1236N-2D2DS-N2	Ethylene Glycol	1033.0	1.77	4"x4	826.4	1.17	4"x4	1239.5	2.47	4"x4
PFI-1236N-2D3ES-N2	Ethylene Glycol	1055.0	1.67	4"x4	844.0	1.11	4"x4	1265.9	2.34	4"x4
PFI-1236N-2D2DS-O2	Ethylene Glycol	1033.0	1.77	4"x4	826.4	1.17	4"x4	1239.5	2.47	4"x4
PFI-1236N-2D3ES-O2	Ethylene Glycol	1055.0	1.67	4"x4	844.0	1.11	4"x4	1265.9	2.34	4"x4
PFI-1236N-2D4DS-P2	Ethylene Glycol	1081.4	1.58	4"x4	865.1	1.05	4"x4	1297.6	2.22	4"x4
PFI-1236N-3D1ES-K2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-1236N-3D1ES-L2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-1236N-3D4ES-M2	Ethylene Glycol	1881.1	4.15	4"x8	1504.9	3.69	4"x4	2257.3	5.82	4"x8
PFI-1236N-3D1DS-N2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-1236N-3D1ES-N2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-1236N-3D1DS-O2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-1236N-3D2DS-O2	Ethylene Glycol	1033.0	2.3	4"x4	826.4	1.53	4"x4	1239.5	3.23	4"x4
PFI-1236N-3D1ES-O2	Ethylene Glycol	1810.7	7.39	4"x4	1448.6	4.89	4"x4	2172.8	8.18	4"x8
PFI-1236N-3D2DS-P2	Ethylene Glycol	1832.7	6.65	4"x4	1466.2	4.4	4"x4	2199.2	7.1	4"x8
PFI-1236N-3D2ES-P2	Ethylene Glycol	1832.7	6.65	4"x4	1466.2	4.4	4"x4	2199.2	7.1	4"x8
PFI-1236N-3D2DS-Q2	Ethylene Glycol	1832.7	6.65	4"x4	1466.2	4.4	4"x4	2199.2	7.1	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-3D4DS-Q2	Ethylene Glycol	1881.1	4.15	4"x8	1504.9	3.69	4"x4	2257.3	5.82	4"x8
PFI-1236N-3D4ES-Q2	Ethylene Glycol	1881.1	4.15	4"x8	1504.9	3.69	4"x4	2257.3	5.82	4"x8
PFI-1236N-3D1ES-R2	Ethylene Glycol	1810.7	7.39	4"x4	1448.6	4.89	4"x4	2172.8	8.18	4"x8
PFI-1236N-3D4ES-R2	Ethylene Glycol	1881.1	4.15	4"x8	1504.9	3.69	4"x4	2257.3	5.82	4"x8
PFI-1236N-4D1DS-K2	Ethylene Glycol	1011.0	3.13	4"x4	808.8	2.08	4"x4	1213.1	4.39	4"x4
PFI-1236N-4D1ES-L2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-1236N-4D2ES-M2	Ethylene Glycol	1832.7	8.2	4"x4	1466.2	5.43	4"x4	2199.2	9.18	4"x8
PFI-1236N-4D2DS-N2	Ethylene Glycol	1832.7	8.2	4"x4	1466.2	5.43	4"x4	2199.2	9.18	4"x8
PFI-1236N-4D1ES-N2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-1236N-4D3DS-O2	Ethylene Glycol	1854.7	7.43	4"x4	1483.8	4.92	4"x4	2225.6	8.09	4"x8
PFI-1236N-4D1ES-O2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-1236N-4D1ES-P2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-1236N-4D1DS-Q2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-1236N-4D2ES-Q2	Ethylene Glycol	1832.7	8.2	4"x4	1466.2	5.43	4"x4	2199.2	9.18	4"x8
PFI-1236N-4D4ES-Q2	Ethylene Glycol	1881.1	5.05	4"x8	1504.9	4.46	4"x4	2257.3	7.07	4"x8
PFI-1236N-4D2ES-R2	Ethylene Glycol	1832.7	8.2	4"x4	1466.2	5.43	4"x4	2199.2	9.18	4"x8
PFI-1236N-4D4ES-R2	Ethylene Glycol	1881.1	5.05	4"x8	1504.9	4.46	4"x4	2257.3	7.07	4"x8
PFI-1236N-5D1DS-K2	Ethylene Glycol	1011.0	3.75	4"x4	808.8	2.48	4"x4	1213.1	5.25	4"x4
PFI-1236N-5D1ES-O2	Ethylene Glycol	1810.7	11.02	4"x4	1448.6	7.29	4"x4	2172.8	13.08	4"x8
PFI-1236N-5D2ES-P2	Ethylene Glycol	1832.7	9.75	4"x4	1466.2	6.46	4"x4	2199.2	11.27	4"x8
PFI-1236N-6D2DS-M2	Ethylene Glycol	1832.7	11.3	4"x4	1466.2	7.48	4"x4	2199.2	13.35	4"x8
PFI-1236N-6D1DS-N2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-1236N-6D1DS-R2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-1236N-6D1ES-R2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-1236N-3D4BS-K2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-3D4BS-L2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-1236N-3D4BS-N2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-1236N-3D4BS-O2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-1236N-3D4BS-P2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-1236N-4D4BS-K2	Ethylene Glycol	1081.4	2.42	4"x4	865.1	1.6	4"x4	1297.6	3.39	4"x4
PFI-1236N-4D4BS-L2	Ethylene Glycol	1081.4	2.42	4"x4	865.1	1.6	4"x4	1297.6	3.39	4"x4
PFI-1236N-4D3BS-M2	Ethylene Glycol	1055.0	2.62	4"x4	844.0	1.74	4"x4	1265.9	3.67	4"x4
PFI-1236N-4D3BS-N2	Ethylene Glycol	1055.0	2.62	4"x4	844.0	1.74	4"x4	1265.9	3.67	4"x4
PFI-1236N-4D3BS-O2	Ethylene Glycol	1055.0	2.62	4"x4	844.0	1.74	4"x4	1265.9	3.67	4"x4
PFI-1236N-4D4BS-P2	Ethylene Glycol	1881.1	5.05	4"x8	1504.9	4.46	4"x4	2257.3	7.07	4"x8
PFI-1236N-4D3BS-Q2	Ethylene Glycol	1854.7	7.43	4"x4	1483.8	4.92	4"x4	2225.6	8.09	4"x8
PFI-1236N-5D2BS-K2	Ethylene Glycol	1033.0	3.38	4"x4	826.4	2.24	4"x4	1239.5	4.73	4"x4
PFI-1236N-5D2BS-L2	Ethylene Glycol	1033.0	3.38	4"x4	826.4	2.24	4"x4	1239.5	4.73	4"x4
PFI-1236N-5D2BS-M2	Ethylene Glycol	1033.0	3.38	4"x4	826.4	2.24	4"x4	1239.5	4.73	4"x4
PFI-1236N-5D2BS-N2	Ethylene Glycol	1033.0	3.38	4"x4	826.4	2.24	4"x4	1239.5	4.73	4"x4
PFI-1236N-5D3BS-O2	Ethylene Glycol	1055.0	3.1	4"x4	844.0	2.05	4"x4	1265.9	4.34	4"x4
PFI-1236N-5D2BS-P2	Ethylene Glycol	1832.7	9.75	4"x4	1466.2	6.46	4"x4	2199.2	11.27	4"x8
PFI-1236N-5D3BS-Q2	Ethylene Glycol	1854.7	8.78	4"x4	1483.8	5.82	4"x4	2225.6	9.9	4"x8
PFI-1236N-6D1BS-K2	Ethylene Glycol	1011.0	4.37	4"x4	808.8	2.89	4"x4	1213.1	6.12	4"x4
PFI-1236N-6D1BS-L2	Ethylene Glycol	1011.0	4.37	4"x4	808.8	2.89	4"x4	1213.1	6.12	4"x4
PFI-1236N-6D1BS-M2	Ethylene Glycol	1011.0	4.37	4"x4	808.8	2.89	4"x4	1213.1	6.12	4"x4
PFI-1236N-6D1BS-N2	Ethylene Glycol	1011.0	4.37	4"x4	808.8	2.89	4"x4	1213.1	6.12	4"x4
PFI-1236N-6D1BS-O2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-1236N-6D1BS-P2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-1236N-6D1BS-Q2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-6D2BS-R2	Ethylene Glycol	1832.7	11.3	4"x4	1466.2	7.48	4"x4	2199.2	13.35	4"x8
PFI-1236N-2D1DZ-M2	Ethylene Glycol	452.7	2.64	4"x4	362.1	1.75	4"x4	543.2	3.7	4"x4
PFI-1236N-2D4EZ-M2	Ethylene Glycol	470.3	1.97	4"x4	376.2	1.3	4"x4	564.3	2.76	4"x4
PFI-1236N-2D1DZ-N2	Ethylene Glycol	452.7	2.64	4"x4	362.1	1.75	4"x4	543.2	3.7	4"x4
PFI-1236N-2D2DZ-N2	Ethylene Glycol	458.2	2.37	4"x4	366.5	1.57	4"x4	549.8	3.32	4"x4
PFI-1236N-2D3EZ-N2	Ethylene Glycol	463.7	2.16	4"x4	370.9	1.43	4"x4	556.4	3.03	4"x4
PFI-1236N-2D2DZ-O2	Ethylene Glycol	458.2	2.37	4"x4	366.5	1.57	4"x4	549.8	3.32	4"x4
PFI-1236N-2D3EZ-O2	Ethylene Glycol	463.7	2.16	4"x4	370.9	1.43	4"x4	556.4	3.03	4"x4
PFI-1236N-2D4DZ-P2	Ethylene Glycol	470.3	1.97	4"x4	376.2	1.3	4"x4	564.3	2.75	4"x4
PFI-1236N-3D1EZ-K2	Ethylene Glycol	452.7	3.66	4"x4	362.1	2.42	4"x4	543.2	5.13	4"x4
PFI-1236N-3D1EZ-L2	Ethylene Glycol	452.7	3.66	4"x4	362.1	2.42	4"x4	543.2	5.13	4"x4
PFI-1236N-3D4EZ-M2	Ethylene Glycol	870.2	8.11	4"x4	696.1	5.36	4"x4	1044.2	11.36	4"x4
PFI-1236N-3D1DZ-N2	Ethylene Glycol	452.7	3.65	4"x4	362.1	2.42	4"x4	543.2	5.11	4"x4
PFI-1236N-3D1EZ-N2	Ethylene Glycol	852.6	11.81	4"x4	682.0	7.81	4"x4	1023.1	16.55	4"x4
PFI-1236N-3D1DZ-O2	Ethylene Glycol	452.7	3.65	4"x4	362.1	2.42	4"x4	543.2	5.11	4"x4
PFI-1236N-3D2DZ-O2	Ethylene Glycol	858.1	10.22	4"x4	686.4	6.76	4"x4	1029.7	14.32	4"x4
PFI-1236N-3D1EZ-O2	Ethylene Glycol	852.6	11.81	4"x4	682.0	7.81	4"x4	1023.1	16.55	4"x4
PFI-1236N-3D2DZ-P2	Ethylene Glycol	858.1	10.22	4"x4	686.4	6.76	4"x4	1029.7	14.32	4"x4
PFI-1236N-3D2EZ-P2	Ethylene Glycol	858.1	10.26	4"x4	686.4	6.79	4"x4	1029.7	14.38	4"x4
PFI-1236N-3D2DZ-Q2	Ethylene Glycol	858.1	10.22	4"x4	686.4	6.76	4"x4	1029.7	14.32	4"x4
PFI-1236N-3D4DZ-Q2	Ethylene Glycol	870.2	8.06	4"x4	696.1	5.33	4"x4	1044.2	11.3	4"x4
PFI-1236N-3D4EZ-Q2	Ethylene Glycol	870.2	8.11	4"x4	696.1	5.36	4"x4	1044.2	11.36	4"x4
PFI-1236N-3D1EZ-R2	Ethylene Glycol	852.6	11.81	4"x4	682.0	7.81	4"x4	1023.1	16.55	4"x4
PFI-1236N-3D4EZ-R2	Ethylene Glycol	870.2	8.11	4"x4	696.1	5.36	4"x4	1044.2	11.36	4"x4
PFI-1236N-4D1DZ-K2	Ethylene Glycol	452.7	4.66	4"x4	362.1	3.08	4"x4	543.2	6.53	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-4D1EZ-L2	Ethylene Glycol	852.6	14.99	4"x4	682.0	9.92	4"x4	1023.1	21.01	4"x4
PFI-1236N-4D2EZ-M2	Ethylene Glycol	858.1	13.03	4"x4	686.4	8.62	4"x4	1029.7	18.27	4"x4
PFI-1236N-4D2DZ-N2	Ethylene Glycol	858.1	12.99	4"x4	686.4	8.59	4"x4	1029.7	18.2	4"x4
PFI-1236N-4D1EZ-N2	Ethylene Glycol	852.6	14.99	4"x4	682.0	9.92	4"x4	1023.1	21.01	4"x4
PFI-1236N-4D3DZ-O2	Ethylene Glycol	863.6	11.49	4"x4	690.8	7.6	4"x4	1036.3	16.1	4"x4
PFI-1236N-4D1EZ-O2	Ethylene Glycol	852.6	14.99	4"x4	682.0	9.92	4"x4	1023.1	21.01	4"x4
PFI-1236N-4D1EZ-P2	Ethylene Glycol	852.6	14.99	4"x4	682.0	9.92	4"x4	1023.1	21.01	4"x4
PFI-1236N-4D1DZ-Q2	Ethylene Glycol	852.6	15.04	4"x4	682.0	9.95	4"x4	1023.1	21.07	4"x4
PFI-1236N-4D2EZ-Q2	Ethylene Glycol	858.1	13.03	4"x4	686.4	8.62	4"x4	1029.7	18.27	4"x4
PFI-1236N-4D4EZ-Q2	Ethylene Glycol	870.2	10.15	4"x4	696.1	6.71	4"x4	1044.2	14.22	4"x4
PFI-1236N-4D2EZ-R2	Ethylene Glycol	858.1	13.03	4"x4	686.4	8.62	4"x4	1029.7	18.27	4"x4
PFI-1236N-4D4EZ-R2	Ethylene Glycol	870.2	10.15	4"x4	696.1	6.71	4"x4	1044.2	14.22	4"x4
PFI-1236N-5D1DZ-K2	Ethylene Glycol	452.7	5.67	4"x4	362.1	3.75	4"x4	543.2	7.94	4"x4
PFI-1236N-5D1EZ-O2	Ethylene Glycol	852.6	18.21	4"x4	682.0	12.05	4"x4	1023.1	25.52	4"x4
PFI-1236N-5D2EZ-P2	Ethylene Glycol	858.1	15.8	4"x4	686.4	10.45	4"x4	1029.7	22.15	4"x4
PFI-1236N-6D2DZ-M2	Ethylene Glycol	858.1	18.53	4"x4	686.4	12.26	4"x4	1029.7	25.97	4"x4
PFI-1236N-6D1DZ-N2	Ethylene Glycol	852.6	21.48	4"x4	682.0	14.21	4"x4	1023.1	30.1	4"x4
PFI-1236N-6D1DZ-R2	Ethylene Glycol	852.6	21.48	4"x4	682.0	14.21	4"x4	1023.1	30.1	4"x4
PFI-1236N-6D1EZ-R2	Ethylene Glycol	852.6	21.52	4"x4	682.0	14.24	4"x4	1023.1	30.16	4"x4
PFI-1236N-3D4BT-K2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1236N-3D4BT-L2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1236N-3D4BT-N2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1236N-3D4BT-O2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1236N-3D4BT-P2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1236N-4D4BT-K2	Ethylene Glycol	470.3	3.24	4"x4	376.2	2.15	4"x4	564.3	4.54	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-4D4BT-L2	Ethylene Glycol	470.3	3.24	4"x4	376.2	2.15	4"x4	564.3	4.54	4"x4
PFI-1236N-4D3BT-M2	Ethylene Glycol	463.7	3.64	4"x4	370.9	2.41	4"x4	556.4	5.1	4"x4
PFI-1236N-4D3BT-N2	Ethylene Glycol	463.7	3.64	4"x4	370.9	2.41	4"x4	556.4	5.1	4"x4
PFI-1236N-4D3BT-O2	Ethylene Glycol	463.7	3.64	4"x4	370.9	2.41	4"x4	556.4	5.1	4"x4
PFI-1236N-4D4BT-P2	Ethylene Glycol	870.2	10.12	4"x4	696.1	6.7	4"x4	1044.2	14.19	4"x4
PFI-1236N-4D3BT-Q2	Ethylene Glycol	863.6	11.51	4"x4	690.8	7.61	4"x4	1036.3	16.13	4"x4
PFI-1236N-5D2BT-K2	Ethylene Glycol	458.2	4.94	4"x4	366.5	3.27	4"x4	549.8	6.91	4"x4
PFI-1236N-5D2BT-L2	Ethylene Glycol	458.2	4.94	4"x4	366.5	3.27	4"x4	549.8	6.91	4"x4
PFI-1236N-5D2BT-M2	Ethylene Glycol	458.2	4.94	4"x4	366.5	3.27	4"x4	549.8	6.91	4"x4
PFI-1236N-5D2BT-N2	Ethylene Glycol	458.2	4.94	4"x4	366.5	3.27	4"x4	549.8	6.91	4"x4
PFI-1236N-5D3BT-O2	Ethylene Glycol	863.6	13.74	4"x4	690.8	9.09	4"x4	1036.3	19.26	4"x4
PFI-1236N-5D2BT-P2	Ethylene Glycol	858.1	15.76	4"x4	686.4	10.43	4"x4	1029.7	22.09	4"x4
PFI-1236N-5D3BT-Q2	Ethylene Glycol	863.6	13.74	4"x4	690.8	9.09	4"x4	1036.3	19.26	4"x4
PFI-1236N-6D1BT-K2	Ethylene Glycol	452.7	6.65	4"x4	362.1	4.4	4"x4	543.2	9.32	4"x4
PFI-1236N-6D1BT-L2	Ethylene Glycol	452.7	6.65	4"x4	362.1	4.4	4"x4	543.2	9.32	4"x4
PFI-1236N-6D1BT-M2	Ethylene Glycol	452.7	6.65	4"x4	362.1	4.4	4"x4	543.2	9.32	4"x4
PFI-1236N-6D1BT-N2	Ethylene Glycol	852.6	21.46	4"x4	682.0	14.19	4"x4	1023.1	30.07	4"x4
PFI-1236N-6D1BT-O2	Ethylene Glycol	852.6	21.46	4"x4	682.0	14.19	4"x4	1023.1	30.07	4"x4
PFI-1236N-6D1BT-P2	Ethylene Glycol	852.6	21.46	4"x4	682.0	14.19	4"x4	1023.1	30.07	4"x4
PFI-1236N-6D1BT-Q2	Ethylene Glycol	852.6	21.46	4"x4	682.0	14.19	4"x4	1023.1	30.07	4"x4
PFI-2418N-2D1DS-M2	Ethylene Glycol	1011.0	1.9	4"x4	808.8	1.26	4"x4	1213.1	2.66	4"x4
PFI-2418N-2D4ES-M2	Ethylene Glycol	1081.4	1.58	4"x4	865.1	1.05	4"x4	1297.6	2.22	4"x4
PFI-2418N-2D1DS-N2	Ethylene Glycol	1011.0	1.9	4"x4	808.8	1.26	4"x4	1213.1	2.66	4"x4
PFI-2418N-2D2DS-N2	Ethylene Glycol	1033.0	1.77	4"x4	826.4	1.17	4"x4	1239.5	2.47	4"x4
PFI-2418N-2D3ES-N2	Ethylene Glycol	1055.0	1.67	4"x4	844.0	1.11	4"x4	1265.9	2.34	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-2D2DS-O2	Ethylene Glycol	1033.0	1.77	4"x4	826.4	1.17	4"x4	1239.5	2.47	4"x4
PFI-2418N-2D3ES-O2	Ethylene Glycol	1055.0	1.67	4"x4	844.0	1.11	4"x4	1265.9	2.34	4"x4
PFI-2418N-2D4DS-P2	Ethylene Glycol	1081.4	1.58	4"x4	865.1	1.05	4"x4	1297.6	2.22	4"x4
PFI-2418N-3D1ES-K2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-2418N-3D1ES-L2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-2418N-3D4ES-M2	Ethylene Glycol	1881.1	4.15	4"x8	1504.9	3.69	4"x4	2257.3	5.82	4"x8
PFI-2418N-3D1DS-N2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-2418N-3D1ES-N2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-2418N-3D1DS-O2	Ethylene Glycol	1011.0	2.52	4"x4	808.8	1.67	4"x4	1213.1	3.53	4"x4
PFI-2418N-3D2DS-O2	Ethylene Glycol	1033.0	2.3	4"x4	826.4	1.53	4"x4	1239.5	3.23	4"x4
PFI-2418N-3D1ES-O2	Ethylene Glycol	1810.7	7.39	4"x4	1448.6	4.89	4"x4	2172.8	8.18	4"x8
PFI-2418N-3D2DS-P2	Ethylene Glycol	1832.7	6.65	4"x4	1466.2	4.4	4"x4	2199.2	7.1	4"x8
PFI-2418N-3D2ES-P2	Ethylene Glycol	1832.7	6.65	4"x4	1466.2	4.4	4"x4	2199.2	7.1	4"x8
PFI-2418N-3D2DS-Q2	Ethylene Glycol	1832.7	6.65	4"x4	1466.2	4.4	4"x4	2199.2	7.1	4"x8
PFI-2418N-3D4DS-Q2	Ethylene Glycol	1881.1	4.15	4"x8	1504.9	3.69	4"x4	2257.3	5.82	4"x8
PFI-2418N-3D4ES-Q2	Ethylene Glycol	1881.1	4.15	4"x8	1504.9	3.69	4"x4	2257.3	5.82	4"x8
PFI-2418N-3D1ES-R2	Ethylene Glycol	1810.7	7.39	4"x4	1448.6	4.89	4"x4	2172.8	8.18	4"x8
PFI-2418N-3D4ES-R2	Ethylene Glycol	1881.1	4.15	4"x8	1504.9	3.69	4"x4	2257.3	5.82	4"x8
PFI-2418N-4D1DS-K2	Ethylene Glycol	1011.0	3.13	4"x4	808.8	2.08	4"x4	1213.1	4.39	4"x4
PFI-2418N-4D1ES-L2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-2418N-4D2ES-M2	Ethylene Glycol	1832.7	8.2	4"x4	1466.2	5.43	4"x4	2199.2	9.18	4"x8
PFI-2418N-4D2DS-N2	Ethylene Glycol	1832.7	8.2	4"x4	1466.2	5.43	4"x4	2199.2	9.18	4"x8
PFI-2418N-4D1ES-N2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-2418N-4D3DS-O2	Ethylene Glycol	1854.7	7.43	4"x4	1483.8	4.92	4"x4	2225.6	8.09	4"x8
PFI-2418N-4D1ES-O2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-4D1ES-P2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-2418N-4D1DS-Q2	Ethylene Glycol	1810.7	9.2	4"x4	1448.6	6.09	4"x4	2172.8	10.63	4"x8
PFI-2418N-4D2ES-Q2	Ethylene Glycol	1832.7	8.2	4"x4	1466.2	5.43	4"x4	2199.2	9.18	4"x8
PFI-2418N-4D4ES-Q2	Ethylene Glycol	1881.1	5.05	4"x8	1504.9	4.46	4"x4	2257.3	7.07	4"x8
PFI-2418N-4D2ES-R2	Ethylene Glycol	1832.7	8.2	4"x4	1466.2	5.43	4"x4	2199.2	9.18	4"x8
PFI-2418N-4D4ES-R2	Ethylene Glycol	1881.1	5.05	4"x8	1504.9	4.46	4"x4	2257.3	7.07	4"x8
PFI-2418N-5D1DS-K2	Ethylene Glycol	1011.0	3.75	4"x4	808.8	2.48	4"x4	1213.1	5.25	4"x4
PFI-2418N-5D1ES-O2	Ethylene Glycol	1810.7	11.02	4"x4	1448.6	7.29	4"x4	2172.8	13.08	4"x8
PFI-2418N-5D2ES-P2	Ethylene Glycol	1832.7	9.75	4"x4	1466.2	6.46	4"x4	2199.2	11.27	4"x8
PFI-2418N-6D2DS-M2	Ethylene Glycol	1832.7	11.3	4"x4	1466.2	7.48	4"x4	2199.2	13.35	4"x8
PFI-2418N-6D1DS-N2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-2418N-6D1DS-R2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-2418N-6D1ES-R2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-2418N-3D4BS-K2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-2418N-3D4BS-L2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-2418N-3D4BS-N2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-2418N-3D4BS-O2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-2418N-3D4BS-P2	Ethylene Glycol	1081.4	2	4"x4	865.1	1.33	4"x4	1297.6	2.8	4"x4
PFI-2418N-4D4BS-K2	Ethylene Glycol	1081.4	2.42	4"x4	865.1	1.6	4"x4	1297.6	3.39	4"x4
PFI-2418N-4D4BS-L2	Ethylene Glycol	1081.4	2.42	4"x4	865.1	1.6	4"x4	1297.6	3.39	4"x4
PFI-2418N-4D3BS-M2	Ethylene Glycol	1055.0	2.62	4"x4	844.0	1.74	4"x4	1265.9	3.67	4"x4
PFI-2418N-4D3BS-N2	Ethylene Glycol	1055.0	2.62	4"x4	844.0	1.74	4"x4	1265.9	3.67	4"x4
PFI-2418N-4D3BS-O2	Ethylene Glycol	1055.0	2.62	4"x4	844.0	1.74	4"x4	1265.9	3.67	4"x4
PFI-2418N-4D4BS-P2	Ethylene Glycol	1881.1	5.05	4"x8	1504.9	4.46	4"x4	2257.3	7.07	4"x8
PFI-2418N-4D3BS-Q2	Ethylene Glycol	1854.7	7.43	4"x4	1483.8	4.92	4"x4	2225.6	8.09	4"x8





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-5D2BS-K2	Ethylene Glycol	1033.0	3.38	4"x4	826.4	2.24	4"x4	1239.5	4.73	4"x4
PFI-2418N-5D2BS-L2	Ethylene Glycol	1033.0	3.38	4"x4	826.4	2.24	4"x4	1239.5	4.73	4"x4
PFI-2418N-5D2BS-M2	Ethylene Glycol	1033.0	3.38	4"x4	826.4	2.24	4"x4	1239.5	4.73	4"x4
PFI-2418N-5D2BS-N2	Ethylene Glycol	1033.0	3.38	4"x4	826.4	2.24	4"x4	1239.5	4.73	4"x4
PFI-2418N-5D3BS-O2	Ethylene Glycol	1055.0	3.1	4"x4	844.0	2.05	4"x4	1265.9	4.34	4"x4
PFI-2418N-5D2BS-P2	Ethylene Glycol	1832.7	9.75	4"x4	1466.2	6.46	4"x4	2199.2	11.27	4"x8
PFI-2418N-5D3BS-Q2	Ethylene Glycol	1854.7	8.78	4"x4	1483.8	5.82	4"x4	2225.6	9.9	4"x8
PFI-2418N-6D1BS-K2	Ethylene Glycol	1011.0	4.37	4"x4	808.8	2.89	4"x4	1213.1	6.12	4"x4
PFI-2418N-6D1BS-L2	Ethylene Glycol	1011.0	4.37	4"x4	808.8	2.89	4"x4	1213.1	6.12	4"x4
PFI-2418N-6D1BS-M2	Ethylene Glycol	1011.0	4.37	4"x4	808.8	2.89	4"x4	1213.1	6.12	4"x4
PFI-2418N-6D1BS-N2	Ethylene Glycol	1011.0	4.37	4"x4	808.8	2.89	4"x4	1213.1	6.12	4"x4
PFI-2418N-6D1BS-O2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-2418N-6D1BS-P2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-2418N-6D1BS-Q2	Ethylene Glycol	1810.7	12.83	4"x4	1448.6	8.49	4"x4	2172.8	15.53	4"x8
PFI-2418N-6D2BS-R2	Ethylene Glycol	1832.7	11.3	4"x4	1466.2	7.48	4"x4	2199.2	13.35	4"x8
PFI-2418N-2D1DZ-M2	Ethylene Glycol	452.7	2.64	4"x4	362.1	1.75	4"x4	543.2	3.7	4"x4
PFI-2418N-2D4EZ-M2	Ethylene Glycol	470.3	1.97	4"x4	376.2	1.3	4"x4	564.3	2.76	4"x4
PFI-2418N-2D1DZ-N2	Ethylene Glycol	452.7	2.64	4"x4	362.1	1.75	4"x4	543.2	3.7	4"x4
PFI-2418N-2D2DZ-N2	Ethylene Glycol	458.2	2.37	4"x4	366.5	1.57	4"x4	549.8	3.32	4"x4
PFI-2418N-2D3EZ-N2	Ethylene Glycol	463.7	2.16	4"x4	370.9	1.43	4"x4	556.4	3.03	4"x4
PFI-2418N-2D2DZ-O2	Ethylene Glycol	458.2	2.37	4"x4	366.5	1.57	4"x4	549.8	3.32	4"x4
PFI-2418N-2D3EZ-O2	Ethylene Glycol	463.7	2.16	4"x4	370.9	1.43	4"x4	556.4	3.03	4"x4
PFI-2418N-2D4DZ-P2	Ethylene Glycol	470.3	1.97	4"x4	376.2	1.3	4"x4	564.3	2.75	4"x4
PFI-2418N-3D1EZ-K2	Ethylene Glycol	452.7	3.66	4"x4	362.1	2.42	4"x4	543.2	5.13	4"x4
PFI-2418N-3D1EZ-L2	Ethylene Glycol	452.7	3.66	4"x4	362.1	2.42	4"x4	543.2	5.13	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-3D4EZ-M2	Ethylene Glycol	870.2	8.11	4"x4	696.1	5.36	4"x4	1044.2	11.36	4"x4
PFI-2418N-3D1DZ-N2	Ethylene Glycol	452.7	3.65	4"x4	362.1	2.42	4"x4	543.2	5.11	4"x4
PFI-2418N-3D1EZ-N2	Ethylene Glycol	852.6	11.81	4"x4	682.0	7.81	4"x4	1023.1	16.55	4"x4
PFI-2418N-3D1DZ-O2	Ethylene Glycol	452.7	3.65	4"x4	362.1	2.42	4"x4	543.2	5.11	4"x4
PFI-2418N-3D2DZ-O2	Ethylene Glycol	858.1	10.22	4"x4	686.4	6.76	4"x4	1029.7	14.32	4"x4
PFI-2418N-3D1EZ-O2	Ethylene Glycol	852.6	11.81	4"x4	682.0	7.81	4"x4	1023.1	16.55	4"x4
PFI-2418N-3D2DZ-P2	Ethylene Glycol	858.1	10.22	4"x4	686.4	6.76	4"x4	1029.7	14.32	4"x4
PFI-2418N-3D2EZ-P2	Ethylene Glycol	858.1	10.26	4"x4	686.4	6.79	4"x4	1029.7	14.38	4"x4
PFI-2418N-3D2DZ-Q2	Ethylene Glycol	858.1	10.22	4"x4	686.4	6.76	4"x4	1029.7	14.32	4"x4
PFI-2418N-3D4DZ-Q2	Ethylene Glycol	870.2	8.06	4"x4	696.1	5.33	4"x4	1044.2	11.3	4"x4
PFI-2418N-3D4EZ-Q2	Ethylene Glycol	870.2	8.11	4"x4	696.1	5.36	4"x4	1044.2	11.36	4"x4
PFI-2418N-3D1EZ-R2	Ethylene Glycol	852.6	11.81	4"x4	682.0	7.81	4"x4	1023.1	16.55	4"x4
PFI-2418N-3D4EZ-R2	Ethylene Glycol	870.2	8.11	4"x4	696.1	5.36	4"x4	1044.2	11.36	4"x4
PFI-2418N-4D1DZ-K2	Ethylene Glycol	452.7	4.66	4"x4	362.1	3.08	4"x4	543.2	6.53	4"x4
PFI-2418N-4D1EZ-L2	Ethylene Glycol	852.6	14.99	4"x4	682.0	9.92	4"x4	1023.1	21.01	4"x4
PFI-2418N-4D2EZ-M2	Ethylene Glycol	858.1	13.03	4"x4	686.4	8.62	4"x4	1029.7	18.27	4"x4
PFI-2418N-4D2DZ-N2	Ethylene Glycol	858.1	12.99	4"x4	686.4	8.59	4"x4	1029.7	18.2	4"x4
PFI-2418N-4D1EZ-N2	Ethylene Glycol	852.6	14.99	4"x4	682.0	9.92	4"x4	1023.1	21.01	4"x4
PFI-2418N-4D3DZ-O2	Ethylene Glycol	863.6	11.49	4"x4	690.8	7.6	4"x4	1036.3	16.1	4"x4
PFI-2418N-4D1EZ-O2	Ethylene Glycol	852.6	14.99	4"x4	682.0	9.92	4"x4	1023.1	21.01	4"x4
PFI-2418N-4D1EZ-P2	Ethylene Glycol	852.6	14.99	4"x4	682.0	9.92	4"x4	1023.1	21.01	4"x4
PFI-2418N-4D1DZ-Q2	Ethylene Glycol	852.6	15.04	4"x4	682.0	9.95	4"x4	1023.1	21.07	4"x4
PFI-2418N-4D2EZ-Q2	Ethylene Glycol	858.1	13.03	4"x4	686.4	8.62	4"x4	1029.7	18.27	4"x4
PFI-2418N-4D4EZ-Q2	Ethylene Glycol	870.2	10.15	4"x4	696.1	6.71	4"x4	1044.2	14.22	4"x4
PFI-2418N-4D2EZ-R2	Ethylene Glycol	858.1	13.03	4"x4	686.4	8.62	4"x4	1029.7	18.27	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-4D4EZ-R2	Ethylene Glycol	870.2	10.15	4"x4	696.1	6.71	4"x4	1044.2	14.22	4"x4
PFI-2418N-5D1DZ-K2	Ethylene Glycol	452.7	5.67	4"x4	362.1	3.75	4"x4	543.2	7.94	4"x4
PFI-2418N-5D1EZ-O2	Ethylene Glycol	852.6	18.21	4"x4	682.0	12.05	4"x4	1023.1	25.52	4"x4
PFI-2418N-5D2EZ-P2	Ethylene Glycol	858.1	15.8	4"x4	686.4	10.45	4"x4	1029.7	22.15	4"x4
PFI-2418N-6D2DZ-M2	Ethylene Glycol	858.1	18.53	4"x4	686.4	12.26	4"x4	1029.7	25.97	4"x4
PFI-2418N-6D1DZ-N2	Ethylene Glycol	852.6	21.48	4"x4	682.0	14.21	4"x4	1023.1	30.1	4"x4
PFI-2418N-6D1DZ-R2	Ethylene Glycol	852.6	21.48	4"x4	682.0	14.21	4"x4	1023.1	30.1	4"x4
PFI-2418N-6D1EZ-R2	Ethylene Glycol	852.6	21.52	4"x4	682.0	14.24	4"x4	1023.1	30.16	4"x4
PFI-2418N-3D4BT-K2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2418N-3D4BT-L2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2418N-3D4BT-N2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2418N-3D4BT-O2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2418N-3D4BT-P2	Ethylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2418N-4D4BT-K2	Ethylene Glycol	470.3	3.24	4"x4	376.2	2.15	4"x4	564.3	4.54	4"x4
PFI-2418N-4D4BT-L2	Ethylene Glycol	470.3	3.24	4"x4	376.2	2.15	4"x4	564.3	4.54	4"x4
PFI-2418N-4D3BT-M2	Ethylene Glycol	463.7	3.64	4"x4	370.9	2.41	4"x4	556.4	5.1	4"x4
PFI-2418N-4D3BT-N2	Ethylene Glycol	463.7	3.64	4"x4	370.9	2.41	4"x4	556.4	5.1	4"x4
PFI-2418N-4D3BT-O2	Ethylene Glycol	463.7	3.64	4"x4	370.9	2.41	4"x4	556.4	5.1	4"x4
PFI-2418N-4D4BT-P2	Ethylene Glycol	870.2	10.12	4"x4	696.1	6.7	4"x4	1044.2	14.19	4"x4
PFI-2418N-4D3BT-Q2	Ethylene Glycol	863.6	11.51	4"x4	690.8	7.61	4"x4	1036.3	16.13	4"x4
PFI-2418N-5D2BT-K2	Ethylene Glycol	458.2	4.94	4"x4	366.5	3.27	4"x4	549.8	6.91	4"x4
PFI-2418N-5D2BT-L2	Ethylene Glycol	458.2	4.94	4"x4	366.5	3.27	4"x4	549.8	6.91	4"x4
PFI-2418N-5D2BT-M2	Ethylene Glycol	458.2	4.94	4"x4	366.5	3.27	4"x4	549.8	6.91	4"x4
PFI-2418N-5D2BT-N2	Ethylene Glycol	458.2	4.94	4"x4	366.5	3.27	4"x4	549.8	6.91	4"x4
PFI-2418N-5D3BT-O2	Ethylene Glycol	863.6	13.74	4"x4	690.8	9.09	4"x4	1036.3	19.26	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-5D2BT-P2	Ethylene Glycol	858.1	15.76	4"x4	686.4	10.43	4"x4	1029.7	22.09	4"x4
PFI-2418N-5D3BT-Q2	Ethylene Glycol	863.6	13.74	4"x4	690.8	9.09	4"x4	1036.3	19.26	4"x4
PFI-2418N-6D1BT-K2	Ethylene Glycol	452.7	6.65	4"x4	362.1	4.4	4"x4	543.2	9.32	4"x4
PFI-2418N-6D1BT-L2	Ethylene Glycol	452.7	6.65	4"x4	362.1	4.4	4"x4	543.2	9.32	4"x4
PFI-2418N-6D1BT-M2	Ethylene Glycol	452.7	6.65	4"x4	362.1	4.4	4"x4	543.2	9.32	4"x4
PFI-2418N-6D1BT-N2	Ethylene Glycol	852.6	21.46	4"x4	682.0	14.19	4"x4	1023.1	30.07	4"x4
PFI-2418N-6D1BT-O2	Ethylene Glycol	852.6	21.46	4"x4	682.0	14.19	4"x4	1023.1	30.07	4"x4
PFI-2418N-6D1BT-P2	Ethylene Glycol	852.6	21.46	4"x4	682.0	14.19	4"x4	1023.1	30.07	4"x4
PFI-2418N-6D1BT-Q2	Ethylene Glycol	852.6	21.46	4"x4	682.0	14.19	4"x4	1023.1	30.07	4"x4
PFI-2436N-2D1DS-M4	Ethylene Glycol	2021.9	1.9	4"x8	1617.5	1.26	4"x8	2426.3	2.66	4"x8
PFI-2436N-2D4ES-M4	Ethylene Glycol	2162.7	1.58	4"x8	1730.2	1.05	4"x8	2595.2	2.22	4"x8
PFI-2436N-2D1DS-N4	Ethylene Glycol	2021.9	1.9	4"x8	1617.5	1.26	4"x8	2426.3	2.66	4"x8
PFI-2436N-2D2DS-N4	Ethylene Glycol	2065.9	1.77	4"x8	1652.7	1.17	4"x8	2479.1	2.47	4"x8
PFI-2436N-2D3ES-N4	Ethylene Glycol	2109.9	1.67	4"x8	1687.9	1.11	4"x8	2531.9	2.34	4"x8
PFI-2436N-2D2DS-O4	Ethylene Glycol	2065.9	1.77	4"x8	1652.7	1.17	4"x8	2479.1	2.47	4"x8
PFI-2436N-2D3ES-O4	Ethylene Glycol	2109.9	1.67	4"x8	1687.9	1.11	4"x8	2531.9	2.34	4"x8
PFI-2436N-2D4DS-P4	Ethylene Glycol	2162.7	1.58	4"x8	1730.2	1.05	4"x8	2595.2	2.22	4"x8
PFI-2436N-3D1ES-K4	Ethylene Glycol	2021.9	2.52	4"x8	1617.5	1.67	4"x8	2426.3	3.53	4"x8
PFI-2436N-3D1ES-L4	Ethylene Glycol	2021.9	2.52	4"x8	1617.5	1.67	4"x8	2426.3	3.53	4"x8
PFI-2436N-3D4ES-M4	Ethylene Glycol	2162.7	2	4"x8	1730.2	1.33	4"x8	2595.2	2.8	4"x8
PFI-2436N-3D1DS-N4	Ethylene Glycol	2021.9	2.52	4"x8	1617.5	1.67	4"x8	2426.3	3.53	4"x8
PFI-2436N-3D1ES-N4	Ethylene Glycol	2021.9	2.52	4"x8	1617.5	1.67	4"x8	2426.3	3.53	4"x8
PFI-2436N-3D1DS-O4	Ethylene Glycol	2021.9	2.52	4"x8	1617.5	1.67	4"x8	2426.3	3.53	4"x8
PFI-2436N-3D2DS-O4	Ethylene Glycol	2065.9	2.3	4"x8	1652.7	1.53	4"x8	2479.1	3.23	4"x8
PFI-2436N-3D1ES-O4	Ethylene Glycol	3621.4	7.39	4"x8	2897.1	4.89	4"x8	4345.7	8.18	4"x16



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-3D2DS-P4	Ethylene Glycol	3665.4	6.65	4"x8	2932.3	4.4	4"x8	4398.5	7.1	4"x16
PFI-2436N-3D2ES-P4	Ethylene Glycol	3665.4	6.65	4"x8	2932.3	4.4	4"x8	4398.5	7.1	4"x16
PFI-2436N-3D2DS-Q4	Ethylene Glycol	3665.4	6.65	4"x8	2932.3	4.4	4"x8	4398.5	7.1	4"x16
PFI-2436N-3D4DS-Q4	Ethylene Glycol	3762.2	4.15	4"x16	3009.8	3.69	4"x8	4514.7	5.82	4"x16
PFI-2436N-3D4ES-Q4	Ethylene Glycol	3762.2	4.15	4"x16	3009.8	3.69	4"x8	4514.7	5.82	4"x16
PFI-2436N-3D1ES-R4	Ethylene Glycol	3621.4	7.39	4"x8	2897.1	4.89	4"x8	4345.7	8.18	4"x16
PFI-2436N-3D4ES-R4	Ethylene Glycol	3762.2	4.15	4"x16	3009.8	3.69	4"x8	4514.7	5.82	4"x16
PFI-2436N-4D1DS-K4	Ethylene Glycol	2021.9	3.13	4"x8	1617.5	2.08	4"x8	2426.3	4.39	4"x8
PFI-2436N-4D1ES-L4	Ethylene Glycol	2021.9	3.13	4"x8	1617.5	2.08	4"x8	2426.3	4.39	4"x8
PFI-2436N-4D2ES-M4	Ethylene Glycol	3665.4	8.2	4"x8	2932.3	5.43	4"x8	4398.5	9.18	4"x16
PFI-2436N-4D2DS-N4	Ethylene Glycol	3665.4	8.2	4"x8	2932.3	5.43	4"x8	4398.5	9.18	4"x16
PFI-2436N-4D1ES-N4	Ethylene Glycol	3621.4	9.2	4"x8	2897.1	6.09	4"x8	4345.7	10.63	4"x16
PFI-2436N-4D3DS-O4	Ethylene Glycol	3709.4	7.43	4"x8	2967.5	4.92	4"x8	4451.3	8.09	4"x16
PFI-2436N-4D1ES-O4	Ethylene Glycol	3621.4	9.2	4"x8	2897.1	6.09	4"x8	4345.7	10.63	4"x16
PFI-2436N-4D1ES-P4	Ethylene Glycol	3621.4	9.2	4"x8	2897.1	6.09	4"x8	4345.7	10.63	4"x16
PFI-2436N-4D1DS-Q4	Ethylene Glycol	3621.4	9.2	4"x8	2897.1	6.09	4"x8	4345.7	10.63	4"x16
PFI-2436N-4D2ES-Q4	Ethylene Glycol	3665.4	8.2	4"x8	2932.3	5.43	4"x8	4398.5	9.18	4"x16
PFI-2436N-4D4ES-Q4	Ethylene Glycol	3762.2	5.05	4"x16	3009.8	4.46	4"x8	4514.7	7.07	4"x16
PFI-2436N-4D2ES-R4	Ethylene Glycol	3665.4	8.2	4"x8	2932.3	5.43	4"x8	4398.5	9.18	4"x16
PFI-2436N-4D4ES-R4	Ethylene Glycol	3762.2	5.05	4"x16	3009.8	4.46	4"x8	4514.7	7.07	4"x16
PFI-2436N-5D1DS-K4	Ethylene Glycol	2021.9	3.75	4"x8	1617.5	2.48	4"x8	2426.3	5.25	4"x8
PFI-2436N-5D1ES-O4	Ethylene Glycol	3621.4	11.02	4"x8	2897.1	7.29	4"x8	4345.7	13.08	4"x16
PFI-2436N-5D2ES-P4	Ethylene Glycol	3665.4	9.75	4"x8	2932.3	6.46	4"x8	4398.5	11.27	4"x16
PFI-2436N-6D2DS-M4	Ethylene Glycol	3665.4	11.3	4"x8	2932.3	7.48	4"x8	4398.5	13.35	4"x16
PFI-2436N-6D1DS-N4	Ethylene Glycol	3621.4	12.83	4"x8	2897.1	8.49	4"x8	4345.7	15.53	4"x16



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-6D1DS-R4	Ethylene Glycol	3621.4	12.83	4"x8	2897.1	8.49	4"x8	4345.7	15.53	4"x16
PFI-2436N-6D1ES-R4	Ethylene Glycol	3621.4	12.83	4"x8	2897.1	8.49	4"x8	4345.7	15.53	4"x16
PFI-2436N-3D4BS-K4	Ethylene Glycol	2162.7	2	4"x8	1730.2	1.33	4"x8	2595.2	2.8	4"x8
PFI-2436N-3D4BS-L4	Ethylene Glycol	2162.7	2	4"x8	1730.2	1.33	4"x8	2595.2	2.8	4"x8
PFI-2436N-3D4BS-N4	Ethylene Glycol	2162.7	2	4"x8	1730.2	1.33	4"x8	2595.2	2.8	4"x8
PFI-2436N-3D4BS-O4	Ethylene Glycol	2162.7	2	4"x8	1730.2	1.33	4"x8	2595.2	2.8	4"x8
PFI-2436N-3D4BS-P4	Ethylene Glycol	2162.7	2	4"x8	1730.2	1.33	4"x8	2595.2	2.8	4"x8
PFI-2436N-4D4BS-K4	Ethylene Glycol	2162.7	2.42	4"x8	1730.2	1.6	4"x8	2595.2	3.39	4"x8
PFI-2436N-4D4BS-L4	Ethylene Glycol	2162.7	2.42	4"x8	1730.2	1.6	4"x8	2595.2	3.39	4"x8
PFI-2436N-4D3BS-M4	Ethylene Glycol	2109.9	2.62	4"x8	1687.9	1.74	4"x8	2531.9	3.67	4"x8
PFI-2436N-4D3BS-N4	Ethylene Glycol	2109.9	2.62	4"x8	1687.9	1.74	4"x8	2531.9	3.67	4"x8
PFI-2436N-4D3BS-O4	Ethylene Glycol	2109.9	2.62	4"x8	1687.9	1.74	4"x8	2531.9	3.67	4"x8
PFI-2436N-4D4BS-P4	Ethylene Glycol	3762.2	5.05	4"x16	3009.8	4.46	4"x8	4514.7	7.07	4"x16
PFI-2436N-4D3BS-Q4	Ethylene Glycol	3709.4	7.43	4"x8	2967.5	4.92	4"x8	4451.3	8.09	4"x16
PFI-2436N-5D2BS-K4	Ethylene Glycol	2065.9	3.38	4"x8	1652.7	2.24	4"x8	2479.1	4.73	4"x8
PFI-2436N-5D2BS-L4	Ethylene Glycol	2065.9	3.38	4"x8	1652.7	2.24	4"x8	2479.1	4.73	4"x8
PFI-2436N-5D2BS-M4	Ethylene Glycol	2065.9	3.38	4"x8	1652.7	2.24	4"x8	2479.1	4.73	4"x8
PFI-2436N-5D2BS-N4	Ethylene Glycol	2065.9	3.38	4"x8	1652.7	2.24	4"x8	2479.1	4.73	4"x8
PFI-2436N-5D3BS-O4	Ethylene Glycol	2109.9	3.1	4"x8	1687.9	2.05	4"x8	2531.9	4.34	4"x8
PFI-2436N-5D2BS-P4	Ethylene Glycol	2065.9	3.38	4"x8	1652.7	2.24	4"x8	2479.1	4.73	4"x8
PFI-2436N-5D3BS-Q4	Ethylene Glycol	3709.4	8.78	4"x8	2967.5	5.81	4"x8	4451.3	9.9	4"x16
PFI-2436N-6D1BS-K4	Ethylene Glycol	2021.9	4.37	4"x8	1617.5	2.89	4"x8	2426.3	6.12	4"x8
PFI-2436N-6D1BS-L4	Ethylene Glycol	2021.9	4.37	4"x8	1617.5	2.89	4"x8	2426.3	6.12	4"x8
PFI-2436N-6D1BS-M4	Ethylene Glycol	2021.9	4.37	4"x8	1617.5	2.89	4"x8	2426.3	6.12	4"x8
PFI-2436N-6D1BS-N4	Ethylene Glycol	2021.9	4.37	4"x8	1617.5	2.89	4"x8	2426.3	6.12	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-6D1BS-O4	Ethylene Glycol	3621.4	12.83	4"x8	2897.1	8.49	4"x8	4345.7	15.53	4"x16
PFI-2436N-6D1BS-P4	Ethylene Glycol	3621.4	12.83	4"x8	2897.1	8.49	4"x8	4345.7	15.53	4"x16
PFI-2436N-6D1BS-Q4	Ethylene Glycol	3621.4	12.83	4"x8	2897.1	8.49	4"x8	4345.7	15.53	4"x16
PFI-2436N-6D2BS-R4	Ethylene Glycol	3665.4	11.3	4"x8	2932.3	7.48	4"x8	4398.5	13.35	4"x16
PFI-2436N-2D1DZ-M4	Ethylene Glycol	905.4	2.64	4"x8	724.3	1.75	4"x8	1086.4	3.7	4"x8
PFI-2436N-2D4EZ-M4	Ethylene Glycol	940.6	1.97	4"x8	752.4	1.3	4"x8	1128.7	2.76	4"x8
PFI-2436N-2D1DZ-N4	Ethylene Glycol	905.4	2.64	4"x8	724.3	1.75	4"x8	1086.4	3.7	4"x8
PFI-2436N-2D2DZ-N4	Ethylene Glycol	916.4	2.37	4"x8	733.1	1.57	4"x8	1099.6	3.32	4"x8
PFI-2436N-2D3EZ-N4	Ethylene Glycol	927.4	2.16	4"x8	741.9	1.43	4"x8	1112.8	3.03	4"x8
PFI-2436N-2D2DZ-O4	Ethylene Glycol	916.4	2.37	4"x8	733.1	1.57	4"x8	1099.6	3.32	4"x8
PFI-2436N-2D3EZ-O4	Ethylene Glycol	927.4	2.16	4"x8	741.9	1.43	4"x8	1112.8	3.03	4"x8
PFI-2436N-2D4DZ-P4	Ethylene Glycol	940.6	1.97	4"x8	752.4	1.3	4"x8	1128.7	2.75	4"x8
PFI-2436N-3D1EZ-K4	Ethylene Glycol	905.4	3.66	4"x8	724.3	2.42	4"x8	1086.4	5.13	4"x8
PFI-2436N-3D1EZ-L4	Ethylene Glycol	905.4	3.66	4"x8	724.3	2.42	4"x8	1086.4	5.13	4"x8
PFI-2436N-3D4EZ-M4	Ethylene Glycol	1740.3	8.1	4"x8	1392.2	5.36	4"x8	2088.4	11.36	4"x8
PFI-2436N-3D1DZ-N4	Ethylene Glycol	905.4	3.65	4"x8	724.3	2.42	4"x8	1086.4	5.11	4"x8
PFI-2436N-3D1EZ-N4	Ethylene Glycol	1705.1	11.81	4"x8	1364.1	7.81	4"x8	2046.1	16.55	4"x8
PFI-2436N-3D1DZ-O4	Ethylene Glycol	905.4	3.65	4"x8	724.3	2.42	4"x8	1086.4	5.11	4"x8
PFI-2436N-3D2DZ-O4	Ethylene Glycol	1716.1	10.22	4"x8	1372.9	6.76	4"x8	2059.3	14.32	4"x8
PFI-2436N-3D1EZ-O4	Ethylene Glycol	1705.1	11.81	4"x8	1364.1	7.81	4"x8	2046.1	16.55	4"x8
PFI-2436N-3D2DZ-P4	Ethylene Glycol	1716.1	10.22	4"x8	1372.9	6.76	4"x8	2059.3	14.32	4"x8
PFI-2436N-3D2EZ-P4	Ethylene Glycol	1716.1	10.26	4"x8	1372.9	6.79	4"x8	2059.3	14.38	4"x8
PFI-2436N-3D2DZ-Q4	Ethylene Glycol	1716.1	10.22	4"x8	1372.9	6.76	4"x8	2059.3	14.32	4"x8
PFI-2436N-3D4DZ-Q4	Ethylene Glycol	1740.3	8.06	4"x8	1392.2	5.33	4"x8	2088.4	11.3	4"x8
PFI-2436N-3D4EZ-Q4	Ethylene Glycol	1740.3	8.1	4"x8	1392.2	5.36	4"x8	2088.4	11.36	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-3D1EZ-R4	Ethylene Glycol	1705.1	11.81	4"x8	1364.1	7.81	4"x8	2046.1	16.55	4"x8
PFI-2436N-3D4EZ-R4	Ethylene Glycol	1740.3	8.1	4"x8	1392.2	5.36	4"x8	2088.4	11.36	4"x8
PFI-2436N-4D1DZ-K4	Ethylene Glycol	905.4	4.66	4"x8	724.3	3.08	4"x8	1086.4	6.53	4"x8
PFI-2436N-4D1EZ-L4	Ethylene Glycol	1705.1	14.99	4"x8	1364.1	9.92	4"x8	2046.1	21.01	4"x8
PFI-2436N-4D2EZ-M4	Ethylene Glycol	1716.1	13.03	4"x8	1372.9	8.62	4"x8	2059.3	18.27	4"x8
PFI-2436N-4D2DZ-N4	Ethylene Glycol	1716.1	12.99	4"x8	1372.9	8.59	4"x8	2059.3	18.2	4"x8
PFI-2436N-4D1EZ-N4	Ethylene Glycol	1705.1	14.99	4"x8	1364.1	9.92	4"x8	2046.1	21.01	4"x8
PFI-2436N-4D3DZ-O4	Ethylene Glycol	1727.1	11.48	4"x8	1381.7	7.6	4"x8	2072.5	16.09	4"x8
PFI-2436N-4D1EZ-O4	Ethylene Glycol	1705.1	14.99	4"x8	1364.1	9.92	4"x8	2046.1	21.01	4"x8
PFI-2436N-4D1EZ-P4	Ethylene Glycol	1705.1	14.99	4"x8	1364.1	9.92	4"x8	2046.1	21.01	4"x8
PFI-2436N-4D1DZ-Q4	Ethylene Glycol	1705.1	15.03	4"x8	1364.1	9.95	4"x8	2046.1	21.07	4"x8
PFI-2436N-4D2EZ-Q4	Ethylene Glycol	1716.1	13.03	4"x8	1372.9	8.62	4"x8	2059.3	18.27	4"x8
PFI-2436N-4D4EZ-Q4	Ethylene Glycol	1740.3	10.14	4"x8	1392.2	6.71	4"x8	2088.4	14.22	4"x8
PFI-2436N-4D2EZ-R4	Ethylene Glycol	1716.1	13.03	4"x8	1372.9	8.62	4"x8	2059.3	18.27	4"x8
PFI-2436N-4D4EZ-R4	Ethylene Glycol	1740.3	10.14	4"x8	1392.2	6.71	4"x8	2088.4	14.22	4"x8
PFI-2436N-5D1DZ-K4	Ethylene Glycol	905.4	5.67	4"x8	724.3	3.75	4"x8	1086.4	7.94	4"x8
PFI-2436N-5D1EZ-O4	Ethylene Glycol	1705.1	18.21	4"x8	1364.1	12.05	4"x8	2046.1	25.52	4"x8
PFI-2436N-5D2EZ-P4	Ethylene Glycol	1716.1	15.8	4"x8	1372.9	10.46	4"x8	2059.3	22.15	4"x8
PFI-2436N-6D2DZ-M4	Ethylene Glycol	1716.1	18.53	4"x8	1372.9	12.26	4"x8	2059.3	25.97	4"x8
PFI-2436N-6D1DZ-N4	Ethylene Glycol	1705.1	21.48	4"x8	1364.1	14.21	4"x8	2046.1	30.1	4"x8
PFI-2436N-6D1DZ-R4	Ethylene Glycol	1705.1	21.48	4"x8	1364.1	14.21	4"x8	2046.1	30.1	4"x8
PFI-2436N-6D1EZ-R4	Ethylene Glycol	1705.1	21.52	4"x8	1364.1	14.24	4"x8	2046.1	30.16	4"x8
PFI-2436N-3D4BT-K4	Ethylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8
PFI-2436N-3D4BT-L4	Ethylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8
PFI-2436N-3D4BT-N4	Ethylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-3D4BT-O4	Ethylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8
PFI-2436N-3D4BT-P4	Ethylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8
PFI-2436N-4D4BT-K4	Ethylene Glycol	940.6	3.24	4"x8	752.4	2.15	4"x8	1128.7	4.54	4"x8
PFI-2436N-4D4BT-L4	Ethylene Glycol	940.6	3.24	4"x8	752.4	2.15	4"x8	1128.7	4.54	4"x8
PFI-2436N-4D3BT-M4	Ethylene Glycol	927.4	3.64	4"x8	741.9	2.41	4"x8	1112.8	5.1	4"x8
PFI-2436N-4D3BT-N4	Ethylene Glycol	927.4	3.64	4"x8	741.9	2.41	4"x8	1112.8	5.1	4"x8
PFI-2436N-4D3BT-O4	Ethylene Glycol	927.4	3.64	4"x8	741.9	2.41	4"x8	1112.8	5.1	4"x8
PFI-2436N-4D4BT-P4	Ethylene Glycol	1740.3	10.12	4"x8	1392.2	6.7	4"x8	2088.4	14.19	4"x8
PFI-2436N-4D3BT-Q4	Ethylene Glycol	1727.1	11.51	4"x8	1381.7	7.61	4"x8	2072.5	16.13	4"x8
PFI-2436N-5D2BT-K4	Ethylene Glycol	916.4	4.94	4"x8	733.1	3.27	4"x8	1099.6	6.91	4"x8
PFI-2436N-5D2BT-L4	Ethylene Glycol	916.4	4.94	4"x8	733.1	3.27	4"x8	1099.6	6.91	4"x8
PFI-2436N-5D2BT-M4	Ethylene Glycol	916.4	4.94	4"x8	733.1	3.27	4"x8	1099.6	6.91	4"x8
PFI-2436N-5D2BT-N4	Ethylene Glycol	916.4	4.94	4"x8	733.1	3.27	4"x8	1099.6	6.91	4"x8
PFI-2436N-5D3BT-O4	Ethylene Glycol	927.4	4.35	4"x8	741.9	2.88	4"x8	1112.8	6.09	4"x8
PFI-2436N-5D2BT-P4	Ethylene Glycol	1716.1	15.76	4"x8	1372.9	10.43	4"x8	2059.3	22.08	4"x8
PFI-2436N-5D3BT-Q4	Ethylene Glycol	1727.1	13.74	4"x8	1381.7	9.09	4"x8	2072.5	19.26	4"x8
PFI-2436N-6D1BT-K4	Ethylene Glycol	905.4	6.65	4"x8	724.3	4.4	4"x8	1086.4	9.32	4"x8
PFI-2436N-6D1BT-L4	Ethylene Glycol	905.4	6.65	4"x8	724.3	4.4	4"x8	1086.4	9.32	4"x8
PFI-2436N-6D1BT-M4	Ethylene Glycol	905.4	6.65	4"x8	724.3	4.4	4"x8	1086.4	9.32	4"x8
PFI-2436N-6D1BT-N4	Ethylene Glycol	1705.1	21.45	4"x8	1364.1	14.2	4"x8	2046.1	30.06	4"x8
PFI-2436N-6D1BT-O4	Ethylene Glycol	1705.1	21.45	4"x8	1364.1	14.2	4"x8	2046.1	30.06	4"x8
PFI-2436N-6D1BT-P4	Ethylene Glycol	1705.1	21.45	4"x8	1364.1	14.2	4"x8	2046.1	30.06	4"x8
PFI-2436N-6D1BT-Q4	Ethylene Glycol	1705.1	21.45	4"x8	1364.1	14.2	4"x8	2046.1	30.06	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0406N-3D1DS-G1	Propylene Glycol	232.9	2.23	4"x1	186.4	1.48	4"x1	279.5	3.12	4"x1
PFI-0406N-3D1ES-H1	Propylene Glycol	232.9	2.23	4"x1	186.4	1.48	4"x1	279.5	3.12	4"x1
PFI-0406N-4D1DS-H1	Propylene Glycol	232.9	2.76	4"x1	186.4	1.83	4"x1	279.5	3.87	4"x1
PFI-0406N-6D1ES-G1	Propylene Glycol	232.9	3.83	4"x1	186.4	2.54	4"x1	279.5	5.36	4"x1
PFI-0406N-6D1ES-H1	Propylene Glycol	232.9	3.83	4"x1	186.4	2.54	4"x1	279.5	5.36	4"x1
PFI-0406N-6D2DS-J1	Propylene Glycol	237.3	3.28	4"x1	189.9	2.17	4"x1	284.8	4.6	4"x1
PFI-0406N-2D3BS-G1	Propylene Glycol	219.9	1.21	4"x1	176.0	0.8	4"x1	263.9	1.69	4"x1
PFI-0406N-2D4BS-H1	Propylene Glycol	219.9	1.1	4"x1	176.0	0.73	4"x1	263.9	1.53	4"x1
PFI-0406N-3D2BS-G1	Propylene Glycol	237.3	1.96	4"x1	189.9	1.3	4"x1	284.8	2.75	4"x1
PFI-0406N-3D3BS-H1	Propylene Glycol	240.6	1.82	4"x1	192.5	1.2	4"x1	288.8	2.54	4"x1
PFI-0406N-4D4BS-G1	Propylene Glycol	245.0	2	4"x1	196.0	1.33	4"x1	294.0	2.8	4"x1
PFI-0406N-4D3BS-H1	Propylene Glycol	240.6	2.2	4"x1	192.5	1.46	4"x1	288.8	3.09	4"x1
PFI-0406N-4D4BS-J1	Propylene Glycol	245.0	2	4"x1	196.0	1.33	4"x1	294.0	2.8	4"x1
PFI-0406N-5D2BS-G1	Propylene Glycol	237.3	2.84	4"x1	189.9	1.88	4"x1	284.8	3.98	4"x1
PFI-0406N-5D4BS-H1	Propylene Glycol	245.0	2.34	4"x1	196.0	1.55	4"x1	294.0	3.27	4"x1
PFI-0406N-5D4BS-J1	Propylene Glycol	245.0	2.34	4"x1	196.0	1.55	4"x1	294.0	3.27	4"x1
PFI-0406N-6D1BS-H1	Propylene Glycol	232.9	3.83	4"x1	186.4	2.54	4"x1	279.5	5.36	4"x1
PFI-0406N-3D1DZ-G1	Propylene Glycol	108.2	2.95	4"x1	86.6	1.95	4"x1	129.9	4.13	4"x1
PFI-0406N-3D1EZ-H1	Propylene Glycol	108.2	2.95	4"x1	86.6	1.96	4"x1	129.9	4.14	4"x1
PFI-0406N-4D1DZ-H1	Propylene Glycol	108.2	3.87	4"x1	86.6	2.56	4"x1	129.9	5.42	4"x1
PFI-0406N-6D1EZ-G1	Propylene Glycol	108.2	5.71	4"x1	86.6	3.78	4"x1	129.9	8.01	4"x1
PFI-0406N-6D1EZ-H1	Propylene Glycol	108.2	5.71	4"x1	86.6	3.78	4"x1	129.9	8.01	4"x1
PFI-0406N-6D2DZ-J1	Propylene Glycol	109.3	4.65	4"x1	87.5	3.08	4"x1	131.2	6.51	4"x1
PFI-0406N-2D3BT-G1	Propylene Glycol	110.0	1.53	4"x1	88.0	1.02	4"x1	132.0	2.15	4"x1
PFI-0406N-2D4BT-H1	Propylene Glycol	110.0	1.29	4"x1	88.0	0.86	4"x1	132.0	1.81	4"x1



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0406N-3D2BT-G1	Propylene Glycol	109.3	2.41	4"x1	87.5	1.6	4"x1	131.2	3.37	4"x1
PFI-0406N-3D3BT-H1	Propylene Glycol	110.4	2.22	4"x1	88.3	1.47	4"x1	132.5	3.11	4"x1
PFI-0406N-4D4BT-G1	Propylene Glycol	111.5	2.47	4"x1	89.2	1.64	4"x1	133.8	3.46	4"x1
PFI-0406N-4D3BT-H1	Propylene Glycol	110.4	2.9	4"x1	88.3	1.92	4"x1	132.5	4.07	4"x1
PFI-0406N-4D4BT-J1	Propylene Glycol	111.5	2.47	4"x1	89.2	1.64	4"x1	133.8	3.46	4"x1
PFI-0406N-5D2BT-G1	Propylene Glycol	109.3	3.89	4"x1	87.5	2.58	4"x1	131.2	5.45	4"x1
PFI-0406N-5D4BT-H1	Propylene Glycol	111.5	3.04	4"x1	89.2	2.01	4"x1	133.8	4.26	4"x1
PFI-0406N-5D4BT-J1	Propylene Glycol	111.5	3.04	4"x1	89.2	2.01	4"x1	133.8	4.26	4"x1
PFI-0406N-6D1BT-H1	Propylene Glycol	108.2	5.69	4"x1	86.6	3.77	4"x1	129.9	7.98	4"x1
PFI-0412N-2D1DS-G2	Propylene Glycol	232.9	2.46	4"x1	186.4	1.63	4"x1	279.5	3.44	4"x1
PFI-0412N-2D4DS-G2	Propylene Glycol	245.0	1.81	4"x1	196.0	1.2	4"x1	294.0	2.54	4"x1
PFI-0412N-3D1DS-G2	Propylene Glycol	232.9	3.37	4"x1	186.4	2.23	4"x1	279.5	4.72	4"x1
PFI-0412N-3D2DS-H2	Propylene Glycol	237.3	2.9	4"x1	189.9	1.92	4"x1	284.8	4.07	4"x1
PFI-0412N-4D1DS-H2	Propylene Glycol	232.9	4.28	4"x1	186.4	2.84	4"x1	279.5	6	4"x1
PFI-0412N-4D3DS-H2	Propylene Glycol	240.6	3.31	4"x1	192.5	2.19	4"x1	288.8	4.64	4"x1
PFI-0412N-4D2ES-J2	Propylene Glycol	237.3	3.66	4"x1	189.9	2.42	4"x1	284.8	5.13	4"x1
PFI-0412N-5D1ES-J2	Propylene Glycol	232.9	5.2	4"x1	186.4	3.44	4"x1	279.5	7.28	4"x1
PFI-0412N-6D1ES-H2	Propylene Glycol	232.9	6.11	4"x1	186.4	4.05	4"x1	279.5	8.56	4"x1
PFI-0412N-6D1ES-J2	Propylene Glycol	232.9	6.11	4"x1	186.4	4.05	4"x1	279.5	8.56	4"x1
PFI-0412N-3D4BS-G2	Propylene Glycol	245.0	2.38	4"x1	196.0	1.58	4"x1	294.0	3.34	4"x1
PFI-0412N-3D4BS-H2	Propylene Glycol	245.0	2.38	4"x1	196.0	1.58	4"x1	294.0	3.34	4"x1
PFI-0412N-3D3BS-J2	Propylene Glycol	240.6	2.65	4"x1	192.5	1.75	4"x1	288.8	3.71	4"x1
PFI-0412N-4D4BS-G2	Propylene Glycol	245.0	2.95	4"x1	196.0	1.96	4"x1	294.0	4.14	4"x1
PFI-0412N-4D2BS-H2	Propylene Glycol	237.3	3.66	4"x1	189.9	2.42	4"x1	284.8	5.13	4"x1
PFI-0412N-4D3BS-H2	Propylene Glycol	240.6	3.31	4"x1	192.5	2.19	4"x1	288.8	4.64	4"x1



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0412N-4D3BS-J2	Propylene Glycol	240.6	3.31	4"x1	192.5	2.19	4"x1	288.8	4.64	4"x1
PFI-0412N-5D2BS-G2	Propylene Glycol	237.3	4.41	4"x1	189.9	2.92	4"x1	284.8	6.18	4"x1
PFI-0412N-6D2BS-G2	Propylene Glycol	237.3	5.17	4"x1	189.9	3.42	4"x1	284.8	7.24	4"x1
PFI-0412N-6D1BS-H2	Propylene Glycol	232.9	6.11	4"x1	186.4	4.05	4"x1	279.5	8.56	4"x1
PFI-0412N-6D2BS-J2	Propylene Glycol	237.3	5.17	4"x1	189.9	3.42	4"x1	284.8	7.24	4"x1
PFI-0412N-2D1DZ-G2	Propylene Glycol	108.2	3.34	4"x1	86.6	2.21	4"x1	129.9	4.68	4"x1
PFI-0412N-2D4DZ-G2	Propylene Glycol	111.5	2.15	4"x1	89.2	1.42	4"x1	133.8	3.01	4"x1
PFI-0412N-3D1DZ-G2	Propylene Glycol	108.2	4.91	4"x1	86.6	3.26	4"x1	129.9	6.89	4"x1
PFI-0412N-3D2DZ-H2	Propylene Glycol	109.3	4.01	4"x1	87.5	2.66	4"x1	131.2	5.61	4"x1
PFI-0412N-4D1DZ-H2	Propylene Glycol	108.2	6.49	4"x1	86.6	4.3	4"x1	129.9	9.1	4"x1
PFI-0412N-4D3DZ-H2	Propylene Glycol	110.4	4.86	4"x1	88.3	3.21	4"x1	132.5	6.8	4"x1
PFI-0412N-4D2EZ-J2	Propylene Glycol	109.3	5.28	4"x1	87.5	3.5	4"x1	131.2	7.4	4"x1
PFI-0412N-5D1EZ-J2	Propylene Glycol	108.2	8.07	4"x1	86.6	5.35	4"x1	129.9	11.3	4"x1
PFI-0412N-6D1EZ-H2	Propylene Glycol	108.2	9.64	4"x1	86.6	6.39	4"x1	129.9	13.5	4"x1
PFI-0412N-6D1EZ-J2	Propylene Glycol	108.2	9.64	4"x1	86.6	6.39	4"x1	129.9	13.5	4"x1
PFI-0412N-3D4BT-G2	Propylene Glycol	111.5	3.12	4"x1	89.2	2.07	4"x1	133.8	4.37	4"x1
PFI-0412N-3D4BT-H2	Propylene Glycol	111.5	3.12	4"x1	89.2	2.07	4"x1	133.8	4.37	4"x1
PFI-0412N-3D3BT-J2	Propylene Glycol	110.4	3.68	4"x1	88.3	2.44	4"x1	132.5	5.16	4"x1
PFI-0412N-4D4BT-G2	Propylene Glycol	111.5	4.1	4"x1	89.2	2.72	4"x1	133.8	5.75	4"x1
PFI-0412N-4D3BT-H2	Propylene Glycol	110.4	4.85	4"x1	88.3	3.21	4"x1	132.5	6.79	4"x1
PFI-0412N-4D3BT-J2	Propylene Glycol	110.4	4.85	4"x1	88.3	3.21	4"x1	132.5	6.79	4"x1
PFI-0412N-5D2BT-G2	Propylene Glycol	109.3	6.54	4"x1	87.5	4.34	4"x1	131.2	9.17	4"x1
PFI-0412N-6D2BT-G2	Propylene Glycol	109.3	7.81	4"x1	87.5	5.18	4"x1	131.2	11	4"x1
PFI-0412N-6D1BT-H2	Propylene Glycol	108.2	9.63	4"x1	86.6	6.38	4"x1	129.9	13.5	4"x1
PFI-0412N-6D2BT-J2	Propylene Glycol	109.3	7.81	4"x1	87.5	5.18	4"x1	131.2	11	4"x1



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-2D3DS-H1	Propylene Glycol	474.7	1.83	4"x2	379.7	1.21	4"x2	569.6	2.56	4"x2
PFI-0709N-3D1DS-H1	Propylene Glycol	461.5	3.03	4"x2	369.2	2.01	4"x2	553.8	4.24	4"x2
PFI-0709N-3D1DS-J1	Propylene Glycol	461.5	3.03	4"x2	369.2	2.01	4"x2	553.8	4.24	4"x2
PFI-0709N-3D3DS-J1	Propylene Glycol	474.7	2.43	4"x2	379.7	1.61	4"x2	569.6	3.4	4"x2
PFI-0709N-3D1ES-J1	Propylene Glycol	461.5	3.03	4"x2	369.2	2.01	4"x2	553.8	4.24	4"x2
PFI-0709N-3D2ES-J1	Propylene Glycol	468.1	2.69	4"x2	374.5	1.78	4"x2	561.7	3.76	4"x2
PFI-0709N-3D1DS-K1	Propylene Glycol	461.5	3.03	4"x2	369.2	2.01	4"x2	553.8	4.24	4"x2
PFI-0709N-3D2DS-K1	Propylene Glycol	468.1	2.69	4"x2	374.5	1.78	4"x2	561.7	3.76	4"x2
PFI-0709N-3D2ES-L1	Propylene Glycol	468.1	2.69	4"x2	374.5	1.78	4"x2	561.7	3.76	4"x2
PFI-0709N-4D4DS-J1	Propylene Glycol	481.3	2.75	4"x2	385.0	1.82	4"x2	577.5	3.85	4"x2
PFI-0709N-4D2DS-K1	Propylene Glycol	468.1	3.37	4"x2	374.5	2.23	4"x2	561.7	4.72	4"x2
PFI-0709N-4D1DS-L1	Propylene Glycol	461.5	3.83	4"x2	369.2	2.54	4"x2	553.8	5.37	4"x2
PFI-0709N-5D4DS-K1	Propylene Glycol	481.3	3.27	4"x2	385.0	2.17	4"x2	577.5	4.58	4"x2
PFI-0709N-5D1DS-L1	Propylene Glycol	461.5	4.64	4"x2	369.2	3.07	4"x2	553.8	6.49	4"x2
PFI-0709N-5D2DS-L1	Propylene Glycol	468.1	4.06	4"x2	374.5	2.69	4"x2	561.7	5.68	4"x2
PFI-0709N-5D3ES-L1	Propylene Glycol	474.7	3.62	4"x2	379.7	2.39	4"x2	569.6	5.06	4"x2
PFI-0709N-6D1ES-H1	Propylene Glycol	461.5	5.44	4"x2	369.2	3.6	4"x2	553.8	7.62	4"x2
PFI-0709N-6D1ES-J1	Propylene Glycol	461.5	5.44	4"x2	369.2	3.6	4"x2	553.8	7.62	4"x2
PFI-0709N-6D1ES-K1	Propylene Glycol	461.5	5.44	4"x2	369.2	3.6	4"x2	553.8	7.62	4"x2
PFI-0709N-6D2ES-L1	Propylene Glycol	468.1	4.74	4"x2	374.5	3.14	4"x2	561.7	6.64	4"x2
PFI-0709N-6D1ES-M1	Propylene Glycol	461.5	5.44	4"x2	369.2	3.6	4"x2	553.8	7.62	4"x2
PFI-0709N-3D4BS-J1	Propylene Glycol	481.3	2.23	4"x2	385.0	1.47	4"x2	577.5	3.11	4"x2
PFI-0709N-3D4BS-K1	Propylene Glycol	481.3	2.23	4"x2	385.0	1.47	4"x2	577.5	3.11	4"x2
PFI-0709N-3D4BS-M1	Propylene Glycol	481.3	2.23	4"x2	385.0	1.47	4"x2	577.5	3.11	4"x2
PFI-0709N-4D2BS-H1	Propylene Glycol	468.1	3.37	4"x2	374.5	2.23	4"x2	561.7	4.72	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-4D2BS-J1	Propylene Glycol	468.1	3.37	4"x2	374.5	2.23	4"x2	561.7	4.72	4"x2
PFI-0709N-4D3BS-K1	Propylene Glycol	474.7	3.02	4"x2	379.7	2	4"x2	569.6	4.23	4"x2
PFI-0709N-4D3BS-L1	Propylene Glycol	474.7	3.02	4"x2	379.7	2	4"x2	569.6	4.23	4"x2
PFI-0709N-4D4BS-M1	Propylene Glycol	481.3	2.75	4"x2	385.0	1.82	4"x2	577.5	3.85	4"x2
PFI-0709N-5D4BS-H1	Propylene Glycol	481.3	3.27	4"x2	385.0	2.17	4"x2	577.5	4.58	4"x2
PFI-0709N-5D3BS-J1	Propylene Glycol	474.7	3.62	4"x2	379.7	2.39	4"x2	569.6	5.06	4"x2
PFI-0709N-5D4BS-K1	Propylene Glycol	481.3	3.27	4"x2	385.0	2.17	4"x2	577.5	4.58	4"x2
PFI-0709N-5D4BS-L1	Propylene Glycol	481.3	3.27	4"x2	385.0	2.17	4"x2	577.5	4.58	4"x2
PFI-0709N-5D4BS-M1	Propylene Glycol	481.3	3.27	4"x2	385.0	2.17	4"x2	577.5	4.58	4"x2
PFI-0709N-6D1BS-H1	Propylene Glycol	461.5	5.44	4"x2	369.2	3.6	4"x2	553.8	7.62	4"x2
PFI-0709N-6D1BS-J1	Propylene Glycol	461.5	5.44	4"x2	369.2	3.6	4"x2	553.8	7.62	4"x2
PFI-0709N-6D1BS-K1	Propylene Glycol	461.5	5.44	4"x2	369.2	3.6	4"x2	553.8	7.62	4"x2
PFI-0709N-6D2BS-L1	Propylene Glycol	468.1	4.74	4"x2	374.5	3.14	4"x2	561.7	6.64	4"x2
PFI-0709N-6D2BS-M1	Propylene Glycol	468.1	4.74	4"x2	374.5	3.14	4"x2	561.7	6.64	4"x2
PFI-0709N-2D3DZ-H1	Propylene Glycol	218.6	2.66	4"x2	174.9	1.76	4"x2	262.4	3.72	4"x2
PFI-0709N-3D1DZ-H1	Propylene Glycol	215.3	4.84	4"x2	172.3	3.21	4"x2	258.4	6.79	4"x2
PFI-0709N-3D1DZ-J1	Propylene Glycol	215.3	4.84	4"x2	172.3	3.21	4"x2	258.4	6.79	4"x2
PFI-0709N-3D3DZ-J1	Propylene Glycol	218.6	3.68	4"x2	174.9	2.44	4"x2	262.4	5.16	4"x2
PFI-0709N-3D1EZ-J1	Propylene Glycol	215.3	4.86	4"x2	172.3	3.22	4"x2	258.4	6.8	4"x2
PFI-0709N-3D2EZ-J1	Propylene Glycol	217.0	4.2	4"x2	173.6	2.78	4"x2	260.4	5.88	4"x2
PFI-0709N-3D1DZ-K1	Propylene Glycol	215.3	4.84	4"x2	172.3	3.21	4"x2	258.4	6.79	4"x2
PFI-0709N-3D2DZ-K1	Propylene Glycol	217.0	4.18	4"x2	173.6	2.77	4"x2	260.4	5.86	4"x2
PFI-0709N-3D2EZ-L1	Propylene Glycol	217.0	4.2	4"x2	173.6	2.78	4"x2	260.4	5.88	4"x2
PFI-0709N-4D4DZ-J1	Propylene Glycol	220.3	4.18	4"x2	176.2	2.77	4"x2	264.3	5.86	4"x2
PFI-0709N-4D2DZ-K1	Propylene Glycol	217.0	5.38	4"x2	173.6	3.56	4"x2	260.4	7.54	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-4D1DZ-L1	Propylene Glycol	215.3	6.26	4"x2	172.3	4.15	4"x2	258.4	8.78	4"x2
PFI-0709N-5D4DZ-K1	Propylene Glycol	220.3	5.08	4"x2	176.2	3.36	4"x2	264.3	7.11	4"x2
PFI-0709N-5D1DZ-L1	Propylene Glycol	215.3	7.68	4"x2	172.3	5.09	4"x2	258.4	10.8	4"x2
PFI-0709N-5D2DZ-L1	Propylene Glycol	217.0	6.58	4"x2	173.6	4.35	4"x2	260.4	9.22	4"x2
PFI-0709N-5D3EZ-L1	Propylene Glycol	218.6	5.74	4"x2	174.9	3.8	4"x2	262.4	8.05	4"x2
PFI-0709N-6D1EZ-H1	Propylene Glycol	215.3	9.11	4"x2	172.3	6.03	4"x2	258.4	12.8	4"x2
PFI-0709N-6D1EZ-J1	Propylene Glycol	215.3	9.11	4"x2	172.3	6.03	4"x2	258.4	12.8	4"x2
PFI-0709N-6D1EZ-K1	Propylene Glycol	215.3	9.11	4"x2	172.3	6.03	4"x2	258.4	12.8	4"x2
PFI-0709N-6D2EZ-L1	Propylene Glycol	217.0	7.79	4"x2	173.6	5.15	4"x2	260.4	10.9	4"x2
PFI-0709N-6D1EZ-M1	Propylene Glycol	215.3	9.11	4"x2	172.3	6.03	4"x2	258.4	12.8	4"x2
PFI-0709N-3D4BT-J1	Propylene Glycol	220.3	3.27	4"x2	176.2	2.16	4"x2	264.3	4.58	4"x2
PFI-0709N-3D4BT-K1	Propylene Glycol	220.3	3.27	4"x2	176.2	2.16	4"x2	264.3	4.58	4"x2
PFI-0709N-3D4BT-M1	Propylene Glycol	220.3	3.27	4"x2	176.2	2.16	4"x2	264.3	4.58	4"x2
PFI-0709N-4D2BT-H1	Propylene Glycol	217.0	5.36	4"x2	173.6	3.55	4"x2	260.4	7.5	4"x2
PFI-0709N-4D2BT-J1	Propylene Glycol	217.0	5.36	4"x2	173.6	3.55	4"x2	260.4	7.5	4"x2
PFI-0709N-4D3BT-K1	Propylene Glycol	218.6	4.68	4"x2	174.9	3.1	4"x2	262.4	6.56	4"x2
PFI-0709N-4D3BT-L1	Propylene Glycol	218.6	4.68	4"x2	174.9	3.1	4"x2	262.4	6.56	4"x2
PFI-0709N-4D4BT-M1	Propylene Glycol	220.3	4.16	4"x2	176.2	2.75	4"x2	264.3	5.82	4"x2
PFI-0709N-5D4BT-H1	Propylene Glycol	220.3	5.05	4"x2	176.2	3.34	4"x2	264.3	7.07	4"x2
PFI-0709N-5D3BT-J1	Propylene Glycol	218.6	5.7	4"x2	174.9	3.78	4"x2	262.4	7.99	4"x2
PFI-0709N-5D4BT-K1	Propylene Glycol	220.3	5.05	4"x2	176.2	3.34	4"x2	264.3	7.07	4"x2
PFI-0709N-5D4BT-L1	Propylene Glycol	220.3	5.05	4"x2	176.2	3.34	4"x2	264.3	7.07	4"x2
PFI-0709N-5D4BT-M1	Propylene Glycol	220.3	5.05	4"x2	176.2	3.34	4"x2	264.3	7.07	4"x2
PFI-0709N-6D1BT-H1	Propylene Glycol	215.3	9.06	4"x2	172.3	6	4"x2	258.4	12.7	4"x2
PFI-0709N-6D1BT-J1	Propylene Glycol	215.3	9.06	4"x2	172.3	6	4"x2	258.4	12.7	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0709N-6D1BT-K1	Propylene Glycol	215.3	9.06	4"x2	172.3	6	4"x2	258.4	12.7	4"x2
PFI-0709N-6D1BT-L1	Propylene Glycol	215.3	9.06	4"x2	172.3	6	4"x2	258.4	12.7	4"x2
PFI-0709N-6D2BT-M1	Propylene Glycol	217.0	7.74	4"x2	173.6	5.12	4"x2	260.4	10.8	4"x2
PFI-0718N-2D2DS-J2	Propylene Glycol	468.1	3.1	4"x2	374.5	2.06	4"x2	561.7	4.35	4"x2
PFI-0718N-2D3DS-K2	Propylene Glycol	474.7	2.79	4"x2	379.7	1.85	4"x2	569.6	3.91	4"x2
PFI-0718N-3D1DS-H2	Propylene Glycol	461.5	4.97	4"x2	369.2	3.29	4"x2	553.8	6.96	4"x2
PFI-0718N-3D1DS-J2	Propylene Glycol	461.5	4.97	4"x2	369.2	3.29	4"x2	553.8	6.96	4"x2
PFI-0718N-3D2DS-J2	Propylene Glycol	468.1	4.34	4"x2	374.5	2.88	4"x2	561.7	6.08	4"x2
PFI-0718N-3D2DS-K2	Propylene Glycol	468.1	4.34	4"x2	374.5	2.88	4"x2	561.7	6.08	4"x2
PFI-0718N-3D3DS-L2	Propylene Glycol	474.7	3.86	4"x2	379.7	2.56	4"x2	569.6	5.41	4"x2
PFI-0718N-3D4DS-M2	Propylene Glycol	481.3	3.49	4"x2	385.0	2.31	4"x2	577.5	4.89	4"x2
PFI-0718N-4D1ES-H2	Propylene Glycol	461.5	6.42	4"x2	369.2	4.25	4"x2	553.8	8.99	4"x2
PFI-0718N-4D2DS-J2	Propylene Glycol	468.1	5.58	4"x2	374.5	3.69	4"x2	561.7	7.81	4"x2
PFI-0718N-4D3DS-K2	Propylene Glycol	474.7	4.94	4"x2	379.7	3.27	4"x2	569.6	6.92	4"x2
PFI-0718N-4D2DS-L2	Propylene Glycol	468.1	5.58	4"x2	374.5	3.69	4"x2	561.7	7.81	4"x2
PFI-0718N-4D2ES-L2	Propylene Glycol	468.1	5.58	4"x2	374.5	3.69	4"x2	561.7	7.81	4"x2
PFI-0718N-4D3DS-M2	Propylene Glycol	474.7	4.94	4"x2	379.7	3.27	4"x2	569.6	6.92	4"x2
PFI-0718N-4D2ES-M2	Propylene Glycol	468.1	5.58	4"x2	374.5	3.69	4"x2	561.7	7.81	4"x2
PFI-0718N-5D1ES-J2	Propylene Glycol	461.5	7.87	4"x2	369.2	5.21	4"x2	553.8	11	4"x2
PFI-0718N-5D1ES-M2	Propylene Glycol	461.5	7.87	4"x2	369.2	5.21	4"x2	553.8	11	4"x2
PFI-0718N-6D1ES-H2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-6D1ES-J2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-6D1ES-K2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-6D1ES-L2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-6D2ES-M2	Propylene Glycol	468.1	8.05	4"x2	374.5	5.33	4"x2	561.7	11.3	4"x2





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0718N-3D4BS-H2	Propylene Glycol	481.3	3.49	4"x2	385.0	2.31	4"x2	577.5	4.89	4"x2
PFI-0718N-3D4BS-J2	Propylene Glycol	481.3	3.49	4"x2	385.0	2.31	4"x2	577.5	4.89	4"x2
PFI-0718N-3D4BS-K2	Propylene Glycol	481.3	3.49	4"x2	385.0	2.31	4"x2	577.5	4.89	4"x2
PFI-0718N-3D4BS-L2	Propylene Glycol	481.3	3.49	4"x2	385.0	2.31	4"x2	577.5	4.89	4"x2
PFI-0718N-3D4BS-M2	Propylene Glycol	481.3	3.49	4"x2	385.0	2.31	4"x2	577.5	4.89	4"x2
PFI-0718N-4D2BS-H2	Propylene Glycol	468.1	5.58	4"x2	374.5	3.69	4"x2	561.7	7.81	4"x2
PFI-0718N-4D4BS-J2	Propylene Glycol	481.3	4.44	4"x2	385.0	2.94	4"x2	577.5	6.21	4"x2
PFI-0718N-4D4BS-K2	Propylene Glycol	481.3	4.44	4"x2	385.0	2.94	4"x2	577.5	6.21	4"x2
PFI-0718N-4D4BS-L2	Propylene Glycol	481.3	4.44	4"x2	385.0	2.94	4"x2	577.5	6.21	4"x2
PFI-0718N-4D4BS-M2	Propylene Glycol	481.3	4.44	4"x2	385.0	2.94	4"x2	577.5	6.21	4"x2
PFI-0718N-5D3BS-H2	Propylene Glycol	474.7	6.01	4"x2	379.7	3.98	4"x2	569.6	8.42	4"x2
PFI-0718N-5D3BS-J2	Propylene Glycol	474.7	6.01	4"x2	379.7	3.98	4"x2	569.6	8.42	4"x2
PFI-0718N-5D3BS-K2	Propylene Glycol	474.7	6.01	4"x2	379.7	3.98	4"x2	569.6	8.42	4"x2
PFI-0718N-5D4BS-L2	Propylene Glycol	481.3	5.38	4"x2	385.0	3.56	4"x2	577.5	7.54	4"x2
PFI-0718N-5D4BS-M2	Propylene Glycol	481.3	5.38	4"x2	385.0	3.56	4"x2	577.5	7.54	4"x2
PFI-0718N-6D1BS-H2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-6D1BS-J2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-6D1BS-K2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-6D1BS-L2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-6D1BS-M2	Propylene Glycol	461.5	9.32	4"x2	369.2	6.17	4"x2	553.8	13.1	4"x2
PFI-0718N-2D2DZ-J2	Propylene Glycol	217.0	4.91	4"x2	173.6	3.25	4"x2	260.4	6.88	4"x2
PFI-0718N-2D3DZ-K2	Propylene Glycol	218.6	4.3	4"x2	174.9	2.85	4"x2	262.4	6.03	4"x2
PFI-0718N-3D1DZ-H2	Propylene Glycol	215.3	8.26	4"x2	172.3	5.47	4"x2	258.4	11.6	4"x2
PFI-0718N-3D1DZ-J2	Propylene Glycol	215.3	8.26	4"x2	172.3	5.47	4"x2	258.4	11.6	4"x2
PFI-0718N-3D2DZ-J2	Propylene Glycol	217.0	7.06	4"x2	173.6	4.68	4"x2	260.4	9.9	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0718N-3D2DZ-K2	Propylene Glycol	217.0	7.06	4"x2	173.6	4.68	4"x2	260.4	9.9	4"x2
PFI-0718N-3D3DZ-L2	Propylene Glycol	218.6	6.15	4"x2	174.9	4.07	4"x2	262.4	8.62	4"x2
PFI-0718N-3D4DZ-M2	Propylene Glycol	220.3	5.44	4"x2	176.2	3.6	4"x2	264.3	7.62	4"x2
PFI-0718N-4D1EZ-H2	Propylene Glycol	215.3	10.8	4"x2	172.3	7.17	4"x2	258.4	15.2	4"x2
PFI-0718N-4D2DZ-J2	Propylene Glycol	217.0	9.22	4"x2	173.6	6.1	4"x2	260.4	12.9	4"x2
PFI-0718N-4D3DZ-K2	Propylene Glycol	218.6	8	4"x2	174.9	5.29	4"x2	262.4	11.2	4"x2
PFI-0718N-4D2DZ-L2	Propylene Glycol	217.0	9.22	4"x2	173.6	6.1	4"x2	260.4	12.9	4"x2
PFI-0718N-4D2EZ-L2	Propylene Glycol	217.0	9.23	4"x2	173.6	6.11	4"x2	260.4	12.9	4"x2
PFI-0718N-4D3DZ-M2	Propylene Glycol	218.6	8	4"x2	174.9	5.29	4"x2	262.4	11.2	4"x2
PFI-0718N-4D2EZ-M2	Propylene Glycol	217.0	9.23	4"x2	173.6	6.11	4"x2	260.4	12.9	4"x2
PFI-0718N-5D1EZ-J2	Propylene Glycol	215.3	13.4	4"x2	172.3	8.86	4"x2	258.4	18.8	4"x2
PFI-0718N-5D1EZ-M2	Propylene Glycol	215.3	13.4	4"x2	172.3	8.86	4"x2	258.4	18.8	4"x2
PFI-0718N-6D1EZ-H2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.6	4"x2	258.4	22.3	4"x2
PFI-0718N-6D1EZ-J2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.6	4"x2	258.4	22.3	4"x2
PFI-0718N-6D1EZ-K2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.6	4"x2	258.4	22.3	4"x2
PFI-0718N-6D1EZ-L2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.6	4"x2	258.4	22.3	4"x2
PFI-0718N-6D2EZ-M2	Propylene Glycol	217.0	13.5	4"x2	173.6	8.96	4"x2	260.4	19	4"x2
PFI-0718N-3D4BT-H2	Propylene Glycol	220.3	5.42	4"x2	176.2	3.58	4"x2	264.3	7.59	4"x2
PFI-0718N-3D4BT-J2	Propylene Glycol	220.3	5.42	4"x2	176.2	3.58	4"x2	264.3	7.59	4"x2
PFI-0718N-3D4BT-K2	Propylene Glycol	220.3	5.42	4"x2	176.2	3.58	4"x2	264.3	7.59	4"x2
PFI-0718N-3D4BT-L2	Propylene Glycol	220.3	5.42	4"x2	176.2	3.58	4"x2	264.3	7.59	4"x2
PFI-0718N-3D4BT-M2	Propylene Glycol	220.3	5.42	4"x2	176.2	3.58	4"x2	264.3	7.59	4"x2
PFI-0718N-4D2BT-H2	Propylene Glycol	217.0	9.19	4"x2	173.6	6.09	4"x2	260.4	12.9	4"x2
PFI-0718N-4D4BT-J2	Propylene Glycol	220.3	7.02	4"x2	176.2	4.65	4"x2	264.3	9.84	4"x2
PFI-0718N-4D4BT-K2	Propylene Glycol	220.3	7.02	4"x2	176.2	4.65	4"x2	264.3	9.84	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-0718N-4D4BT-L2	Propylene Glycol	220.3	7.02	4"x2	176.2	4.65	4"x2	264.3	9.84	4"x2
PFI-0718N-4D4BT-M2	Propylene Glycol	220.3	7.02	4"x2	176.2	4.65	4"x2	264.3	9.84	4"x2
PFI-0718N-5D3BT-H2	Propylene Glycol	218.6	9.82	4"x2	174.9	6.5	4"x2	262.4	13.8	4"x2
PFI-0718N-5D3BT-J2	Propylene Glycol	218.6	9.82	4"x2	174.9	6.5	4"x2	262.4	13.8	4"x2
PFI-0718N-5D3BT-K2	Propylene Glycol	218.6	9.82	4"x2	174.9	6.5	4"x2	262.4	13.8	4"x2
PFI-0718N-5D4BT-L2	Propylene Glycol	220.3	8.63	4"x2	176.2	5.71	4"x2	264.3	12.1	4"x2
PFI-0718N-5D4BT-M2	Propylene Glycol	220.3	8.63	4"x2	176.2	5.71	4"x2	264.3	12.1	4"x2
PFI-0718N-6D1BT-H2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.5	4"x2	258.4	22.3	4"x2
PFI-0718N-6D1BT-J2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.5	4"x2	258.4	22.3	4"x2
PFI-0718N-6D1BT-K2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.5	4"x2	258.4	22.3	4"x2
PFI-0718N-6D1BT-L2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.5	4"x2	258.4	22.3	4"x2
PFI-0718N-6D1BT-M2	Propylene Glycol	215.3	15.9	4"x2	172.3	10.5	4"x2	258.4	22.3	4"x2
PFI-1012N-2D2DS-J1	Propylene Glycol	494.5	1.75	4"x2	395.6	1.16	4"x2	593.4	2.44	4"x2
PFI-1012N-2D4ES-K1	Propylene Glycol	514.3	1.54	4"x2	411.4	1.02	4"x2	617.1	2.15	4"x2
PFI-1012N-2D2ES-L1	Propylene Glycol	494.5	1.75	4"x2	395.6	1.16	4"x2	593.4	2.44	4"x2
PFI-1012N-2D4ES-M1	Propylene Glycol	514.3	1.54	4"x2	411.4	1.02	4"x2	617.1	2.15	4"x2
PFI-1012N-2D4ES-N1	Propylene Glycol	514.3	1.54	4"x2	411.4	1.02	4"x2	617.1	2.15	4"x2
PFI-1012N-3D1DS-K1	Propylene Glycol	485.7	2.51	4"x2	388.5	1.66	4"x2	582.8	3.51	4"x2
PFI-1012N-3D1DS-L1	Propylene Glycol	485.7	2.51	4"x2	388.5	1.66	4"x2	582.8	3.51	4"x2
PFI-1012N-3D4DS-L1	Propylene Glycol	514.3	1.95	4"x2	411.4	1.29	4"x2	617.1	2.73	4"x2
PFI-1012N-3D2ES-M1	Propylene Glycol	494.5	2.28	4"x2	395.6	1.51	4"x2	593.4	3.19	4"x2
PFI-1012N-3D1DS-N1	Propylene Glycol	485.7	2.51	4"x2	388.5	1.66	4"x2	582.8	3.51	4"x2
PFI-1012N-3D3DS-N1	Propylene Glycol	505.5	2.07	4"x2	404.4	1.37	4"x2	606.6	2.9	4"x2
PFI-1012N-3D1DS-O1	Propylene Glycol	485.7	2.51	4"x2	388.5	1.66	4"x2	582.8	3.51	4"x2
PFI-1012N-3D4ES-O1	Propylene Glycol	514.3	1.95	4"x2	411.4	1.29	4"x2	617.1	2.73	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-4D4ES-J1	Propylene Glycol	514.3	2.36	4"x2	411.4	1.56	4"x2	617.1	3.3	4"x2
PFI-1012N-4D2DS-K1	Propylene Glycol	494.5	2.81	4"x2	395.6	1.86	4"x2	593.4	3.94	4"x2
PFI-1012N-4D3DS-L1	Propylene Glycol	505.5	2.53	4"x2	404.4	1.67	4"x2	606.6	3.54	4"x2
PFI-1012N-4D1DS-M1	Propylene Glycol	485.7	3.12	4"x2	388.5	2.07	4"x2	582.8	4.37	4"x2
PFI-1012N-4D2ES-N1	Propylene Glycol	494.5	2.81	4"x2	395.6	1.86	4"x2	593.4	3.94	4"x2
PFI-1012N-4D1DS-O1	Propylene Glycol	485.7	3.12	4"x2	388.5	2.07	4"x2	582.8	4.37	4"x2
PFI-1012N-5D1DS-L1	Propylene Glycol	485.7	3.74	4"x2	388.5	2.47	4"x2	582.8	5.23	4"x2
PFI-1012N-5D2DS-M1	Propylene Glycol	494.5	3.35	4"x2	395.6	2.22	4"x2	593.4	4.69	4"x2
PFI-1012N-5D2DS-O1	Propylene Glycol	494.5	3.35	4"x2	395.6	2.22	4"x2	593.4	4.69	4"x2
PFI-1012N-6D1ES-J1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1ES-K1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1DS-L1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1ES-L1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1ES-M1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1DS-N1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1ES-O1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-3D3BS-K1	Propylene Glycol	505.5	2.07	4"x2	404.4	1.37	4"x2	606.6	2.9	4"x2
PFI-1012N-3D4BS-L1	Propylene Glycol	514.3	1.95	4"x2	411.4	1.29	4"x2	617.1	2.73	4"x2
PFI-1012N-3D4BS-M1	Propylene Glycol	514.3	1.95	4"x2	411.4	1.29	4"x2	617.1	2.73	4"x2
PFI-1012N-3D4BS-N1	Propylene Glycol	514.3	1.95	4"x2	411.4	1.29	4"x2	617.1	2.73	4"x2
PFI-1012N-3D4BS-O1	Propylene Glycol	514.3	1.95	4"x2	411.4	1.29	4"x2	617.1	2.73	4"x2
PFI-1012N-4D4BS-J1	Propylene Glycol	514.3	2.36	4"x2	411.4	1.56	4"x2	617.1	3.3	4"x2
PFI-1012N-4D4BS-K1	Propylene Glycol	514.3	2.36	4"x2	411.4	1.56	4"x2	617.1	3.3	4"x2
PFI-1012N-4D3BS-L1	Propylene Glycol	505.5	2.53	4"x2	404.4	1.67	4"x2	606.6	3.54	4"x2
PFI-1012N-4D4BS-M1	Propylene Glycol	514.3	2.36	4"x2	411.4	1.56	4"x2	617.1	3.3	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-4D3BS-N1	Propylene Glycol	505.5	2.53	4"x2	404.4	1.67	4"x2	606.6	3.54	4"x2
PFI-1012N-4D4BS-O1	Propylene Glycol	514.3	2.36	4"x2	411.4	1.56	4"x2	617.1	3.3	4"x2
PFI-1012N-5D4BS-J1	Propylene Glycol	514.3	2.76	4"x2	411.4	1.83	4"x2	617.1	3.87	4"x2
PFI-1012N-5D4BS-K1	Propylene Glycol	514.3	2.76	4"x2	411.4	1.83	4"x2	617.1	3.87	4"x2
PFI-1012N-5D4BS-L1	Propylene Glycol	514.3	2.76	4"x2	411.4	1.83	4"x2	617.1	3.87	4"x2
PFI-1012N-5D2BS-M1	Propylene Glycol	494.5	3.35	4"x2	395.6	2.22	4"x2	593.4	4.69	4"x2
PFI-1012N-5D4BS-N1	Propylene Glycol	514.3	2.76	4"x2	411.4	1.83	4"x2	617.1	3.87	4"x2
PFI-1012N-5D2BS-O1	Propylene Glycol	494.5	3.35	4"x2	395.6	2.22	4"x2	593.4	4.69	4"x2
PFI-1012N-6D1BS-J1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1BS-K1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1BS-L1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1BS-M1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1BS-N1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-6D1BS-O1	Propylene Glycol	485.7	4.35	4"x2	388.5	2.88	4"x2	582.8	6.09	4"x2
PFI-1012N-2D2DZ-J1	Propylene Glycol	223.6	2.41	4"x2	178.9	1.6	4"x2	268.3	3.38	4"x2
PFI-1012N-2D4EZ-K1	Propylene Glycol	228.5	1.98	4"x2	182.8	1.31	4"x2	274.2	2.77	4"x2
PFI-1012N-2D2EZ-L1	Propylene Glycol	223.6	2.42	4"x2	178.9	1.6	4"x2	268.3	3.38	4"x2
PFI-1012N-2D4EZ-M1	Propylene Glycol	228.5	1.98	4"x2	182.8	1.31	4"x2	274.2	2.77	4"x2
PFI-1012N-2D4EZ-N1	Propylene Glycol	228.5	1.98	4"x2	182.8	1.31	4"x2	274.2	2.77	4"x2
PFI-1012N-3D1DZ-K1	Propylene Glycol	221.4	3.74	4"x2	177.1	2.48	4"x2	265.7	5.24	4"x2
PFI-1012N-3D1DZ-L1	Propylene Glycol	221.4	3.74	4"x2	177.1	2.48	4"x2	265.7	5.24	4"x2
PFI-1012N-3D4DZ-L1	Propylene Glycol	228.5	2.63	4"x2	182.8	1.74	4"x2	274.2	3.68	4"x2
PFI-1012N-3D2EZ-M1	Propylene Glycol	223.6	3.31	4"x2	178.9	2.19	4"x2	268.3	4.63	4"x2
PFI-1012N-3D1DZ-N1	Propylene Glycol	221.4	3.74	4"x2	177.1	2.48	4"x2	265.7	5.24	4"x2
PFI-1012N-3D3DZ-N1	Propylene Glycol	226.3	2.88	4"x2	181.1	1.91	4"x2	271.6	4.04	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-3D1DZ-O1	Propylene Glycol	221.4	3.74	4"x2	177.1	2.48	4"x2	265.7	5.24	4"x2
PFI-1012N-3D4EZ-O1	Propylene Glycol	228.5	2.64	4"x2	182.8	1.75	4"x2	274.2	3.7	4"x2
PFI-1012N-4D4EZ-J1	Propylene Glycol	228.5	3.3	4"x2	182.8	2.19	4"x2	274.2	4.62	4"x2
PFI-1012N-4D2DZ-K1	Propylene Glycol	223.6	4.19	4"x2	178.9	2.77	4"x2	268.3	5.87	4"x2
PFI-1012N-4D3DZ-L1	Propylene Glycol	226.3	3.63	4"x2	181.1	2.4	4"x2	271.6	5.09	4"x2
PFI-1012N-4D1DZ-M1	Propylene Glycol	221.4	4.78	4"x2	177.1	3.16	4"x2	265.7	6.7	4"x2
PFI-1012N-4D2EZ-N1	Propylene Glycol	223.6	4.2	4"x2	178.9	2.78	4"x2	268.3	5.88	4"x2
PFI-1012N-4D1DZ-O1	Propylene Glycol	221.4	4.78	4"x2	177.1	3.16	4"x2	265.7	6.7	4"x2
PFI-1012N-5D1DZ-L1	Propylene Glycol	221.4	5.82	4"x2	177.1	3.85	4"x2	265.7	8.16	4"x2
PFI-1012N-5D2DZ-M1	Propylene Glycol	223.6	5.08	4"x2	178.9	3.36	4"x2	268.3	7.11	4"x2
PFI-1012N-5D2DZ-O1	Propylene Glycol	223.6	5.08	4"x2	178.9	3.36	4"x2	268.3	7.11	4"x2
PFI-1012N-6D1EZ-J1	Propylene Glycol	221.4	6.88	4"x2	177.1	4.55	4"x2	265.7	9.63	4"x2
PFI-1012N-6D1EZ-K1	Propylene Glycol	221.4	6.88	4"x2	177.1	4.55	4"x2	265.7	9.63	4"x2
PFI-1012N-6D1DZ-L1	Propylene Glycol	221.4	6.86	4"x2	177.1	4.54	4"x2	265.7	9.62	4"x2
PFI-1012N-6D1EZ-L1	Propylene Glycol	221.4	6.88	4"x2	177.1	4.55	4"x2	265.7	9.63	4"x2
PFI-1012N-6D1EZ-M1	Propylene Glycol	221.4	6.88	4"x2	177.1	4.55	4"x2	265.7	9.63	4"x2
PFI-1012N-6D1DZ-N1	Propylene Glycol	221.4	6.86	4"x2	177.1	4.54	4"x2	265.7	9.62	4"x2
PFI-1012N-6D1EZ-O1	Propylene Glycol	221.4	6.88	4"x2	177.1	4.55	4"x2	265.7	9.63	4"x2
PFI-1012N-3D3BT-K1	Propylene Glycol	226.3	2.86	4"x2	181.1	1.9	4"x2	271.6	4.01	4"x2
PFI-1012N-3D4BT-L1	Propylene Glycol	228.5	2.61	4"x2	182.8	1.73	4"x2	274.2	3.66	4"x2
PFI-1012N-3D4BT-M1	Propylene Glycol	228.5	2.61	4"x2	182.8	1.73	4"x2	274.2	3.66	4"x2
PFI-1012N-3D4BT-N1	Propylene Glycol	228.5	2.61	4"x2	182.8	1.73	4"x2	274.2	3.66	4"x2
PFI-1012N-3D4BT-O1	Propylene Glycol	228.5	2.61	4"x2	182.8	1.73	4"x2	274.2	3.66	4"x2
PFI-1012N-4D4BT-J1	Propylene Glycol	228.5	3.27	4"x2	182.8	2.16	4"x2	274.2	4.58	4"x2
PFI-1012N-4D4BT-K1	Propylene Glycol	228.5	3.27	4"x2	182.8	2.16	4"x2	274.2	4.58	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1012N-4D3BT-L1	Propylene Glycol	226.3	3.61	4"x2	181.1	2.39	4"x2	271.6	5.05	4"x2
PFI-1012N-4D4BT-M1	Propylene Glycol	228.5	3.27	4"x2	182.8	2.16	4"x2	274.2	4.58	4"x2
PFI-1012N-4D3BT-N1	Propylene Glycol	226.3	3.61	4"x2	181.1	2.39	4"x2	271.6	5.05	4"x2
PFI-1012N-4D4BT-O1	Propylene Glycol	228.5	3.27	4"x2	182.8	2.16	4"x2	274.2	4.58	4"x2
PFI-1012N-5D4BT-J1	Propylene Glycol	228.5	3.92	4"x2	182.8	2.6	4"x2	274.2	5.5	4"x2
PFI-1012N-5D4BT-K1	Propylene Glycol	228.5	3.92	4"x2	182.8	2.6	4"x2	274.2	5.5	4"x2
PFI-1012N-5D4BT-L1	Propylene Glycol	228.5	3.92	4"x2	182.8	2.6	4"x2	274.2	5.5	4"x2
PFI-1012N-5D2BT-M1	Propylene Glycol	223.6	5.05	4"x2	178.9	3.34	4"x2	268.3	7.07	4"x2
PFI-1012N-5D4BT-N1	Propylene Glycol	228.5	3.92	4"x2	182.8	2.6	4"x2	274.2	5.5	4"x2
PFI-1012N-5D2BT-O1	Propylene Glycol	223.6	5.05	4"x2	178.9	3.34	4"x2	268.3	7.07	4"x2
PFI-1012N-6D1BT-J1	Propylene Glycol	221.4	6.83	4"x2	177.1	4.52	4"x2	265.7	9.57	4"x2
PFI-1012N-6D1BT-K1	Propylene Glycol	221.4	6.83	4"x2	177.1	4.52	4"x2	265.7	9.57	4"x2
PFI-1012N-6D1BT-L1	Propylene Glycol	221.4	6.83	4"x2	177.1	4.52	4"x2	265.7	9.57	4"x2
PFI-1012N-6D2BT-M1	Propylene Glycol	223.6	5.94	4"x2	178.9	3.93	4"x2	268.3	8.32	4"x2
PFI-1012N-6D1BT-N1	Propylene Glycol	221.4	6.83	4"x2	177.1	4.52	4"x2	265.7	9.57	4"x2
PFI-1012N-6D1BT-O1	Propylene Glycol	221.4	6.83	4"x2	177.1	4.52	4"x2	265.7	9.57	4"x2
PFI-1024N-2D2DS-J2	Propylene Glycol	989.0	1.75	4"x4	791.2	1.16	4"x4	1186.7	2.44	4"x4
PFI-1024N-2D4ES-K2	Propylene Glycol	1028.6	1.54	4"x4	822.8	1.02	4"x4	1234.3	2.15	4"x4
PFI-1024N-2D2ES-L2	Propylene Glycol	989.0	1.75	4"x4	791.2	1.16	4"x4	1186.7	2.44	4"x4
PFI-1024N-2D4ES-M2	Propylene Glycol	1028.6	1.54	4"x4	822.8	1.02	4"x4	1234.3	2.15	4"x4
PFI-1024N-2D4ES-N2	Propylene Glycol	1028.6	1.54	4"x4	822.8	1.02	4"x4	1234.3	2.15	4"x4
PFI-1024N-3D1DS-K2	Propylene Glycol	971.4	2.51	4"x4	777.1	1.66	4"x4	1165.6	3.51	4"x4
PFI-1024N-3D1DS-L2	Propylene Glycol	971.4	2.51	4"x4	777.1	1.66	4"x4	1165.6	3.51	4"x4
PFI-1024N-3D4DS-L2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-1024N-3D2ES-M2	Propylene Glycol	989.0	2.28	4"x4	791.2	1.51	4"x4	1186.7	3.19	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-3D1DS-N2	Propylene Glycol	971.4	2.51	4"x4	777.1	1.66	4"x4	1165.6	3.51	4"x4
PFI-1024N-3D3DS-N2	Propylene Glycol	1011.0	2.07	4"x4	808.8	1.37	4"x4	1213.1	2.9	4"x4
PFI-1024N-3D1DS-O2	Propylene Glycol	971.4	2.51	4"x4	777.1	1.66	4"x4	1165.6	3.51	4"x4
PFI-1024N-3D4ES-O2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-1024N-4D4ES-J2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-1024N-4D2DS-K2	Propylene Glycol	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.94	4"x4
PFI-1024N-4D3DS-L2	Propylene Glycol	1011.0	2.53	4"x4	808.8	1.67	4"x4	1213.1	3.54	4"x4
PFI-1024N-4D1DS-M2	Propylene Glycol	971.4	3.12	4"x4	777.1	2.07	4"x4	1165.6	4.37	4"x4
PFI-1024N-4D2ES-N2	Propylene Glycol	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.94	4"x4
PFI-1024N-4D1DS-O2	Propylene Glycol	971.4	3.12	4"x4	777.1	2.07	4"x4	1165.6	4.37	4"x4
PFI-1024N-5D1DS-L2	Propylene Glycol	971.4	3.74	4"x4	777.1	2.47	4"x4	1165.6	5.23	4"x4
PFI-1024N-5D2DS-M2	Propylene Glycol	989.0	3.35	4"x4	791.2	2.22	4"x4	1186.7	4.68	4"x4
PFI-1024N-5D2DS-O2	Propylene Glycol	989.0	3.35	4"x4	791.2	2.22	4"x4	1186.7	4.68	4"x4
PFI-1024N-6D1ES-J2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1ES-K2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1DS-L2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1ES-L2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1ES-M2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1DS-N2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1ES-O2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-3D3BS-K2	Propylene Glycol	1011.0	2.07	4"x4	808.8	1.37	4"x4	1213.1	2.9	4"x4
PFI-1024N-3D4BS-L2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-1024N-3D4BS-M2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-1024N-3D4BS-N2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-1024N-3D4BS-O2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-4D4BS-J2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-1024N-4D4BS-K2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-1024N-4D3BS-L2	Propylene Glycol	1011.0	2.53	4"x4	808.8	1.67	4"x4	1213.1	3.54	4"x4
PFI-1024N-4D4BS-M2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-1024N-4D3BS-N2	Propylene Glycol	1011.0	2.53	4"x4	808.8	1.67	4"x4	1213.1	3.54	4"x4
PFI-1024N-4D4BS-O2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-1024N-5D4BS-J2	Propylene Glycol	1028.6	2.76	4"x4	822.8	1.83	4"x4	1234.3	3.87	4"x4
PFI-1024N-5D4BS-K2	Propylene Glycol	1028.6	2.76	4"x4	822.8	1.83	4"x4	1234.3	3.87	4"x4
PFI-1024N-5D4BS-L2	Propylene Glycol	1028.6	2.76	4"x4	822.8	1.83	4"x4	1234.3	3.87	4"x4
PFI-1024N-5D2BS-M2	Propylene Glycol	989.0	3.35	4"x4	791.2	2.22	4"x4	1186.7	4.68	4"x4
PFI-1024N-5D4BS-N2	Propylene Glycol	1028.6	2.76	4"x4	822.8	1.83	4"x4	1234.3	3.87	4"x4
PFI-1024N-5D2BS-O2	Propylene Glycol	989.0	3.35	4"x4	791.2	2.22	4"x4	1186.7	4.68	4"x4
PFI-1024N-6D1BS-J2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1BS-K2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1BS-L2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1BS-M2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1BS-N2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-6D1BS-O2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-1024N-2D2DZ-J2	Propylene Glycol	447.2	2.41	4"x4	357.7	1.6	4"x4	536.6	3.38	4"x4
PFI-1024N-2D4EZ-K2	Propylene Glycol	457.1	1.98	4"x4	365.7	1.31	4"x4	548.5	2.77	4"x4
PFI-1024N-2D2EZ-L2	Propylene Glycol	447.2	2.42	4"x4	357.7	1.6	4"x4	536.6	3.38	4"x4
PFI-1024N-2D4EZ-M2	Propylene Glycol	457.1	1.98	4"x4	365.7	1.31	4"x4	548.5	2.77	4"x4
PFI-1024N-2D4EZ-N2	Propylene Glycol	457.1	1.98	4"x4	365.7	1.31	4"x4	548.5	2.77	4"x4
PFI-1024N-3D1DZ-K2	Propylene Glycol	442.8	3.74	4"x4	354.2	2.48	4"x4	531.3	5.24	4"x4
PFI-1024N-3D1DZ-L2	Propylene Glycol	442.8	3.74	4"x4	354.2	2.48	4"x4	531.3	5.24	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-3D4DZ-L2	Propylene Glycol	457.1	2.63	4"x4	365.7	1.74	4"x4	548.5	3.68	4"x4
PFI-1024N-3D2EZ-M2	Propylene Glycol	447.2	3.31	4"x4	357.7	2.19	4"x4	536.6	4.63	4"x4
PFI-1024N-3D1DZ-N2	Propylene Glycol	442.8	3.74	4"x4	354.2	2.48	4"x4	531.3	5.24	4"x4
PFI-1024N-3D3DZ-N2	Propylene Glycol	452.7	2.88	4"x4	362.1	1.91	4"x4	543.2	4.04	4"x4
PFI-1024N-3D1DZ-O2	Propylene Glycol	442.8	3.74	4"x4	354.2	2.48	4"x4	531.3	5.24	4"x4
PFI-1024N-3D4EZ-O2	Propylene Glycol	457.1	2.64	4"x4	365.7	1.75	4"x4	548.5	3.7	4"x4
PFI-1024N-4D4EZ-J2	Propylene Glycol	457.1	3.3	4"x4	365.7	2.19	4"x4	548.5	4.63	4"x4
PFI-1024N-4D2DZ-K2	Propylene Glycol	447.2	4.19	4"x4	357.7	2.77	4"x4	536.6	5.87	4"x4
PFI-1024N-4D3DZ-L2	Propylene Glycol	452.7	3.63	4"x4	362.1	2.4	4"x4	543.2	5.09	4"x4
PFI-1024N-4D1DZ-M2	Propylene Glycol	442.8	4.78	4"x4	354.2	3.16	4"x4	531.3	6.7	4"x4
PFI-1024N-4D2EZ-N2	Propylene Glycol	447.2	4.2	4"x4	357.7	2.78	4"x4	536.6	5.88	4"x4
PFI-1024N-4D1DZ-O2	Propylene Glycol	442.8	4.78	4"x4	354.2	3.16	4"x4	531.3	6.7	4"x4
PFI-1024N-5D1DZ-L2	Propylene Glycol	442.8	5.82	4"x4	354.2	3.85	4"x4	531.3	8.16	4"x4
PFI-1024N-5D2DZ-M2	Propylene Glycol	447.2	5.08	4"x4	357.7	3.36	4"x4	536.6	7.11	4"x4
PFI-1024N-5D2DZ-O2	Propylene Glycol	447.2	5.08	4"x4	357.7	3.36	4"x4	536.6	7.11	4"x4
PFI-1024N-6D1EZ-J2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-1024N-6D1EZ-K2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-1024N-6D1DZ-L2	Propylene Glycol	442.8	6.86	4"x4	354.2	4.54	4"x4	531.3	9.62	4"x4
PFI-1024N-6D1EZ-L2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-1024N-6D1EZ-M2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-1024N-6D1DZ-N2	Propylene Glycol	442.8	6.86	4"x4	354.2	4.54	4"x4	531.3	9.62	4"x4
PFI-1024N-6D1EZ-O2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-1024N-3D3BT-K2	Propylene Glycol	452.7	2.87	4"x4	362.1	1.9	4"x4	543.2	4.01	4"x4
PFI-1024N-3D4BT-L2	Propylene Glycol	457.1	2.61	4"x4	365.7	1.73	4"x4	548.5	3.66	4"x4
PFI-1024N-3D4BT-M2	Propylene Glycol	457.1	2.61	4"x4	365.7	1.73	4"x4	548.5	3.66	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1024N-3D4BT-N2	Propylene Glycol	457.1	2.61	4"x4	365.7	1.73	4"x4	548.5	3.66	4"x4
PFI-1024N-3D4BT-O2	Propylene Glycol	457.1	2.61	4"x4	365.7	1.73	4"x4	548.5	3.66	4"x4
PFI-1024N-4D4BT-J2	Propylene Glycol	457.1	3.27	4"x4	365.7	2.16	4"x4	548.5	4.58	4"x4
PFI-1024N-4D4BT-K2	Propylene Glycol	457.1	3.27	4"x4	365.7	2.16	4"x4	548.5	4.58	4"x4
PFI-1024N-4D3BT-L2	Propylene Glycol	452.7	3.61	4"x4	362.1	2.39	4"x4	543.2	5.05	4"x4
PFI-1024N-4D4BT-M2	Propylene Glycol	457.1	3.27	4"x4	365.7	2.16	4"x4	548.5	4.58	4"x4
PFI-1024N-4D3BT-N2	Propylene Glycol	452.7	3.61	4"x4	362.1	2.39	4"x4	543.2	5.05	4"x4
PFI-1024N-4D4BT-O2	Propylene Glycol	457.1	3.27	4"x4	365.7	2.16	4"x4	548.5	4.58	4"x4
PFI-1024N-5D4BT-J2	Propylene Glycol	457.1	3.92	4"x4	365.7	2.6	4"x4	548.5	5.5	4"x4
PFI-1024N-5D4BT-K2	Propylene Glycol	457.1	3.92	4"x4	365.7	2.6	4"x4	548.5	5.5	4"x4
PFI-1024N-5D4BT-L2	Propylene Glycol	457.1	3.92	4"x4	365.7	2.6	4"x4	548.5	5.5	4"x4
PFI-1024N-5D2BT-M2	Propylene Glycol	447.2	5.05	4"x4	357.7	3.34	4"x4	536.6	7.07	4"x4
PFI-1024N-5D4BT-N2	Propylene Glycol	457.1	3.92	4"x4	365.7	2.6	4"x4	548.5	5.5	4"x4
PFI-1024N-5D2BT-O2	Propylene Glycol	447.2	5.05	4"x4	357.7	3.34	4"x4	536.6	7.07	4"x4
PFI-1024N-6D1BT-J2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-1024N-6D1BT-K2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-1024N-6D1BT-L2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-1024N-6D2BT-M2	Propylene Glycol	447.2	5.94	4"x4	357.7	3.93	4"x4	536.6	8.32	4"x4
PFI-1024N-6D1BT-N2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-1024N-6D1BT-O2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-2012N-2D2DS-J2	Propylene Glycol	989.0	1.75	4"x4	791.2	1.16	4"x4	1186.7	2.44	4"x4
PFI-2012N-2D4ES-K2	Propylene Glycol	1028.6	1.54	4"x4	822.8	1.02	4"x4	1234.3	2.15	4"x4
PFI-2012N-2D2ES-L2	Propylene Glycol	989.0	1.75	4"x4	791.2	1.16	4"x4	1186.7	2.44	4"x4
PFI-2012N-2D4ES-M2	Propylene Glycol	1028.6	1.54	4"x4	822.8	1.02	4"x4	1234.3	2.15	4"x4
PFI-2012N-2D4ES-N2	Propylene Glycol	1028.6	1.54	4"x4	822.8	1.02	4"x4	1234.3	2.15	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-3D1DS-K2	Propylene Glycol	971.4	2.51	4"x4	777.1	1.66	4"x4	1165.6	3.51	4"x4
PFI-2012N-3D1DS-L2	Propylene Glycol	971.4	2.51	4"x4	777.1	1.66	4"x4	1165.6	3.51	4"x4
PFI-2012N-3D4DS-L2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-2012N-3D2ES-M2	Propylene Glycol	989.0	2.28	4"x4	791.2	1.51	4"x4	1186.7	3.19	4"x4
PFI-2012N-3D1DS-N2	Propylene Glycol	971.4	2.51	4"x4	777.1	1.66	4"x4	1165.6	3.51	4"x4
PFI-2012N-3D3DS-N2	Propylene Glycol	1011.0	2.07	4"x4	808.8	1.37	4"x4	1213.1	2.9	4"x4
PFI-2012N-3D1DS-O2	Propylene Glycol	971.4	2.51	4"x4	777.1	1.66	4"x4	1165.6	3.51	4"x4
PFI-2012N-3D4ES-O2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-2012N-4D4ES-J2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-2012N-4D2DS-K2	Propylene Glycol	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.94	4"x4
PFI-2012N-4D3DS-L2	Propylene Glycol	1011.0	2.53	4"x4	808.8	1.67	4"x4	1213.1	3.54	4"x4
PFI-2012N-4D1DS-M2	Propylene Glycol	971.4	3.12	4"x4	777.1	2.07	4"x4	1165.6	4.37	4"x4
PFI-2012N-4D2ES-N2	Propylene Glycol	989.0	2.81	4"x4	791.2	1.86	4"x4	1186.7	3.94	4"x4
PFI-2012N-4D1DS-O2	Propylene Glycol	971.4	3.12	4"x4	777.1	2.07	4"x4	1165.6	4.37	4"x4
PFI-2012N-5D1DS-L2	Propylene Glycol	971.4	3.74	4"x4	777.1	2.47	4"x4	1165.6	5.23	4"x4
PFI-2012N-5D2DS-M2	Propylene Glycol	989.0	3.35	4"x4	791.2	2.22	4"x4	1186.7	4.68	4"x4
PFI-2012N-5D2DS-O2	Propylene Glycol	989.0	3.35	4"x4	791.2	2.22	4"x4	1186.7	4.68	4"x4
PFI-2012N-6D1ES-J2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1ES-K2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1DS-L2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1ES-L2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1ES-M2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1DS-N2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1ES-O2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-3D3BS-K2	Propylene Glycol	1011.0	2.07	4"x4	808.8	1.37	4"x4	1213.1	2.9	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-3D4BS-L2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-2012N-3D4BS-M2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-2012N-3D4BS-N2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-2012N-3D4BS-O2	Propylene Glycol	1028.6	1.95	4"x4	822.8	1.29	4"x4	1234.3	2.73	4"x4
PFI-2012N-4D4BS-J2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-2012N-4D4BS-K2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-2012N-4D3BS-L2	Propylene Glycol	1011.0	2.53	4"x4	808.8	1.67	4"x4	1213.1	3.54	4"x4
PFI-2012N-4D4BS-M2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-2012N-4D3BS-N2	Propylene Glycol	1011.0	2.53	4"x4	808.8	1.67	4"x4	1213.1	3.54	4"x4
PFI-2012N-4D4BS-O2	Propylene Glycol	1028.6	2.36	4"x4	822.8	1.56	4"x4	1234.3	3.3	4"x4
PFI-2012N-5D4BS-J2	Propylene Glycol	1028.6	2.76	4"x4	822.8	1.83	4"x4	1234.3	3.87	4"x4
PFI-2012N-5D4BS-K2	Propylene Glycol	1028.6	2.76	4"x4	822.8	1.83	4"x4	1234.3	3.87	4"x4
PFI-2012N-5D4BS-L2	Propylene Glycol	1028.6	2.76	4"x4	822.8	1.83	4"x4	1234.3	3.87	4"x4
PFI-2012N-5D2BS-M2	Propylene Glycol	989.0	3.35	4"x4	791.2	2.22	4"x4	1186.7	4.68	4"x4
PFI-2012N-5D4BS-N2	Propylene Glycol	1028.6	2.76	4"x4	822.8	1.83	4"x4	1234.3	3.87	4"x4
PFI-2012N-5D2BS-O2	Propylene Glycol	989.0	3.35	4"x4	791.2	2.22	4"x4	1186.7	4.68	4"x4
PFI-2012N-6D1BS-J2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1BS-K2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1BS-L2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1BS-M2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1BS-N2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-6D1BS-O2	Propylene Glycol	971.4	4.35	4"x4	777.1	2.88	4"x4	1165.6	6.09	4"x4
PFI-2012N-2D2DZ-J2	Propylene Glycol	447.2	2.41	4"x4	357.7	1.6	4"x4	536.6	3.38	4"x4
PFI-2012N-2D4EZ-K2	Propylene Glycol	457.1	1.98	4"x4	365.7	1.31	4"x4	548.5	2.77	4"x4
PFI-2012N-2D2EZ-L2	Propylene Glycol	447.2	2.42	4"x4	357.7	1.6	4"x4	536.6	3.38	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-2D4EZ-M2	Propylene Glycol	457.1	1.98	4"x4	365.7	1.31	4"x4	548.5	2.77	4"x4
PFI-2012N-2D4EZ-N2	Propylene Glycol	457.1	1.98	4"x4	365.7	1.31	4"x4	548.5	2.77	4"x4
PFI-2012N-3D1DZ-K2	Propylene Glycol	442.8	3.74	4"x4	354.2	2.48	4"x4	531.3	5.24	4"x4
PFI-2012N-3D1DZ-L2	Propylene Glycol	442.8	3.74	4"x4	354.2	2.48	4"x4	531.3	5.24	4"x4
PFI-2012N-3D4DZ-L2	Propylene Glycol	457.1	2.63	4"x4	365.7	1.74	4"x4	548.5	3.68	4"x4
PFI-2012N-3D2EZ-M2	Propylene Glycol	447.2	3.31	4"x4	357.7	2.19	4"x4	536.6	4.63	4"x4
PFI-2012N-3D1DZ-N2	Propylene Glycol	442.8	3.74	4"x4	354.2	2.48	4"x4	531.3	5.24	4"x4
PFI-2012N-3D3DZ-N2	Propylene Glycol	452.7	2.88	4"x4	362.1	1.91	4"x4	543.2	4.04	4"x4
PFI-2012N-3D1DZ-O2	Propylene Glycol	442.8	3.74	4"x4	354.2	2.48	4"x4	531.3	5.24	4"x4
PFI-2012N-3D4EZ-O2	Propylene Glycol	457.1	2.64	4"x4	365.7	1.75	4"x4	548.5	3.7	4"x4
PFI-2012N-4D4EZ-J2	Propylene Glycol	457.1	3.3	4"x4	365.7	2.19	4"x4	548.5	4.63	4"x4
PFI-2012N-4D2DZ-K2	Propylene Glycol	447.2	4.19	4"x4	357.7	2.77	4"x4	536.6	5.87	4"x4
PFI-2012N-4D3DZ-L2	Propylene Glycol	452.7	3.63	4"x4	362.1	2.4	4"x4	543.2	5.09	4"x4
PFI-2012N-4D1DZ-M2	Propylene Glycol	442.8	4.78	4"x4	354.2	3.16	4"x4	531.3	6.7	4"x4
PFI-2012N-4D2EZ-N2	Propylene Glycol	447.2	4.2	4"x4	357.7	2.78	4"x4	536.6	5.88	4"x4
PFI-2012N-4D1DZ-O2	Propylene Glycol	442.8	4.78	4"x4	354.2	3.16	4"x4	531.3	6.7	4"x4
PFI-2012N-5D1DZ-L2	Propylene Glycol	442.8	5.82	4"x4	354.2	3.85	4"x4	531.3	8.16	4"x4
PFI-2012N-5D2DZ-M2	Propylene Glycol	447.2	5.08	4"x4	357.7	3.36	4"x4	536.6	7.11	4"x4
PFI-2012N-5D2DZ-O2	Propylene Glycol	447.2	5.08	4"x4	357.7	3.36	4"x4	536.6	7.11	4"x4
PFI-2012N-6D1EZ-J2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-2012N-6D1EZ-K2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-2012N-6D1DZ-L2	Propylene Glycol	442.8	6.86	4"x4	354.2	4.54	4"x4	531.3	9.62	4"x4
PFI-2012N-6D1EZ-L2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-2012N-6D1EZ-M2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-2012N-6D1DZ-N2	Propylene Glycol	442.8	6.86	4"x4	354.2	4.54	4"x4	531.3	9.62	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2012N-6D1EZ-O2	Propylene Glycol	442.8	6.88	4"x4	354.2	4.55	4"x4	531.3	9.63	4"x4
PFI-2012N-3D3BT-K2	Propylene Glycol	452.7	2.87	4"x4	362.1	1.9	4"x4	543.2	4.01	4"x4
PFI-2012N-3D4BT-L2	Propylene Glycol	457.1	2.61	4"x4	365.7	1.73	4"x4	548.5	3.66	4"x4
PFI-2012N-3D4BT-M2	Propylene Glycol	457.1	2.61	4"x4	365.7	1.73	4"x4	548.5	3.66	4"x4
PFI-2012N-3D4BT-N2	Propylene Glycol	457.1	2.61	4"x4	365.7	1.73	4"x4	548.5	3.66	4"x4
PFI-2012N-3D4BT-O2	Propylene Glycol	457.1	2.61	4"x4	365.7	1.73	4"x4	548.5	3.66	4"x4
PFI-2012N-4D4BT-J2	Propylene Glycol	457.1	3.27	4"x4	365.7	2.16	4"x4	548.5	4.58	4"x4
PFI-2012N-4D4BT-K2	Propylene Glycol	457.1	3.27	4"x4	365.7	2.16	4"x4	548.5	4.58	4"x4
PFI-2012N-4D3BT-L2	Propylene Glycol	452.7	3.61	4"x4	362.1	2.39	4"x4	543.2	5.05	4"x4
PFI-2012N-4D4BT-M2	Propylene Glycol	457.1	3.27	4"x4	365.7	2.16	4"x4	548.5	4.58	4"x4
PFI-2012N-4D3BT-N2	Propylene Glycol	452.7	3.61	4"x4	362.1	2.39	4"x4	543.2	5.05	4"x4
PFI-2012N-4D4BT-O2	Propylene Glycol	457.1	3.27	4"x4	365.7	2.16	4"x4	548.5	4.58	4"x4
PFI-2012N-5D4BT-J2	Propylene Glycol	457.1	3.92	4"x4	365.7	2.6	4"x4	548.5	5.5	4"x4
PFI-2012N-5D4BT-K2	Propylene Glycol	457.1	3.92	4"x4	365.7	2.6	4"x4	548.5	5.5	4"x4
PFI-2012N-5D4BT-L2	Propylene Glycol	457.1	3.92	4"x4	365.7	2.6	4"x4	548.5	5.5	4"x4
PFI-2012N-5D2BT-M2	Propylene Glycol	447.2	5.05	4"x4	357.7	3.34	4"x4	536.6	7.07	4"x4
PFI-2012N-5D4BT-N2	Propylene Glycol	457.1	3.92	4"x4	365.7	2.6	4"x4	548.5	5.5	4"x4
PFI-2012N-5D2BT-O2	Propylene Glycol	447.2	5.05	4"x4	357.7	3.34	4"x4	536.6	7.07	4"x4
PFI-2012N-6D1BT-J2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-2012N-6D1BT-K2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-2012N-6D1BT-L2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-2012N-6D2BT-M2	Propylene Glycol	447.2	5.94	4"x4	357.7	3.93	4"x4	536.6	8.32	4"x4
PFI-2012N-6D1BT-N2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-2012N-6D1BT-O2	Propylene Glycol	442.8	6.83	4"x4	354.2	4.52	4"x4	531.3	9.57	4"x4
PFI-1212N-2D4DS-K1	Propylene Glycol	540.7	1.41	4"x2	432.5	0.93	4"x2	648.8	1.97	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-2D3ES-L1	Propylene Glycol	527.5	1.46	4"x2	422.0	0.97	4"x2	633.0	2.04	4"x2
PFI-1212N-2D4DS-M1	Propylene Glycol	540.7	1.41	4"x2	432.5	0.93	4"x2	648.8	1.97	4"x2
PFI-1212N-2D4ES-M1	Propylene Glycol	540.7	1.41	4"x2	432.5	0.93	4"x2	648.8	1.97	4"x2
PFI-1212N-2D4ES-N1	Propylene Glycol	540.7	1.41	4"x2	432.5	0.93	4"x2	648.8	1.97	4"x2
PFI-1212N-2D4ES-O1	Propylene Glycol	540.7	1.41	4"x2	432.5	0.93	4"x2	648.8	1.97	4"x2
PFI-1212N-3D2DS-L1	Propylene Glycol	516.5	1.92	4"x2	413.2	1.27	4"x2	619.8	2.69	4"x2
PFI-1212N-3D3DS-M1	Propylene Glycol	527.5	1.81	4"x2	422.0	1.2	4"x2	633.0	2.53	4"x2
PFI-1212N-3D2ES-M1	Propylene Glycol	516.5	1.92	4"x2	413.2	1.27	4"x2	619.8	2.69	4"x2
PFI-1212N-3D2DS-N1	Propylene Glycol	516.5	1.92	4"x2	413.2	1.27	4"x2	619.8	2.69	4"x2
PFI-1212N-3D2ES-N1	Propylene Glycol	516.5	1.92	4"x2	413.2	1.27	4"x2	619.8	2.69	4"x2
PFI-1212N-3D4ES-O1	Propylene Glycol	540.7	1.71	4"x2	432.5	1.14	4"x2	648.8	2.4	4"x2
PFI-1212N-3D1DS-P1	Propylene Glycol	505.5	2.07	4"x2	404.4	1.37	4"x2	606.6	2.9	4"x2
PFI-1212N-4D1ES-K1	Propylene Glycol	505.5	2.53	4"x2	404.4	1.67	4"x2	606.6	3.54	4"x2
PFI-1212N-4D3ES-M1	Propylene Glycol	527.5	2.16	4"x2	422.0	1.43	4"x2	633.0	3.03	4"x2
PFI-1212N-4D2DS-N1	Propylene Glycol	516.5	2.32	4"x2	413.2	1.54	4"x2	619.8	3.25	4"x2
PFI-1212N-4D3DS-P1	Propylene Glycol	527.5	2.16	4"x2	422.0	1.43	4"x2	633.0	3.03	4"x2
PFI-1212N-5D2ES-K1	Propylene Glycol	516.5	2.72	4"x2	413.2	1.8	4"x2	619.8	3.8	4"x2
PFI-1212N-5D2ES-L1	Propylene Glycol	516.5	2.72	4"x2	413.2	1.8	4"x2	619.8	3.8	4"x2
PFI-1212N-5D2DS-N1	Propylene Glycol	516.5	2.72	4"x2	413.2	1.8	4"x2	619.8	3.8	4"x2
PFI-1212N-5D1DS-O1	Propylene Glycol	505.5	2.98	4"x2	404.4	1.98	4"x2	606.6	4.18	4"x2
PFI-1212N-5D4DS-O1	Propylene Glycol	540.7	2.33	4"x2	432.5	1.55	4"x2	648.8	3.27	4"x2
PFI-1212N-5D2ES-P1	Propylene Glycol	516.5	2.72	4"x2	413.2	1.8	4"x2	619.8	3.8	4"x2
PFI-1212N-6D1ES-L1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-6D1ES-M1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-6D1ES-N1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-6D1ES-O1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-6D1ES-P1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-3D3BS-L1	Propylene Glycol	527.5	1.81	4"x2	422.0	1.2	4"x2	633.0	2.53	4"x2
PFI-1212N-3D4BS-N1	Propylene Glycol	540.7	1.71	4"x2	432.5	1.14	4"x2	648.8	2.4	4"x2
PFI-1212N-3D4BS-O1	Propylene Glycol	540.7	1.71	4"x2	432.5	1.14	4"x2	648.8	2.4	4"x2
PFI-1212N-4D4BS-K1	Propylene Glycol	540.7	2.02	4"x2	432.5	1.34	4"x2	648.8	2.83	4"x2
PFI-1212N-4D3BS-L1	Propylene Glycol	527.5	2.16	4"x2	422.0	1.43	4"x2	633.0	3.03	4"x2
PFI-1212N-4D4BS-M1	Propylene Glycol	540.7	2.02	4"x2	432.5	1.34	4"x2	648.8	2.83	4"x2
PFI-1212N-4D3BS-N1	Propylene Glycol	527.5	2.16	4"x2	422.0	1.43	4"x2	633.0	3.03	4"x2
PFI-1212N-4D4BS-O1	Propylene Glycol	540.7	2.02	4"x2	432.5	1.34	4"x2	648.8	2.83	4"x2
PFI-1212N-4D4BS-P1	Propylene Glycol	540.7	2.02	4"x2	432.5	1.34	4"x2	648.8	2.83	4"x2
PFI-1212N-5D2BS-K1	Propylene Glycol	516.5	2.72	4"x2	413.2	1.8	4"x2	619.8	3.8	4"x2
PFI-1212N-5D3BS-L1	Propylene Glycol	527.5	2.51	4"x2	422.0	1.67	4"x2	633.0	3.52	4"x2
PFI-1212N-5D2BS-M1	Propylene Glycol	516.5	2.72	4"x2	413.2	1.8	4"x2	619.8	3.8	4"x2
PFI-1212N-5D2BS-N1	Propylene Glycol	516.5	2.72	4"x2	413.2	1.8	4"x2	619.8	3.8	4"x2
PFI-1212N-5D3BS-O1	Propylene Glycol	527.5	2.51	4"x2	422.0	1.67	4"x2	633.0	3.52	4"x2
PFI-1212N-5D2BS-P1	Propylene Glycol	516.5	2.72	4"x2	413.2	1.8	4"x2	619.8	3.8	4"x2
PFI-1212N-6D1BS-K1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-6D1BS-L1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-6D1BS-M1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-6D1BS-N1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-6D1BS-O1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-6D1BS-P1	Propylene Glycol	505.5	3.44	4"x2	404.4	2.28	4"x2	606.6	4.82	4"x2
PFI-1212N-2D4DZ-K1	Propylene Glycol	235.1	1.66	4"x2	188.1	1.1	4"x2	282.2	2.32	4"x2
PFI-1212N-2D3EZ-L1	Propylene Glycol	231.8	1.8	4"x2	185.5	1.19	4"x2	278.2	2.52	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-2D4DZ-M1	Propylene Glycol	235.1	1.66	4"x2	188.1	1.1	4"x2	282.2	2.32	4"x2
PFI-1212N-2D4EZ-M1	Propylene Glycol	235.1	1.66	4"x2	188.1	1.1	4"x2	282.2	2.33	4"x2
PFI-1212N-2D4EZ-N1	Propylene Glycol	235.1	1.66	4"x2	188.1	1.1	4"x2	282.2	2.33	4"x2
PFI-1212N-2D4EZ-O1	Propylene Glycol	235.1	1.66	4"x2	188.1	1.1	4"x2	282.2	2.33	4"x2
PFI-1212N-3D2DZ-L1	Propylene Glycol	229.1	2.58	4"x2	183.3	1.71	4"x2	274.9	3.62	4"x2
PFI-1212N-3D3DZ-M1	Propylene Glycol	231.8	2.35	4"x2	185.5	1.56	4"x2	278.2	3.29	4"x2
PFI-1212N-3D2EZ-M1	Propylene Glycol	229.1	2.59	4"x2	183.3	1.72	4"x2	274.9	3.63	4"x2
PFI-1212N-3D2DZ-N1	Propylene Glycol	229.1	2.58	4"x2	183.3	1.71	4"x2	274.9	3.62	4"x2
PFI-1212N-3D2EZ-N1	Propylene Glycol	229.1	2.59	4"x2	183.3	1.72	4"x2	274.9	3.63	4"x2
PFI-1212N-3D4EZ-O1	Propylene Glycol	235.1	2.15	4"x2	188.1	1.42	4"x2	282.2	3.01	4"x2
PFI-1212N-3D1DZ-P1	Propylene Glycol	226.3	2.89	4"x2	181.1	1.92	4"x2	271.6	4.05	4"x2
PFI-1212N-4D1EZ-K1	Propylene Glycol	226.3	3.65	4"x2	181.1	2.42	4"x2	271.6	5.11	4"x2
PFI-1212N-4D3EZ-M1	Propylene Glycol	231.8	2.92	4"x2	185.5	1.93	4"x2	278.2	4.09	4"x2
PFI-1212N-4D2DZ-N1	Propylene Glycol	229.1	3.23	4"x2	183.3	2.14	4"x2	274.9	4.52	4"x2
PFI-1212N-4D3DZ-P1	Propylene Glycol	231.8	2.91	4"x2	185.5	1.93	4"x2	278.2	4.08	4"x2
PFI-1212N-5D2EZ-K1	Propylene Glycol	229.1	3.88	4"x2	183.3	2.57	4"x2	274.9	5.43	4"x2
PFI-1212N-5D2EZ-L1	Propylene Glycol	229.1	3.88	4"x2	183.3	2.57	4"x2	274.9	5.43	4"x2
PFI-1212N-5D2DZ-N1	Propylene Glycol	229.1	3.87	4"x2	183.3	2.56	4"x2	274.9	5.42	4"x2
PFI-1212N-5D1DZ-O1	Propylene Glycol	226.3	4.39	4"x2	181.1	2.91	4"x2	271.6	6.15	4"x2
PFI-1212N-5D4DZ-O1	Propylene Glycol	235.1	3.1	4"x2	188.1	2.05	4"x2	282.2	4.35	4"x2
PFI-1212N-5D2EZ-P1	Propylene Glycol	229.1	3.88	4"x2	183.3	2.57	4"x2	274.9	5.43	4"x2
PFI-1212N-6D1EZ-L1	Propylene Glycol	226.3	5.15	4"x2	181.1	3.41	4"x2	271.6	7.21	4"x2
PFI-1212N-6D1EZ-M1	Propylene Glycol	226.3	5.15	4"x2	181.1	3.41	4"x2	271.6	7.21	4"x2
PFI-1212N-6D1EZ-N1	Propylene Glycol	226.3	5.15	4"x2	181.1	3.41	4"x2	271.6	7.21	4"x2
PFI-1212N-6D1EZ-O1	Propylene Glycol	226.3	5.15	4"x2	181.1	3.41	4"x2	271.6	7.21	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1212N-6D1EZ-P1	Propylene Glycol	426.3	16.6	4"x2	341.0	11	4"x2	511.5	23.3	4"x2
PFI-1212N-3D3BT-L1	Propylene Glycol	231.8	2.33	4"x2	185.5	1.55	4"x2	278.2	3.27	4"x2
PFI-1212N-3D4BT-N1	Propylene Glycol	235.1	2.12	4"x2	188.1	1.4	4"x2	282.2	2.97	4"x2
PFI-1212N-3D4BT-O1	Propylene Glycol	235.1	2.12	4"x2	188.1	1.4	4"x2	282.2	2.97	4"x2
PFI-1212N-4D4BT-K1	Propylene Glycol	235.1	2.6	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1212N-4D3BT-L1	Propylene Glycol	231.8	2.89	4"x2	185.5	1.91	4"x2	278.2	4.05	4"x2
PFI-1212N-4D4BT-M1	Propylene Glycol	235.1	2.6	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1212N-4D3BT-N1	Propylene Glycol	231.8	2.89	4"x2	185.5	1.91	4"x2	278.2	4.05	4"x2
PFI-1212N-4D4BT-O1	Propylene Glycol	235.1	2.6	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1212N-4D4BT-P1	Propylene Glycol	235.1	2.6	4"x2	188.1	1.72	4"x2	282.2	3.64	4"x2
PFI-1212N-5D2BT-K1	Propylene Glycol	229.1	3.84	4"x2	183.3	2.54	4"x2	274.9	5.38	4"x2
PFI-1212N-5D3BT-L1	Propylene Glycol	231.8	3.44	4"x2	185.5	2.28	4"x2	278.2	4.82	4"x2
PFI-1212N-5D2BT-M1	Propylene Glycol	229.1	3.84	4"x2	183.3	2.54	4"x2	274.9	5.38	4"x2
PFI-1212N-5D2BT-N1	Propylene Glycol	229.1	3.84	4"x2	183.3	2.54	4"x2	274.9	5.38	4"x2
PFI-1212N-5D3BT-O1	Propylene Glycol	231.8	3.44	4"x2	185.5	2.28	4"x2	278.2	4.82	4"x2
PFI-1212N-5D2BT-P1	Propylene Glycol	229.1	3.84	4"x2	183.3	2.54	4"x2	274.9	5.38	4"x2
PFI-1212N-6D1BT-K1	Propylene Glycol	226.3	5.11	4"x2	181.1	3.38	4"x2	271.6	7.16	4"x2
PFI-1212N-6D1BT-L1	Propylene Glycol	226.3	5.11	4"x2	181.1	3.38	4"x2	271.6	7.16	4"x2
PFI-1212N-6D1BT-M1	Propylene Glycol	226.3	5.11	4"x2	181.1	3.38	4"x2	271.6	7.16	4"x2
PFI-1212N-6D1BT-N1	Propylene Glycol	226.3	5.11	4"x2	181.1	3.38	4"x2	271.6	7.16	4"x2
PFI-1212N-6D1BT-O1	Propylene Glycol	226.3	5.11	4"x2	181.1	3.38	4"x2	271.6	7.16	4"x2
PFI-1212N-6D1BT-P1	Propylene Glycol	226.3	5.11	4"x2	181.1	3.38	4"x2	271.6	7.16	4"x2
PFI-1224N-2D4DS-K2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4
PFI-1224N-2D3ES-L2	Propylene Glycol	1055.0	1.46	4"x4	844.0	0.97	4"x4	1265.9	2.04	4"x4
PFI-1224N-2D4DS-M2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-2D4ES-M2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4
PFI-1224N-2D4ES-N2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4
PFI-1224N-2D4ES-O2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4
PFI-1224N-3D2DS-L2	Propylene Glycol	1033.0	1.92	4"x4	826.4	1.27	4"x4	1239.5	2.69	4"x4
PFI-1224N-3D3DS-M2	Propylene Glycol	1055.0	1.81	4"x4	844.0	1.2	4"x4	1265.9	2.53	4"x4
PFI-1224N-3D2ES-M2	Propylene Glycol	1033.0	1.92	4"x4	826.4	1.27	4"x4	1239.5	2.69	4"x4
PFI-1224N-3D2DS-N2	Propylene Glycol	1033.0	1.92	4"x4	826.4	1.27	4"x4	1239.5	2.69	4"x4
PFI-1224N-3D2ES-N2	Propylene Glycol	1033.0	1.92	4"x4	826.4	1.27	4"x4	1239.5	2.69	4"x4
PFI-1224N-3D4ES-O2	Propylene Glycol	1081.4	1.71	4"x4	865.1	1.14	4"x4	1297.6	2.4	4"x4
PFI-1224N-3D1DS-P2	Propylene Glycol	1011.0	2.07	4"x4	808.8	1.37	4"x4	1213.1	2.9	4"x4
PFI-1224N-4D1ES-K2	Propylene Glycol	1011.0	2.53	4"x4	808.8	1.67	4"x4	1213.1	3.54	4"x4
PFI-1224N-4D3ES-M2	Propylene Glycol	1055.0	2.16	4"x4	844.0	1.43	4"x4	1265.9	3.03	4"x4
PFI-1224N-4D2DS-N2	Propylene Glycol	1033.0	2.32	4"x4	826.4	1.54	4"x4	1239.5	3.25	4"x4
PFI-1224N-4D3DS-P2	Propylene Glycol	1055.0	2.16	4"x4	844.0	1.43	4"x4	1265.9	3.03	4"x4
PFI-1224N-5D2ES-K2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-1224N-5D2ES-L2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-1224N-5D2DS-N2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-1224N-5D1DS-O2	Propylene Glycol	1011.0	2.98	4"x4	808.8	1.98	4"x4	1213.1	4.18	4"x4
PFI-1224N-5D4DS-O2	Propylene Glycol	1081.4	2.33	4"x4	865.1	1.55	4"x4	1297.6	3.27	4"x4
PFI-1224N-5D2ES-P2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-1224N-6D1ES-L2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1ES-M2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1ES-N2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1ES-O2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1ES-P2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-3D3BS-L2	Propylene Glycol	1055.0	1.81	4"x4	844.0	1.2	4"x4	1265.9	2.53	4"x4
PFI-1224N-3D4BS-N2	Propylene Glycol	1081.4	1.71	4"x4	865.1	1.14	4"x4	1297.6	2.4	4"x4
PFI-1224N-3D4BS-O2	Propylene Glycol	1081.4	1.71	4"x4	865.1	1.14	4"x4	1297.6	2.4	4"x4
PFI-1224N-4D4BS-K2	Propylene Glycol	1081.4	2.02	4"x4	865.1	1.34	4"x4	1297.6	2.83	4"x4
PFI-1224N-4D3BS-L2	Propylene Glycol	1055.0	2.16	4"x4	844.0	1.43	4"x4	1265.9	3.03	4"x4
PFI-1224N-4D4BS-M2	Propylene Glycol	1081.4	2.02	4"x4	865.1	1.34	4"x4	1297.6	2.83	4"x4
PFI-1224N-4D3BS-N2	Propylene Glycol	1055.0	2.16	4"x4	844.0	1.43	4"x4	1265.9	3.03	4"x4
PFI-1224N-4D4BS-O2	Propylene Glycol	1081.4	2.02	4"x4	865.1	1.34	4"x4	1297.6	2.83	4"x4
PFI-1224N-4D4BS-P2	Propylene Glycol	1081.4	2.02	4"x4	865.1	1.34	4"x4	1297.6	2.83	4"x4
PFI-1224N-5D2BS-K2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-1224N-5D3BS-L2	Propylene Glycol	1055.0	2.51	4"x4	844.0	1.67	4"x4	1265.9	3.52	4"x4
PFI-1224N-5D2BS-M2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-1224N-5D2BS-N2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-1224N-5D3BS-O2	Propylene Glycol	1055.0	2.51	4"x4	844.0	1.67	4"x4	1265.9	3.52	4"x4
PFI-1224N-5D2BS-P2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-1224N-6D1BS-K2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1BS-L2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1BS-M2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1BS-N2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1BS-O2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-6D1BS-P2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-1224N-2D4DZ-K2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.32	4"x4
PFI-1224N-2D3EZ-L2	Propylene Glycol	463.7	1.8	4"x4	370.9	1.19	4"x4	556.4	2.52	4"x4
PFI-1224N-2D4DZ-M2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.32	4"x4
PFI-1224N-2D4EZ-M2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.33	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-2D4EZ-N2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.33	4"x4
PFI-1224N-2D4EZ-O2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.33	4"x4
PFI-1224N-3D2DZ-L2	Propylene Glycol	458.2	2.58	4"x4	366.5	1.71	4"x4	549.8	3.62	4"x4
PFI-1224N-3D3DZ-M2	Propylene Glycol	463.7	2.35	4"x4	370.9	1.56	4"x4	556.4	3.29	4"x4
PFI-1224N-3D2EZ-M2	Propylene Glycol	458.2	2.59	4"x4	366.5	1.72	4"x4	549.8	3.63	4"x4
PFI-1224N-3D2DZ-N2	Propylene Glycol	458.2	2.58	4"x4	366.5	1.71	4"x4	549.8	3.62	4"x4
PFI-1224N-3D2EZ-N2	Propylene Glycol	458.2	2.59	4"x4	366.5	1.72	4"x4	549.8	3.63	4"x4
PFI-1224N-3D4EZ-O2	Propylene Glycol	470.3	2.15	4"x4	376.2	1.42	4"x4	564.3	3.01	4"x4
PFI-1224N-3D1DZ-P2	Propylene Glycol	452.7	2.89	4"x4	362.1	1.91	4"x4	543.2	4.05	4"x4
PFI-1224N-4D1EZ-K2	Propylene Glycol	452.7	3.65	4"x4	362.1	2.42	4"x4	543.2	5.11	4"x4
PFI-1224N-4D3EZ-M2	Propylene Glycol	463.7	2.92	4"x4	370.9	1.93	4"x4	556.4	4.09	4"x4
PFI-1224N-4D2DZ-N2	Propylene Glycol	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.52	4"x4
PFI-1224N-4D3DZ-P2	Propylene Glycol	463.7	2.91	4"x4	370.9	1.93	4"x4	556.4	4.08	4"x4
PFI-1224N-5D2EZ-K2	Propylene Glycol	458.2	3.88	4"x4	366.5	2.57	4"x4	549.8	5.43	4"x4
PFI-1224N-5D2EZ-L2	Propylene Glycol	458.2	3.88	4"x4	366.5	2.57	4"x4	549.8	5.43	4"x4
PFI-1224N-5D2DZ-N2	Propylene Glycol	458.2	3.87	4"x4	366.5	2.56	4"x4	549.8	5.42	4"x4
PFI-1224N-5D1DZ-O2	Propylene Glycol	452.7	4.39	4"x4	362.1	2.9	4"x4	543.2	6.15	4"x4
PFI-1224N-5D4DZ-O2	Propylene Glycol	470.3	3.1	4"x4	376.2	2.05	4"x4	564.3	4.35	4"x4
PFI-1224N-5D2EZ-P2	Propylene Glycol	458.2	3.88	4"x4	366.5	2.57	4"x4	549.8	5.43	4"x4
PFI-1224N-6D1EZ-L2	Propylene Glycol	452.7	5.15	4"x4	362.1	3.41	4"x4	543.2	7.21	4"x4
PFI-1224N-6D1EZ-M2	Propylene Glycol	452.7	5.15	4"x4	362.1	3.41	4"x4	543.2	7.21	4"x4
PFI-1224N-6D1EZ-N2	Propylene Glycol	452.7	5.15	4"x4	362.1	3.41	4"x4	543.2	7.21	4"x4
PFI-1224N-6D1EZ-O2	Propylene Glycol	452.7	5.15	4"x4	362.1	3.41	4"x4	543.2	7.21	4"x4
PFI-1224N-6D1EZ-P2	Propylene Glycol	852.6	16.6	4"x4	682.0	11	4"x4	1023.1	23.3	4"x4
PFI-1224N-3D3BT-L2	Propylene Glycol	463.7	2.33	4"x4	370.9	1.55	4"x4	556.4	3.27	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1224N-3D4BT-N2	Propylene Glycol	470.3	2.12	4"x4	376.2	1.4	4"x4	564.3	2.97	4"x4
PFI-1224N-3D4BT-O2	Propylene Glycol	470.3	2.12	4"x4	376.2	1.4	4"x4	564.3	2.97	4"x4
PFI-1224N-4D4BT-K2	Propylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1224N-4D3BT-L2	Propylene Glycol	463.7	2.89	4"x4	370.9	1.91	4"x4	556.4	4.05	4"x4
PFI-1224N-4D4BT-M2	Propylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1224N-4D3BT-N2	Propylene Glycol	463.7	2.89	4"x4	370.9	1.91	4"x4	556.4	4.05	4"x4
PFI-1224N-4D4BT-O2	Propylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1224N-4D4BT-P2	Propylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-1224N-5D2BT-K2	Propylene Glycol	458.2	3.84	4"x4	366.5	2.54	4"x4	549.8	5.38	4"x4
PFI-1224N-5D3BT-L2	Propylene Glycol	463.7	3.44	4"x4	370.9	2.28	4"x4	556.4	4.82	4"x4
PFI-1224N-5D2BT-M2	Propylene Glycol	458.2	3.84	4"x4	366.5	2.54	4"x4	549.8	5.38	4"x4
PFI-1224N-5D2BT-N2	Propylene Glycol	458.2	3.84	4"x4	366.5	2.54	4"x4	549.8	5.38	4"x4
PFI-1224N-5D3BT-O2	Propylene Glycol	463.7	3.44	4"x4	370.9	2.28	4"x4	556.4	4.82	4"x4
PFI-1224N-5D2BT-P2	Propylene Glycol	458.2	3.84	4"x4	366.5	2.54	4"x4	549.8	5.38	4"x4
PFI-1224N-6D1BT-K2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-1224N-6D1BT-L2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-1224N-6D1BT-M2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-1224N-6D1BT-N2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-1224N-6D1BT-O2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-1224N-6D1BT-P2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-2412N-2D4DS-K2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4
PFI-2412N-2D3ES-L2	Propylene Glycol	1055.0	1.46	4"x4	844.0	0.97	4"x4	1265.9	2.04	4"x4
PFI-2412N-2D4DS-M2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4
PFI-2412N-2D4ES-M2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4
PFI-2412N-2D4ES-N2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-2D4ES-O2	Propylene Glycol	1081.4	1.41	4"x4	865.1	0.93	4"x4	1297.6	1.97	4"x4
PFI-2412N-3D2DS-L2	Propylene Glycol	1033.0	1.92	4"x4	826.4	1.27	4"x4	1239.5	2.69	4"x4
PFI-2412N-3D3DS-M2	Propylene Glycol	1055.0	1.81	4"x4	844.0	1.2	4"x4	1265.9	2.53	4"x4
PFI-2412N-3D2ES-M2	Propylene Glycol	1033.0	1.92	4"x4	826.4	1.27	4"x4	1239.5	2.69	4"x4
PFI-2412N-3D2DS-N2	Propylene Glycol	1033.0	1.92	4"x4	826.4	1.27	4"x4	1239.5	2.69	4"x4
PFI-2412N-3D2ES-N2	Propylene Glycol	1033.0	1.92	4"x4	826.4	1.27	4"x4	1239.5	2.69	4"x4
PFI-2412N-3D4ES-O2	Propylene Glycol	1081.4	1.71	4"x4	865.1	1.14	4"x4	1297.6	2.4	4"x4
PFI-2412N-3D1DS-P2	Propylene Glycol	1011.0	2.07	4"x4	808.8	1.37	4"x4	1213.1	2.9	4"x4
PFI-2412N-4D1ES-K2	Propylene Glycol	1011.0	2.53	4"x4	808.8	1.67	4"x4	1213.1	3.54	4"x4
PFI-2412N-4D3ES-M2	Propylene Glycol	1055.0	2.16	4"x4	844.0	1.43	4"x4	1265.9	3.03	4"x4
PFI-2412N-4D2DS-N2	Propylene Glycol	1033.0	2.32	4"x4	826.4	1.54	4"x4	1239.5	3.25	4"x4
PFI-2412N-4D3DS-P2	Propylene Glycol	1055.0	2.16	4"x4	844.0	1.43	4"x4	1265.9	3.03	4"x4
PFI-2412N-5D2ES-K2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-2412N-5D2ES-L2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-2412N-5D2DS-N2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-2412N-5D1DS-O2	Propylene Glycol	1011.0	2.98	4"x4	808.8	1.98	4"x4	1213.1	4.18	4"x4
PFI-2412N-5D4DS-O2	Propylene Glycol	1081.4	2.33	4"x4	865.1	1.55	4"x4	1297.6	3.27	4"x4
PFI-2412N-5D2ES-P2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-2412N-6D1ES-L2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1ES-M2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1ES-N2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1ES-O2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1ES-P2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-3D3BS-L2	Propylene Glycol	1055.0	1.81	4"x4	844.0	1.2	4"x4	1265.9	2.53	4"x4
PFI-2412N-3D4BS-N2	Propylene Glycol	1081.4	1.71	4"x4	865.1	1.14	4"x4	1297.6	2.4	4"x4





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-3D4BS-O2	Propylene Glycol	1081.4	1.71	4"x4	865.1	1.14	4"x4	1297.6	2.4	4"x4
PFI-2412N-4D4BS-K2	Propylene Glycol	1081.4	2.02	4"x4	865.1	1.34	4"x4	1297.6	2.83	4"x4
PFI-2412N-4D3BS-L2	Propylene Glycol	1055.0	2.16	4"x4	844.0	1.43	4"x4	1265.9	3.03	4"x4
PFI-2412N-4D4BS-M2	Propylene Glycol	1081.4	2.02	4"x4	865.1	1.34	4"x4	1297.6	2.83	4"x4
PFI-2412N-4D3BS-N2	Propylene Glycol	1055.0	2.16	4"x4	844.0	1.43	4"x4	1265.9	3.03	4"x4
PFI-2412N-4D4BS-O2	Propylene Glycol	1081.4	2.02	4"x4	865.1	1.34	4"x4	1297.6	2.83	4"x4
PFI-2412N-4D4BS-P2	Propylene Glycol	1081.4	2.02	4"x4	865.1	1.34	4"x4	1297.6	2.83	4"x4
PFI-2412N-5D2BS-K2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-2412N-5D3BS-L2	Propylene Glycol	1055.0	2.51	4"x4	844.0	1.67	4"x4	1265.9	3.52	4"x4
PFI-2412N-5D2BS-M2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-2412N-5D2BS-N2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-2412N-5D3BS-O2	Propylene Glycol	1055.0	2.51	4"x4	844.0	1.67	4"x4	1265.9	3.52	4"x4
PFI-2412N-5D2BS-P2	Propylene Glycol	1033.0	2.72	4"x4	826.4	1.8	4"x4	1239.5	3.8	4"x4
PFI-2412N-6D1BS-K2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1BS-L2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1BS-M2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1BS-N2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1BS-O2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-6D1BS-P2	Propylene Glycol	1011.0	3.44	4"x4	808.8	2.28	4"x4	1213.1	4.82	4"x4
PFI-2412N-2D4DZ-K2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.32	4"x4
PFI-2412N-2D3EZ-L2	Propylene Glycol	463.7	1.8	4"x4	370.9	1.19	4"x4	556.4	2.52	4"x4
PFI-2412N-2D4DZ-M2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.32	4"x4
PFI-2412N-2D4EZ-M2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.33	4"x4
PFI-2412N-2D4EZ-N2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.33	4"x4
PFI-2412N-2D4EZ-O2	Propylene Glycol	470.3	1.66	4"x4	376.2	1.1	4"x4	564.3	2.33	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-3D2DZ-L2	Propylene Glycol	458.2	2.58	4"x4	366.5	1.71	4"x4	549.8	3.62	4"x4
PFI-2412N-3D3DZ-M2	Propylene Glycol	463.7	2.35	4"x4	370.9	1.56	4"x4	556.4	3.29	4"x4
PFI-2412N-3D2EZ-M2	Propylene Glycol	458.2	2.59	4"x4	366.5	1.72	4"x4	549.8	3.63	4"x4
PFI-2412N-3D2DZ-N2	Propylene Glycol	458.2	2.58	4"x4	366.5	1.71	4"x4	549.8	3.62	4"x4
PFI-2412N-3D2EZ-N2	Propylene Glycol	458.2	2.59	4"x4	366.5	1.72	4"x4	549.8	3.63	4"x4
PFI-2412N-3D4EZ-O2	Propylene Glycol	470.3	2.15	4"x4	376.2	1.42	4"x4	564.3	3.01	4"x4
PFI-2412N-3D1DZ-P2	Propylene Glycol	452.7	2.89	4"x4	362.1	1.91	4"x4	543.2	4.05	4"x4
PFI-2412N-4D1EZ-K2	Propylene Glycol	452.7	3.65	4"x4	362.1	2.42	4"x4	543.2	5.11	4"x4
PFI-2412N-4D3EZ-M2	Propylene Glycol	463.7	2.92	4"x4	370.9	1.93	4"x4	556.4	4.09	4"x4
PFI-2412N-4D2DZ-N2	Propylene Glycol	458.2	3.23	4"x4	366.5	2.14	4"x4	549.8	4.52	4"x4
PFI-2412N-4D3DZ-P2	Propylene Glycol	463.7	2.91	4"x4	370.9	1.93	4"x4	556.4	4.08	4"x4
PFI-2412N-5D2EZ-K2	Propylene Glycol	458.2	3.88	4"x4	366.5	2.57	4"x4	549.8	5.43	4"x4
PFI-2412N-5D2EZ-L2	Propylene Glycol	458.2	3.88	4"x4	366.5	2.57	4"x4	549.8	5.43	4"x4
PFI-2412N-5D2DZ-N2	Propylene Glycol	458.2	3.87	4"x4	366.5	2.56	4"x4	549.8	5.42	4"x4
PFI-2412N-5D1DZ-O2	Propylene Glycol	452.7	4.39	4"x4	362.1	2.9	4"x4	543.2	6.15	4"x4
PFI-2412N-5D4DZ-O2	Propylene Glycol	470.3	3.1	4"x4	376.2	2.05	4"x4	564.3	4.35	4"x4
PFI-2412N-5D2EZ-P2	Propylene Glycol	458.2	3.88	4"x4	366.5	2.57	4"x4	549.8	5.43	4"x4
PFI-2412N-6D1EZ-L2	Propylene Glycol	452.7	5.15	4"x4	362.1	3.41	4"x4	543.2	7.21	4"x4
PFI-2412N-6D1EZ-M2	Propylene Glycol	452.7	5.15	4"x4	362.1	3.41	4"x4	543.2	7.21	4"x4
PFI-2412N-6D1EZ-N2	Propylene Glycol	452.7	5.15	4"x4	362.1	3.41	4"x4	543.2	7.21	4"x4
PFI-2412N-6D1EZ-O2	Propylene Glycol	452.7	5.15	4"x4	362.1	3.41	4"x4	543.2	7.21	4"x4
PFI-2412N-6D1EZ-P2	Propylene Glycol	852.6	16.6	4"x4	682.0	11	4"x4	1023.1	23.3	4"x4
PFI-2412N-3D3BT-L2	Propylene Glycol	463.7	2.33	4"x4	370.9	1.55	4"x4	556.4	3.27	4"x4
PFI-2412N-3D4BT-N2	Propylene Glycol	470.3	2.12	4"x4	376.2	1.4	4"x4	564.3	2.97	4"x4
PFI-2412N-3D4BT-O2	Propylene Glycol	470.3	2.12	4"x4	376.2	1.4	4"x4	564.3	2.97	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2412N-4D4BT-K2	Propylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2412N-4D3BT-L2	Propylene Glycol	463.7	2.89	4"x4	370.9	1.91	4"x4	556.4	4.05	4"x4
PFI-2412N-4D4BT-M2	Propylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2412N-4D3BT-N2	Propylene Glycol	463.7	2.89	4"x4	370.9	1.91	4"x4	556.4	4.05	4"x4
PFI-2412N-4D4BT-O2	Propylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2412N-4D4BT-P2	Propylene Glycol	470.3	2.6	4"x4	376.2	1.72	4"x4	564.3	3.64	4"x4
PFI-2412N-5D2BT-K2	Propylene Glycol	458.2	3.84	4"x4	366.5	2.54	4"x4	549.8	5.38	4"x4
PFI-2412N-5D3BT-L2	Propylene Glycol	463.7	3.44	4"x4	370.9	2.28	4"x4	556.4	4.82	4"x4
PFI-2412N-5D2BT-M2	Propylene Glycol	458.2	3.84	4"x4	366.5	2.54	4"x4	549.8	5.38	4"x4
PFI-2412N-5D2BT-N2	Propylene Glycol	458.2	3.84	4"x4	366.5	2.54	4"x4	549.8	5.38	4"x4
PFI-2412N-5D3BT-O2	Propylene Glycol	463.7	3.44	4"x4	370.9	2.28	4"x4	556.4	4.82	4"x4
PFI-2412N-5D2BT-P2	Propylene Glycol	458.2	3.84	4"x4	366.5	2.54	4"x4	549.8	5.38	4"x4
PFI-2412N-6D1BT-K2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-2412N-6D1BT-L2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-2412N-6D1BT-M2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-2412N-6D1BT-N2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-2412N-6D1BT-O2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-2412N-6D1BT-P2	Propylene Glycol	452.7	5.11	4"x4	362.1	3.38	4"x4	543.2	7.16	4"x4
PFI-2424N-2D4DS-K4	Propylene Glycol	2162.7	1.41	4"x8	1730.2	0.93	4"x8	2595.2	1.97	4"x8
PFI-2424N-2D3ES-L4	Propylene Glycol	2109.9	1.46	4"x8	1687.9	0.97	4"x8	2531.9	2.04	4"x8
PFI-2424N-2D4DS-M4	Propylene Glycol	2162.7	1.41	4"x8	1730.2	0.93	4"x8	2595.2	1.97	4"x8
PFI-2424N-2D4ES-M4	Propylene Glycol	2162.7	1.41	4"x8	1730.2	0.93	4"x8	2595.2	1.97	4"x8
PFI-2424N-2D4ES-N4	Propylene Glycol	2162.7	1.41	4"x8	1730.2	0.93	4"x8	2595.2	1.97	4"x8
PFI-2424N-2D4ES-O4	Propylene Glycol	2162.7	1.41	4"x8	1730.2	0.93	4"x8	2595.2	1.97	4"x8
PFI-2424N-3D2DS-L4	Propylene Glycol	2065.9	1.92	4"x8	1652.7	1.27	4"x8	2479.1	2.69	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-3D3DS-M4	Propylene Glycol	2109.9	1.81	4"x8	1687.9	1.2	4"x8	2531.9	2.53	4"x8
PFI-2424N-3D2ES-M4	Propylene Glycol	2065.9	1.92	4"x8	1652.7	1.27	4"x8	2479.1	2.69	4"x8
PFI-2424N-3D2DS-N4	Propylene Glycol	2065.9	1.92	4"x8	1652.7	1.27	4"x8	2479.1	2.69	4"x8
PFI-2424N-3D2ES-N4	Propylene Glycol	2065.9	1.92	4"x8	1652.7	1.27	4"x8	2479.1	2.69	4"x8
PFI-2424N-3D4ES-O4	Propylene Glycol	2162.7	1.71	4"x8	1730.2	1.14	4"x8	2595.2	2.4	4"x8
PFI-2424N-3D1DS-P4	Propylene Glycol	2021.9	2.07	4"x8	1617.5	1.37	4"x8	2426.3	2.9	4"x8
PFI-2424N-4D1ES-K4	Propylene Glycol	2021.9	2.53	4"x8	1617.5	1.67	4"x8	2426.3	3.54	4"x8
PFI-2424N-4D3ES-M4	Propylene Glycol	2109.9	2.16	4"x8	1687.9	1.43	4"x8	2531.9	3.03	4"x8
PFI-2424N-4D2DS-N4	Propylene Glycol	2065.9	2.32	4"x8	1652.7	1.54	4"x8	2479.1	3.25	4"x8
PFI-2424N-4D3DS-P4	Propylene Glycol	2109.9	2.16	4"x8	1687.9	1.43	4"x8	2531.9	3.03	4"x8
PFI-2424N-5D2ES-K4	Propylene Glycol	2065.9	2.72	4"x8	1652.7	1.8	4"x8	2479.1	3.8	4"x8
PFI-2424N-5D2ES-L4	Propylene Glycol	2065.9	2.72	4"x8	1652.7	1.8	4"x8	2479.1	3.8	4"x8
PFI-2424N-5D2DS-N4	Propylene Glycol	2065.9	2.72	4"x8	1652.7	1.8	4"x8	2479.1	3.8	4"x8
PFI-2424N-5D1DS-O4	Propylene Glycol	2021.9	2.98	4"x8	1617.5	1.98	4"x8	2426.3	4.18	4"x8
PFI-2424N-5D4DS-O4	Propylene Glycol	2162.7	2.33	4"x8	1730.2	1.55	4"x8	2595.2	3.27	4"x8
PFI-2424N-5D2ES-P4	Propylene Glycol	2065.9	2.72	4"x8	1652.7	1.8	4"x8	2479.1	3.8	4"x8
PFI-2424N-6D1ES-L4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1ES-M4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1ES-N4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1ES-O4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1ES-P4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-3D3BS-L4	Propylene Glycol	2109.9	1.81	4"x8	1687.9	1.2	4"x8	2531.9	2.53	4"x8
PFI-2424N-3D4BS-N4	Propylene Glycol	2162.7	1.71	4"x8	1730.2	1.14	4"x8	2595.2	2.4	4"x8
PFI-2424N-3D4BS-O4	Propylene Glycol	2162.7	1.71	4"x8	1730.2	1.14	4"x8	2595.2	2.4	4"x8
PFI-2424N-4D4BS-K4	Propylene Glycol	2162.7	2.02	4"x8	1730.2	1.34	4"x8	2595.2	2.83	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-4D3BS-L4	Propylene Glycol	2109.9	2.16	4"x8	1687.9	1.43	4"x8	2531.9	3.03	4"x8
PFI-2424N-4D4BS-M4	Propylene Glycol	2162.7	2.02	4"x8	1730.2	1.34	4"x8	2595.2	2.83	4"x8
PFI-2424N-4D3BS-N4	Propylene Glycol	2109.9	2.16	4"x8	1687.9	1.43	4"x8	2531.9	3.03	4"x8
PFI-2424N-4D4BS-O4	Propylene Glycol	2162.7	2.02	4"x8	1730.2	1.34	4"x8	2595.2	2.83	4"x8
PFI-2424N-4D4BS-P4	Propylene Glycol	2162.7	2.02	4"x8	1730.2	1.34	4"x8	2595.2	2.83	4"x8
PFI-2424N-5D2BS-K4	Propylene Glycol	2065.9	2.72	4"x8	1652.7	1.8	4"x8	2479.1	3.8	4"x8
PFI-2424N-5D3BS-L4	Propylene Glycol	2109.9	2.51	4"x8	1687.9	1.67	4"x8	2531.9	3.52	4"x8
PFI-2424N-5D2BS-M4	Propylene Glycol	2065.9	2.72	4"x8	1652.7	1.8	4"x8	2479.1	3.8	4"x8
PFI-2424N-5D2BS-N4	Propylene Glycol	2065.9	2.72	4"x8	1652.7	1.8	4"x8	2479.1	3.8	4"x8
PFI-2424N-5D3BS-O4	Propylene Glycol	2109.9	2.51	4"x8	1687.9	1.67	4"x8	2531.9	3.52	4"x8
PFI-2424N-5D2BS-P4	Propylene Glycol	2065.9	2.72	4"x8	1652.7	1.8	4"x8	2479.1	3.8	4"x8
PFI-2424N-6D1BS-K4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1BS-L4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1BS-M4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1BS-N4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1BS-O4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-6D1BS-P4	Propylene Glycol	2021.9	3.44	4"x8	1617.5	2.28	4"x8	2426.3	4.82	4"x8
PFI-2424N-2D4DZ-K4	Propylene Glycol	940.6	1.66	4"x8	752.4	1.1	4"x8	1128.7	2.32	4"x8
PFI-2424N-2D3EZ-L4	Propylene Glycol	927.4	1.8	4"x8	741.9	1.19	4"x8	1112.8	2.52	4"x8
PFI-2424N-2D4DZ-M4	Propylene Glycol	940.6	1.66	4"x8	752.4	1.1	4"x8	1128.7	2.32	4"x8
PFI-2424N-2D4EZ-M4	Propylene Glycol	940.6	1.66	4"x8	752.4	1.1	4"x8	1128.7	2.33	4"x8
PFI-2424N-2D4EZ-N4	Propylene Glycol	940.6	1.66	4"x8	752.4	1.1	4"x8	1128.7	2.33	4"x8
PFI-2424N-2D4EZ-O4	Propylene Glycol	940.6	1.66	4"x8	752.4	1.1	4"x8	1128.7	2.33	4"x8
PFI-2424N-3D2DZ-L4	Propylene Glycol	916.4	2.58	4"x8	733.1	1.71	4"x8	1099.6	3.62	4"x8
PFI-2424N-3D3DZ-M4	Propylene Glycol	927.4	2.35	4"x8	741.9	1.56	4"x8	1112.8	3.29	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-3D2EZ-M4	Propylene Glycol	916.4	2.59	4"x8	733.1	1.72	4"x8	1099.6	3.63	4"x8
PFI-2424N-3D2DZ-N4	Propylene Glycol	916.4	2.58	4"x8	733.1	1.71	4"x8	1099.6	3.62	4"x8
PFI-2424N-3D2EZ-N4	Propylene Glycol	916.4	2.59	4"x8	733.1	1.72	4"x8	1099.6	3.63	4"x8
PFI-2424N-3D4EZ-O4	Propylene Glycol	940.6	2.15	4"x8	752.4	1.42	4"x8	1128.7	3.01	4"x8
PFI-2424N-3D1DZ-P4	Propylene Glycol	905.4	2.89	4"x8	724.3	1.91	4"x8	1086.4	4.05	4"x8
PFI-2424N-4D1EZ-K4	Propylene Glycol	905.4	3.65	4"x8	724.3	2.42	4"x8	1086.4	5.11	4"x8
PFI-2424N-4D3EZ-M4	Propylene Glycol	927.4	2.92	4"x8	741.9	1.93	4"x8	1112.8	4.09	4"x8
PFI-2424N-4D2DZ-N4	Propylene Glycol	916.4	3.23	4"x8	733.1	2.14	4"x8	1099.6	4.52	4"x8
PFI-2424N-4D3DZ-P4	Propylene Glycol	927.4	2.91	4"x8	741.9	1.93	4"x8	1112.8	4.08	4"x8
PFI-2424N-5D2EZ-K4	Propylene Glycol	916.4	3.88	4"x8	733.1	2.57	4"x8	1099.6	5.43	4"x8
PFI-2424N-5D2EZ-L4	Propylene Glycol	916.4	3.88	4"x8	733.1	2.57	4"x8	1099.6	5.43	4"x8
PFI-2424N-5D2DZ-N4	Propylene Glycol	916.4	3.87	4"x8	733.1	2.56	4"x8	1099.6	5.42	4"x8
PFI-2424N-5D1DZ-O4	Propylene Glycol	905.4	4.39	4"x8	724.3	2.9	4"x8	1086.4	6.15	4"x8
PFI-2424N-5D4DZ-O4	Propylene Glycol	940.6	3.1	4"x8	752.4	2.05	4"x8	1128.7	4.35	4"x8
PFI-2424N-5D2EZ-P4	Propylene Glycol	916.4	3.88	4"x8	733.1	2.57	4"x8	1099.6	5.43	4"x8
PFI-2424N-6D1EZ-L4	Propylene Glycol	905.4	5.15	4"x8	724.3	3.41	4"x8	1086.4	7.21	4"x8
PFI-2424N-6D1EZ-M4	Propylene Glycol	905.4	5.15	4"x8	724.3	3.41	4"x8	1086.4	7.21	4"x8
PFI-2424N-6D1EZ-N4	Propylene Glycol	905.4	5.15	4"x8	724.3	3.41	4"x8	1086.4	7.21	4"x8
PFI-2424N-6D1EZ-O4	Propylene Glycol	905.4	5.15	4"x8	724.3	3.41	4"x8	1086.4	7.21	4"x8
PFI-2424N-6D1EZ-P4	Propylene Glycol	1705.1	16.6	4"x8	1364.1	11	4"x8	2046.1	23.3	4"x8
PFI-2424N-3D3BT-L4	Propylene Glycol	927.4	2.33	4"x8	741.9	1.55	4"x8	1112.8	3.27	4"x8
PFI-2424N-3D4BT-N4	Propylene Glycol	940.6	2.12	4"x8	752.4	1.4	4"x8	1128.7	2.97	4"x8
PFI-2424N-3D4BT-O4	Propylene Glycol	940.6	2.12	4"x8	752.4	1.4	4"x8	1128.7	2.97	4"x8
PFI-2424N-4D4BT-K4	Propylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8
PFI-2424N-4D3BT-L4	Propylene Glycol	927.4	2.89	4"x8	741.9	1.91	4"x8	1112.8	4.05	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2424N-4D4BT-M4	Propylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8
PFI-2424N-4D3BT-N4	Propylene Glycol	927.4	2.89	4"x8	741.9	1.91	4"x8	1112.8	4.05	4"x8
PFI-2424N-4D4BT-O4	Propylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8
PFI-2424N-4D4BT-P4	Propylene Glycol	940.6	2.6	4"x8	752.4	1.72	4"x8	1128.7	3.64	4"x8
PFI-2424N-5D2BT-K4	Propylene Glycol	916.4	3.84	4"x8	733.1	2.54	4"x8	1099.6	5.38	4"x8
PFI-2424N-5D3BT-L4	Propylene Glycol	927.4	3.44	4"x8	741.9	2.28	4"x8	1112.8	4.82	4"x8
PFI-2424N-5D2BT-M4	Propylene Glycol	916.4	3.84	4"x8	733.1	2.54	4"x8	1099.6	5.38	4"x8
PFI-2424N-5D2BT-N4	Propylene Glycol	916.4	3.84	4"x8	733.1	2.54	4"x8	1099.6	5.38	4"x8
PFI-2424N-5D3BT-O4	Propylene Glycol	927.4	3.44	4"x8	741.9	2.28	4"x8	1112.8	4.82	4"x8
PFI-2424N-5D2BT-P4	Propylene Glycol	916.4	3.84	4"x8	733.1	2.54	4"x8	1099.6	5.38	4"x8
PFI-2424N-6D1BT-K4	Propylene Glycol	905.4	5.11	4"x8	724.3	3.38	4"x8	1086.4	7.16	4"x8
PFI-2424N-6D1BT-L4	Propylene Glycol	905.4	5.11	4"x8	724.3	3.38	4"x8	1086.4	7.16	4"x8
PFI-2424N-6D1BT-M4	Propylene Glycol	905.4	5.11	4"x8	724.3	3.38	4"x8	1086.4	7.16	4"x8
PFI-2424N-6D1BT-N4	Propylene Glycol	905.4	5.11	4"x8	724.3	3.38	4"x8	1086.4	7.16	4"x8
PFI-2424N-6D1BT-O4	Propylene Glycol	905.4	5.11	4"x8	724.3	3.38	4"x8	1086.4	7.16	4"x8
PFI-2424N-6D1BT-P4	Propylene Glycol	905.4	5.11	4"x8	724.3	3.38	4"x8	1086.4	7.16	4"x8
PFI-1218N-2D1DS-M1	Propylene Glycol	505.5	2	4"x2	404.4	1.33	4"x2	606.6	2.8	4"x2
PFI-1218N-2D4ES-M1	Propylene Glycol	540.7	1.67	4"x2	432.5	1.1	4"x2	648.8	2.33	4"x2
PFI-1218N-2D1DS-N1	Propylene Glycol	505.5	2	4"x2	404.4	1.33	4"x2	606.6	2.8	4"x2
PFI-1218N-2D2DS-N1	Propylene Glycol	516.5	1.86	4"x2	413.2	1.23	4"x2	619.8	2.6	4"x2
PFI-1218N-2D3ES-N1	Propylene Glycol	527.5	1.76	4"x2	422.0	1.16	4"x2	633.0	2.46	4"x2
PFI-1218N-2D2DS-O1	Propylene Glycol	516.5	1.86	4"x2	413.2	1.23	4"x2	619.8	2.6	4"x2
PFI-1218N-2D3ES-O1	Propylene Glycol	527.5	1.76	4"x2	422.0	1.16	4"x2	633.0	2.46	4"x2
PFI-1218N-2D4DS-P1	Propylene Glycol	540.7	1.67	4"x2	432.5	1.1	4"x2	648.8	2.33	4"x2
PFI-1218N-3D1ES-K1	Propylene Glycol	505.5	2.65	4"x2	404.4	1.76	4"x2	606.6	3.71	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-3D1ES-L1	Propylene Glycol	505.5	2.65	4"x2	404.4	1.76	4"x2	606.6	3.71	4"x2
PFI-1218N-3D4ES-M1	Propylene Glycol	940.6	4.37	4"x4	752.4	3.88	4"x2	1128.7	6.12	4"x4
PFI-1218N-3D1DS-N1	Propylene Glycol	505.5	2.65	4"x2	404.4	1.76	4"x2	606.6	3.71	4"x2
PFI-1218N-3D1ES-N1	Propylene Glycol	505.5	2.65	4"x2	404.4	1.76	4"x2	606.6	3.71	4"x2
PFI-1218N-3D1DS-O1	Propylene Glycol	505.5	2.65	4"x2	404.4	1.76	4"x2	606.6	3.71	4"x2
PFI-1218N-3D2DS-O1	Propylene Glycol	516.5	2.43	4"x2	413.2	1.61	4"x2	619.8	3.4	4"x2
PFI-1218N-3D1ES-O1	Propylene Glycol	905.4	7.78	4"x2	724.3	5.15	4"x2	1086.4	8.61	4"x4
PFI-1218N-3D2DS-P1	Propylene Glycol	916.4	7	4"x2	733.1	4.63	4"x2	1099.6	7.47	4"x4
PFI-1218N-3D2ES-P1	Propylene Glycol	916.4	7	4"x2	733.1	4.63	4"x2	1099.6	7.47	4"x4
PFI-1218N-3D2DS-Q1	Propylene Glycol	916.4	7	4"x2	733.1	4.63	4"x2	1099.6	7.47	4"x4
PFI-1218N-3D4DS-Q1	Propylene Glycol	940.6	4.37	4"x4	752.4	3.88	4"x2	1128.7	6.12	4"x4
PFI-1218N-3D4ES-Q1	Propylene Glycol	940.6	4.37	4"x4	752.4	3.88	4"x2	1128.7	6.12	4"x4
PFI-1218N-3D1ES-R1	Propylene Glycol	905.4	7.78	4"x2	724.3	5.15	4"x2	1086.4	8.61	4"x4
PFI-1218N-3D4ES-R1	Propylene Glycol	940.6	4.37	4"x4	752.4	3.88	4"x2	1128.7	6.12	4"x4
PFI-1218N-4D1DS-K1	Propylene Glycol	505.5	3.3	4"x2	404.4	2.18	4"x2	606.6	4.62	4"x2
PFI-1218N-4D1ES-L1	Propylene Glycol	905.4	9.69	4"x2	724.3	6.41	4"x2	1086.4	11.2	4"x4
PFI-1218N-4D2ES-M1	Propylene Glycol	916.4	8.63	4"x2	733.1	5.71	4"x2	1099.6	9.66	4"x4
PFI-1218N-4D2DS-N1	Propylene Glycol	916.4	8.63	4"x2	733.1	5.71	4"x2	1099.6	9.66	4"x4
PFI-1218N-4D1ES-N1	Propylene Glycol	905.4	9.69	4"x2	724.3	6.41	4"x2	1086.4	11.2	4"x4
PFI-1218N-4D3DS-O1	Propylene Glycol	927.4	7.82	4"x2	741.9	5.18	4"x2	1112.8	8.51	4"x4
PFI-1218N-4D1ES-O1	Propylene Glycol	905.4	9.69	4"x2	724.3	6.41	4"x2	1086.4	11.2	4"x4
PFI-1218N-4D1ES-P1	Propylene Glycol	905.4	9.69	4"x2	724.3	6.41	4"x2	1086.4	11.2	4"x4
PFI-1218N-4D1DS-Q1	Propylene Glycol	905.4	9.69	4"x2	724.3	6.41	4"x2	1086.4	11.2	4"x4
PFI-1218N-4D2ES-Q1	Propylene Glycol	916.4	8.63	4"x2	733.1	5.71	4"x2	1099.6	9.66	4"x4
PFI-1218N-4D4ES-Q1	Propylene Glycol	940.6	5.31	4"x4	752.4	4.69	4"x2	1128.7	7.44	4"x4





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-4D2ES-R1	Propylene Glycol	916.4	8.63	4"x2	733.1	5.71	4"x2	1099.6	9.66	4"x4
PFI-1218N-4D4ES-R1	Propylene Glycol	940.6	5.31	4"x4	752.4	4.69	4"x2	1128.7	7.44	4"x4
PFI-1218N-5D1DS-K1	Propylene Glycol	505.5	3.95	4"x2	404.4	2.61	4"x2	606.6	5.53	4"x2
PFI-1218N-5D1ES-O1	Propylene Glycol	905.4	11.6	4"x2	724.3	7.67	4"x2	1086.4	13.8	4"x4
PFI-1218N-5D2ES-P1	Propylene Glycol	916.4	10.3	4"x2	733.1	6.79	4"x2	1099.6	11.9	4"x4
PFI-1218N-6D2DS-M1	Propylene Glycol	916.4	11.9	4"x2	733.1	7.88	4"x2	1099.6	14.1	4"x4
PFI-1218N-6D1DS-N1	Propylene Glycol	905.4	13.5	4"x2	724.3	8.94	4"x2	1086.4	16.3	4"x4
PFI-1218N-6D1DS-R1	Propylene Glycol	905.4	13.5	4"x2	724.3	8.94	4"x2	1086.4	16.3	4"x4
PFI-1218N-6D1ES-R1	Propylene Glycol	905.4	13.5	4"x2	724.3	8.94	4"x2	1086.4	16.3	4"x4
PFI-1218N-6D3ES-R1	Propylene Glycol	927.4	10.7	4"x2	741.9	7.06	4"x2	1112.8	12.3	4"x4
PFI-1218N-3D4BS-K1	Propylene Glycol	540.7	2.11	4"x2	432.5	1.4	4"x2	648.8	2.95	4"x2
PFI-1218N-3D4BS-L1	Propylene Glycol	540.7	2.11	4"x2	432.5	1.4	4"x2	648.8	2.95	4"x2
PFI-1218N-3D4BS-N1	Propylene Glycol	540.7	2.11	4"x2	432.5	1.4	4"x2	648.8	2.95	4"x2
PFI-1218N-3D4BS-O1	Propylene Glycol	540.7	2.11	4"x2	432.5	1.4	4"x2	648.8	2.95	4"x2
PFI-1218N-3D4BS-P1	Propylene Glycol	540.7	2.11	4"x2	432.5	1.4	4"x2	648.8	2.95	4"x2
PFI-1218N-4D4BS-K1	Propylene Glycol	540.7	2.55	4"x2	432.5	1.69	4"x2	648.8	3.57	4"x2
PFI-1218N-4D4BS-L1	Propylene Glycol	540.7	2.55	4"x2	432.5	1.69	4"x2	648.8	3.57	4"x2
PFI-1218N-4D3BS-M1	Propylene Glycol	527.5	2.76	4"x2	422.0	1.83	4"x2	633.0	3.86	4"x2
PFI-1218N-4D3BS-N1	Propylene Glycol	527.5	2.76	4"x2	422.0	1.83	4"x2	633.0	3.86	4"x2
PFI-1218N-4D3BS-O1	Propylene Glycol	527.5	2.76	4"x2	422.0	1.83	4"x2	633.0	3.86	4"x2
PFI-1218N-4D4BS-P1	Propylene Glycol	940.6	5.31	4"x4	752.4	4.69	4"x2	1128.7	7.44	4"x4
PFI-1218N-4D3BS-Q1	Propylene Glycol	927.4	7.82	4"x2	741.9	5.18	4"x2	1112.8	8.51	4"x4
PFI-1218N-5D2BS-K1	Propylene Glycol	516.5	3.56	4"x2	413.2	2.36	4"x2	619.8	4.98	4"x2
PFI-1218N-5D2BS-L1	Propylene Glycol	516.5	3.56	4"x2	413.2	2.36	4"x2	619.8	4.98	4"x2
PFI-1218N-5D2BS-M1	Propylene Glycol	516.5	3.56	4"x2	413.2	2.36	4"x2	619.8	4.98	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-5D2BS-N1	Propylene Glycol	516.5	3.56	4"x2	413.2	2.36	4"x2	619.8	4.98	4"x2
PFI-1218N-5D3BS-O1	Propylene Glycol	527.5	3.26	4"x2	422.0	2.16	4"x2	633.0	4.56	4"x2
PFI-1218N-5D2BS-P1	Propylene Glycol	916.4	10.3	4"x2	733.1	6.79	4"x2	1099.6	11.9	4"x4
PFI-1218N-5D3BS-Q1	Propylene Glycol	927.4	9.25	4"x2	741.9	6.12	4"x2	1112.8	10.4	4"x4
PFI-1218N-6D1BS-K1	Propylene Glycol	505.5	4.6	4"x2	404.4	3.04	4"x2	606.6	6.44	4"x2
PFI-1218N-6D1BS-L1	Propylene Glycol	505.5	4.6	4"x2	404.4	3.04	4"x2	606.6	6.44	4"x2
PFI-1218N-6D1BS-M1	Propylene Glycol	505.5	4.6	4"x2	404.4	3.04	4"x2	606.6	6.44	4"x2
PFI-1218N-6D1BS-N1	Propylene Glycol	505.5	4.6	4"x2	404.4	3.04	4"x2	606.6	6.44	4"x2
PFI-1218N-6D1BS-O1	Propylene Glycol	905.4	13.5	4"x2	724.3	8.94	4"x2	1086.4	16.3	4"x4
PFI-1218N-6D1BS-P1	Propylene Glycol	905.4	13.5	4"x2	724.3	8.94	4"x2	1086.4	16.3	4"x4
PFI-1218N-6D1BS-Q1	Propylene Glycol	905.4	13.5	4"x2	724.3	8.94	4"x2	1086.4	16.3	4"x4
PFI-1218N-6D2BS-R1	Propylene Glycol	916.4	11.9	4"x2	733.1	7.88	4"x2	1099.6	14.1	4"x4
PFI-1218N-2D1DZ-M1	Propylene Glycol	226.3	2.78	4"x2	181.1	1.84	4"x2	271.6	3.89	4"x2
PFI-1218N-2D4EZ-M1	Propylene Glycol	235.1	2.07	4"x2	188.1	1.37	4"x2	282.2	2.9	4"x2
PFI-1218N-2D1DZ-N1	Propylene Glycol	226.3	2.78	4"x2	181.1	1.84	4"x2	271.6	3.89	4"x2
PFI-1218N-2D2DZ-N1	Propylene Glycol	229.1	2.49	4"x2	183.3	1.65	4"x2	274.9	3.48	4"x2
PFI-1218N-2D3EZ-N1	Propylene Glycol	231.8	2.27	4"x2	185.5	1.5	4"x2	278.2	3.18	4"x2
PFI-1218N-2D2DZ-O1	Propylene Glycol	229.1	2.49	4"x2	183.3	1.65	4"x2	274.9	3.48	4"x2
PFI-1218N-2D3EZ-O1	Propylene Glycol	231.8	2.27	4"x2	185.5	1.5	4"x2	278.2	3.18	4"x2
PFI-1218N-2D4DZ-P1	Propylene Glycol	235.1	2.06	4"x2	188.1	1.37	4"x2	282.2	2.89	4"x2
PFI-1218N-3D1EZ-K1	Propylene Glycol	226.3	3.84	4"x2	181.1	2.55	4"x2	271.6	5.39	4"x2
PFI-1218N-3D1EZ-L1	Propylene Glycol	226.3	3.84	4"x2	181.1	2.55	4"x2	271.6	5.39	4"x2
PFI-1218N-3D4EZ-M1	Propylene Glycol	435.1	8.52	4"x2	348.1	5.64	4"x2	522.1	11.9	4"x2
PFI-1218N-3D1DZ-N1	Propylene Glycol	226.3	3.83	4"x2	181.1	2.54	4"x2	271.6	5.37	4"x2
PFI-1218N-3D1EZ-N1	Propylene Glycol	426.3	12.4	4"x2	341.0	8.21	4"x2	511.5	17.4	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-3D1DZ-O1	Propylene Glycol	226.3	3.83	4"x2	181.1	2.54	4"x2	271.6	5.37	4"x2
PFI-1218N-3D2DZ-O1	Propylene Glycol	429.0	10.7	4"x2	343.2	7.11	4"x2	514.8	15.1	4"x2
PFI-1218N-3D1EZ-O1	Propylene Glycol	426.3	12.4	4"x2	341.0	8.21	4"x2	511.5	17.4	4"x2
PFI-1218N-3D2DZ-P1	Propylene Glycol	429.0	10.7	4"x2	343.2	7.11	4"x2	514.8	15.1	4"x2
PFI-1218N-3D2EZ-P1	Propylene Glycol	429.0	10.8	4"x2	343.2	7.14	4"x2	514.8	15.1	4"x2
PFI-1218N-3D2DZ-Q1	Propylene Glycol	429.0	10.7	4"x2	343.2	7.11	4"x2	514.8	15.1	4"x2
PFI-1218N-3D4DZ-Q1	Propylene Glycol	435.1	8.47	4"x2	348.1	5.61	4"x2	522.1	11.9	4"x2
PFI-1218N-3D4EZ-Q1	Propylene Glycol	435.1	8.52	4"x2	348.1	5.64	4"x2	522.1	11.9	4"x2
PFI-1218N-3D1EZ-R1	Propylene Glycol	426.3	12.4	4"x2	341.0	8.21	4"x2	511.5	17.4	4"x2
PFI-1218N-3D4EZ-R1	Propylene Glycol	435.1	8.52	4"x2	348.1	5.64	4"x2	522.1	11.9	4"x2
PFI-1218N-4D1DZ-K1	Propylene Glycol	226.3	4.9	4"x2	181.1	3.24	4"x2	271.6	6.86	4"x2
PFI-1218N-4D1EZ-L1	Propylene Glycol	426.3	15.8	4"x2	341.0	10.4	4"x2	511.5	22.1	4"x2
PFI-1218N-4D2EZ-M1	Propylene Glycol	429.0	13.7	4"x2	343.2	9.06	4"x2	514.8	19.2	4"x2
PFI-1218N-4D2DZ-N1	Propylene Glycol	429.0	13.7	4"x2	343.2	9.04	4"x2	514.8	19.1	4"x2
PFI-1218N-4D1EZ-N1	Propylene Glycol	426.3	15.8	4"x2	341.0	10.4	4"x2	511.5	22.1	4"x2
PFI-1218N-4D3DZ-O1	Propylene Glycol	431.8	12.1	4"x2	345.4	7.99	4"x2	518.1	16.9	4"x2
PFI-1218N-4D1EZ-O1	Propylene Glycol	426.3	15.8	4"x2	341.0	10.4	4"x2	511.5	22.1	4"x2
PFI-1218N-4D1EZ-P1	Propylene Glycol	426.3	15.8	4"x2	341.0	10.4	4"x2	511.5	22.1	4"x2
PFI-1218N-4D1DZ-Q1	Propylene Glycol	426.3	15.8	4"x2	341.0	10.5	4"x2	511.5	22.2	4"x2
PFI-1218N-4D2EZ-Q1	Propylene Glycol	429.0	13.7	4"x2	343.2	9.06	4"x2	514.8	19.2	4"x2
PFI-1218N-4D4EZ-Q1	Propylene Glycol	435.1	10.7	4"x2	348.1	7.06	4"x2	522.1	15	4"x2
PFI-1218N-4D2EZ-R1	Propylene Glycol	429.0	13.7	4"x2	343.2	9.06	4"x2	514.8	19.2	4"x2
PFI-1218N-4D4EZ-R1	Propylene Glycol	435.1	10.7	4"x2	348.1	7.06	4"x2	522.1	15	4"x2
PFI-1218N-5D1DZ-K1	Propylene Glycol	226.3	5.96	4"x2	181.1	3.95	4"x2	271.6	8.35	4"x2
PFI-1218N-5D1EZ-O1	Propylene Glycol	426.3	19.2	4"x2	341.0	12.7	4"x2	511.5	26.8	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-5D2EZ-P1	Propylene Glycol	429.0	16.6	4"x2	343.2	11	4"x2	514.8	23.3	4"x2
PFI-1218N-6D2DZ-M1	Propylene Glycol	429.0	19.5	4"x2	343.2	12.9	4"x2	514.8	27.3	4"x2
PFI-1218N-6D1DZ-N1	Propylene Glycol	426.3	22.6	4"x2	341.0	15	4"x2	511.5	31.7	4"x2
PFI-1218N-6D1DZ-R1	Propylene Glycol	426.3	22.6	4"x2	341.0	15	4"x2	511.5	31.7	4"x2
PFI-1218N-6D1EZ-R1	Propylene Glycol	426.3	22.6	4"x2	341.0	15	4"x2	511.5	31.7	4"x2
PFI-1218N-3D4BT-K1	Propylene Glycol	235.1	2.73	4"x2	188.1	1.81	4"x2	282.2	3.82	4"x2
PFI-1218N-3D4BT-L1	Propylene Glycol	235.1	2.73	4"x2	188.1	1.81	4"x2	282.2	3.82	4"x2
PFI-1218N-3D4BT-N1	Propylene Glycol	235.1	2.73	4"x2	188.1	1.81	4"x2	282.2	3.82	4"x2
PFI-1218N-3D4BT-O1	Propylene Glycol	235.1	2.73	4"x2	188.1	1.81	4"x2	282.2	3.82	4"x2
PFI-1218N-3D4BT-P1	Propylene Glycol	235.1	2.73	4"x2	188.1	1.81	4"x2	282.2	3.82	4"x2
PFI-1218N-4D4BT-K1	Propylene Glycol	235.1	3.41	4"x2	188.1	2.26	4"x2	282.2	4.77	4"x2
PFI-1218N-4D4BT-L1	Propylene Glycol	235.1	3.41	4"x2	188.1	2.26	4"x2	282.2	4.77	4"x2
PFI-1218N-4D3BT-M1	Propylene Glycol	231.8	3.83	4"x2	185.5	2.53	4"x2	278.2	5.36	4"x2
PFI-1218N-4D3BT-N1	Propylene Glycol	231.8	3.83	4"x2	185.5	2.53	4"x2	278.2	5.36	4"x2
PFI-1218N-4D3BT-O1	Propylene Glycol	231.8	3.83	4"x2	185.5	2.53	4"x2	278.2	5.36	4"x2
PFI-1218N-4D4BT-P1	Propylene Glycol	435.1	10.6	4"x2	348.1	7.04	4"x2	522.1	14.9	4"x2
PFI-1218N-4D3BT-Q1	Propylene Glycol	431.8	12.1	4"x2	345.4	8	4"x2	518.1	17	4"x2
PFI-1218N-5D2BT-K1	Propylene Glycol	229.1	5.19	4"x2	183.3	3.44	4"x2	274.9	7.27	4"x2
PFI-1218N-5D2BT-L1	Propylene Glycol	229.1	5.19	4"x2	183.3	3.44	4"x2	274.9	7.27	4"x2
PFI-1218N-5D2BT-M1	Propylene Glycol	229.1	5.19	4"x2	183.3	3.44	4"x2	274.9	7.27	4"x2
PFI-1218N-5D2BT-N1	Propylene Glycol	229.1	5.19	4"x2	183.3	3.44	4"x2	274.9	7.27	4"x2
PFI-1218N-5D3BT-O1	Propylene Glycol	431.8	14.5	4"x2	345.4	9.57	4"x2	518.1	20.3	4"x2
PFI-1218N-5D2BT-P1	Propylene Glycol	429.0	16.6	4"x2	343.2	11	4"x2	514.8	23.2	4"x2
PFI-1218N-5D3BT-Q1	Propylene Glycol	431.8	14.5	4"x2	345.4	9.57	4"x2	518.1	20.3	4"x2
PFI-1218N-6D1BT-K1	Propylene Glycol	226.3	6.99	4"x2	181.1	4.63	4"x2	271.6	9.8	4"x2



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1218N-6D1BT-L1	Propylene Glycol	226.3	6.99	4"x2	181.1	4.63	4"x2	271.6	9.8	4"x2
PFI-1218N-6D1BT-M1	Propylene Glycol	226.3	6.99	4"x2	181.1	4.63	4"x2	271.6	9.8	4"x2
PFI-1218N-6D1BT-N1	Propylene Glycol	426.3	22.6	4"x2	341.0	14.9	4"x2	511.5	31.6	4"x2
PFI-1218N-6D1BT-O1	Propylene Glycol	426.3	22.6	4"x2	341.0	14.9	4"x2	511.5	31.6	4"x2
PFI-1218N-6D1BT-P1	Propylene Glycol	426.3	22.6	4"x2	341.0	14.9	4"x2	511.5	31.6	4"x2
PFI-1218N-6D1BT-Q1	Propylene Glycol	426.3	22.6	4"x2	341.0	14.9	4"x2	511.5	31.6	4"x2
PFI-1236N-2D1DS-M2	Propylene Glycol	1011.0	2	4"x4	808.8	1.33	4"x4	1213.1	2.8	4"x4
PFI-1236N-2D4ES-M2	Propylene Glycol	1081.4	1.67	4"x4	865.1	1.11	4"x4	1297.6	2.33	4"x4
PFI-1236N-2D1DS-N2	Propylene Glycol	1011.0	2	4"x4	808.8	1.33	4"x4	1213.1	2.8	4"x4
PFI-1236N-2D2DS-N2	Propylene Glycol	1033.0	1.86	4"x4	826.4	1.23	4"x4	1239.5	2.6	4"x4
PFI-1236N-2D3ES-N2	Propylene Glycol	1055.0	1.76	4"x4	844.0	1.16	4"x4	1265.9	2.46	4"x4
PFI-1236N-2D2DS-O2	Propylene Glycol	1033.0	1.86	4"x4	826.4	1.23	4"x4	1239.5	2.6	4"x4
PFI-1236N-2D3ES-O2	Propylene Glycol	1055.0	1.76	4"x4	844.0	1.16	4"x4	1265.9	2.46	4"x4
PFI-1236N-2D4DS-P2	Propylene Glycol	1081.4	1.67	4"x4	865.1	1.11	4"x4	1297.6	2.33	4"x4
PFI-1236N-3D1ES-K2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-1236N-3D1ES-L2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-1236N-3D4ES-M2	Propylene Glycol	1881.1	4.37	4"x8	1504.9	3.88	4"x4	2257.3	6.12	4"x8
PFI-1236N-3D1DS-N2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-1236N-3D1ES-N2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-1236N-3D1DS-O2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-1236N-3D2DS-O2	Propylene Glycol	1033.0	2.43	4"x4	826.4	1.61	4"x4	1239.5	3.4	4"x4
PFI-1236N-3D1ES-O2	Propylene Glycol	1810.7	7.78	4"x4	1448.6	5.15	4"x4	2172.8	8.61	4"x8
PFI-1236N-3D2DS-P2	Propylene Glycol	1832.7	7	4"x4	1466.2	4.63	4"x4	2199.2	7.47	4"x8
PFI-1236N-3D2ES-P2	Propylene Glycol	1832.7	7	4"x4	1466.2	4.63	4"x4	2199.2	7.47	4"x8
PFI-1236N-3D2DS-Q2	Propylene Glycol	1832.7	7	4"x4	1466.2	4.63	4"x4	2199.2	7.47	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-3D4DS-Q2	Propylene Glycol	1881.1	4.37	4"x8	1504.9	3.88	4"x4	2257.3	6.12	4"x8
PFI-1236N-3D4ES-Q2	Propylene Glycol	1881.1	4.37	4"x8	1504.9	3.88	4"x4	2257.3	6.12	4"x8
PFI-1236N-3D1ES-R2	Propylene Glycol	1810.7	7.78	4"x4	1448.6	5.15	4"x4	2172.8	8.61	4"x8
PFI-1236N-3D4ES-R2	Propylene Glycol	1881.1	4.37	4"x8	1504.9	3.88	4"x4	2257.3	6.12	4"x8
PFI-1236N-4D1DS-K2	Propylene Glycol	1011.0	3.3	4"x4	808.8	2.18	4"x4	1213.1	4.62	4"x4
PFI-1236N-4D1ES-L2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-1236N-4D2ES-M2	Propylene Glycol	1832.7	8.63	4"x4	1466.2	5.71	4"x4	2199.2	9.66	4"x8
PFI-1236N-4D2DS-N2	Propylene Glycol	1832.7	8.63	4"x4	1466.2	5.71	4"x4	2199.2	9.66	4"x8
PFI-1236N-4D1ES-N2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-1236N-4D3DS-O2	Propylene Glycol	1854.7	7.82	4"x4	1483.8	5.18	4"x4	2225.6	8.51	4"x8
PFI-1236N-4D1ES-O2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-1236N-4D1ES-P2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-1236N-4D1DS-Q2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-1236N-4D2ES-Q2	Propylene Glycol	1832.7	8.63	4"x4	1466.2	5.71	4"x4	2199.2	9.66	4"x8
PFI-1236N-4D4ES-Q2	Propylene Glycol	1881.1	5.31	4"x8	1504.9	4.69	4"x4	2257.3	7.44	4"x8
PFI-1236N-4D2ES-R2	Propylene Glycol	1832.7	8.63	4"x4	1466.2	5.71	4"x4	2199.2	9.66	4"x8
PFI-1236N-4D4ES-R2	Propylene Glycol	1881.1	5.31	4"x8	1504.9	4.69	4"x4	2257.3	7.44	4"x8
PFI-1236N-5D1DS-K2	Propylene Glycol	1011.0	3.95	4"x4	808.8	2.61	4"x4	1213.1	5.53	4"x4
PFI-1236N-5D1ES-O2	Propylene Glycol	1810.7	11.6	4"x4	1448.6	7.67	4"x4	2172.8	13.8	4"x8
PFI-1236N-5D2ES-P2	Propylene Glycol	1832.7	10.3	4"x4	1466.2	6.79	4"x4	2199.2	11.9	4"x8
PFI-1236N-6D2DS-M2	Propylene Glycol	1832.7	11.9	4"x4	1466.2	7.88	4"x4	2199.2	14.1	4"x8
PFI-1236N-6D1DS-N2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-1236N-6D1DS-R2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-1236N-6D1ES-R2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-1236N-3D4BS-K2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-3D4BS-L2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-1236N-3D4BS-N2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-1236N-3D4BS-O2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-1236N-3D4BS-P2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-1236N-4D4BS-K2	Propylene Glycol	1081.4	2.55	4"x4	865.1	1.69	4"x4	1297.6	3.57	4"x4
PFI-1236N-4D4BS-L2	Propylene Glycol	1081.4	2.55	4"x4	865.1	1.69	4"x4	1297.6	3.57	4"x4
PFI-1236N-4D3BS-M2	Propylene Glycol	1055.0	2.76	4"x4	844.0	1.83	4"x4	1265.9	3.86	4"x4
PFI-1236N-4D3BS-N2	Propylene Glycol	1055.0	2.76	4"x4	844.0	1.83	4"x4	1265.9	3.86	4"x4
PFI-1236N-4D3BS-O2	Propylene Glycol	1055.0	2.76	4"x4	844.0	1.83	4"x4	1265.9	3.86	4"x4
PFI-1236N-4D4BS-P2	Propylene Glycol	1881.1	5.31	4"x8	1504.9	4.69	4"x4	2257.3	7.44	4"x8
PFI-1236N-4D3BS-Q2	Propylene Glycol	1854.7	7.82	4"x4	1483.8	5.18	4"x4	2225.6	8.51	4"x8
PFI-1236N-5D2BS-K2	Propylene Glycol	1033.0	3.56	4"x4	826.4	2.36	4"x4	1239.5	4.98	4"x4
PFI-1236N-5D2BS-L2	Propylene Glycol	1033.0	3.56	4"x4	826.4	2.36	4"x4	1239.5	4.98	4"x4
PFI-1236N-5D2BS-M2	Propylene Glycol	1033.0	3.56	4"x4	826.4	2.36	4"x4	1239.5	4.98	4"x4
PFI-1236N-5D2BS-N2	Propylene Glycol	1033.0	3.56	4"x4	826.4	2.36	4"x4	1239.5	4.98	4"x4
PFI-1236N-5D3BS-O2	Propylene Glycol	1055.0	3.26	4"x4	844.0	2.16	4"x4	1265.9	4.56	4"x4
PFI-1236N-5D2BS-P2	Propylene Glycol	1832.7	10.3	4"x4	1466.2	6.79	4"x4	2199.2	11.9	4"x8
PFI-1236N-5D3BS-Q2	Propylene Glycol	1854.7	9.24	4"x4	1483.8	6.12	4"x4	2225.6	10.4	4"x8
PFI-1236N-6D1BS-K2	Propylene Glycol	1011.0	4.6	4"x4	808.8	3.04	4"x4	1213.1	6.44	4"x4
PFI-1236N-6D1BS-L2	Propylene Glycol	1011.0	4.6	4"x4	808.8	3.04	4"x4	1213.1	6.44	4"x4
PFI-1236N-6D1BS-M2	Propylene Glycol	1011.0	4.6	4"x4	808.8	3.04	4"x4	1213.1	6.44	4"x4
PFI-1236N-6D1BS-N2	Propylene Glycol	1011.0	4.6	4"x4	808.8	3.04	4"x4	1213.1	6.44	4"x4
PFI-1236N-6D1BS-O2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-1236N-6D1BS-P2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-1236N-6D1BS-Q2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-6D2BS-R2	Propylene Glycol	1832.7	11.9	4"x4	1466.2	7.88	4"x4	2199.2	14.1	4"x8
PFI-1236N-2D1DZ-M2	Propylene Glycol	452.7	2.78	4"x4	362.1	1.84	4"x4	543.2	3.89	4"x4
PFI-1236N-2D4EZ-M2	Propylene Glycol	470.3	2.07	4"x4	376.2	1.37	4"x4	564.3	2.9	4"x4
PFI-1236N-2D1DZ-N2	Propylene Glycol	452.7	2.78	4"x4	362.1	1.84	4"x4	543.2	3.89	4"x4
PFI-1236N-2D2DZ-N2	Propylene Glycol	458.2	2.49	4"x4	366.5	1.65	4"x4	549.8	3.48	4"x4
PFI-1236N-2D3EZ-N2	Propylene Glycol	463.7	2.27	4"x4	370.9	1.5	4"x4	556.4	3.18	4"x4
PFI-1236N-2D2DZ-O2	Propylene Glycol	458.2	2.49	4"x4	366.5	1.65	4"x4	549.8	3.48	4"x4
PFI-1236N-2D3EZ-O2	Propylene Glycol	463.7	2.27	4"x4	370.9	1.5	4"x4	556.4	3.18	4"x4
PFI-1236N-2D4DZ-P2	Propylene Glycol	470.3	2.06	4"x4	376.2	1.37	4"x4	564.3	2.89	4"x4
PFI-1236N-3D1EZ-K2	Propylene Glycol	452.7	3.85	4"x4	362.1	2.55	4"x4	543.2	5.39	4"x4
PFI-1236N-3D1EZ-L2	Propylene Glycol	452.7	3.85	4"x4	362.1	2.55	4"x4	543.2	5.39	4"x4
PFI-1236N-3D4EZ-M2	Propylene Glycol	870.2	8.52	4"x4	696.1	5.63	4"x4	1044.2	11.9	4"x4
PFI-1236N-3D1DZ-N2	Propylene Glycol	452.7	3.84	4"x4	362.1	2.54	4"x4	543.2	5.37	4"x4
PFI-1236N-3D1EZ-N2	Propylene Glycol	852.6	12.4	4"x4	682.0	8.21	4"x4	1023.1	17.4	4"x4
PFI-1236N-3D1DZ-O2	Propylene Glycol	452.7	3.84	4"x4	362.1	2.54	4"x4	543.2	5.37	4"x4
PFI-1236N-3D2DZ-O2	Propylene Glycol	858.1	10.7	4"x4	686.4	7.11	4"x4	1029.7	15.1	4"x4
PFI-1236N-3D1EZ-O2	Propylene Glycol	852.6	12.4	4"x4	682.0	8.21	4"x4	1023.1	17.4	4"x4
PFI-1236N-3D2DZ-P2	Propylene Glycol	858.1	10.7	4"x4	686.4	7.11	4"x4	1029.7	15.1	4"x4
PFI-1236N-3D2EZ-P2	Propylene Glycol	858.1	10.8	4"x4	686.4	7.14	4"x4	1029.7	15.1	4"x4
PFI-1236N-3D2DZ-Q2	Propylene Glycol	858.1	10.7	4"x4	686.4	7.11	4"x4	1029.7	15.1	4"x4
PFI-1236N-3D4DZ-Q2	Propylene Glycol	870.2	8.47	4"x4	696.1	5.6	4"x4	1044.2	11.9	4"x4
PFI-1236N-3D4EZ-Q2	Propylene Glycol	870.2	8.52	4"x4	696.1	5.63	4"x4	1044.2	11.9	4"x4
PFI-1236N-3D1EZ-R2	Propylene Glycol	852.6	12.4	4"x4	682.0	8.21	4"x4	1023.1	17.4	4"x4
PFI-1236N-3D4EZ-R2	Propylene Glycol	870.2	8.52	4"x4	696.1	5.63	4"x4	1044.2	11.9	4"x4
PFI-1236N-4D1DZ-K2	Propylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-4D1EZ-L2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.4	4"x4	1023.1	22.1	4"x4
PFI-1236N-4D2EZ-M2	Propylene Glycol	858.1	13.7	4"x4	686.4	9.06	4"x4	1029.7	19.2	4"x4
PFI-1236N-4D2DZ-N2	Propylene Glycol	858.1	13.7	4"x4	686.4	9.04	4"x4	1029.7	19.1	4"x4
PFI-1236N-4D1EZ-N2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.4	4"x4	1023.1	22.1	4"x4
PFI-1236N-4D3DZ-O2	Propylene Glycol	863.6	12.1	4"x4	690.8	7.99	4"x4	1036.3	16.9	4"x4
PFI-1236N-4D1EZ-O2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.4	4"x4	1023.1	22.1	4"x4
PFI-1236N-4D1EZ-P2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.4	4"x4	1023.1	22.1	4"x4
PFI-1236N-4D1DZ-Q2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.5	4"x4	1023.1	22.2	4"x4
PFI-1236N-4D2EZ-Q2	Propylene Glycol	858.1	13.7	4"x4	686.4	9.06	4"x4	1029.7	19.2	4"x4
PFI-1236N-4D4EZ-Q2	Propylene Glycol	870.2	10.7	4"x4	696.1	7.05	4"x4	1044.2	15	4"x4
PFI-1236N-4D2EZ-R2	Propylene Glycol	858.1	13.7	4"x4	686.4	9.06	4"x4	1029.7	19.2	4"x4
PFI-1236N-4D4EZ-R2	Propylene Glycol	870.2	10.7	4"x4	696.1	7.05	4"x4	1044.2	15	4"x4
PFI-1236N-5D1DZ-K2	Propylene Glycol	452.7	5.96	4"x4	362.1	3.95	4"x4	543.2	8.35	4"x4
PFI-1236N-5D1EZ-O2	Propylene Glycol	852.6	19.2	4"x4	682.0	12.7	4"x4	1023.1	26.9	4"x4
PFI-1236N-5D2EZ-P2	Propylene Glycol	858.1	16.6	4"x4	686.4	11	4"x4	1029.7	23.3	4"x4
PFI-1236N-6D2DZ-M2	Propylene Glycol	858.1	19.5	4"x4	686.4	12.9	4"x4	1029.7	27.3	4"x4
PFI-1236N-6D1DZ-N2	Propylene Glycol	852.6	22.6	4"x4	682.0	15	4"x4	1023.1	31.7	4"x4
PFI-1236N-6D1DZ-R2	Propylene Glycol	852.6	22.6	4"x4	682.0	15	4"x4	1023.1	31.7	4"x4
PFI-1236N-6D1EZ-R2	Propylene Glycol	852.6	22.6	4"x4	682.0	15	4"x4	1023.1	31.7	4"x4
PFI-1236N-3D4BT-K2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-1236N-3D4BT-L2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-1236N-3D4BT-N2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-1236N-3D4BT-O2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-1236N-3D4BT-P2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-1236N-4D4BT-K2	Propylene Glycol	470.3	3.41	4"x4	376.2	2.26	4"x4	564.3	4.77	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-1236N-4D4BT-L2	Propylene Glycol	470.3	3.41	4"x4	376.2	2.26	4"x4	564.3	4.77	4"x4
PFI-1236N-4D3BT-M2	Propylene Glycol	463.7	3.83	4"x4	370.9	2.53	4"x4	556.4	5.36	4"x4
PFI-1236N-4D3BT-N2	Propylene Glycol	463.7	3.83	4"x4	370.9	2.53	4"x4	556.4	5.36	4"x4
PFI-1236N-4D3BT-O2	Propylene Glycol	463.7	3.83	4"x4	370.9	2.53	4"x4	556.4	5.36	4"x4
PFI-1236N-4D4BT-P2	Propylene Glycol	870.2	10.6	4"x4	696.1	7.04	4"x4	1044.2	14.9	4"x4
PFI-1236N-4D3BT-Q2	Propylene Glycol	863.6	12.1	4"x4	690.8	8	4"x4	1036.3	17	4"x4
PFI-1236N-5D2BT-K2	Propylene Glycol	458.2	5.19	4"x4	366.5	3.44	4"x4	549.8	7.27	4"x4
PFI-1236N-5D2BT-L2	Propylene Glycol	458.2	5.19	4"x4	366.5	3.44	4"x4	549.8	7.27	4"x4
PFI-1236N-5D2BT-M2	Propylene Glycol	458.2	5.19	4"x4	366.5	3.44	4"x4	549.8	7.27	4"x4
PFI-1236N-5D2BT-N2	Propylene Glycol	458.2	5.19	4"x4	366.5	3.44	4"x4	549.8	7.27	4"x4
PFI-1236N-5D3BT-O2	Propylene Glycol	863.6	14.5	4"x4	690.8	9.57	4"x4	1036.3	20.3	4"x4
PFI-1236N-5D2BT-P2	Propylene Glycol	858.1	16.6	4"x4	686.4	11	4"x4	1029.7	23.2	4"x4
PFI-1236N-5D3BT-Q2	Propylene Glycol	863.6	14.5	4"x4	690.8	9.57	4"x4	1036.3	20.3	4"x4
PFI-1236N-6D1BT-K2	Propylene Glycol	452.7	7	4"x4	362.1	4.63	4"x4	543.2	9.8	4"x4
PFI-1236N-6D1BT-L2	Propylene Glycol	452.7	7	4"x4	362.1	4.63	4"x4	543.2	9.8	4"x4
PFI-1236N-6D1BT-M2	Propylene Glycol	452.7	7	4"x4	362.1	4.63	4"x4	543.2	9.8	4"x4
PFI-1236N-6D1BT-N2	Propylene Glycol	852.6	22.6	4"x4	682.0	14.9	4"x4	1023.1	31.6	4"x4
PFI-1236N-6D1BT-O2	Propylene Glycol	852.6	22.6	4"x4	682.0	14.9	4"x4	1023.1	31.6	4"x4
PFI-1236N-6D1BT-P2	Propylene Glycol	852.6	22.6	4"x4	682.0	14.9	4"x4	1023.1	31.6	4"x4
PFI-1236N-6D1BT-Q2	Propylene Glycol	852.6	22.6	4"x4	682.0	14.9	4"x4	1023.1	31.6	4"x4
PFI-2418N-2D1DS-M2	Propylene Glycol	1011.0	2	4"x4	808.8	1.33	4"x4	1213.1	2.8	4"x4
PFI-2418N-2D4ES-M2	Propylene Glycol	1081.4	1.67	4"x4	865.1	1.11	4"x4	1297.6	2.33	4"x4
PFI-2418N-2D1DS-N2	Propylene Glycol	1011.0	2	4"x4	808.8	1.33	4"x4	1213.1	2.8	4"x4
PFI-2418N-2D2DS-N2	Propylene Glycol	1033.0	1.86	4"x4	826.4	1.23	4"x4	1239.5	2.6	4"x4
PFI-2418N-2D3ES-N2	Propylene Glycol	1055.0	1.76	4"x4	844.0	1.16	4"x4	1265.9	2.46	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-2D2DS-O2	Propylene Glycol	1033.0	1.86	4"x4	826.4	1.23	4"x4	1239.5	2.6	4"x4
PFI-2418N-2D3ES-O2	Propylene Glycol	1055.0	1.76	4"x4	844.0	1.16	4"x4	1265.9	2.46	4"x4
PFI-2418N-2D4DS-P2	Propylene Glycol	1081.4	1.67	4"x4	865.1	1.11	4"x4	1297.6	2.33	4"x4
PFI-2418N-3D1ES-K2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-2418N-3D1ES-L2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-2418N-3D4ES-M2	Propylene Glycol	1881.1	4.37	4"x8	1504.9	3.88	4"x4	2257.3	6.12	4"x8
PFI-2418N-3D1DS-N2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-2418N-3D1ES-N2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-2418N-3D1DS-O2	Propylene Glycol	1011.0	2.65	4"x4	808.8	1.76	4"x4	1213.1	3.71	4"x4
PFI-2418N-3D2DS-O2	Propylene Glycol	1033.0	2.43	4"x4	826.4	1.61	4"x4	1239.5	3.4	4"x4
PFI-2418N-3D1ES-O2	Propylene Glycol	1810.7	7.78	4"x4	1448.6	5.15	4"x4	2172.8	8.61	4"x8
PFI-2418N-3D2DS-P2	Propylene Glycol	1832.7	7	4"x4	1466.2	4.63	4"x4	2199.2	7.47	4"x8
PFI-2418N-3D2ES-P2	Propylene Glycol	1832.7	7	4"x4	1466.2	4.63	4"x4	2199.2	7.47	4"x8
PFI-2418N-3D2DS-Q2	Propylene Glycol	1832.7	7	4"x4	1466.2	4.63	4"x4	2199.2	7.47	4"x8
PFI-2418N-3D4DS-Q2	Propylene Glycol	1881.1	4.37	4"x8	1504.9	3.88	4"x4	2257.3	6.12	4"x8
PFI-2418N-3D4ES-Q2	Propylene Glycol	1881.1	4.37	4"x8	1504.9	3.88	4"x4	2257.3	6.12	4"x8
PFI-2418N-3D1ES-R2	Propylene Glycol	1810.7	7.78	4"x4	1448.6	5.15	4"x4	2172.8	8.61	4"x8
PFI-2418N-3D4ES-R2	Propylene Glycol	1881.1	4.37	4"x8	1504.9	3.88	4"x4	2257.3	6.12	4"x8
PFI-2418N-4D1DS-K2	Propylene Glycol	1011.0	3.3	4"x4	808.8	2.18	4"x4	1213.1	4.62	4"x4
PFI-2418N-4D1ES-L2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-2418N-4D2ES-M2	Propylene Glycol	1832.7	8.63	4"x4	1466.2	5.71	4"x4	2199.2	9.66	4"x8
PFI-2418N-4D2DS-N2	Propylene Glycol	1832.7	8.63	4"x4	1466.2	5.71	4"x4	2199.2	9.66	4"x8
PFI-2418N-4D1ES-N2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-2418N-4D3DS-O2	Propylene Glycol	1854.7	7.82	4"x4	1483.8	5.18	4"x4	2225.6	8.51	4"x8
PFI-2418N-4D1ES-O2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-4D1ES-P2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-2418N-4D1DS-Q2	Propylene Glycol	1810.7	9.69	4"x4	1448.6	6.41	4"x4	2172.8	11.2	4"x8
PFI-2418N-4D2ES-Q2	Propylene Glycol	1832.7	8.63	4"x4	1466.2	5.71	4"x4	2199.2	9.66	4"x8
PFI-2418N-4D4ES-Q2	Propylene Glycol	1881.1	5.31	4"x8	1504.9	4.69	4"x4	2257.3	7.44	4"x8
PFI-2418N-4D2ES-R2	Propylene Glycol	1832.7	8.63	4"x4	1466.2	5.71	4"x4	2199.2	9.66	4"x8
PFI-2418N-4D4ES-R2	Propylene Glycol	1881.1	5.31	4"x8	1504.9	4.69	4"x4	2257.3	7.44	4"x8
PFI-2418N-5D1DS-K2	Propylene Glycol	1011.0	3.95	4"x4	808.8	2.61	4"x4	1213.1	5.53	4"x4
PFI-2418N-5D1ES-O2	Propylene Glycol	1810.7	11.6	4"x4	1448.6	7.67	4"x4	2172.8	13.8	4"x8
PFI-2418N-5D2ES-P2	Propylene Glycol	1832.7	10.3	4"x4	1466.2	6.79	4"x4	2199.2	11.9	4"x8
PFI-2418N-6D2DS-M2	Propylene Glycol	1832.7	11.9	4"x4	1466.2	7.88	4"x4	2199.2	14.1	4"x8
PFI-2418N-6D1DS-N2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-2418N-6D1DS-R2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-2418N-6D1ES-R2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-2418N-3D4BS-K2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-2418N-3D4BS-L2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-2418N-3D4BS-N2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-2418N-3D4BS-O2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-2418N-3D4BS-P2	Propylene Glycol	1081.4	2.11	4"x4	865.1	1.4	4"x4	1297.6	2.95	4"x4
PFI-2418N-4D4BS-K2	Propylene Glycol	1081.4	2.55	4"x4	865.1	1.69	4"x4	1297.6	3.57	4"x4
PFI-2418N-4D4BS-L2	Propylene Glycol	1081.4	2.55	4"x4	865.1	1.69	4"x4	1297.6	3.57	4"x4
PFI-2418N-4D3BS-M2	Propylene Glycol	1055.0	2.76	4"x4	844.0	1.83	4"x4	1265.9	3.86	4"x4
PFI-2418N-4D3BS-N2	Propylene Glycol	1055.0	2.76	4"x4	844.0	1.83	4"x4	1265.9	3.86	4"x4
PFI-2418N-4D3BS-O2	Propylene Glycol	1055.0	2.76	4"x4	844.0	1.83	4"x4	1265.9	3.86	4"x4
PFI-2418N-4D4BS-P2	Propylene Glycol	1881.1	5.31	4"x8	1504.9	4.69	4"x4	2257.3	7.44	4"x8
PFI-2418N-4D3BS-Q2	Propylene Glycol	1854.7	7.82	4"x4	1483.8	5.18	4"x4	2225.6	8.51	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-5D2BS-K2	Propylene Glycol	1033.0	3.56	4"x4	826.4	2.36	4"x4	1239.5	4.98	4"x4
PFI-2418N-5D2BS-L2	Propylene Glycol	1033.0	3.56	4"x4	826.4	2.36	4"x4	1239.5	4.98	4"x4
PFI-2418N-5D2BS-M2	Propylene Glycol	1033.0	3.56	4"x4	826.4	2.36	4"x4	1239.5	4.98	4"x4
PFI-2418N-5D2BS-N2	Propylene Glycol	1033.0	3.56	4"x4	826.4	2.36	4"x4	1239.5	4.98	4"x4
PFI-2418N-5D3BS-O2	Propylene Glycol	1055.0	3.26	4"x4	844.0	2.16	4"x4	1265.9	4.56	4"x4
PFI-2418N-5D2BS-P2	Propylene Glycol	1832.7	10.3	4"x4	1466.2	6.79	4"x4	2199.2	11.9	4"x8
PFI-2418N-5D3BS-Q2	Propylene Glycol	1854.7	9.24	4"x4	1483.8	6.12	4"x4	2225.6	10.4	4"x8
PFI-2418N-6D1BS-K2	Propylene Glycol	1011.0	4.6	4"x4	808.8	3.04	4"x4	1213.1	6.44	4"x4
PFI-2418N-6D1BS-L2	Propylene Glycol	1011.0	4.6	4"x4	808.8	3.04	4"x4	1213.1	6.44	4"x4
PFI-2418N-6D1BS-M2	Propylene Glycol	1011.0	4.6	4"x4	808.8	3.04	4"x4	1213.1	6.44	4"x4
PFI-2418N-6D1BS-N2	Propylene Glycol	1011.0	4.6	4"x4	808.8	3.04	4"x4	1213.1	6.44	4"x4
PFI-2418N-6D1BS-O2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-2418N-6D1BS-P2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-2418N-6D1BS-Q2	Propylene Glycol	1810.7	13.5	4"x4	1448.6	8.94	4"x4	2172.8	16.3	4"x8
PFI-2418N-6D2BS-R2	Propylene Glycol	1832.7	11.9	4"x4	1466.2	7.88	4"x4	2199.2	14.1	4"x8
PFI-2418N-2D1DZ-M2	Propylene Glycol	452.7	2.78	4"x4	362.1	1.84	4"x4	543.2	3.89	4"x4
PFI-2418N-2D4EZ-M2	Propylene Glycol	470.3	2.07	4"x4	376.2	1.37	4"x4	564.3	2.9	4"x4
PFI-2418N-2D1DZ-N2	Propylene Glycol	452.7	2.78	4"x4	362.1	1.84	4"x4	543.2	3.89	4"x4
PFI-2418N-2D2DZ-N2	Propylene Glycol	458.2	2.49	4"x4	366.5	1.65	4"x4	549.8	3.48	4"x4
PFI-2418N-2D3EZ-N2	Propylene Glycol	463.7	2.27	4"x4	370.9	1.5	4"x4	556.4	3.18	4"x4
PFI-2418N-2D2DZ-O2	Propylene Glycol	458.2	2.49	4"x4	366.5	1.65	4"x4	549.8	3.48	4"x4
PFI-2418N-2D3EZ-O2	Propylene Glycol	463.7	2.27	4"x4	370.9	1.5	4"x4	556.4	3.18	4"x4
PFI-2418N-2D4DZ-P2	Propylene Glycol	470.3	2.06	4"x4	376.2	1.37	4"x4	564.3	2.89	4"x4
PFI-2418N-3D1EZ-K2	Propylene Glycol	452.7	3.85	4"x4	362.1	2.55	4"x4	543.2	5.39	4"x4
PFI-2418N-3D1EZ-L2	Propylene Glycol	452.7	3.85	4"x4	362.1	2.55	4"x4	543.2	5.39	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-3D4EZ-M2	Propylene Glycol	870.2	8.52	4"x4	696.1	5.63	4"x4	1044.2	11.9	4"x4
PFI-2418N-3D1DZ-N2	Propylene Glycol	452.7	3.84	4"x4	362.1	2.54	4"x4	543.2	5.37	4"x4
PFI-2418N-3D1EZ-N2	Propylene Glycol	852.6	12.4	4"x4	682.0	8.21	4"x4	1023.1	17.4	4"x4
PFI-2418N-3D1DZ-O2	Propylene Glycol	452.7	3.84	4"x4	362.1	2.54	4"x4	543.2	5.37	4"x4
PFI-2418N-3D2DZ-O2	Propylene Glycol	858.1	10.7	4"x4	686.4	7.11	4"x4	1029.7	15.1	4"x4
PFI-2418N-3D1EZ-O2	Propylene Glycol	852.6	12.4	4"x4	682.0	8.21	4"x4	1023.1	17.4	4"x4
PFI-2418N-3D2DZ-P2	Propylene Glycol	858.1	10.7	4"x4	686.4	7.11	4"x4	1029.7	15.1	4"x4
PFI-2418N-3D2EZ-P2	Propylene Glycol	858.1	10.8	4"x4	686.4	7.14	4"x4	1029.7	15.1	4"x4
PFI-2418N-3D2DZ-Q2	Propylene Glycol	858.1	10.7	4"x4	686.4	7.11	4"x4	1029.7	15.1	4"x4
PFI-2418N-3D4DZ-Q2	Propylene Glycol	870.2	8.47	4"x4	696.1	5.6	4"x4	1044.2	11.9	4"x4
PFI-2418N-3D4EZ-Q2	Propylene Glycol	870.2	8.52	4"x4	696.1	5.63	4"x4	1044.2	11.9	4"x4
PFI-2418N-3D1EZ-R2	Propylene Glycol	852.6	12.4	4"x4	682.0	8.21	4"x4	1023.1	17.4	4"x4
PFI-2418N-3D4EZ-R2	Propylene Glycol	870.2	8.52	4"x4	696.1	5.63	4"x4	1044.2	11.9	4"x4
PFI-2418N-4D1DZ-K2	Propylene Glycol	452.7	4.9	4"x4	362.1	3.24	4"x4	543.2	6.86	4"x4
PFI-2418N-4D1EZ-L2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.4	4"x4	1023.1	22.1	4"x4
PFI-2418N-4D2EZ-M2	Propylene Glycol	858.1	13.7	4"x4	686.4	9.06	4"x4	1029.7	19.2	4"x4
PFI-2418N-4D2DZ-N2	Propylene Glycol	858.1	13.7	4"x4	686.4	9.04	4"x4	1029.7	19.1	4"x4
PFI-2418N-4D1EZ-N2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.4	4"x4	1023.1	22.1	4"x4
PFI-2418N-4D3DZ-O2	Propylene Glycol	863.6	12.1	4"x4	690.8	7.99	4"x4	1036.3	16.9	4"x4
PFI-2418N-4D1EZ-O2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.4	4"x4	1023.1	22.1	4"x4
PFI-2418N-4D1EZ-P2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.4	4"x4	1023.1	22.1	4"x4
PFI-2418N-4D1DZ-Q2	Propylene Glycol	852.6	15.8	4"x4	682.0	10.5	4"x4	1023.1	22.2	4"x4
PFI-2418N-4D2EZ-Q2	Propylene Glycol	858.1	13.7	4"x4	686.4	9.06	4"x4	1029.7	19.2	4"x4
PFI-2418N-4D4EZ-Q2	Propylene Glycol	870.2	10.7	4"x4	696.1	7.05	4"x4	1044.2	15	4"x4
PFI-2418N-4D2EZ-R2	Propylene Glycol	858.1	13.7	4"x4	686.4	9.06	4"x4	1029.7	19.2	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-4D4EZ-R2	Propylene Glycol	870.2	10.7	4"x4	696.1	7.05	4"x4	1044.2	15	4"x4
PFI-2418N-5D1DZ-K2	Propylene Glycol	452.7	5.96	4"x4	362.1	3.95	4"x4	543.2	8.35	4"x4
PFI-2418N-5D1EZ-O2	Propylene Glycol	852.6	19.2	4"x4	682.0	12.7	4"x4	1023.1	26.9	4"x4
PFI-2418N-5D2EZ-P2	Propylene Glycol	858.1	16.6	4"x4	686.4	11	4"x4	1029.7	23.3	4"x4
PFI-2418N-6D2DZ-M2	Propylene Glycol	858.1	19.5	4"x4	686.4	12.9	4"x4	1029.7	27.3	4"x4
PFI-2418N-6D1DZ-N2	Propylene Glycol	852.6	22.6	4"x4	682.0	15	4"x4	1023.1	31.7	4"x4
PFI-2418N-6D1DZ-R2	Propylene Glycol	852.6	22.6	4"x4	682.0	15	4"x4	1023.1	31.7	4"x4
PFI-2418N-6D1EZ-R2	Propylene Glycol	852.6	22.6	4"x4	682.0	15	4"x4	1023.1	31.7	4"x4
PFI-2418N-3D4BT-K2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-2418N-3D4BT-L2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-2418N-3D4BT-N2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-2418N-3D4BT-O2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-2418N-3D4BT-P2	Propylene Glycol	470.3	2.73	4"x4	376.2	1.81	4"x4	564.3	3.82	4"x4
PFI-2418N-4D4BT-K2	Propylene Glycol	470.3	3.41	4"x4	376.2	2.26	4"x4	564.3	4.77	4"x4
PFI-2418N-4D4BT-L2	Propylene Glycol	470.3	3.41	4"x4	376.2	2.26	4"x4	564.3	4.77	4"x4
PFI-2418N-4D3BT-M2	Propylene Glycol	463.7	3.83	4"x4	370.9	2.53	4"x4	556.4	5.36	4"x4
PFI-2418N-4D3BT-N2	Propylene Glycol	463.7	3.83	4"x4	370.9	2.53	4"x4	556.4	5.36	4"x4
PFI-2418N-4D3BT-O2	Propylene Glycol	463.7	3.83	4"x4	370.9	2.53	4"x4	556.4	5.36	4"x4
PFI-2418N-4D4BT-P2	Propylene Glycol	870.2	10.6	4"x4	696.1	7.04	4"x4	1044.2	14.9	4"x4
PFI-2418N-4D3BT-Q2	Propylene Glycol	863.6	12.1	4"x4	690.8	8	4"x4	1036.3	17	4"x4
PFI-2418N-5D2BT-K2	Propylene Glycol	458.2	5.19	4"x4	366.5	3.44	4"x4	549.8	7.27	4"x4
PFI-2418N-5D2BT-L2	Propylene Glycol	458.2	5.19	4"x4	366.5	3.44	4"x4	549.8	7.27	4"x4
PFI-2418N-5D2BT-M2	Propylene Glycol	458.2	5.19	4"x4	366.5	3.44	4"x4	549.8	7.27	4"x4
PFI-2418N-5D2BT-N2	Propylene Glycol	458.2	5.19	4"x4	366.5	3.44	4"x4	549.8	7.27	4"x4
PFI-2418N-5D3BT-O2	Propylene Glycol	863.6	14.5	4"x4	690.8	9.57	4"x4	1036.3	20.3	4"x4



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2418N-5D2BT-P2	Propylene Glycol	858.1	16.6	4"x4	686.4	11	4"x4	1029.7	23.2	4"x4
PFI-2418N-5D3BT-Q2	Propylene Glycol	863.6	14.5	4"x4	690.8	9.57	4"x4	1036.3	20.3	4"x4
PFI-2418N-6D1BT-K2	Propylene Glycol	452.7	7	4"x4	362.1	4.63	4"x4	543.2	9.8	4"x4
PFI-2418N-6D1BT-L2	Propylene Glycol	452.7	7	4"x4	362.1	4.63	4"x4	543.2	9.8	4"x4
PFI-2418N-6D1BT-M2	Propylene Glycol	452.7	7	4"x4	362.1	4.63	4"x4	543.2	9.8	4"x4
PFI-2418N-6D1BT-N2	Propylene Glycol	852.6	22.6	4"x4	682.0	14.9	4"x4	1023.1	31.6	4"x4
PFI-2418N-6D1BT-O2	Propylene Glycol	852.6	22.6	4"x4	682.0	14.9	4"x4	1023.1	31.6	4"x4
PFI-2418N-6D1BT-P2	Propylene Glycol	852.6	22.6	4"x4	682.0	14.9	4"x4	1023.1	31.6	4"x4
PFI-2418N-6D1BT-Q2	Propylene Glycol	852.6	22.6	4"x4	682.0	14.9	4"x4	1023.1	31.6	4"x4
PFI-2436N-2D1DS-M4	Propylene Glycol	2021.9	2	4"x8	1617.5	1.33	4"x8	2426.3	2.8	4"x8
PFI-2436N-2D4ES-M4	Propylene Glycol	2162.7	1.67	4"x8	1730.2	1.11	4"x8	2595.2	2.33	4"x8
PFI-2436N-2D1DS-N4	Propylene Glycol	2021.9	2	4"x8	1617.5	1.33	4"x8	2426.3	2.8	4"x8
PFI-2436N-2D2DS-N4	Propylene Glycol	2065.9	1.86	4"x8	1652.7	1.23	4"x8	2479.1	2.6	4"x8
PFI-2436N-2D3ES-N4	Propylene Glycol	2109.9	1.76	4"x8	1687.9	1.16	4"x8	2531.9	2.46	4"x8
PFI-2436N-2D2DS-O4	Propylene Glycol	2065.9	1.86	4"x8	1652.7	1.23	4"x8	2479.1	2.6	4"x8
PFI-2436N-2D3ES-O4	Propylene Glycol	2109.9	1.76	4"x8	1687.9	1.16	4"x8	2531.9	2.46	4"x8
PFI-2436N-2D4DS-P4	Propylene Glycol	2162.7	1.67	4"x8	1730.2	1.11	4"x8	2595.2	2.33	4"x8
PFI-2436N-3D1ES-K4	Propylene Glycol	2021.9	2.65	4"x8	1617.5	1.76	4"x8	2426.3	3.71	4"x8
PFI-2436N-3D1ES-L4	Propylene Glycol	2021.9	2.65	4"x8	1617.5	1.76	4"x8	2426.3	3.71	4"x8
PFI-2436N-3D4ES-M4	Propylene Glycol	2162.7	2.11	4"x8	1730.2	1.4	4"x8	2595.2	2.95	4"x8
PFI-2436N-3D1DS-N4	Propylene Glycol	2021.9	2.65	4"x8	1617.5	1.76	4"x8	2426.3	3.71	4"x8
PFI-2436N-3D1ES-N4	Propylene Glycol	2021.9	2.65	4"x8	1617.5	1.76	4"x8	2426.3	3.71	4"x8
PFI-2436N-3D1DS-O4	Propylene Glycol	2021.9	2.65	4"x8	1617.5	1.76	4"x8	2426.3	3.71	4"x8
PFI-2436N-3D2DS-O4	Propylene Glycol	2065.9	2.43	4"x8	1652.7	1.61	4"x8	2479.1	3.4	4"x8
PFI-2436N-3D1ES-O4	Propylene Glycol	3621.4	7.78	4"x8	2897.1	5.15	4"x8	4345.7	8.61	4"x16





## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-3D2DS-P4	Propylene Glycol	3665.4	7	4"x8	2932.3	4.63	4"x8	4398.5	7.47	4"x16
PFI-2436N-3D2ES-P4	Propylene Glycol	3665.4	7	4"x8	2932.3	4.63	4"x8	4398.5	7.47	4"x16
PFI-2436N-3D2DS-Q4	Propylene Glycol	3665.4	7	4"x8	2932.3	4.63	4"x8	4398.5	7.47	4"x16
PFI-2436N-3D4DS-Q4	Propylene Glycol	3762.2	4.37	4"x16	3009.8	3.88	4"x8	4514.7	6.12	4"x16
PFI-2436N-3D4ES-Q4	Propylene Glycol	3762.2	4.37	4"x16	3009.8	3.88	4"x8	4514.7	6.12	4"x16
PFI-2436N-3D1ES-R4	Propylene Glycol	3621.4	7.78	4"x8	2897.1	5.15	4"x8	4345.7	8.61	4"x16
PFI-2436N-3D4ES-R4	Propylene Glycol	3762.2	4.37	4"x16	3009.8	3.88	4"x8	4514.7	6.12	4"x16
PFI-2436N-4D1DS-K4	Propylene Glycol	2021.9	3.3	4"x8	1617.5	2.18	4"x8	2426.3	4.62	4"x8
PFI-2436N-4D1ES-L4	Propylene Glycol	2021.9	3.3	4"x8	1617.5	2.18	4"x8	2426.3	4.62	4"x8
PFI-2436N-4D2ES-M4	Propylene Glycol	3665.4	8.63	4"x8	2932.3	5.71	4"x8	4398.5	9.66	4"x16
PFI-2436N-4D2DS-N4	Propylene Glycol	3665.4	8.63	4"x8	2932.3	5.71	4"x8	4398.5	9.66	4"x16
PFI-2436N-4D1ES-N4	Propylene Glycol	3621.4	9.69	4"x8	2897.1	6.41	4"x8	4345.7	11.2	4"x16
PFI-2436N-4D3DS-O4	Propylene Glycol	3709.4	7.82	4"x8	2967.5	5.18	4"x8	4451.3	8.52	4"x16
PFI-2436N-4D1ES-O4	Propylene Glycol	3621.4	9.69	4"x8	2897.1	6.41	4"x8	4345.7	11.2	4"x16
PFI-2436N-4D1ES-P4	Propylene Glycol	3621.4	9.69	4"x8	2897.1	6.41	4"x8	4345.7	11.2	4"x16
PFI-2436N-4D1DS-Q4	Propylene Glycol	3621.4	9.69	4"x8	2897.1	6.41	4"x8	4345.7	11.2	4"x16
PFI-2436N-4D2ES-Q4	Propylene Glycol	3665.4	8.63	4"x8	2932.3	5.71	4"x8	4398.5	9.66	4"x16
PFI-2436N-4D4ES-Q4	Propylene Glycol	3762.2	5.31	4"x16	3009.8	4.69	4"x8	4514.7	7.44	4"x16
PFI-2436N-4D2ES-R4	Propylene Glycol	3665.4	8.63	4"x8	2932.3	5.71	4"x8	4398.5	9.66	4"x16
PFI-2436N-4D4ES-R4	Propylene Glycol	3762.2	5.31	4"x16	3009.8	4.69	4"x8	4514.7	7.44	4"x16
PFI-2436N-5D1DS-K4	Propylene Glycol	2021.9	3.95	4"x8	1617.5	2.61	4"x8	2426.3	5.53	4"x8
PFI-2436N-5D1ES-O4	Propylene Glycol	3621.4	11.6	4"x8	2897.1	7.67	4"x8	4345.7	13.8	4"x16
PFI-2436N-5D2ES-P4	Propylene Glycol	3665.4	10.3	4"x8	2932.3	6.79	4"x8	4398.5	11.9	4"x16
PFI-2436N-6D2DS-M4	Propylene Glycol	3665.4	11.9	4"x8	2932.3	7.87	4"x8	4398.5	14.1	4"x16
PFI-2436N-6D1DS-N4	Propylene Glycol	3621.4	13.5	4"x8	2897.1	8.94	4"x8	4345.7	16.3	4"x16



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-6D1DS-R4	Propylene Glycol	3621.4	13.5	4"x8	2897.1	8.94	4"x8	4345.7	16.3	4"x16
PFI-2436N-6D1ES-R4	Propylene Glycol	3621.4	13.5	4"x8	2897.1	8.94	4"x8	4345.7	16.3	4"x16
PFI-2436N-3D4BS-K4	Propylene Glycol	2162.7	2.11	4"x8	1730.2	1.4	4"x8	2595.2	2.95	4"x8
PFI-2436N-3D4BS-L4	Propylene Glycol	2162.7	2.11	4"x8	1730.2	1.4	4"x8	2595.2	2.95	4"x8
PFI-2436N-3D4BS-N4	Propylene Glycol	2162.7	2.11	4"x8	1730.2	1.4	4"x8	2595.2	2.95	4"x8
PFI-2436N-3D4BS-O4	Propylene Glycol	2162.7	2.11	4"x8	1730.2	1.4	4"x8	2595.2	2.95	4"x8
PFI-2436N-3D4BS-P4	Propylene Glycol	2162.7	2.11	4"x8	1730.2	1.4	4"x8	2595.2	2.95	4"x8
PFI-2436N-4D4BS-K4	Propylene Glycol	2162.7	2.55	4"x8	1730.2	1.69	4"x8	2595.2	3.57	4"x8
PFI-2436N-4D4BS-L4	Propylene Glycol	2162.7	2.55	4"x8	1730.2	1.69	4"x8	2595.2	3.57	4"x8
PFI-2436N-4D3BS-M4	Propylene Glycol	2109.9	2.76	4"x8	1687.9	1.83	4"x8	2531.9	3.86	4"x8
PFI-2436N-4D3BS-N4	Propylene Glycol	2109.9	2.76	4"x8	1687.9	1.83	4"x8	2531.9	3.86	4"x8
PFI-2436N-4D3BS-O4	Propylene Glycol	2109.9	2.76	4"x8	1687.9	1.83	4"x8	2531.9	3.86	4"x8
PFI-2436N-4D4BS-P4	Propylene Glycol	3762.2	5.31	4"x16	3009.8	4.69	4"x8	4514.7	7.44	4"x16
PFI-2436N-4D3BS-Q4	Propylene Glycol	3709.4	7.82	4"x8	2967.5	5.18	4"x8	4451.3	8.52	4"x16
PFI-2436N-5D2BS-K4	Propylene Glycol	2065.9	3.56	4"x8	1652.7	2.36	4"x8	2479.1	4.98	4"x8
PFI-2436N-5D2BS-L4	Propylene Glycol	2065.9	3.56	4"x8	1652.7	2.36	4"x8	2479.1	4.98	4"x8
PFI-2436N-5D2BS-M4	Propylene Glycol	2065.9	3.56	4"x8	1652.7	2.36	4"x8	2479.1	4.98	4"x8
PFI-2436N-5D2BS-N4	Propylene Glycol	2065.9	3.56	4"x8	1652.7	2.36	4"x8	2479.1	4.98	4"x8
PFI-2436N-5D3BS-O4	Propylene Glycol	2109.9	3.26	4"x8	1687.9	2.16	4"x8	2531.9	4.56	4"x8
PFI-2436N-5D2BS-P4	Propylene Glycol	2065.9	3.56	4"x8	1652.7	2.36	4"x8	2479.1	4.98	4"x8
PFI-2436N-5D3BS-Q4	Propylene Glycol	3709.4	9.24	4"x8	2967.5	6.12	4"x8	4451.3	10.4	4"x16
PFI-2436N-6D1BS-K4	Propylene Glycol	2021.9	4.6	4"x8	1617.5	3.04	4"x8	2426.3	6.44	4"x8
PFI-2436N-6D1BS-L4	Propylene Glycol	2021.9	4.6	4"x8	1617.5	3.04	4"x8	2426.3	6.44	4"x8
PFI-2436N-6D1BS-M4	Propylene Glycol	2021.9	4.6	4"x8	1617.5	3.04	4"x8	2426.3	6.44	4"x8
PFI-2436N-6D1BS-N4	Propylene Glycol	2021.9	4.6	4"x8	1617.5	3.04	4"x8	2426.3	6.44	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-6D1BS-O4	Propylene Glycol	3621.4	13.5	4"x8	2897.1	8.94	4"x8	4345.7	16.3	4"x16
PFI-2436N-6D1BS-P4	Propylene Glycol	3621.4	13.5	4"x8	2897.1	8.94	4"x8	4345.7	16.3	4"x16
PFI-2436N-6D1BS-Q4	Propylene Glycol	3621.4	13.5	4"x8	2897.1	8.94	4"x8	4345.7	16.3	4"x16
PFI-2436N-6D2BS-R4	Propylene Glycol	3665.4	11.9	4"x8	2932.3	7.87	4"x8	4398.5	14.1	4"x16
PFI-2436N-2D1DZ-M4	Propylene Glycol	905.4	2.78	4"x8	724.3	1.84	4"x8	1086.4	3.89	4"x8
PFI-2436N-2D4EZ-M4	Propylene Glycol	940.6	2.07	4"x8	752.4	1.37	4"x8	1128.7	2.9	4"x8
PFI-2436N-2D1DZ-N4	Propylene Glycol	905.4	2.78	4"x8	724.3	1.84	4"x8	1086.4	3.89	4"x8
PFI-2436N-2D2DZ-N4	Propylene Glycol	916.4	2.49	4"x8	733.1	1.65	4"x8	1099.6	3.48	4"x8
PFI-2436N-2D3EZ-N4	Propylene Glycol	927.4	2.27	4"x8	741.9	1.5	4"x8	1112.8	3.18	4"x8
PFI-2436N-2D2DZ-O4	Propylene Glycol	916.4	2.49	4"x8	733.1	1.65	4"x8	1099.6	3.48	4"x8
PFI-2436N-2D3EZ-O4	Propylene Glycol	927.4	2.27	4"x8	741.9	1.5	4"x8	1112.8	3.18	4"x8
PFI-2436N-2D4DZ-P4	Propylene Glycol	940.6	2.06	4"x8	752.4	1.37	4"x8	1128.7	2.89	4"x8
PFI-2436N-3D1EZ-K4	Propylene Glycol	905.4	3.85	4"x8	724.3	2.55	4"x8	1086.4	5.39	4"x8
PFI-2436N-3D1EZ-L4	Propylene Glycol	905.4	3.85	4"x8	724.3	2.55	4"x8	1086.4	5.39	4"x8
PFI-2436N-3D4EZ-M4	Propylene Glycol	1740.3	8.52	4"x8	1392.2	5.63	4"x8	2088.4	11.9	4"x8
PFI-2436N-3D1DZ-N4	Propylene Glycol	905.4	3.84	4"x8	724.3	2.54	4"x8	1086.4	5.37	4"x8
PFI-2436N-3D1EZ-N4	Propylene Glycol	1705.1	12.4	4"x8	1364.1	8.21	4"x8	2046.1	17.4	4"x8
PFI-2436N-3D1DZ-O4	Propylene Glycol	905.4	3.84	4"x8	724.3	2.54	4"x8	1086.4	5.37	4"x8
PFI-2436N-3D2DZ-O4	Propylene Glycol	1716.1	10.7	4"x8	1372.9	7.11	4"x8	2059.3	15.1	4"x8
PFI-2436N-3D1EZ-O4	Propylene Glycol	1705.1	12.4	4"x8	1364.1	8.21	4"x8	2046.1	17.4	4"x8
PFI-2436N-3D2DZ-P4	Propylene Glycol	1716.1	10.7	4"x8	1372.9	7.11	4"x8	2059.3	15.1	4"x8
PFI-2436N-3D2EZ-P4	Propylene Glycol	1716.1	10.8	4"x8	1372.9	7.14	4"x8	2059.3	15.1	4"x8
PFI-2436N-3D2DZ-Q4	Propylene Glycol	1716.1	10.7	4"x8	1372.9	7.11	4"x8	2059.3	15.1	4"x8
PFI-2436N-3D4DZ-Q4	Propylene Glycol	1740.3	8.47	4"x8	1392.2	5.6	4"x8	2088.4	11.9	4"x8
PFI-2436N-3D4EZ-Q4	Propylene Glycol	1740.3	8.52	4"x8	1392.2	5.63	4"x8	2088.4	11.9	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-3D1EZ-R4	Propylene Glycol	1705.1	12.4	4"x8	1364.1	8.21	4"x8	2046.1	17.4	4"x8
PFI-2436N-3D4EZ-R4	Propylene Glycol	1740.3	8.52	4"x8	1392.2	5.63	4"x8	2088.4	11.9	4"x8
PFI-2436N-4D1DZ-K4	Propylene Glycol	905.4	4.9	4"x8	724.3	3.24	4"x8	1086.4	6.86	4"x8
PFI-2436N-4D1EZ-L4	Propylene Glycol	1705.1	15.8	4"x8	1364.1	10.4	4"x8	2046.1	22.1	4"x8
PFI-2436N-4D2EZ-M4	Propylene Glycol	1716.1	13.7	4"x8	1372.9	9.07	4"x8	2059.3	19.2	4"x8
PFI-2436N-4D2DZ-N4	Propylene Glycol	1716.1	13.7	4"x8	1372.9	9.04	4"x8	2059.3	19.1	4"x8
PFI-2436N-4D1EZ-N4	Propylene Glycol	1705.1	15.8	4"x8	1364.1	10.4	4"x8	2046.1	22.1	4"x8
PFI-2436N-4D3DZ-O4	Propylene Glycol	1727.1	12.1	4"x8	1381.7	7.99	4"x8	2072.5	16.9	4"x8
PFI-2436N-4D1EZ-O4	Propylene Glycol	1705.1	15.8	4"x8	1364.1	10.4	4"x8	2046.1	22.1	4"x8
PFI-2436N-4D1EZ-P4	Propylene Glycol	1705.1	15.8	4"x8	1364.1	10.4	4"x8	2046.1	22.1	4"x8
PFI-2436N-4D1DZ-Q4	Propylene Glycol	1705.1	15.8	4"x8	1364.1	10.5	4"x8	2046.1	22.2	4"x8
PFI-2436N-4D2EZ-Q4	Propylene Glycol	1716.1	13.7	4"x8	1372.9	9.07	4"x8	2059.3	19.2	4"x8
PFI-2436N-4D4EZ-Q4	Propylene Glycol	1740.3	10.7	4"x8	1392.2	7.05	4"x8	2088.4	15	4"x8
PFI-2436N-4D2EZ-R4	Propylene Glycol	1716.1	13.7	4"x8	1372.9	9.07	4"x8	2059.3	19.2	4"x8
PFI-2436N-4D4EZ-R4	Propylene Glycol	1740.3	10.7	4"x8	1392.2	7.05	4"x8	2088.4	15	4"x8
PFI-2436N-5D1DZ-K4	Propylene Glycol	905.4	5.96	4"x8	724.3	3.95	4"x8	1086.4	8.35	4"x8
PFI-2436N-5D1EZ-O4	Propylene Glycol	1705.1	19.2	4"x8	1364.1	12.7	4"x8	2046.1	26.8	4"x8
PFI-2436N-5D2EZ-P4	Propylene Glycol	1716.1	16.6	4"x8	1372.9	11	4"x8	2059.3	23.3	4"x8
PFI-2436N-6D2DZ-M4	Propylene Glycol	1716.1	19.5	4"x8	1372.9	12.9	4"x8	2059.3	27.3	4"x8
PFI-2436N-6D1DZ-N4	Propylene Glycol	1705.1	22.6	4"x8	1364.1	15	4"x8	2046.1	31.7	4"x8
PFI-2436N-6D1DZ-R4	Propylene Glycol	1705.1	22.6	4"x8	1364.1	15	4"x8	2046.1	31.7	4"x8
PFI-2436N-6D1EZ-R4	Propylene Glycol	1705.1	22.6	4"x8	1364.1	15	4"x8	2046.1	31.7	4"x8
PFI-2436N-3D4BT-K4	Propylene Glycol	940.6	2.73	4"x8	752.4	1.81	4"x8	1128.7	3.82	4"x8
PFI-2436N-3D4BT-L4	Propylene Glycol	940.6	2.73	4"x8	752.4	1.81	4"x8	1128.7	3.82	4"x8
PFI-2436N-3D4BT-N4	Propylene Glycol	940.6	2.73	4"x8	752.4	1.81	4"x8	1128.7	3.82	4"x8



## PFI Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
PFI-2436N-3D4BT-O4	Propylene Glycol	940.6	2.73	4"x8	752.4	1.81	4"x8	1128.7	3.82	4"x8
PFI-2436N-3D4BT-P4	Propylene Glycol	940.6	2.73	4"x8	752.4	1.81	4"x8	1128.7	3.82	4"x8
PFI-2436N-4D4BT-K4	Propylene Glycol	940.6	3.41	4"x8	752.4	2.26	4"x8	1128.7	4.77	4"x8
PFI-2436N-4D4BT-L4	Propylene Glycol	940.6	3.41	4"x8	752.4	2.26	4"x8	1128.7	4.77	4"x8
PFI-2436N-4D3BT-M4	Propylene Glycol	927.4	3.83	4"x8	741.9	2.53	4"x8	1112.8	5.36	4"x8
PFI-2436N-4D3BT-N4	Propylene Glycol	927.4	3.83	4"x8	741.9	2.53	4"x8	1112.8	5.36	4"x8
PFI-2436N-4D3BT-O4	Propylene Glycol	927.4	3.83	4"x8	741.9	2.53	4"x8	1112.8	5.36	4"x8
PFI-2436N-4D4BT-P4	Propylene Glycol	1740.3	10.6	4"x8	1392.2	7.04	4"x8	2088.4	14.9	4"x8
PFI-2436N-4D3BT-Q4	Propylene Glycol	1727.1	12.1	4"x8	1381.7	8	4"x8	2072.5	17	4"x8
PFI-2436N-5D2BT-K4	Propylene Glycol	916.4	5.19	4"x8	733.1	3.44	4"x8	1099.6	7.27	4"x8
PFI-2436N-5D2BT-L4	Propylene Glycol	916.4	5.19	4"x8	733.1	3.44	4"x8	1099.6	7.27	4"x8
PFI-2436N-5D2BT-M4	Propylene Glycol	916.4	5.19	4"x8	733.1	3.44	4"x8	1099.6	7.27	4"x8
PFI-2436N-5D2BT-N4	Propylene Glycol	916.4	5.19	4"x8	733.1	3.44	4"x8	1099.6	7.27	4"x8
PFI-2436N-5D3BT-O4	Propylene Glycol	927.4	4.58	4"x8	741.9	3.03	4"x8	1112.8	6.41	4"x8
PFI-2436N-5D2BT-P4	Propylene Glycol	1716.1	16.6	4"x8	1372.9	11	4"x8	2059.3	23.2	4"x8
PFI-2436N-5D3BT-Q4	Propylene Glycol	1727.1	14.5	4"x8	1381.7	9.57	4"x8	2072.5	20.3	4"x8
PFI-2436N-6D1BT-K4	Propylene Glycol	905.4	7	4"x8	724.3	4.63	4"x8	1086.4	9.8	4"x8
PFI-2436N-6D1BT-L4	Propylene Glycol	905.4	7	4"x8	724.3	4.63	4"x8	1086.4	9.8	4"x8
PFI-2436N-6D1BT-M4	Propylene Glycol	905.4	7	4"x8	724.3	4.63	4"x8	1086.4	9.8	4"x8
PFI-2436N-6D1BT-N4	Propylene Glycol	1705.1	22.6	4"x8	1364.1	14.9	4"x8	2046.1	31.6	4"x8
PFI-2436N-6D1BT-O4	Propylene Glycol	1705.1	22.6	4"x8	1364.1	14.9	4"x8	2046.1	31.6	4"x8
PFI-2436N-6D1BT-P4	Propylene Glycol	1705.1	22.6	4"x8	1364.1	14.9	4"x8	2046.1	31.6	4"x8
PFI-2436N-6D1BT-Q4	Propylene Glycol	1705.1	22.6	4"x8	1364.1	14.9	4"x8	2046.1	31.6	4"x8