



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-20D-10	Water	935.8	3.62	4"x4	748.6	3.45	4"x2	1122.9	5.06	4"x4
FXV3-1224-20D-15	Water	935.8	3.62	4"x4	748.6	3.45	4"x2	1122.9	5.06	4"x4
FXV3-1224-20D-20	Water	935.8	3.62	4"x4	748.6	3.45	4"x2	1122.9	5.06	4"x4
FXV3-1224-20D-25	Water	1335.6	6.98	4"x4	1068.5	4.62	4"x4	1602.8	8.92	4"x6
FXV3-1224-20D-30	Water	1335.6	6.98	4"x4	1068.5	4.62	4"x4	1602.8	8.92	4"x6
FXV3-1224-20D-40	Water	1335.6	6.98	4"x4	1068.5	4.62	4"x4	1602.8	8.92	4"x6
FXV3-1224-20D-50	Water	1335.6	6.98	4"x4	1068.5	4.62	4"x4	1602.8	8.92	4"x6
FXV3-1224-20D-60	Water	1335.6	6.98	4"x4	1068.5	4.62	4"x4	1602.8	8.92	4"x6
FXV3-1224-20D-75	Water	1335.6	6.98	4"x4	1068.5	4.62	4"x4	1602.8	8.92	4"x6
FXV3-1224-24D-10	Water	935.8	4.22	4"x4	748.6	3.86	4"x2	1122.9	5.91	4"x4
FXV3-1224-24D-15	Water	935.8	4.22	4"x4	748.6	3.86	4"x2	1122.9	5.91	4"x4
FXV3-1224-24D-20	Water	935.8	4.22	4"x4	748.6	3.86	4"x2	1122.9	5.91	4"x4
FXV3-1224-24D-25	Water	1335.6	8.14	4"x4	1068.5	5.39	4"x4	1602.8	10.54	4"x6
FXV3-1224-24D-30	Water	1335.6	8.14	4"x4	1068.5	5.39	4"x4	1602.8	10.54	4"x6
FXV3-1224-24D-40	Water	1335.6	8.14	4"x4	1068.5	5.39	4"x4	1602.8	10.54	4"x6
FXV3-1224-24D-50	Water	1335.6	8.14	4"x4	1068.5	5.39	4"x4	1602.8	10.54	4"x6
FXV3-1224-24D-60	Water	1335.6	8.14	4"x4	1068.5	5.39	4"x4	1602.8	10.54	4"x6
FXV3-1224-24D-75	Water	1335.6	8.14	4"x4	1068.5	5.39	4"x4	1602.8	10.54	4"x6
FXV3-1224-24T-10	Water	1103.7	2.19	6"x2	883.0	1.45	6"x2	1324.5	3.06	6"x2
FXV3-1224-24T-15	Water	1103.7	2.19	6"x2	883.0	1.45	6"x2	1324.5	3.06	6"x2
FXV3-1224-24T-20	Water	1103.7	2.19	6"x2	883.0	1.45	6"x2	1324.5	3.06	6"x2
FXV3-1224-24T-25	Water	1103.7	2.19	6"x2	883.0	1.45	6"x2	1324.5	3.06	6"x2
FXV3-1224-24T-30	Water	1103.7	2.19	6"x2	883.0	1.45	6"x2	1324.5	3.06	6"x2
FXV3-1224-24T-40	Water	1103.7	2.19	6"x2	883.0	1.45	6"x2	1324.5	3.06	6"x2
FXV3-1224-24T-50	Water	1803.5	4.39	8"x2	1442.8	3.58	6"x2	2164.2	6.14	8"x2
FXV3-1224-24T-60	Water	1803.5	4.39	8"x2	1442.8	3.58	6"x2	2164.2	6.14	8"x2
FXV3-1224-24T-75	Water	1803.5	4.39	8"x2	1442.8	3.58	6"x2	2164.2	6.14	8"x2
FXV3-1224-24Q-10	Water	1171.7	1.47	6"x2	937.4	0.98	6"x2	1406.1	2.06	6"x2
FXV3-1224-24Q-15	Water	1171.7	1.47	6"x2	937.4	0.98	6"x2	1406.1	2.06	6"x2
FXV3-1224-24Q-20	Water	1171.7	1.47	6"x2	937.4	0.98	6"x2	1406.1	2.06	6"x2
FXV3-1224-24Q-25	Water	1171.7	1.47	6"x2	937.4	0.98	6"x2	1406.1	2.06	6"x2
FXV3-1224-24Q-30	Water	1171.7	1.47	6"x2	937.4	0.98	6"x2	1406.1	2.06	6"x2
FXV3-1224-24Q-40	Water	1171.7	1.47	6"x2	937.4	0.98	6"x2	1406.1	2.06	6"x2
FXV3-1224-24Q-50	Water	1171.7	1.47	6"x2	937.4	0.98	6"x2	1406.1	2.06	6"x2
FXV3-1224-24Q-60	Water	1871.5	2.40	8"x2	1497.2	2.31	6"x2	2245.8	3.35	8"x2
FXV3-1224-24Q-75	Water	1871.5	2.40	8"x2	1497.2	2.31	6"x2	2245.8	3.35	8"x2
FXV3-1224-28D-10	Water	935.8	4.82	4"x4	748.6	4.27	4"x2	1122.9	6.75	4"x4
FXV3-1224-28D-15	Water	935.8	4.82	4"x4	748.6	4.27	4"x2	1122.9	6.75	4"x4
FXV3-1224-28D-20	Water	1335.6	9.30	4"x4	1068.5	6.16	4"x4	1602.8	12.17	4"x6
FXV3-1224-28D-25	Water	1335.6	9.30	4"x4	1068.5	6.16	4"x4	1602.8	12.17	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-28D-30	Water	1335.6	9.30	4"x4	1068.5	6.16	4"x4	1602.8	12.17	4"x6
FXV3-1224-28D-40	Water	1335.6	9.30	4"x4	1068.5	6.16	4"x4	1602.8	12.17	4"x6
FXV3-1224-28D-50	Water	1335.6	9.30	4"x4	1068.5	6.16	4"x4	1602.8	12.17	4"x6
FXV3-1224-28D-60	Water	1335.6	9.30	4"x4	1068.5	6.16	4"x4	1602.8	12.17	4"x6
FXV3-1224-28D-75	Water	1335.6	9.30	4"x4	1068.5	6.16	4"x4	1602.8	12.17	4"x6
FXV3-1224-30T-10	Water	1103.7	2.57	6"x2	883.0	1.70	6"x2	1324.5	3.60	6"x2
FXV3-1224-30T-15	Water	1103.7	2.57	6"x2	883.0	1.70	6"x2	1324.5	3.60	6"x2
FXV3-1224-30T-20	Water	1103.7	2.57	6"x2	883.0	1.70	6"x2	1324.5	3.60	6"x2
FXV3-1224-30T-25	Water	1103.7	2.57	6"x2	883.0	1.70	6"x2	1324.5	3.60	6"x2
FXV3-1224-30T-30	Water	1803.5	5.35	8"x2	1442.8	4.22	6"x2	2164.2	7.49	8"x2
FXV3-1224-30T-40	Water	1803.5	5.35	8"x2	1442.8	4.22	6"x2	2164.2	7.49	8"x2
FXV3-1224-30T-50	Water	1803.5	5.35	8"x2	1442.8	4.22	6"x2	2164.2	7.49	8"x2
FXV3-1224-30T-60	Water	1803.5	5.35	8"x2	1442.8	4.22	6"x2	2164.2	7.49	8"x2
FXV3-1224-30T-75	Water	1803.5	5.35	8"x2	1442.8	4.22	6"x2	2164.2	7.49	8"x2
FXV3-1224-32D-10	Water	935.8	5.42	4"x4	748.6	4.67	4"x2	1122.9	7.59	4"x4
FXV3-1224-32D-15	Water	935.8	5.42	4"x4	748.6	4.67	4"x2	1122.9	7.59	4"x4
FXV3-1224-32D-20	Water	1335.6	10.46	4"x4	1068.5	6.93	4"x4	1602.8	13.79	4"x6
FXV3-1224-32D-25	Water	1335.6	10.46	4"x4	1068.5	6.93	4"x4	1602.8	13.79	4"x6
FXV3-1224-32D-30	Water	1335.6	10.46	4"x4	1068.5	6.93	4"x4	1602.8	13.79	4"x6
FXV3-1224-32D-40	Water	1335.6	10.46	4"x4	1068.5	6.93	4"x4	1602.8	13.79	4"x6
FXV3-1224-32D-50	Water	1335.6	10.46	4"x4	1068.5	6.93	4"x4	1602.8	13.79	4"x6
FXV3-1224-32D-60	Water	1335.6	10.46	4"x4	1068.5	6.93	4"x4	1602.8	13.79	4"x6
FXV3-1224-32D-75	Water	1335.6	10.46	4"x4	1068.5	6.93	4"x4	1602.8	13.79	4"x6
FXV3-1224-32Q-10	Water	1171.7	1.73	6"x2	937.4	1.15	6"x2	1406.1	2.42	6"x2
FXV3-1224-32Q-15	Water	1171.7	1.73	6"x2	937.4	1.15	6"x2	1406.1	2.42	6"x2
FXV3-1224-32Q-20	Water	1171.7	1.73	6"x2	937.4	1.15	6"x2	1406.1	2.42	6"x2
FXV3-1224-32Q-25	Water	1171.7	1.73	6"x2	937.4	1.15	6"x2	1406.1	2.42	6"x2
FXV3-1224-32Q-30	Water	1171.7	1.73	6"x2	937.4	1.15	6"x2	1406.1	2.42	6"x2
FXV3-1224-32Q-40	Water	1871.5	3.01	8"x2	1497.2	2.72	6"x2	2245.8	4.21	8"x2
FXV3-1224-32Q-50	Water	1871.5	3.01	8"x2	1497.2	2.72	6"x2	2245.8	4.21	8"x2
FXV3-1224-32Q-60	Water	1871.5	3.01	8"x2	1497.2	2.72	6"x2	2245.8	4.21	8"x2
FXV3-1224-32Q-75	Water	1871.5	3.01	8"x2	1497.2	2.72	6"x2	2245.8	4.21	8"x2
FXV3-1224-36D-10	Water	935.8	6.02	4"x4	748.6	5.08	4"x2	1122.9	8.43	4"x4
FXV3-1224-36D-15	Water	1335.6	11.62	4"x4	1068.5	7.69	4"x4	1602.8	15.42	4"x6
FXV3-1224-36D-20	Water	1335.6	11.62	4"x4	1068.5	7.69	4"x4	1602.8	15.42	4"x6
FXV3-1224-36D-25	Water	1335.6	11.62	4"x4	1068.5	7.69	4"x4	1602.8	15.42	4"x6
FXV3-1224-36D-30	Water	1335.6	11.62	4"x4	1068.5	7.69	4"x4	1602.8	15.42	4"x6
FXV3-1224-36D-40	Water	1335.6	11.62	4"x4	1068.5	7.69	4"x4	1602.8	15.42	4"x6
FXV3-1224-36D-50	Water	1335.6	11.62	4"x4	1068.5	7.69	4"x4	1602.8	15.42	4"x6
FXV3-1224-36D-60	Water	1335.6	11.62	4"x4	1068.5	7.69	4"x4	1602.8	15.42	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-36D-75	Water	1335.6	11.62	4"x4	1068.5	7.69	4"x4	1602.8	15.42	4"x6
FXV3-1224-36T-10	Water	1103.7	2.96	6"x2	883.0	1.96	6"x2	1324.5	4.14	6"x2
FXV3-1224-36T-15	Water	1103.7	2.96	6"x2	883.0	1.96	6"x2	1324.5	4.14	6"x2
FXV3-1224-36T-20	Water	1103.7	2.96	6"x2	883.0	1.96	6"x2	1324.5	4.14	6"x2
FXV3-1224-36T-25	Water	1803.5	6.31	8"x2	1442.8	4.86	6"x2	2164.2	8.83	8"x2
FXV3-1224-36T-30	Water	1803.5	6.31	8"x2	1442.8	4.86	6"x2	2164.2	8.83	8"x2
FXV3-1224-36T-40	Water	1803.5	6.31	8"x2	1442.8	4.86	6"x2	2164.2	8.83	8"x2
FXV3-1224-36T-50	Water	1803.5	6.31	8"x2	1442.8	4.86	6"x2	2164.2	8.83	8"x2
FXV3-1224-36T-60	Water	1803.5	6.31	8"x2	1442.8	4.86	6"x2	2164.2	8.83	8"x2
FXV3-1224-36T-75	Water	1803.5	6.31	8"x2	1442.8	4.86	6"x2	2164.2	8.83	8"x2
FXV3-1224-36Q-10	Water	1171.7	1.86	6"x2	937.4	1.23	6"x2	1406.1	2.60	6"x2
FXV3-1224-36Q-15	Water	1171.7	1.86	6"x2	937.4	1.23	6"x2	1406.1	2.60	6"x2
FXV3-1224-36Q-20	Water	1171.7	1.86	6"x2	937.4	1.23	6"x2	1406.1	2.60	6"x2
FXV3-1224-36Q-25	Water	1171.7	1.86	6"x2	937.4	1.23	6"x2	1406.1	2.60	6"x2
FXV3-1224-36Q-30	Water	1871.5	3.31	8"x2	1497.2	2.92	6"x2	2245.8	4.64	8"x2
FXV3-1224-36Q-40	Water	1871.5	3.31	8"x2	1497.2	2.92	6"x2	2245.8	4.64	8"x2
FXV3-1224-36Q-50	Water	1871.5	3.31	8"x2	1497.2	2.92	6"x2	2245.8	4.64	8"x2
FXV3-1224-36Q-60	Water	1871.5	3.31	8"x2	1497.2	2.92	6"x2	2245.8	4.64	8"x2
FXV3-1224-36Q-75	Water	1871.5	3.31	8"x2	1497.2	2.92	6"x2	2245.8	4.64	8"x2
FXV-288-31M	Water	949.8	3.73	4"x4	759.8	3.44	4"x2	1139.7	5.22	4"x4
FXV-288-31N	Water	1349.6	7.14	4"x4	1079.7	4.73	4"x4	1619.6	9.24	4"x6
FXV-288-31O	Water	1349.6	7.14	4"x4	1079.7	4.73	4"x4	1619.6	9.24	4"x6
FXV-288-31P	Water	1349.6	7.14	4"x4	1079.7	4.73	4"x4	1619.6	9.24	4"x6
FXV-288-31Q	Water	1349.6	7.14	4"x4	1079.7	4.73	4"x4	1619.6	9.24	4"x6
FXV-288-31R	Water	1349.6	7.14	4"x4	1079.7	4.73	4"x4	1619.6	9.24	4"x6
FXV-288-41M	Water	949.8	4.37	4"x4	759.8	3.92	4"x2	1139.7	6.12	4"x4
FXV-288-41N	Water	1349.6	8.37	4"x4	1079.7	5.54	4"x4	1619.6	10.96	4"x6
FXV-288-41O	Water	1349.6	8.37	4"x4	1079.7	5.54	4"x4	1619.6	10.96	4"x6
FXV-288-41P	Water	1349.6	8.37	4"x4	1079.7	5.54	4"x4	1619.6	10.96	4"x6
FXV-288-41Q	Water	1349.6	8.37	4"x4	1079.7	5.54	4"x4	1619.6	10.96	4"x6
FXV-288-41R	Water	1349.6	8.37	4"x4	1079.7	5.54	4"x4	1619.6	10.96	4"x6
FXV-288-2TM	Water	1124.7	2.25	6"x2	899.8	1.49	6"x2	1349.7	3.15	6"x2
FXV-288-2TN	Water	1124.7	2.25	6"x2	899.8	1.49	6"x2	1349.7	3.15	6"x2
FXV-288-2TO	Water	1124.7	2.25	6"x2	899.8	1.49	6"x2	1349.7	3.15	6"x2
FXV-288-2TP	Water	1124.7	2.25	6"x2	899.8	1.49	6"x2	1349.7	3.15	6"x2
FXV-288-2TQ	Water	1824.5	4.53	8"x2	1459.6	3.64	6"x2	2189.4	6.34	8"x2
FXV-288-2TR	Water	1824.5	4.53	8"x2	1459.6	3.64	6"x2	2189.4	6.34	8"x2
FXV-288-1QM	Water	1199.7	1.49	6"x2	959.8	0.99	6"x2	1439.7	2.09	6"x2
FXV-288-1QN	Water	1199.7	1.49	6"x2	959.8	0.99	6"x2	1439.7	2.09	6"x2
FXV-288-1QO	Water	1199.7	1.49	6"x2	959.8	0.99	6"x2	1439.7	2.09	6"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV-288-1QP	Water	1199.7	1.49	6"x2	959.8	0.99	6"x2	1439.7	2.09	6"x2
FXV-288-1QQ	Water	1199.7	1.49	6"x2	959.8	0.99	6"x2	1439.7	2.09	6"x2
FXV-288-1QR	Water	1899.5	2.45	8"x2	1519.6	2.31	6"x2	2279.4	3.42	8"x2
FXV3-1426-20D-15	Water	935.8	4.06	4"x4	748.6	3.75	4"x2	1122.9	5.69	4"x4
FXV3-1426-20D-20	Water	1335.6	7.84	4"x4	1068.5	5.19	4"x4	1602.8	10.13	4"x6
FXV3-1426-20D-25	Water	1335.6	7.84	4"x4	1068.5	5.19	4"x4	1602.8	10.13	4"x6
FXV3-1426-20D-30	Water	1335.6	7.84	4"x4	1068.5	5.19	4"x4	1602.8	10.13	4"x6
FXV3-1426-20D-40	Water	1335.6	7.84	4"x4	1068.5	5.19	4"x4	1602.8	10.13	4"x6
FXV3-1426-20D-50	Water	1335.6	7.84	4"x4	1068.5	5.19	4"x4	1602.8	10.13	4"x6
FXV3-1426-20D-60	Water	1335.6	7.84	4"x4	1068.5	5.19	4"x4	1602.8	10.13	4"x6
FXV3-1426-20D-75	Water	1335.6	7.84	4"x4	1068.5	5.19	4"x4	1602.8	10.13	4"x6
FXV3-1426-20D-100	Water	1335.6	7.84	4"x4	1068.5	5.19	4"x4	1602.8	10.13	4"x6
FXV3-1426-24D-15	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24D-20	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24D-25	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24D-30	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24D-40	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24D-50	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24D-60	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24D-75	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24D-100	Water	1335.6	9.18	4"x4	1068.5	6.08	4"x4	1602.8	11.99	4"x6
FXV3-1426-24T-15	Water	1103.7	2.42	6"x2	883.0	1.60	6"x2	1324.5	3.38	6"x2
FXV3-1426-24T-20	Water	1103.7	2.42	6"x2	883.0	1.60	6"x2	1324.5	3.38	6"x2
FXV3-1426-24T-25	Water	1803.5	4.96	8"x2	1442.8	3.96	6"x2	2164.2	6.94	8"x2
FXV3-1426-24T-30	Water	1803.5	4.96	8"x2	1442.8	3.96	6"x2	2164.2	6.94	8"x2
FXV3-1426-24T-40	Water	1803.5	4.96	8"x2	1442.8	3.96	6"x2	2164.2	6.94	8"x2
FXV3-1426-24T-50	Water	1803.5	4.96	8"x2	1442.8	3.96	6"x2	2164.2	6.94	8"x2
FXV3-1426-24T-60	Water	1803.5	4.96	8"x2	1442.8	3.96	6"x2	2164.2	6.94	8"x2
FXV3-1426-24T-75	Water	1803.5	4.96	8"x2	1442.8	3.96	6"x2	2164.2	6.94	8"x2
FXV3-1426-24T-100	Water	1803.5	4.96	8"x2	1442.8	3.96	6"x2	2164.2	6.94	8"x2
FXV3-1426-24Q-15	Water	1171.7	1.59	6"x2	937.4	1.05	6"x2	1406.1	2.22	6"x2
FXV3-1426-24Q-20	Water	1171.7	1.59	6"x2	937.4	1.05	6"x2	1406.1	2.22	6"x2
FXV3-1426-24Q-25	Water	1171.7	1.59	6"x2	937.4	1.05	6"x2	1406.1	2.22	6"x2
FXV3-1426-24Q-30	Water	1871.5	2.67	8"x2	1497.2	2.49	6"x2	2245.8	3.74	8"x2
FXV3-1426-24Q-40	Water	1871.5	2.67	8"x2	1497.2	2.49	6"x2	2245.8	3.74	8"x2
FXV3-1426-24Q-50	Water	1871.5	2.67	8"x2	1497.2	2.49	6"x2	2245.8	3.74	8"x2
FXV3-1426-24Q-60	Water	1871.5	2.67	8"x2	1497.2	2.49	6"x2	2245.8	3.74	8"x2
FXV3-1426-24Q-75	Water	1871.5	2.67	8"x2	1497.2	2.49	6"x2	2245.8	3.74	8"x2
FXV3-1426-24Q-100	Water	1871.5	2.67	8"x2	1497.2	2.49	6"x2	2245.8	3.74	8"x2
FXV3-1426-28D-15	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-28D-20	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6
FXV3-1426-28D-25	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6
FXV3-1426-28D-30	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6
FXV3-1426-28D-40	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6
FXV3-1426-28D-50	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6
FXV3-1426-28D-60	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6
FXV3-1426-28D-75	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6
FXV3-1426-28D-100	Water	1335.6	10.51	4"x4	1068.5	6.96	4"x4	1602.8	13.86	4"x6
FXV3-1426-30T-15	Water	1103.7	2.86	6"x2	883.0	1.89	6"x2	1324.5	4.00	6"x2
FXV3-1426-30T-20	Water	1803.5	6.06	8"x2	1442.8	4.69	6"x2	2164.2	8.49	8"x2
FXV3-1426-30T-25	Water	1803.5	6.06	8"x2	1442.8	4.69	6"x2	2164.2	8.49	8"x2
FXV3-1426-30T-30	Water	1803.5	6.06	8"x2	1442.8	4.69	6"x2	2164.2	8.49	8"x2
FXV3-1426-30T-40	Water	1803.5	6.06	8"x2	1442.8	4.69	6"x2	2164.2	8.49	8"x2
FXV3-1426-30T-50	Water	1803.5	6.06	8"x2	1442.8	4.69	6"x2	2164.2	8.49	8"x2
FXV3-1426-30T-60	Water	1803.5	6.06	8"x2	1442.8	4.69	6"x2	2164.2	8.49	8"x2
FXV3-1426-30T-75	Water	1803.5	6.06	8"x2	1442.8	4.69	6"x2	2164.2	8.49	8"x2
FXV3-1426-30T-100	Water	1803.5	6.06	8"x2	1442.8	4.69	6"x2	2164.2	8.49	8"x2
FXV3-1426-32D-15	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32D-20	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32D-25	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32D-30	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32D-40	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32D-50	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32D-60	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32D-75	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32D-100	Water	1335.6	11.84	4"x4	1068.5	7.84	4"x4	1602.8	15.73	4"x6
FXV3-1426-32Q-15	Water	1171.7	1.88	6"x2	937.4	1.25	6"x2	1406.1	2.64	6"x2
FXV3-1426-32Q-20	Water	1871.5	3.37	8"x2	1497.2	2.96	6"x2	2245.8	4.72	8"x2
FXV3-1426-32Q-25	Water	1871.5	3.37	8"x2	1497.2	2.96	6"x2	2245.8	4.72	8"x2
FXV3-1426-32Q-30	Water	1871.5	3.37	8"x2	1497.2	2.96	6"x2	2245.8	4.72	8"x2
FXV3-1426-32Q-40	Water	1871.5	3.37	8"x2	1497.2	2.96	6"x2	2245.8	4.72	8"x2
FXV3-1426-32Q-50	Water	1871.5	3.37	8"x2	1497.2	2.96	6"x2	2245.8	4.72	8"x2
FXV3-1426-32Q-60	Water	1871.5	3.37	8"x2	1497.2	2.96	6"x2	2245.8	4.72	8"x2
FXV3-1426-32Q-75	Water	1871.5	3.37	8"x2	1497.2	2.96	6"x2	2245.8	4.72	8"x2
FXV3-1426-32Q-100	Water	1871.5	3.37	8"x2	1497.2	2.96	6"x2	2245.8	4.72	8"x2
FXV3-1426-36D-15	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6
FXV3-1426-36D-20	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6
FXV3-1426-36D-25	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6
FXV3-1426-36D-30	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6
FXV3-1426-36D-40	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-36D-50	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6
FXV3-1426-36D-60	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6
FXV3-1426-36D-75	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6
FXV3-1426-36D-100	Water	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.59	4"x6
FXV3-1426-36T-15	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36T-20	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36T-25	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36T-30	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36T-40	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36T-50	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36T-60	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36T-75	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36T-100	Water	1803.5	7.17	8"x2	1442.8	5.42	6"x2	2164.2	10.04	8"x2
FXV3-1426-36Q-15	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV3-1426-36Q-20	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV3-1426-36Q-25	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV3-1426-36Q-30	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV3-1426-36Q-40	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV3-1426-36Q-50	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV3-1426-36Q-60	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV3-1426-36Q-75	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV3-1426-36Q-100	Water	1871.5	3.72	8"x2	1497.2	3.19	6"x2	2245.8	5.21	8"x2
FXV-364-31N	Water	1349.6	8.06	4"x4	1079.7	5.34	4"x4	1619.6	10.43	4"x6
FXV-364-31O	Water	1349.6	8.06	4"x4	1079.7	5.34	4"x4	1619.6	10.43	4"x6
FXV-364-31P	Water	1349.6	8.06	4"x4	1079.7	5.34	4"x4	1619.6	10.43	4"x6
FXV-364-31Q	Water	1349.6	8.06	4"x4	1079.7	5.34	4"x4	1619.6	10.43	4"x6
FXV-364-31R	Water	1349.6	8.06	4"x4	1079.7	5.34	4"x4	1619.6	10.43	4"x6
FXV-364-31S	Water	1349.6	8.06	4"x4	1079.7	5.34	4"x4	1619.6	10.43	4"x6
FXV-364-41N	Water	1349.6	9.44	4"x4	1079.7	6.25	4"x4	1619.6	12.36	4"x6
FXV-364-41O	Water	1349.6	9.44	4"x4	1079.7	6.25	4"x4	1619.6	12.36	4"x6
FXV-364-41P	Water	1349.6	9.44	4"x4	1079.7	6.25	4"x4	1619.6	12.36	4"x6
FXV-364-41Q	Water	1349.6	9.44	4"x4	1079.7	6.25	4"x4	1619.6	12.36	4"x6
FXV-364-41R	Water	1349.6	9.44	4"x4	1079.7	6.25	4"x4	1619.6	12.36	4"x6
FXV-364-41S	Water	1349.6	9.44	4"x4	1079.7	6.25	4"x4	1619.6	12.36	4"x6
FXV-364-2TN	Water	1824.5	5.07	8"x2	1459.6	4.07	6"x2	2189.4	7.10	8"x2
FXV-364-2TO	Water	1824.5	5.07	8"x2	1459.6	4.07	6"x2	2189.4	7.10	8"x2
FXV-364-2TP	Water	1824.5	5.07	8"x2	1459.6	4.07	6"x2	2189.4	7.10	8"x2
FXV-364-2TQ	Water	1824.5	5.07	8"x2	1459.6	4.07	6"x2	2189.4	7.10	8"x2
FXV-364-2TR	Water	1824.5	5.07	8"x2	1459.6	4.07	6"x2	2189.4	7.10	8"x2
FXV-364-2TS	Water	1824.5	5.07	8"x2	1459.6	4.07	6"x2	2189.4	7.10	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV-364-1QN	Water	1199.7	1.64	6"x2	959.8	1.09	6"x2	1439.7	2.30	6"x2
FXV-364-1QO	Water	1899.5	2.79	8"x2	1519.6	2.54	6"x2	2279.4	3.90	8"x2
FXV-364-1QP	Water	1899.5	2.79	8"x2	1519.6	2.54	6"x2	2279.4	3.90	8"x2
FXV-364-1QQ	Water	1899.5	2.79	8"x2	1519.6	2.54	6"x2	2279.4	3.90	8"x2
FXV-364-1QR	Water	1899.5	2.79	8"x2	1519.6	2.54	6"x2	2279.4	3.90	8"x2
FXV-364-1QS	Water	1899.5	2.79	8"x2	1519.6	2.54	6"x2	2279.4	3.90	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-20D-10	30% Ethylene Glycol	935.8	4.10	4"x4	748.6	3.91	4"x2	1122.9	5.74	4"x4
FXV3-1224-20D-15	30% Ethylene Glycol	935.8	4.10	4"x4	748.6	3.91	4"x2	1122.9	5.74	4"x4
FXV3-1224-20D-20	30% Ethylene Glycol	935.8	4.10	4"x4	748.6	3.91	4"x2	1122.9	5.74	4"x4
FXV3-1224-20D-25	30% Ethylene Glycol	935.8	4.10	4"x4	748.6	3.91	4"x4	1122.9	5.74	4"x6
FXV3-1224-20D-30	30% Ethylene Glycol	1335.6	7.91	4"x4	1068.5	5.24	4"x4	1602.8	10.11	4"x6
FXV3-1224-20D-40	30% Ethylene Glycol	1335.6	7.91	4"x4	1068.5	5.24	4"x4	1602.8	10.11	4"x6
FXV3-1224-20D-50	30% Ethylene Glycol	1335.6	7.91	4"x4	1068.5	5.24	4"x4	1602.8	10.11	4"x6
FXV3-1224-20D-60	30% Ethylene Glycol	1335.6	7.91	4"x4	1068.5	5.24	4"x4	1602.8	10.11	4"x6
FXV3-1224-20D-75	30% Ethylene Glycol	1335.6	7.91	4"x4	1068.5	5.24	4"x4	1602.8	10.11	4"x6
FXV3-1224-24D-10	30% Ethylene Glycol	935.8	4.78	4"x4	748.6	4.37	4"x2	1122.9	6.69	4"x4
FXV3-1224-24D-15	30% Ethylene Glycol	935.8	4.78	4"x4	748.6	4.37	4"x2	1122.9	6.69	4"x4
FXV3-1224-24D-20	30% Ethylene Glycol	1335.6	9.23	4"x4	1068.5	6.11	4"x2	1602.8	11.95	4"x4
FXV3-1224-24D-25	30% Ethylene Glycol	1335.6	9.23	4"x4	1068.5	6.11	4"x4	1602.8	11.95	4"x6
FXV3-1224-24D-30	30% Ethylene Glycol	1335.6	9.23	4"x4	1068.5	6.11	4"x4	1602.8	11.95	4"x6
FXV3-1224-24D-40	30% Ethylene Glycol	1335.6	9.23	4"x4	1068.5	6.11	4"x4	1602.8	11.95	4"x6
FXV3-1224-24D-50	30% Ethylene Glycol	1335.6	9.23	4"x4	1068.5	6.11	4"x4	1602.8	11.95	4"x6
FXV3-1224-24D-60	30% Ethylene Glycol	1335.6	9.23	4"x4	1068.5	6.11	4"x4	1602.8	11.95	4"x6
FXV3-1224-24D-75	30% Ethylene Glycol	1335.6	9.23	4"x4	1068.5	6.11	4"x4	1602.8	11.95	4"x6
FXV3-1224-24T-10	30% Ethylene Glycol	1103.7	2.48	6"x2	883.0	1.64	6"x2	1324.5	3.46	6"x2
FXV3-1224-24T-15	30% Ethylene Glycol	1103.7	2.48	6"x2	883.0	1.64	6"x2	1324.5	3.46	6"x2
FXV3-1224-24T-20	30% Ethylene Glycol	1103.7	2.48	6"x2	883.0	1.64	6"x2	1324.5	3.46	6"x2
FXV3-1224-24T-25	30% Ethylene Glycol	1103.7	2.48	6"x2	883.0	1.64	6"x2	1324.5	3.46	6"x2
FXV3-1224-24T-30	30% Ethylene Glycol	1103.7	2.48	6"x2	883.0	1.64	6"x2	1324.5	3.46	6"x2
FXV3-1224-24T-40	30% Ethylene Glycol	1103.7	2.48	6"x2	883.0	1.64	6"x2	1324.5	3.46	6"x2
FXV3-1224-24T-50	30% Ethylene Glycol	1803.5	4.97	8"x2	1442.8	4.06	6"x2	2164.2	6.96	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-24T-60	30% Ethylene Glycol	1803.5	4.97	8"x2	1442.8	4.06	6"x2	2164.2	6.96	8"x2
FXV3-1224-24T-75	30% Ethylene Glycol	1803.5	4.97	8"x2	1442.8	4.06	6"x2	2164.2	6.96	8"x2
FXV3-1224-24Q-10	30% Ethylene Glycol	1171.7	1.67	6"x2	937.4	1.10	6"x2	1406.1	2.33	6"x2
FXV3-1224-24Q-15	30% Ethylene Glycol	1171.7	1.67	6"x2	937.4	1.10	6"x2	1406.1	2.33	6"x2
FXV3-1224-24Q-20	30% Ethylene Glycol	1171.7	1.67	6"x2	937.4	1.10	6"x2	1406.1	2.33	6"x2
FXV3-1224-24Q-25	30% Ethylene Glycol	1171.7	1.67	6"x2	937.4	1.10	6"x2	1406.1	2.33	6"x2
FXV3-1224-24Q-30	30% Ethylene Glycol	1171.7	1.67	6"x2	937.4	1.10	6"x2	1406.1	2.33	6"x2
FXV3-1224-24Q-40	30% Ethylene Glycol	1171.7	1.67	6"x2	937.4	1.10	6"x2	1406.1	2.33	6"x2
FXV3-1224-24Q-50	30% Ethylene Glycol	1171.7	1.67	6"x2	937.4	1.10	6"x2	1406.1	2.33	6"x2
FXV3-1224-24Q-60	30% Ethylene Glycol	1171.7	1.67	8"x2	937.4	1.10	6"x2	1406.1	2.33	8"x2
FXV3-1224-24Q-75	30% Ethylene Glycol	1871.5	2.71	8"x2	1497.2	2.62	6"x2	2245.8	3.80	8"x2
FXV3-1224-28D-10	30% Ethylene Glycol	935.8	5.46	4"x4	748.6	4.83	4"x2	1122.9	7.65	4"x4
FXV3-1224-28D-15	30% Ethylene Glycol	935.8	5.46	4"x4	748.6	4.83	4"x2	1122.9	7.65	4"x4
FXV3-1224-28D-20	30% Ethylene Glycol	1335.6	10.54	4"x4	1068.5	6.98	4"x4	1602.8	13.79	4"x6
FXV3-1224-28D-25	30% Ethylene Glycol	1335.6	10.54	4"x4	1068.5	6.98	4"x4	1602.8	13.79	4"x6
FXV3-1224-28D-30	30% Ethylene Glycol	1335.6	10.54	4"x4	1068.5	6.98	4"x4	1602.8	13.79	4"x6
FXV3-1224-28D-40	30% Ethylene Glycol	1335.6	10.54	4"x4	1068.5	6.98	4"x4	1602.8	13.79	4"x6
FXV3-1224-28D-50	30% Ethylene Glycol	1335.6	10.54	4"x4	1068.5	6.98	4"x4	1602.8	13.79	4"x6
FXV3-1224-28D-60	30% Ethylene Glycol	1335.6	10.54	4"x4	1068.5	6.98	4"x4	1602.8	13.79	4"x6
FXV3-1224-28D-75	30% Ethylene Glycol	1335.6	10.54	4"x4	1068.5	6.98	4"x4	1602.8	13.79	4"x6
FXV3-1224-30T-10	30% Ethylene Glycol	1103.7	2.92	6"x2	883.0	1.93	6"x2	1324.5	4.08	6"x2
FXV3-1224-30T-15	30% Ethylene Glycol	1103.7	2.92	6"x2	883.0	1.93	6"x2	1324.5	4.08	6"x2
FXV3-1224-30T-20	30% Ethylene Glycol	1103.7	2.92	6"x2	883.0	1.93	6"x2	1324.5	4.08	6"x2
FXV3-1224-30T-25	30% Ethylene Glycol	1103.7	2.92	6"x2	883.0	1.93	6"x2	1324.5	4.08	6"x2
FXV3-1224-30T-30	30% Ethylene Glycol	1803.5	6.06	8"x2	1442.8	4.78	6"x2	2164.2	8.48	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-30T-40	30% Ethylene Glycol	1803.5	6.06	8"x2	1442.8	4.78	6"x2	2164.2	8.48	8"x2
FXV3-1224-30T-50	30% Ethylene Glycol	1803.5	6.06	8"x2	1442.8	4.78	6"x2	2164.2	8.48	8"x2
FXV3-1224-30T-60	30% Ethylene Glycol	1803.5	6.06	8"x2	1442.8	4.78	6"x2	2164.2	8.48	8"x2
FXV3-1224-30T-75	30% Ethylene Glycol	1803.5	6.06	8"x2	1442.8	4.78	6"x2	2164.2	8.48	8"x2
FXV3-1224-32D-10	30% Ethylene Glycol	935.8	6.14	4"x4	748.6	5.30	4"x2	1122.9	8.60	4"x4
FXV3-1224-32D-15	30% Ethylene Glycol	935.8	6.14	4"x4	748.6	5.30	4"x2	1122.9	8.60	4"x4
FXV3-1224-32D-20	30% Ethylene Glycol	1335.6	11.85	4"x4	1068.5	7.85	4"x4	1602.8	15.63	4"x6
FXV3-1224-32D-25	30% Ethylene Glycol	1335.6	11.85	4"x4	1068.5	7.85	4"x4	1602.8	15.63	4"x6
FXV3-1224-32D-30	30% Ethylene Glycol	1335.6	11.85	4"x4	1068.5	7.85	4"x4	1602.8	15.63	4"x6
FXV3-1224-32D-40	30% Ethylene Glycol	1335.6	11.85	4"x4	1068.5	7.85	4"x4	1602.8	15.63	4"x6
FXV3-1224-32D-50	30% Ethylene Glycol	1335.6	11.85	4"x4	1068.5	7.85	4"x4	1602.8	15.63	4"x6
FXV3-1224-32D-60	30% Ethylene Glycol	1335.6	11.85	4"x4	1068.5	7.85	4"x4	1602.8	15.63	4"x6
FXV3-1224-32D-75	30% Ethylene Glycol	1335.6	11.85	4"x4	1068.5	7.85	4"x4	1602.8	15.63	4"x6
FXV3-1224-32Q-10	30% Ethylene Glycol	1171.7	1.96	6"x2	937.4	1.30	6"x2	1406.1	2.74	6"x2
FXV3-1224-32Q-15	30% Ethylene Glycol	1171.7	1.96	6"x2	937.4	1.30	6"x2	1406.1	2.74	6"x2
FXV3-1224-32Q-20	30% Ethylene Glycol	1171.7	1.96	6"x2	937.4	1.30	6"x2	1406.1	2.74	6"x2
FXV3-1224-32Q-25	30% Ethylene Glycol	1171.7	1.96	6"x2	937.4	1.30	6"x2	1406.1	2.74	6"x2
FXV3-1224-32Q-30	30% Ethylene Glycol	1171.7	1.96	6"x2	937.4	1.30	6"x2	1406.1	2.74	6"x2
FXV3-1224-32Q-40	30% Ethylene Glycol	1871.5	3.41	8"x2	1497.2	3.08	6"x2	2245.8	4.77	8"x2
FXV3-1224-32Q-50	30% Ethylene Glycol	1871.5	3.41	8"x2	1497.2	3.08	6"x2	2245.8	4.77	8"x2
FXV3-1224-32Q-60	30% Ethylene Glycol	1871.5	3.41	8"x2	1497.2	3.08	6"x2	2245.8	4.77	8"x2
FXV3-1224-32Q-75	30% Ethylene Glycol	1871.5	3.41	8"x2	1497.2	3.08	6"x2	2245.8	4.77	8"x2
FXV3-1224-36D-10	30% Ethylene Glycol	935.8	6.82	4"x4	748.6	5.76	4"x2	1122.9	9.55	4"x4
FXV3-1224-36D-15	30% Ethylene Glycol	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.47	4"x6
FXV3-1224-36D-20	30% Ethylene Glycol	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.47	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-36D-25	30% Ethylene Glycol	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.47	4"x6
FXV3-1224-36D-30	30% Ethylene Glycol	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.47	4"x6
FXV3-1224-36D-40	30% Ethylene Glycol	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.47	4"x6
FXV3-1224-36D-50	30% Ethylene Glycol	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.47	4"x6
FXV3-1224-36D-60	30% Ethylene Glycol	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.47	4"x6
FXV3-1224-36D-75	30% Ethylene Glycol	1335.6	13.17	4"x4	1068.5	8.72	4"x4	1602.8	17.47	4"x6
FXV3-1224-36T-10	30% Ethylene Glycol	1103.7	3.35	6"x2	883.0	2.22	6"x2	1324.5	4.69	6"x2
FXV3-1224-36T-15	30% Ethylene Glycol	1103.7	3.35	6"x2	883.0	2.22	6"x2	1324.5	4.69	6"x2
FXV3-1224-36T-20	30% Ethylene Glycol	1103.7	3.35	6"x2	883.0	2.22	6"x2	1324.5	4.69	6"x2
FXV3-1224-36T-25	30% Ethylene Glycol	1803.5	7.15	8"x2	1442.8	5.50	6"x2	2164.2	10.01	8"x2
FXV3-1224-36T-30	30% Ethylene Glycol	1803.5	7.15	8"x2	1442.8	5.50	6"x2	2164.2	10.01	8"x2
FXV3-1224-36T-40	30% Ethylene Glycol	1803.5	7.15	8"x2	1442.8	5.50	6"x2	2164.2	10.01	8"x2
FXV3-1224-36T-50	30% Ethylene Glycol	1803.5	7.15	8"x2	1442.8	5.50	6"x2	2164.2	10.01	8"x2
FXV3-1224-36T-60	30% Ethylene Glycol	1803.5	7.15	8"x2	1442.8	5.50	6"x2	2164.2	10.01	8"x2
FXV3-1224-36T-75	30% Ethylene Glycol	1803.5	7.15	8"x2	1442.8	5.50	6"x2	2164.2	10.01	8"x2
FXV3-1224-36Q-10	30% Ethylene Glycol	1171.7	2.11	6"x2	937.4	1.39	6"x2	1406.1	2.95	6"x2
FXV3-1224-36Q-15	30% Ethylene Glycol	1171.7	2.11	6"x2	937.4	1.39	6"x2	1406.1	2.95	6"x2
FXV3-1224-36Q-20	30% Ethylene Glycol	1171.7	2.11	6"x2	937.4	1.39	6"x2	1406.1	2.95	6"x2
FXV3-1224-36Q-25	30% Ethylene Glycol	1171.7	2.11	6"x2	937.4	1.39	6"x2	1406.1	2.95	6"x2
FXV3-1224-36Q-30	30% Ethylene Glycol	1871.5	3.75	8"x2	1497.2	3.31	6"x2	2245.8	5.26	8"x2
FXV3-1224-36Q-40	30% Ethylene Glycol	1871.5	3.75	8"x2	1497.2	3.31	6"x2	2245.8	5.26	8"x2
FXV3-1224-36Q-50	30% Ethylene Glycol	1871.5	3.75	8"x2	1497.2	3.31	6"x2	2245.8	5.26	8"x2
FXV3-1224-36Q-60	30% Ethylene Glycol	1871.5	3.75	8"x2	1497.2	3.31	6"x2	2245.8	5.26	8"x2
FXV3-1224-36Q-75	30% Ethylene Glycol	1871.5	3.75	8"x2	1497.2	3.31	6"x2	2245.8	5.26	8"x2
FXV-288-31M	30% Ethylene Glycol	949.8	4.23	4"x4	759.8	3.90	4"x2	1139.7	5.92	4"x4



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV-288-31N	30% Ethylene Glycol	949.8	4.23	4"x4	759.8	3.90	4"x4	1139.7	5.92	4"x6
FXV-288-31O	30% Ethylene Glycol	1349.6	8.09	4"x4	1079.7	5.36	4"x4	1619.6	10.48	4"x6
FXV-288-31P	30% Ethylene Glycol	1349.6	8.09	4"x4	1079.7	5.36	4"x4	1619.6	10.48	4"x6
FXV-288-31Q	30% Ethylene Glycol	1349.6	8.09	4"x4	1079.7	5.36	4"x4	1619.6	10.48	4"x6
FXV-288-31R	30% Ethylene Glycol	1349.6	8.09	4"x4	1079.7	5.36	4"x4	1619.6	10.48	4"x6
FXV-288-41M	30% Ethylene Glycol	1349.6	9.48	4"x4	1079.7	6.28	4"x2	1619.6	12.43	4"x4
FXV-288-41N	30% Ethylene Glycol	1349.6	9.48	4"x4	1079.7	6.28	4"x4	1619.6	12.43	4"x6
FXV-288-41O	30% Ethylene Glycol	1349.6	9.48	4"x4	1079.7	6.28	4"x4	1619.6	12.43	4"x6
FXV-288-41P	30% Ethylene Glycol	1349.6	9.48	4"x4	1079.7	6.28	4"x4	1619.6	12.43	4"x6
FXV-288-41Q	30% Ethylene Glycol	1349.6	9.48	4"x4	1079.7	6.28	4"x4	1619.6	12.43	4"x6
FXV-288-41R	30% Ethylene Glycol	1349.6	9.48	4"x4	1079.7	6.28	4"x4	1619.6	12.43	4"x6
FXV-288-2TM	30% Ethylene Glycol	1124.7	2.55	6"x2	899.8	1.69	6"x2	1349.7	3.57	6"x2
FXV-288-2TN	30% Ethylene Glycol	1124.7	2.55	6"x2	899.8	1.69	6"x2	1349.7	3.57	6"x2
FXV-288-2TO	30% Ethylene Glycol	1124.7	2.55	6"x2	899.8	1.69	6"x2	1349.7	3.57	6"x2
FXV-288-2TP	30% Ethylene Glycol	1124.7	2.55	6"x2	899.8	1.69	6"x2	1349.7	3.57	6"x2
FXV-288-2TQ	30% Ethylene Glycol	1824.5	5.13	8"x2	1459.6	4.13	6"x2	2189.4	7.18	8"x2
FXV-288-2TR	30% Ethylene Glycol	1824.5	5.13	8"x2	1459.6	4.13	6"x2	2189.4	7.18	8"x2
FXV-288-1QM	30% Ethylene Glycol	1199.7	1.69	6"x2	959.8	1.12	6"x2	1439.7	2.37	6"x2
FXV-288-1QN	30% Ethylene Glycol	1199.7	1.69	6"x2	959.8	1.12	6"x2	1439.7	2.37	6"x2
FXV-288-1QO	30% Ethylene Glycol	1199.7	1.69	6"x2	959.8	1.12	6"x2	1439.7	2.37	6"x2
FXV-288-1QP	30% Ethylene Glycol	1199.7	1.69	6"x2	959.8	1.12	6"x2	1439.7	2.37	6"x2
FXV-288-1QQ	30% Ethylene Glycol	1199.7	1.69	6"x2	959.8	1.12	6"x2	1439.7	2.37	6"x2
FXV-288-1QR	30% Ethylene Glycol	1199.7	1.69	8"x2	959.8	1.12	6"x2	1439.7	2.37	8"x2
FXV3-1426-20D-15	30% Ethylene Glycol	935.8	4.61	4"x4	748.6	4.25	4"x2	1122.9	6.45	4"x4
FXV3-1426-20D-20	30% Ethylene Glycol	1335.6	8.89	4"x4	1068.5	5.89	4"x4	1602.8	11.48	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-20D-25	30% Ethylene Glycol	1335.6	8.89	4"x4	1068.5	5.89	4"x4	1602.8	11.48	4"x6
FXV3-1426-20D-30	30% Ethylene Glycol	1335.6	8.89	4"x4	1068.5	5.89	4"x4	1602.8	11.48	4"x6
FXV3-1426-20D-40	30% Ethylene Glycol	1335.6	8.89	4"x4	1068.5	5.89	4"x4	1602.8	11.48	4"x6
FXV3-1426-20D-50	30% Ethylene Glycol	1335.6	8.89	4"x4	1068.5	5.89	4"x4	1602.8	11.48	4"x6
FXV3-1426-20D-60	30% Ethylene Glycol	1335.6	8.89	4"x4	1068.5	5.89	4"x4	1602.8	11.48	4"x6
FXV3-1426-20D-75	30% Ethylene Glycol	1335.6	8.89	4"x4	1068.5	5.89	4"x4	1602.8	11.48	4"x6
FXV3-1426-20D-100	30% Ethylene Glycol	1335.6	8.89	4"x4	1068.5	5.89	4"x4	1602.8	11.48	4"x6
FXV3-1426-24D-15	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24D-20	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24D-25	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24D-30	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24D-40	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24D-50	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24D-60	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24D-75	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24D-100	30% Ethylene Glycol	1335.6	10.40	4"x4	1068.5	6.89	4"x4	1602.8	13.59	4"x6
FXV3-1426-24T-15	30% Ethylene Glycol	1103.7	2.74	6"x2	883.0	1.81	6"x2	1324.5	3.83	6"x2
FXV3-1426-24T-20	30% Ethylene Glycol	1103.7	2.74	6"x2	883.0	1.81	6"x2	1324.5	3.83	6"x2
FXV3-1426-24T-25	30% Ethylene Glycol	1803.5	5.62	8"x2	1442.8	4.49	6"x2	2164.2	7.87	8"x2
FXV3-1426-24T-30	30% Ethylene Glycol	1803.5	5.62	8"x2	1442.8	4.49	6"x2	2164.2	7.87	8"x2
FXV3-1426-24T-40	30% Ethylene Glycol	1803.5	5.62	8"x2	1442.8	4.49	6"x2	2164.2	7.87	8"x2
FXV3-1426-24T-50	30% Ethylene Glycol	1803.5	5.62	8"x2	1442.8	4.49	6"x2	2164.2	7.87	8"x2
FXV3-1426-24T-60	30% Ethylene Glycol	1803.5	5.62	8"x2	1442.8	4.49	6"x2	2164.2	7.87	8"x2
FXV3-1426-24T-75	30% Ethylene Glycol	1803.5	5.62	8"x2	1442.8	4.49	6"x2	2164.2	7.87	8"x2
FXV3-1426-24T-100	30% Ethylene Glycol	1803.5	5.62	8"x2	1442.8	4.49	6"x2	2164.2	7.87	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-24Q-15	30% Ethylene Glycol	1171.7	1.80	6"x2	937.4	1.19	6"x2	1406.1	2.52	6"x2
FXV3-1426-24Q-20	30% Ethylene Glycol	1171.7	1.80	6"x2	937.4	1.19	6"x2	1406.1	2.52	6"x2
FXV3-1426-24Q-25	30% Ethylene Glycol	1171.7	1.80	6"x2	937.4	1.19	6"x2	1406.1	2.52	6"x2
FXV3-1426-24Q-30	30% Ethylene Glycol	1871.5	3.02	8"x2	1497.2	2.83	6"x2	2245.8	4.23	8"x2
FXV3-1426-24Q-40	30% Ethylene Glycol	1871.5	3.02	8"x2	1497.2	2.83	6"x2	2245.8	4.23	8"x2
FXV3-1426-24Q-50	30% Ethylene Glycol	1871.5	3.02	8"x2	1497.2	2.83	6"x2	2245.8	4.23	8"x2
FXV3-1426-24Q-60	30% Ethylene Glycol	1871.5	3.02	8"x2	1497.2	2.83	6"x2	2245.8	4.23	8"x2
FXV3-1426-24Q-75	30% Ethylene Glycol	1871.5	3.02	8"x2	1497.2	2.83	6"x2	2245.8	4.23	8"x2
FXV3-1426-24Q-100	30% Ethylene Glycol	1871.5	3.02	8"x2	1497.2	2.83	6"x2	2245.8	4.23	8"x2
FXV3-1426-28D-15	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-28D-20	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-28D-25	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-28D-30	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-28D-40	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-28D-50	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-28D-60	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-28D-75	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-28D-100	30% Ethylene Glycol	1335.6	11.91	4"x4	1068.5	7.89	4"x4	1602.8	15.71	4"x6
FXV3-1426-30T-15	30% Ethylene Glycol	1103.7	3.24	6"x2	883.0	2.15	6"x2	1324.5	4.54	6"x2
FXV3-1426-30T-20	30% Ethylene Glycol	1803.5	6.87	8"x2	1442.8	5.32	6"x2	2164.2	9.62	8"x2
FXV3-1426-30T-25	30% Ethylene Glycol	1803.5	6.87	8"x2	1442.8	5.32	6"x2	2164.2	9.62	8"x2
FXV3-1426-30T-30	30% Ethylene Glycol	1803.5	6.87	8"x2	1442.8	5.32	6"x2	2164.2	9.62	8"x2
FXV3-1426-30T-40	30% Ethylene Glycol	1803.5	6.87	8"x2	1442.8	5.32	6"x2	2164.2	9.62	8"x2
FXV3-1426-30T-50	30% Ethylene Glycol	1803.5	6.87	8"x2	1442.8	5.32	6"x2	2164.2	9.62	8"x2
FXV3-1426-30T-60	30% Ethylene Glycol	1803.5	6.87	8"x2	1442.8	5.32	6"x2	2164.2	9.62	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-30T-75	30% Ethylene Glycol	1803.5	6.87	8"x2	1442.8	5.32	6"x2	2164.2	9.62	8"x2
FXV3-1426-30T-100	30% Ethylene Glycol	1803.5	6.87	8"x2	1442.8	5.32	6"x2	2164.2	9.62	8"x2
FXV3-1426-32D-15	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32D-20	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32D-25	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32D-30	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32D-40	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32D-50	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32D-60	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32D-75	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32D-100	30% Ethylene Glycol	1335.6	13.42	4"x4	1068.5	8.89	4"x4	1602.8	17.82	4"x6
FXV3-1426-32Q-15	30% Ethylene Glycol	1171.7	2.13	6"x2	937.4	1.41	6"x2	1406.1	2.99	6"x2
FXV3-1426-32Q-20	30% Ethylene Glycol	1871.5	3.82	8"x2	1497.2	3.35	6"x2	2245.8	5.35	8"x2
FXV3-1426-32Q-25	30% Ethylene Glycol	1871.5	3.82	8"x2	1497.2	3.35	6"x2	2245.8	5.35	8"x2
FXV3-1426-32Q-30	30% Ethylene Glycol	1871.5	3.82	8"x2	1497.2	3.35	6"x2	2245.8	5.35	8"x2
FXV3-1426-32Q-40	30% Ethylene Glycol	1871.5	3.82	8"x2	1497.2	3.35	6"x2	2245.8	5.35	8"x2
FXV3-1426-32Q-50	30% Ethylene Glycol	1871.5	3.82	8"x2	1497.2	3.35	6"x2	2245.8	5.35	8"x2
FXV3-1426-32Q-60	30% Ethylene Glycol	1871.5	3.82	8"x2	1497.2	3.35	6"x2	2245.8	5.35	8"x2
FXV3-1426-32Q-75	30% Ethylene Glycol	1871.5	3.82	8"x2	1497.2	3.35	6"x2	2245.8	5.35	8"x2
FXV3-1426-32Q-100	30% Ethylene Glycol	1871.5	3.82	8"x2	1497.2	3.35	6"x2	2245.8	5.35	8"x2
FXV3-1426-36D-15	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6
FXV3-1426-36D-20	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6
FXV3-1426-36D-25	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6
FXV3-1426-36D-30	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6
FXV3-1426-36D-40	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-36D-50	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6
FXV3-1426-36D-60	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6
FXV3-1426-36D-75	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6
FXV3-1426-36D-100	30% Ethylene Glycol	1335.6	14.93	4"x4	1068.5	9.89	4"x4	1602.8	19.94	4"x6
FXV3-1426-36T-15	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36T-20	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36T-25	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36T-30	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36T-40	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36T-50	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36T-60	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36T-75	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36T-100	30% Ethylene Glycol	1803.5	8.12	8"x2	1442.8	6.15	6"x2	2164.2	11.37	8"x2
FXV3-1426-36Q-15	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV3-1426-36Q-20	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV3-1426-36Q-25	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV3-1426-36Q-30	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV3-1426-36Q-40	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV3-1426-36Q-50	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV3-1426-36Q-60	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV3-1426-36Q-75	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV3-1426-36Q-100	30% Ethylene Glycol	1871.5	4.22	8"x2	1497.2	3.62	6"x2	2245.8	5.91	8"x2
FXV-364-31N	30% Ethylene Glycol	1349.6	9.13	4"x4	1079.7	6.05	4"x4	1619.6	11.82	4"x6
FXV-364-31O	30% Ethylene Glycol	1349.6	9.13	4"x4	1079.7	6.05	4"x4	1619.6	11.82	4"x6
FXV-364-31P	30% Ethylene Glycol	1349.6	9.13	4"x4	1079.7	6.05	4"x4	1619.6	11.82	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV-364-31Q	30% Ethylene Glycol	1349.6	9.13	4"x4	1079.7	6.05	4"x4	1619.6	11.82	4"x6
FXV-364-31R	30% Ethylene Glycol	1349.6	9.13	4"x4	1079.7	6.05	4"x4	1619.6	11.82	4"x6
FXV-364-31S	30% Ethylene Glycol	1349.6	9.13	4"x4	1079.7	6.05	4"x4	1619.6	11.82	4"x6
FXV-364-41N	30% Ethylene Glycol	1349.6	10.70	4"x4	1079.7	7.08	4"x4	1619.6	14.01	4"x6
FXV-364-41O	30% Ethylene Glycol	1349.6	10.70	4"x4	1079.7	7.08	4"x4	1619.6	14.01	4"x6
FXV-364-41P	30% Ethylene Glycol	1349.6	10.70	4"x4	1079.7	7.08	4"x4	1619.6	14.01	4"x6
FXV-364-41Q	30% Ethylene Glycol	1349.6	10.70	4"x4	1079.7	7.08	4"x4	1619.6	14.01	4"x6
FXV-364-41R	30% Ethylene Glycol	1349.6	10.70	4"x4	1079.7	7.08	4"x4	1619.6	14.01	4"x6
FXV-364-41S	30% Ethylene Glycol	1349.6	10.70	4"x4	1079.7	7.08	4"x4	1619.6	14.01	4"x6
FXV-364-2TN	30% Ethylene Glycol	1824.5	5.75	8"x2	1459.6	4.61	6"x2	2189.4	8.05	8"x2
FXV-364-2TO	30% Ethylene Glycol	1824.5	5.75	8"x2	1459.6	4.61	6"x2	2189.4	8.05	8"x2
FXV-364-2TP	30% Ethylene Glycol	1824.5	5.75	8"x2	1459.6	4.61	6"x2	2189.4	8.05	8"x2
FXV-364-2TQ	30% Ethylene Glycol	1824.5	5.75	8"x2	1459.6	4.61	6"x2	2189.4	8.05	8"x2
FXV-364-2TR	30% Ethylene Glycol	1824.5	5.75	8"x2	1459.6	4.61	6"x2	2189.4	8.05	8"x2
FXV-364-2TS	30% Ethylene Glycol	1824.5	5.75	8"x2	1459.6	4.61	6"x2	2189.4	8.05	8"x2
FXV-364-1QN	30% Ethylene Glycol	1199.7	1.86	6"x2	959.8	1.23	6"x2	1439.7	2.60	6"x2
FXV-364-1QO	30% Ethylene Glycol	1899.5	3.16	8"x2	1519.6	2.88	6"x2	2279.4	4.42	8"x2
FXV-364-1QP	30% Ethylene Glycol	1899.5	3.16	8"x2	1519.6	2.88	6"x2	2279.4	4.42	8"x2
FXV-364-1QQ	30% Ethylene Glycol	1899.5	3.16	8"x2	1519.6	2.88	6"x2	2279.4	4.42	8"x2
FXV-364-1QR	30% Ethylene Glycol	1899.5	3.16	8"x2	1519.6	2.88	6"x2	2279.4	4.42	8"x2
FXV-364-1QS	30% Ethylene Glycol	1899.5	3.16	8"x2	1519.6	2.88	6"x2	2279.4	4.42	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-20D-10	30% Propylene Glycol	935.8	4.31	4"x4	748.6	4.12	4"x2	1122.9	6.04	4"x4
FXV3-1224-20D-15	30% Propylene Glycol	935.8	4.31	4"x4	748.6	4.12	4"x2	1122.9	6.04	4"x4
FXV3-1224-20D-20	30% Propylene Glycol	935.8	4.31	4"x4	748.6	4.12	4"x2	1122.9	6.04	4"x4
FXV3-1224-20D-25	30% Propylene Glycol	935.8	4.31	4"x4	748.6	4.12	4"x4	1122.9	6.04	4"x6
FXV3-1224-20D-30	30% Propylene Glycol	935.8	4.31	4"x4	748.6	4.12	4"x4	1122.9	6.04	4"x6
FXV3-1224-20D-40	30% Propylene Glycol	1335.6	8.33	4"x4	1068.5	5.51	4"x4	1602.8	10.64	4"x6
FXV3-1224-20D-50	30% Propylene Glycol	1335.6	8.33	4"x4	1068.5	5.51	4"x4	1602.8	10.64	4"x6
FXV3-1224-20D-60	30% Propylene Glycol	1335.6	8.33	4"x4	1068.5	5.51	4"x4	1602.8	10.64	4"x6
FXV3-1224-20D-75	30% Propylene Glycol	1335.6	8.33	4"x4	1068.5	5.51	4"x4	1602.8	10.64	4"x6
FXV3-1224-24D-10	30% Propylene Glycol	935.8	5.03	4"x4	748.6	4.60	4"x2	1122.9	7.04	4"x4
FXV3-1224-24D-15	30% Propylene Glycol	935.8	5.03	4"x4	748.6	4.60	4"x2	1122.9	7.04	4"x4
FXV3-1224-24D-20	30% Propylene Glycol	935.8	5.03	4"x4	748.6	4.60	4"x2	1122.9	7.04	4"x4
FXV3-1224-24D-25	30% Propylene Glycol	1335.6	9.71	4"x4	1068.5	6.43	4"x4	1602.8	12.58	4"x6
FXV3-1224-24D-30	30% Propylene Glycol	1335.6	9.71	4"x4	1068.5	6.43	4"x4	1602.8	12.58	4"x6
FXV3-1224-24D-40	30% Propylene Glycol	1335.6	9.71	4"x4	1068.5	6.43	4"x4	1602.8	12.58	4"x6
FXV3-1224-24D-50	30% Propylene Glycol	1335.6	9.71	4"x4	1068.5	6.43	4"x4	1602.8	12.58	4"x6
FXV3-1224-24D-60	30% Propylene Glycol	1335.6	9.71	4"x4	1068.5	6.43	4"x4	1602.8	12.58	4"x6
FXV3-1224-24D-75	30% Propylene Glycol	1335.6	9.71	4"x4	1068.5	6.43	4"x4	1602.8	12.58	4"x6
FXV3-1224-24T-10	30% Propylene Glycol	1103.7	2.61	6"x2	883.0	1.73	6"x2	1324.5	3.65	6"x2
FXV3-1224-24T-15	30% Propylene Glycol	1103.7	2.61	6"x2	883.0	1.73	6"x2	1324.5	3.65	6"x2
FXV3-1224-24T-20	30% Propylene Glycol	1103.7	2.61	6"x2	883.0	1.73	6"x2	1324.5	3.65	6"x2
FXV3-1224-24T-25	30% Propylene Glycol	1103.7	2.61	6"x2	883.0	1.73	6"x2	1324.5	3.65	6"x2
FXV3-1224-24T-30	30% Propylene Glycol	1103.7	2.61	6"x2	883.0	1.73	6"x2	1324.5	3.65	6"x2
FXV3-1224-24T-40	30% Propylene Glycol	1103.7	2.61	6"x2	883.0	1.73	6"x2	1324.5	3.65	6"x2
FXV3-1224-24T-50	30% Propylene Glycol	1103.7	2.61	8"x2	883.0	1.73	6"x2	1324.5	3.65	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-24T-60	30% Propylene Glycol	1103.7	2.61	8"x2	883.0	1.73	6"x2	1324.5	3.65	8"x2
FXV3-1224-24T-75	30% Propylene Glycol	1803.5	5.23	8"x2	1442.8	4.27	6"x2	2164.2	7.32	8"x2
FXV3-1224-24Q-10	30% Propylene Glycol	1171.7	1.76	6"x2	937.4	1.16	6"x2	1406.1	2.46	6"x2
FXV3-1224-24Q-15	30% Propylene Glycol	1171.7	1.76	6"x2	937.4	1.16	6"x2	1406.1	2.46	6"x2
FXV3-1224-24Q-20	30% Propylene Glycol	1171.7	1.76	6"x2	937.4	1.16	6"x2	1406.1	2.46	6"x2
FXV3-1224-24Q-25	30% Propylene Glycol	1171.7	1.76	6"x2	937.4	1.16	6"x2	1406.1	2.46	6"x2
FXV3-1224-24Q-30	30% Propylene Glycol	1171.7	1.76	6"x2	937.4	1.16	6"x2	1406.1	2.46	6"x2
FXV3-1224-24Q-40	30% Propylene Glycol	1171.7	1.76	6"x2	937.4	1.16	6"x2	1406.1	2.46	6"x2
FXV3-1224-24Q-50	30% Propylene Glycol	1171.7	1.76	6"x2	937.4	1.16	6"x2	1406.1	2.46	6"x2
FXV3-1224-24Q-60	30% Propylene Glycol	1171.7	1.76	8"x2	937.4	1.16	6"x2	1406.1	2.46	8"x2
FXV3-1224-24Q-75	30% Propylene Glycol	1171.7	1.76	8"x2	937.4	1.16	6"x2	1406.1	2.46	8"x2
FXV3-1224-28D-10	30% Propylene Glycol	935.8	5.75	4"x4	748.6	5.09	4"x2	1122.9	8.05	4"x4
FXV3-1224-28D-15	30% Propylene Glycol	935.8	5.75	4"x4	748.6	5.09	4"x2	1122.9	8.05	4"x4
FXV3-1224-28D-20	30% Propylene Glycol	935.8	5.75	4"x4	748.6	5.09	4"x4	1122.9	8.05	4"x6
FXV3-1224-28D-25	30% Propylene Glycol	1335.6	11.09	4"x4	1068.5	7.35	4"x4	1602.8	14.51	4"x6
FXV3-1224-28D-30	30% Propylene Glycol	1335.6	11.09	4"x4	1068.5	7.35	4"x4	1602.8	14.51	4"x6
FXV3-1224-28D-40	30% Propylene Glycol	1335.6	11.09	4"x4	1068.5	7.35	4"x4	1602.8	14.51	4"x6
FXV3-1224-28D-50	30% Propylene Glycol	1335.6	11.09	4"x4	1068.5	7.35	4"x4	1602.8	14.51	4"x6
FXV3-1224-28D-60	30% Propylene Glycol	1335.6	11.09	4"x4	1068.5	7.35	4"x4	1602.8	14.51	4"x6
FXV3-1224-28D-75	30% Propylene Glycol	1335.6	11.09	4"x4	1068.5	7.35	4"x4	1602.8	14.51	4"x6
FXV3-1224-30T-10	30% Propylene Glycol	1103.7	3.07	6"x2	883.0	2.03	6"x2	1324.5	4.29	6"x2
FXV3-1224-30T-15	30% Propylene Glycol	1103.7	3.07	6"x2	883.0	2.03	6"x2	1324.5	4.29	6"x2
FXV3-1224-30T-20	30% Propylene Glycol	1103.7	3.07	6"x2	883.0	2.03	6"x2	1324.5	4.29	6"x2
FXV3-1224-30T-25	30% Propylene Glycol	1103.7	3.07	6"x2	883.0	2.03	6"x2	1324.5	4.29	6"x2
FXV3-1224-30T-30	30% Propylene Glycol	1103.7	3.07	8"x2	883.0	2.03	6"x2	1324.5	4.29	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-30T-40	30% Propylene Glycol	1803.5	6.38	8"x2	1442.8	5.03	6"x2	2164.2	8.93	8"x2
FXV3-1224-30T-50	30% Propylene Glycol	1803.5	6.38	8"x2	1442.8	5.03	6"x2	2164.2	8.93	8"x2
FXV3-1224-30T-60	30% Propylene Glycol	1803.5	6.38	8"x2	1442.8	5.03	6"x2	2164.2	8.93	8"x2
FXV3-1224-30T-75	30% Propylene Glycol	1803.5	6.38	8"x2	1442.8	5.03	6"x2	2164.2	8.93	8"x2
FXV3-1224-32D-10	30% Propylene Glycol	935.8	6.46	4"x4	748.6	5.57	4"x2	1122.9	9.05	4"x4
FXV3-1224-32D-15	30% Propylene Glycol	935.8	6.46	4"x4	748.6	5.57	4"x2	1122.9	9.05	4"x4
FXV3-1224-32D-20	30% Propylene Glycol	1335.6	12.48	4"x4	1068.5	8.26	4"x4	1602.8	16.45	4"x6
FXV3-1224-32D-25	30% Propylene Glycol	1335.6	12.48	4"x4	1068.5	8.26	4"x4	1602.8	16.45	4"x6
FXV3-1224-32D-30	30% Propylene Glycol	1335.6	12.48	4"x4	1068.5	8.26	4"x4	1602.8	16.45	4"x6
FXV3-1224-32D-40	30% Propylene Glycol	1335.6	12.48	4"x4	1068.5	8.26	4"x4	1602.8	16.45	4"x6
FXV3-1224-32D-50	30% Propylene Glycol	1335.6	12.48	4"x4	1068.5	8.26	4"x4	1602.8	16.45	4"x6
FXV3-1224-32D-60	30% Propylene Glycol	1335.6	12.48	4"x4	1068.5	8.26	4"x4	1602.8	16.45	4"x6
FXV3-1224-32D-75	30% Propylene Glycol	1335.6	12.48	4"x4	1068.5	8.26	4"x4	1602.8	16.45	4"x6
FXV3-1224-32Q-10	30% Propylene Glycol	1171.7	2.06	6"x2	937.4	1.37	6"x2	1406.1	2.89	6"x2
FXV3-1224-32Q-15	30% Propylene Glycol	1171.7	2.06	6"x2	937.4	1.37	6"x2	1406.1	2.89	6"x2
FXV3-1224-32Q-20	30% Propylene Glycol	1171.7	2.06	6"x2	937.4	1.37	6"x2	1406.1	2.89	6"x2
FXV3-1224-32Q-25	30% Propylene Glycol	1171.7	2.06	6"x2	937.4	1.37	6"x2	1406.1	2.89	6"x2
FXV3-1224-32Q-30	30% Propylene Glycol	1171.7	2.06	6"x2	937.4	1.37	6"x2	1406.1	2.89	6"x2
FXV3-1224-32Q-40	30% Propylene Glycol	1171.7	2.06	8"x2	937.4	1.37	6"x2	1406.1	2.89	8"x2
FXV3-1224-32Q-50	30% Propylene Glycol	1871.5	3.59	8"x2	1497.2	3.24	6"x2	2245.8	5.02	8"x2
FXV3-1224-32Q-60	30% Propylene Glycol	1871.5	3.59	8"x2	1497.2	3.24	6"x2	2245.8	5.02	8"x2
FXV3-1224-32Q-75	30% Propylene Glycol	1871.5	3.59	8"x2	1497.2	3.24	6"x2	2245.8	5.02	8"x2
FXV3-1224-36D-10	30% Propylene Glycol	935.8	7.18	4"x4	748.6	6.06	4"x2	1122.9	10.05	4"x4
FXV3-1224-36D-15	30% Propylene Glycol	935.8	7.18	4"x4	748.6	6.06	4"x4	1122.9	10.05	4"x6
FXV3-1224-36D-20	30% Propylene Glycol	1335.6	13.86	4"x4	1068.5	9.18	4"x4	1602.8	18.39	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1224-36D-25	30% Propylene Glycol	1335.6	13.86	4"x4	1068.5	9.18	4"x4	1602.8	18.39	4"x6
FXV3-1224-36D-30	30% Propylene Glycol	1335.6	13.86	4"x4	1068.5	9.18	4"x4	1602.8	18.39	4"x6
FXV3-1224-36D-40	30% Propylene Glycol	1335.6	13.86	4"x4	1068.5	9.18	4"x4	1602.8	18.39	4"x6
FXV3-1224-36D-50	30% Propylene Glycol	1335.6	13.86	4"x4	1068.5	9.18	4"x4	1602.8	18.39	4"x6
FXV3-1224-36D-60	30% Propylene Glycol	1335.6	13.86	4"x4	1068.5	9.18	4"x4	1602.8	18.39	4"x6
FXV3-1224-36D-75	30% Propylene Glycol	1335.6	13.86	4"x4	1068.5	9.18	4"x4	1602.8	18.39	4"x6
FXV3-1224-36T-10	30% Propylene Glycol	1103.7	3.53	6"x2	883.0	2.34	6"x2	1324.5	4.94	6"x2
FXV3-1224-36T-15	30% Propylene Glycol	1103.7	3.53	6"x2	883.0	2.34	6"x2	1324.5	4.94	6"x2
FXV3-1224-36T-20	30% Propylene Glycol	1103.7	3.53	6"x2	883.0	2.34	6"x2	1324.5	4.94	6"x2
FXV3-1224-36T-25	30% Propylene Glycol	1103.7	3.53	8"x2	883.0	2.34	6"x2	1324.5	4.94	8"x2
FXV3-1224-36T-30	30% Propylene Glycol	1803.5	7.53	8"x2	1442.8	5.79	6"x2	2164.2	10.53	8"x2
FXV3-1224-36T-40	30% Propylene Glycol	1803.5	7.53	8"x2	1442.8	5.79	6"x2	2164.2	10.53	8"x2
FXV3-1224-36T-50	30% Propylene Glycol	1803.5	7.53	8"x2	1442.8	5.79	6"x2	2164.2	10.53	8"x2
FXV3-1224-36T-60	30% Propylene Glycol	1803.5	7.53	8"x2	1442.8	5.79	6"x2	2164.2	10.53	8"x2
FXV3-1224-36T-75	30% Propylene Glycol	1803.5	7.53	8"x2	1442.8	5.79	6"x2	2164.2	10.53	8"x2
FXV3-1224-36Q-10	30% Propylene Glycol	1171.7	2.22	6"x2	937.4	1.47	6"x2	1406.1	3.10	6"x2
FXV3-1224-36Q-15	30% Propylene Glycol	1171.7	2.22	6"x2	937.4	1.47	6"x2	1406.1	3.10	6"x2
FXV3-1224-36Q-20	30% Propylene Glycol	1171.7	2.22	6"x2	937.4	1.47	6"x2	1406.1	3.10	6"x2
FXV3-1224-36Q-25	30% Propylene Glycol	1171.7	2.22	6"x2	937.4	1.47	6"x2	1406.1	3.10	6"x2
FXV3-1224-36Q-30	30% Propylene Glycol	1171.7	2.22	8"x2	937.4	1.47	6"x2	1406.1	3.10	8"x2
FXV3-1224-36Q-40	30% Propylene Glycol	1871.5	3.95	8"x2	1497.2	3.48	6"x2	2245.8	5.53	8"x2
FXV3-1224-36Q-50	30% Propylene Glycol	1871.5	3.95	8"x2	1497.2	3.48	6"x2	2245.8	5.53	8"x2
FXV3-1224-36Q-60	30% Propylene Glycol	1871.5	3.95	8"x2	1497.2	3.48	6"x2	2245.8	5.53	8"x2
FXV3-1224-36Q-75	30% Propylene Glycol	1871.5	3.95	8"x2	1497.2	3.48	6"x2	2245.8	5.53	8"x2
FXV-288-31M	30% Propylene Glycol	949.8	4.45	4"x4	759.8	4.11	4"x2	1139.7	6.23	4"x4



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV-288-31N	30% Propylene Glycol	949.8	4.45	4"x4	759.8	4.11	4"x4	1139.7	6.23	4"x6
FXV-288-31O	30% Propylene Glycol	949.8	4.45	4"x4	759.8	4.11	4"x4	1139.7	6.23	4"x6
FXV-288-31P	30% Propylene Glycol	1349.6	8.52	4"x4	1079.7	5.64	4"x4	1619.6	11.03	4"x6
FXV-288-31Q	30% Propylene Glycol	1349.6	8.52	4"x4	1079.7	5.64	4"x4	1619.6	11.03	4"x6
FXV-288-31R	30% Propylene Glycol	1349.6	8.52	4"x4	1079.7	5.64	4"x4	1619.6	11.03	4"x6
FXV-288-41M	30% Propylene Glycol	949.8	5.21	4"x4	759.8	4.68	4"x2	1139.7	7.30	4"x4
FXV-288-41N	30% Propylene Glycol	1349.6	9.98	4"x4	1079.7	6.61	4"x4	1619.6	13.08	4"x6
FXV-288-41O	30% Propylene Glycol	1349.6	9.98	4"x4	1079.7	6.61	4"x4	1619.6	13.08	4"x6
FXV-288-41P	30% Propylene Glycol	1349.6	9.98	4"x4	1079.7	6.61	4"x4	1619.6	13.08	4"x6
FXV-288-41Q	30% Propylene Glycol	1349.6	9.98	4"x4	1079.7	6.61	4"x4	1619.6	13.08	4"x6
FXV-288-41R	30% Propylene Glycol	1349.6	9.98	4"x4	1079.7	6.61	4"x4	1619.6	13.08	4"x6
FXV-288-2TM	30% Propylene Glycol	1124.7	2.68	6"x2	899.8	1.78	6"x2	1349.7	3.76	6"x2
FXV-288-2TN	30% Propylene Glycol	1124.7	2.68	6"x2	899.8	1.78	6"x2	1349.7	3.76	6"x2
FXV-288-2TO	30% Propylene Glycol	1124.7	2.68	6"x2	899.8	1.78	6"x2	1349.7	3.76	6"x2
FXV-288-2TP	30% Propylene Glycol	1124.7	2.68	6"x2	899.8	1.78	6"x2	1349.7	3.76	6"x2
FXV-288-2TQ	30% Propylene Glycol	1124.7	2.68	8"x2	899.8	1.78	6"x2	1349.7	3.76	8"x2
FXV-288-2TR	30% Propylene Glycol	1124.7	2.68	8"x2	899.8	1.78	6"x2	1349.7	3.76	8"x2
FXV-288-1QM	30% Propylene Glycol	1199.7	1.78	6"x2	959.8	1.18	6"x2	1439.7	2.49	6"x2
FXV-288-1QN	30% Propylene Glycol	1199.7	1.78	6"x2	959.8	1.18	6"x2	1439.7	2.49	6"x2
FXV-288-1QO	30% Propylene Glycol	1199.7	1.78	6"x2	959.8	1.18	6"x2	1439.7	2.49	6"x2
FXV-288-1QP	30% Propylene Glycol	1199.7	1.78	6"x2	959.8	1.18	6"x2	1439.7	2.49	6"x2
FXV-288-1QQ	30% Propylene Glycol	1199.7	1.78	6"x2	959.8	1.18	6"x2	1439.7	2.49	6"x2
FXV-288-1QR	30% Propylene Glycol	1199.7	1.78	8"x2	959.8	1.18	6"x2	1439.7	2.49	8"x2
FXV3-1426-20D-15	30% Propylene Glycol	935.8	4.85	4"x4	748.6	4.48	4"x2	1122.9	6.79	4"x4
FXV3-1426-20D-20	30% Propylene Glycol	935.8	4.85	4"x4	748.6	4.48	4"x4	1122.9	6.79	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-20D-25	30% Propylene Glycol	1335.6	9.36	4"x4	1068.5	6.20	4"x4	1602.8	12.08	4"x6
FXV3-1426-20D-30	30% Propylene Glycol	1335.6	9.36	4"x4	1068.5	6.20	4"x4	1602.8	12.08	4"x6
FXV3-1426-20D-40	30% Propylene Glycol	1335.6	9.36	4"x4	1068.5	6.20	4"x4	1602.8	12.08	4"x6
FXV3-1426-20D-50	30% Propylene Glycol	1335.6	9.36	4"x4	1068.5	6.20	4"x4	1602.8	12.08	4"x6
FXV3-1426-20D-60	30% Propylene Glycol	1335.6	9.36	4"x4	1068.5	6.20	4"x4	1602.8	12.08	4"x6
FXV3-1426-20D-75	30% Propylene Glycol	1335.6	9.36	4"x4	1068.5	6.20	4"x4	1602.8	12.08	4"x6
FXV3-1426-20D-100	30% Propylene Glycol	1335.6	9.36	4"x4	1068.5	6.20	4"x4	1602.8	12.08	4"x6
FXV3-1426-24D-15	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24D-20	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24D-25	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24D-30	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24D-40	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24D-50	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24D-60	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24D-75	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24D-100	30% Propylene Glycol	1335.6	10.95	4"x4	1068.5	7.25	4"x4	1602.8	14.31	4"x6
FXV3-1426-24T-15	30% Propylene Glycol	1103.7	2.88	6"x2	883.0	1.91	6"x2	1324.5	4.03	6"x2
FXV3-1426-24T-20	30% Propylene Glycol	1103.7	2.88	6"x2	883.0	1.91	6"x2	1324.5	4.03	6"x2
FXV3-1426-24T-25	30% Propylene Glycol	1103.7	2.88	8"x2	883.0	1.91	6"x2	1324.5	4.03	8"x2
FXV3-1426-24T-30	30% Propylene Glycol	1103.7	2.88	8"x2	883.0	1.91	6"x2	1324.5	4.03	8"x2
FXV3-1426-24T-40	30% Propylene Glycol	1803.5	5.91	8"x2	1442.8	4.73	6"x2	2164.2	8.28	8"x2
FXV3-1426-24T-50	30% Propylene Glycol	1803.5	5.91	8"x2	1442.8	4.73	6"x2	2164.2	8.28	8"x2
FXV3-1426-24T-60	30% Propylene Glycol	1803.5	5.91	8"x2	1442.8	4.73	6"x2	2164.2	8.28	8"x2
FXV3-1426-24T-75	30% Propylene Glycol	1803.5	5.91	8"x2	1442.8	4.73	6"x2	2164.2	8.28	8"x2
FXV3-1426-24T-100	30% Propylene Glycol	1803.5	5.91	8"x2	1442.8	4.73	6"x2	2164.2	8.28	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-24Q-15	30% Propylene Glycol	1171.7	1.89	6"x2	937.4	1.25	6"x2	1406.1	2.65	6"x2
FXV3-1426-24Q-20	30% Propylene Glycol	1171.7	1.89	6"x2	937.4	1.25	6"x2	1406.1	2.65	6"x2
FXV3-1426-24Q-25	30% Propylene Glycol	1171.7	1.89	6"x2	937.4	1.25	6"x2	1406.1	2.65	6"x2
FXV3-1426-24Q-30	30% Propylene Glycol	1171.7	1.89	8"x2	937.4	1.25	6"x2	1406.1	2.65	8"x2
FXV3-1426-24Q-40	30% Propylene Glycol	1171.7	1.89	8"x2	937.4	1.25	6"x2	1406.1	2.65	8"x2
FXV3-1426-24Q-50	30% Propylene Glycol	1871.5	3.18	8"x2	1497.2	2.97	6"x2	2245.8	4.46	8"x2
FXV3-1426-24Q-60	30% Propylene Glycol	1871.5	3.18	8"x2	1497.2	2.97	6"x2	2245.8	4.46	8"x2
FXV3-1426-24Q-75	30% Propylene Glycol	1871.5	3.18	8"x2	1497.2	2.97	6"x2	2245.8	4.46	8"x2
FXV3-1426-24Q-100	30% Propylene Glycol	1871.5	3.18	8"x2	1497.2	2.97	6"x2	2245.8	4.46	8"x2
FXV3-1426-28D-15	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-28D-20	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-28D-25	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-28D-30	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-28D-40	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-28D-50	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-28D-60	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-28D-75	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-28D-100	30% Propylene Glycol	1335.6	12.54	4"x4	1068.5	8.30	4"x4	1602.8	16.53	4"x6
FXV3-1426-30T-15	30% Propylene Glycol	1103.7	3.41	6"x2	883.0	2.26	6"x2	1324.5	4.77	6"x2
FXV3-1426-30T-20	30% Propylene Glycol	1803.5	7.23	8"x2	1442.8	5.60	6"x2	2164.2	10.12	8"x2
FXV3-1426-30T-25	30% Propylene Glycol	1803.5	7.23	8"x2	1442.8	5.60	6"x2	2164.2	10.12	8"x2
FXV3-1426-30T-30	30% Propylene Glycol	1803.5	7.23	8"x2	1442.8	5.60	6"x2	2164.2	10.12	8"x2
FXV3-1426-30T-40	30% Propylene Glycol	1803.5	7.23	8"x2	1442.8	5.60	6"x2	2164.2	10.12	8"x2
FXV3-1426-30T-50	30% Propylene Glycol	1803.5	7.23	8"x2	1442.8	5.60	6"x2	2164.2	10.12	8"x2
FXV3-1426-30T-60	30% Propylene Glycol	1803.5	7.23	8"x2	1442.8	5.60	6"x2	2164.2	10.12	8"x2



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-30T-75	30% Propylene Glycol	1803.5	7.23	8"x2	1442.8	5.60	6"x2	2164.2	10.12	8"x2
FXV3-1426-30T-100	30% Propylene Glycol	1803.5	7.23	8"x2	1442.8	5.60	6"x2	2164.2	10.12	8"x2
FXV3-1426-32D-15	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32D-20	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32D-25	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32D-30	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32D-40	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32D-50	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32D-60	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32D-75	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32D-100	30% Propylene Glycol	1335.6	14.12	4"x4	1068.5	9.35	4"x4	1602.8	18.76	4"x6
FXV3-1426-32Q-15	30% Propylene Glycol	1171.7	2.25	6"x2	937.4	1.49	6"x2	1406.1	3.14	6"x2
FXV3-1426-32Q-20	30% Propylene Glycol	1171.7	2.25	8"x2	937.4	1.49	6"x2	1406.1	3.14	8"x2
FXV3-1426-32Q-25	30% Propylene Glycol	1871.5	4.02	8"x2	1497.2	3.53	6"x2	2245.8	5.63	8"x2
FXV3-1426-32Q-30	30% Propylene Glycol	1871.5	4.02	8"x2	1497.2	3.53	6"x2	2245.8	5.63	8"x2
FXV3-1426-32Q-40	30% Propylene Glycol	1871.5	4.02	8"x2	1497.2	3.53	6"x2	2245.8	5.63	8"x2
FXV3-1426-32Q-50	30% Propylene Glycol	1871.5	4.02	8"x2	1497.2	3.53	6"x2	2245.8	5.63	8"x2
FXV3-1426-32Q-60	30% Propylene Glycol	1871.5	4.02	8"x2	1497.2	3.53	6"x2	2245.8	5.63	8"x2
FXV3-1426-32Q-75	30% Propylene Glycol	1871.5	4.02	8"x2	1497.2	3.53	6"x2	2245.8	5.63	8"x2
FXV3-1426-32Q-100	30% Propylene Glycol	1871.5	4.02	8"x2	1497.2	3.53	6"x2	2245.8	5.63	8"x2
FXV3-1426-36D-15	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6
FXV3-1426-36D-20	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6
FXV3-1426-36D-25	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6
FXV3-1426-36D-30	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6
FXV3-1426-36D-40	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV3-1426-36D-50	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6
FXV3-1426-36D-60	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6
FXV3-1426-36D-75	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6
FXV3-1426-36D-100	30% Propylene Glycol	1335.6	15.71	4"x4	1068.5	10.40	4"x4	1602.8	20.99	4"x6
FXV3-1426-36T-15	30% Propylene Glycol	1103.7	3.94	8"x2	883.0	2.61	6"x2	1324.5	5.52	8"x2
FXV3-1426-36T-20	30% Propylene Glycol	1803.5	8.55	8"x2	1442.8	6.47	6"x2	2164.2	11.97	8"x2
FXV3-1426-36T-25	30% Propylene Glycol	1803.5	8.55	8"x2	1442.8	6.47	6"x2	2164.2	11.97	8"x2
FXV3-1426-36T-30	30% Propylene Glycol	1803.5	8.55	8"x2	1442.8	6.47	6"x2	2164.2	11.97	8"x2
FXV3-1426-36T-40	30% Propylene Glycol	1803.5	8.55	8"x2	1442.8	6.47	6"x2	2164.2	11.97	8"x2
FXV3-1426-36T-50	30% Propylene Glycol	1803.5	8.55	8"x2	1442.8	6.47	6"x2	2164.2	11.97	8"x2
FXV3-1426-36T-60	30% Propylene Glycol	1803.5	8.55	8"x2	1442.8	6.47	6"x2	2164.2	11.97	8"x2
FXV3-1426-36T-75	30% Propylene Glycol	1803.5	8.55	8"x2	1442.8	6.47	6"x2	2164.2	11.97	8"x2
FXV3-1426-36T-100	30% Propylene Glycol	1803.5	8.55	8"x2	1442.8	6.47	6"x2	2164.2	11.97	8"x2
FXV3-1426-36Q-15	30% Propylene Glycol	1171.7	2.42	8"x2	937.4	1.60	6"x2	1406.1	3.39	8"x2
FXV3-1426-36Q-20	30% Propylene Glycol	1171.7	2.42	8"x2	937.4	1.60	6"x2	1406.1	3.39	8"x2
FXV3-1426-36Q-25	30% Propylene Glycol	1871.5	4.44	8"x2	1497.2	3.81	6"x2	2245.8	6.22	8"x2
FXV3-1426-36Q-30	30% Propylene Glycol	1871.5	4.44	8"x2	1497.2	3.81	6"x2	2245.8	6.22	8"x2
FXV3-1426-36Q-40	30% Propylene Glycol	1871.5	4.44	8"x2	1497.2	3.81	6"x2	2245.8	6.22	8"x2
FXV3-1426-36Q-50	30% Propylene Glycol	1871.5	4.44	8"x2	1497.2	3.81	6"x2	2245.8	6.22	8"x2
FXV3-1426-36Q-60	30% Propylene Glycol	1871.5	4.44	8"x2	1497.2	3.81	6"x2	2245.8	6.22	8"x2
FXV3-1426-36Q-75	30% Propylene Glycol	1871.5	4.44	8"x2	1497.2	3.81	6"x2	2245.8	6.22	8"x2
FXV3-1426-36Q-100	30% Propylene Glycol	1871.5	4.44	8"x2	1497.2	3.81	6"x2	2245.8	6.22	8"x2
FXV-364-31N	30% Propylene Glycol	1349.6	9.61	4"x4	1079.7	6.36	4"x4	1619.6	12.44	4"x6
FXV-364-31O	30% Propylene Glycol	1349.6	9.61	4"x4	1079.7	6.36	4"x4	1619.6	12.44	4"x6
FXV-364-31P	30% Propylene Glycol	1349.6	9.61	4"x4	1079.7	6.36	4"x4	1619.6	12.44	4"x6



FXV3 Closed Circuit Cooling Tower Pressure Drop IP Units (psi)

Product model number	Process Fluid	First Flow			Second Flow			Third Flow		
		gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)	gpm	psi	Std. coil conn. (Size x Quantity)
FXV-364-31Q	30% Propylene Glycol	1349.6	9.61	4"x4	1079.7	6.36	4"x4	1619.6	12.44	4"x6
FXV-364-31R	30% Propylene Glycol	1349.6	9.61	4"x4	1079.7	6.36	4"x4	1619.6	12.44	4"x6
FXV-364-31S	30% Propylene Glycol	1349.6	9.61	4"x4	1079.7	6.36	4"x4	1619.6	12.44	4"x6
FXV-364-41N	30% Propylene Glycol	1349.6	11.26	4"x4	1079.7	7.45	4"x4	1619.6	14.74	4"x6
FXV-364-41O	30% Propylene Glycol	1349.6	11.26	4"x4	1079.7	7.45	4"x4	1619.6	14.74	4"x6
FXV-364-41P	30% Propylene Glycol	1349.6	11.26	4"x4	1079.7	7.45	4"x4	1619.6	14.74	4"x6
FXV-364-41Q	30% Propylene Glycol	1349.6	11.26	4"x4	1079.7	7.45	4"x4	1619.6	14.74	4"x6
FXV-364-41R	30% Propylene Glycol	1349.6	11.26	4"x4	1079.7	7.45	4"x4	1619.6	14.74	4"x6
FXV-364-41S	30% Propylene Glycol	1349.6	11.26	4"x4	1079.7	7.45	4"x4	1619.6	14.74	4"x6
FXV-364-2TN	30% Propylene Glycol	1124.7	3.00	8"x2	899.8	1.99	6"x2	1349.7	4.20	8"x2
FXV-364-2TO	30% Propylene Glycol	1124.7	3.00	8"x2	899.8	1.99	6"x2	1349.7	4.20	8"x2
FXV-364-2TP	30% Propylene Glycol	1824.5	6.05	8"x2	1459.6	4.85	6"x2	2189.4	8.47	8"x2
FXV-364-2TQ	30% Propylene Glycol	1824.5	6.05	8"x2	1459.6	4.85	6"x2	2189.4	8.47	8"x2
FXV-364-2TR	30% Propylene Glycol	1824.5	6.05	8"x2	1459.6	4.85	6"x2	2189.4	8.47	8"x2
FXV-364-2TS	30% Propylene Glycol	1824.5	6.05	8"x2	1459.6	4.85	6"x2	2189.4	8.47	8"x2
FXV-364-1QN	30% Propylene Glycol	1199.7	1.96	6"x2	959.8	1.30	6"x2	1439.7	2.74	6"x2
FXV-364-1QO	30% Propylene Glycol	1199.7	1.96	8"x2	959.8	1.30	6"x2	1439.7	2.74	8"x2
FXV-364-1QP	30% Propylene Glycol	1199.7	1.96	8"x2	959.8	1.30	6"x2	1439.7	2.74	8"x2
FXV-364-1QQ	30% Propylene Glycol	1899.5	3.33	8"x2	1519.6	3.03	6"x2	2279.4	4.66	8"x2
FXV-364-1QR	30% Propylene Glycol	1899.5	3.33	8"x2	1519.6	3.03	6"x2	2279.4	4.66	8"x2
FXV-364-1QS	30% Propylene Glycol	1899.5	3.33	8"x2	1519.6	3.03	6"x2	2279.4	4.66	8"x2